

BCN-P5999-0940-D(2404)	回送回送
------------------------	---

EtherNet/IP Configuration Tool インストール手順書

ご使用の前にお読みください

ご使用になる前に、本資料をお読みください。お読みになった後は、いつでも使用できるように大切に保管してください。また、本製品のユーザが代わる場合も、必ず最終ユーザのお手元に届くようお願いいたします。使用時の注意事項については、下記を参照してください。
LJMJELSEC iQ-R EtherNet/IPネットワークインタフェースユニットユーザーズマニュアル(スタートアップ編) [SH-081912]
LJMJELSEC iQ-R EtherNet/IPネットワークインタフェースユニットユーザーズマニュアル(応用編) [SH-081914]

▲ 本書に関するご注意

- 本書の内容の一部または全部を当社に断りなく、いかなる形でも転載または複製することは、固くお断りします。
- 本書の記述内容はソフトウェア、ハードウェアの改訂に追従するように努力しておりますが、やむなく同期できない場合も生じます。
- 本書に記載されている内容はお断りなしに変更することがありますのでご了承ください。

1. 動作環境

項目	内容	
パソコン本体	Microsoft® Windows®が動作するパーソナルコンピュータ	
CPU	Windows11	2コア以上の64ビット互換プロセッサまたは System on a Chip(SoC)
	Windows10	Intel® Core™ 2 Duo 2GHz以上推奨
必要メモリ	Windows11	4GB以上推奨
	Windows10	OSが64ビット版の場合:2GB以上推奨 <p>OSが32ビット版の場合:1GB以上推奨</p>
ハードディスク空き容量	250MB以上	
ディスプレイ	解像度1024×768ドット以上	
OS	<ul style="list-style-type: none">Windows 11 (Home, Pro, Enterprise) Windows 10 (Home, Pro, Enterprise, Education)	
(日本語版、英語版、中国語簡体字版) ^{*1}		

*1 選択ボタンの表示などは、OSの言語に依存するため、OSの言語が表示される場合があります。

- .NET Framework 3.5(.NET 2.0および3.0を含む)および.NET Framework 4.8 Advanced Servicesを有効化する必要があります。詳細は、テクニカルニュースNo. FA-D-0207を参照してください。
- 下記の機能を使用した場合、本製品は正常に動作しない可能性があります。
 - Windows互換モードでのアプリケーション起動
 - ユーザ簡易切替え
 - リモートデスクトップ
 - タッチ機能
 - クライアントHyper-Vなどの仮想環境
 - タブレットモード
 - 仮想デスクトップ
 - 統合書き込みフィルター
 - テラストカーソルインジケーター
- 下記の場合、本製品の画面が正常に動作しない可能性があります。
 - 画面上のテキストやその他の項目のサイズを既定値(96 DPI、100%、9ptなど)以外に変更した場合
 - 動作中に画面の解像度を変更した場合
 - 動作中にWindowsのテーマを変更した場合
 - マルチディスプレイに設定した場合
- 「管理者」で使用してください。
- Windowsファイアウォールの設定が有効な場合、「ユニット検索機能」、「直接接続機能」が正常に動作しない可能性があります。Windowsファイアウォールの設定を無効にしてください。
- 本製品では小数点を表す記号としてピリオド(.)を使用します。コントロールパネルの「小数点の記号」の設定にかかわらず、小数点を入力するときはピリオドを入力してください。

2. インストール手順

2.1 インストール前に確認してください。

- パソコンへは、「管理者」または「Administrator」のユーザとしてログオンしてください。
- インストールを行う前に、動作させているすべてのアプリケーションを終了させてください。他のアプリケーションが動作している状態でインストールすると、製品が正常に動作しない場合があります。
- 入手した圧縮ファイルを解凍します。
- 解凍されたフォルダ内の「setup.exe」をダブルクリックし、インストーラを起動します。
- 画面の指示に従って必要事項を選択または入力します。

3. アンインストール手順

Windowsのコントロールパネルからアンインストールしてください。

EtherNet/IPは、ODVAの商標です。Intelは、米国およびその他の国におけるIntel Corporationの登録商標または商標です。

MicrosoftおよびWindowsは、マイクロソフトグループの企業の商標です。本文中における会社名、システム名、製品名などは、一般に各社の登録商標または商標です。本文中で、商標記号(™、®)は明記していない場合があります。

EtherNet/IP Configuration Tool Installation Instructions

Before Using the Product

Please read this document before use. Keep the document in a safe place for future reference. Make sure that the end users read the document.

For the precautions on using EtherNet/IP Configuration Tool, refer to the following manuals.

LJMJELSEC iQ-R EtherNet/IP Network Interface Module User's Manual (Startup) [SH-081913ENG]
LJMJELSEC iQ-R EtherNet/IP Network Interface Module User's Manual (Application) [SH-081915ENG]

▲ Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.

1. Operating Environment

Item	Contents	
Personal computer	A personal computer on which Microsoft® Windows® operates	
CPU	Windows11	2 or more cores on a compatible 64-bit processor or System on a Chip (SoC)
	Windows10	Intel® Core™ 2 Duo Processor 2GHz or more recommended
Required memory	Windows11	4GB or more recommended
	Windows10	64-bit OS: 2GB or more recommended <p>32-bit OS: 1GB or more recommended</p>
Available hard disk capacity	250MB or more	
Monitor	Resolution 1024 × 768 pixels or higher	
OS	<ul style="list-style-type: none">Windows 11 (Home, Pro, Enterprise) Windows 10 (Home, Pro, Enterprise, Education)	
(Japanese version, English version, Simplified Chinese version) ^{*1}		

*1 The language of some displays such as selection buttons depends on the language of the operating system used. They may be displayed in the language of the operating system.

- .NET Framework 3.5 (including .NET 2.0 and 3.0) or .NET Framework 4.8 Advanced Services needs to be enabled. For details, refer to TECHNICAL BULLETIN No. FA-A-0207.
- When the following functions are used, this product may not run properly.
 - Application start-up in Windows compatibility mode
 - Fast user switching
 - Remote desktop
 - Touch function
 - Virtual environment such as Client Hyper-V
 - Tablet mode
 - Virtual Desktops
 - Unified Write Filter
 - Text cursor indicator
- In the following cases, the screen of this product may not work properly.
 - The size of the text and/or other items on the screen are changed to values other than default values (such as 96 DPI, 100%, and 9 pt).
 - The resolution of the screen is changed in operation.
 - The Windows theme is changed in operation.
 - The multi-display is set.
- Use the product as an administrator.
- If the Windows firewall setting is enabled, the 'module search function' and 'direct connection function' may not run correctly. Disable the Windows firewall setting.
- In this product, the period (.) is used as the symbol of the decimal point. Regardless of the setting of 'Decimal symbol' on the control panel, use the period when enter the decimal point.

EtherNet/IP Configuration Tool 安装步骤说明书

使用前请务必阅读

使用前请务必阅读本资料。阅读后请妥善保管，以便随时使用。此外，本产品的用户发生变更时，请务必将本资料转交给最终用户。

关于使用时的注意事项，请参照以下手册。

LJMJELSEC iQ-R EtherNet/IP网络接口模块用户手册(入门篇) [SH-081970CHN]

LJMJELSEC iQ-R EtherNet/IP网络接口模块用户手册(应用篇) [SH-081971CHN]

▲ 本说明书相关注意事项

- 未经三菱电机株式会社许可，禁止以任何形式转载或复制本说明书的部分或全部内容。
- 本说明书的记载内容尽量跟随软件、硬件的改版进程，但仍有可能无法完全同步。
- 本说明书中记载的内容可能在事先未知会的情况下进行修改，敬请谅解。

1. 运行环境

項目	内容	
个人计算机	基于Microsoft® Windows®下运行的个人计算机	
CPU	Windows11	2核心及以上的64位兼容处理器或System on a Chip(SoC)
	Windows10	建议Intel® Core™ 2 Duo 2GHz及以上
必要内存	Windows11	建议4GB及以上
	Windows10	OS为64位版时：建议2GB及以上 <p>OS为32位版时：建议1GB及以上</p>
硬盘可用空间	250MB及以上	
显示器	分辨率1024×768像素及以上	
OS	<ul style="list-style-type: none">Windows 11 (Home, Pro, Enterprise) Windows 10 (Home, Pro, Enterprise, Education)	
(日语版、英语版、简体中文版) ^{*1}		

*1 因选择按钮的显示等取决于操作系统的语言，所以有可能显示操作系统的语言。

- 需要启用NET Framework 3.5(包括.NET 2.0和3.0)及.NET Framework 4.8 Advanced Services。详细内容请参照技术简讯No. FA-A-0207(英语版)。
- 如果使用下述功能，有可能导致本产品无法正常运行。
 - Windows兼容模式下的应用程序启动
 - 用户简易切换
 - 远程桌面
 - 触摸功能
 - 客户端Hyper-V等虚拟环境
 - 平板模式
 - 虚拟桌面
 - 统一写入筛选器
 - 文本光标指示器
- 下述情况下，有可能导致本产品的画面无法正常运行。
 - 将画面上的文字及其他项目的尺寸更改为默认值（96 DPI，100%，9pt等）以外时
 - 在运行中更改了画面的分辨率时
 - 在运行中更改了Windows主题时
 - 设置为多屏显示时
- 请以“管理员”使用。
- Windows防火墙的设置启用时，“模块搜索功能”、“直接连接功能”可能无法正常运行。请将Windows防火墙的设置设为禁用。
- 本产品中表示小数点的符号使用（.）。无论控制面板的“小数点”的设置如何，输入小数点时请输入（.）。

2. 安装步骤

2.1 安装前请确认

- 安装至个人计算机时，请以“管理员”或“Administrator”权限的用户进行登录。
- 安装前，请结束所有运行的应用程序。如果在其他应用程序运行的状态下进行安装，有可能导致产品无法正常运行。

- 将取得的压缩文件解压缩。
- 双击解压缩的文件夹中的“setup.exe”，启动安装程序。
- 请按照画面指示选择或输入必要事项。

3. 卸载步骤

应通过Windows的控制面板进行卸载。

EtherNet/IP is a trademark of ODVA, Inc. Intel is either registered trademarks or trademarks of Intel Corporation in the United States and/or other countries.

Microsoft and Windows are trademarks of the Microsoft group of companies. The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as “™” or “®” are not specified in this manual.

2. Installation

2.1 Items to be checked before installation

- Log on to the personal computer as an administrator.
- Close all running applications before installation. If the product is installed while other applications are running, it may not operate normally.

- Unzip the compressed folder.
- Double-click “setup.exe” in the unzipped folder to start the installer.
- Select or enter the necessary information by following the on-screen instructions.

3. Uninstallation

Uninstall EtherNet/IP Configuration Tool from the control panel of Windows.

EtherNet/IP is a trademark of ODVA, Inc. Intel is either registered trademarks or trademarks of Intel Corporation in the United States and/or other countries.

Microsoft and Windows are trademarks of the Microsoft group of companies. The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as “™” or “®” are not specified in this manual.

三菱電機株式会社

〒100-8310 東京都千代田区丸の内2-7-3（東京ビル）

MITSUBISHI ELECTRIC CORPORATION
HEAD OFFICE: TOKYO BLDG. 2-7-3, MARUNOUCHI, CHYODOKU, TOKYO 100-8310, JAPAN
NAGOYA WORKS: 1-14, YADA-MINAMI 5-CHOME, HIGASHIKU, NAGOYA 461-8670, JAPAN

GXC-EIP-INSTL-M