

BCN-P5999-1284-B(2309)	<b>MELSOFT</b> 
------------------------	---

## MELSEC-A/QnA→MELSEC iQ-R 変換サポートツール インストール手順書

### ご使用の前にお読みください

ご使用になる前に、本資料をお読みください。お読みになった後は、いつでも使用できるように大切に保管してください。また、本製品のユーザが代わる場合も、必ず最終ユーザのお手元に届くようお願いいたします。使用時の注意事項については、下記を参照してください。

マニュアル名称	マニュアル番号
MELSEC-A/QnA→MELSEC iQ-R変換サポートツールオペレーティングマニュアル	SH-082276

#### △ 本書に関するご注意

- 本書の内容の一部または全部を当社に断りなく、いかなる形でも転載または複製することは、固くお断りします。
- 本書の記述内容はソフトウェア、ハードウェアの改訂に追従するように努力しておりますが、やむなく同期できない場合も生じます。
- 本書に記載されている内容はお断りなしに変更することがありますのでご了承ください。

### 1. 動作環境

項目	内容
パソコン本体	Microsoft® Windows®が動作するパーソナルコンピュータ
CPU	Intel® Core™ 2 Duo 2GHz以上推奨
必要メモリ	OSが64ビット版の場合: 2GB以上推奨 <p>OSが32ビット版の場合: 1GB以上推奨</p>
ハードディスク空き容量	インストール時: 100MB以上
ディスプレイ	解像度1024×768ドット以上
OS <p>(日本語版、英語版)</p>	<ul style="list-style-type: none"><li>Windows 11 (Home, Pro, Enterprise, Education)</li> <li>Windows 10 (Home, Pro, Enterprise, Education, IoT Enterprise 2016 LTSP<sup>*1</sup>)</li></ul>
ソフトウェア	<ul style="list-style-type: none"><li>GX Developer Version 8.508E以降<sup>*2</sup></li> <li>GX Works2 Version 1.615R以降<sup>*2</sup></li> <li>GX Works3 Version 1.085P以降<sup>*2</sup></li> <li>Acrobat Reader®</li></ul>
ブラウザ	<ul style="list-style-type: none"><li>Microsoft Edge®</li> <li>Google Chrome® 114以降</li></ul>

\*1 64ビット版のみ対応しています。

\*2 記載のソフトウェアすべてがインストールされたパソコンでのみ動作します。

- 「標準ユーザ」または「管理者」で使用してください。
- 下記の機能を使用した場合、本製品は正常に動作しない可能性があります。
  - Windows互換モードでのアプリケーション起動
  - ユーザ簡易切替
  - リモートデスクトップ
  - タッチ機能
  - クライアントHyper-V
  - 仮想デスクトップ
  - タブレットモード
  - 統合書き込みフィルター
  - テキストカーソルインジケーター
- 下記の場合、本製品の画面が正常に動作しない可能性があります。
  - 画面上のテキストやその他の項目のサイズが100%(96DPI、9ptなど)以外の場合
    - 動作中に画面の解像度を変更した場合
    - 動作中にWindowsのテーマを変更した場合
    - マルチディスプレイに設定した場合
- MELSEC-A/QnA→MELSEC iQ-R 変換サポートツールではサロゲートベア文字、環境依存文字はサポートしていません。

### 2. インストール手順

#### 2.1 インストール前に確認してください。

- パソコンへは、「管理者」または「Administrator」のユーザとしてログオンしてください。
- インストールを行う前に、動作させているすべてのアプリケーションを終了させてください。他のアプリケーションが動作している状態でインストールすると、製品が正常に動作しない場合があります。

#### 2.2 手順

- 入手した圧縮ファイルを解凍します。
- 解凍されたフォルダー内の“setup.exe”をダブルクリックし、インストーラを起動します。
- 画面の指示に従って必要事項を選択または入力します。

### 3. アンインストール手順

Windowsのコントロールパネルからアンインストールしてください。

Acrobat Readerは、Adobe Systems Incorporated(アドビシステムズ社)の米国、およびその他の国における登録商標または商標です。
Google Chromeは、Google LLCの登録商標または商標です。
Intelは、米国およびその他の国におけるIntel Corporationの登録商標または商標です。

Microsoft、Windows、およびMicrosoft Edgeは、マイクロソフトグループの企業の商標です。
本文中における会社名、システム名、製品名などは、一般に各社の登録商標または商標です。
本文中で、商標記号(™、®)は明記していない場合があります。

## MELSEC-A/QnA → MELSEC iQ-R Conversion Support Tool Installation Instructions

### Before Using the Product

Please read this document before use. Keep the document in a safe place for future reference. Make sure that the end users read the document. For the precautions on using, refer to the following manual.

Manual name	Manual number
MELSEC-A/QnA → MELSEC iQ-R Conversion Support Tool Operating Manual	SH-082277ENG

#### △ Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.

### 1. Operating Environment

Item	Contents
Personal computer	A personal computer on which Microsoft® Windows® operates
CPU	Intel® Core® 2 Duo Processor 2GHz or more recommended
Required memory	64-bit OS: Recommended 2GB or more <p>32-bit OS: Recommended 1GB or more</p>
Available hard disk capacity	For installation: 100MB or more
Monitor	Resolution 1024 × 768 pixels or higher
OS <p>(English version, Japanese version)</p>	<ul style="list-style-type: none"><li>Windows 11 (Home, Pro, Enterprise, Education)</li> <li>Windows 10 (Home, Pro, Enterprise, Education, IoT Enterprise 2016 LTSP<sup>*1</sup>)</li></ul>
Software	<ul style="list-style-type: none"><li>GX Developer Version 8.508E or later<sup>*2</sup></li> <li>GX Works2 Version 1.615R or later<sup>*2</sup></li> <li>GX Works3 Version 1.085P or later<sup>*2</sup></li> <li>Acrobat Reader®</li></ul>
Browser	<ul style="list-style-type: none"><li>Microsoft Edge®</li> <li>Google Chrome® 114 or later</li></ul>

\*1 64-bit version only

\*2 This product only operates on a personal computer on which all of the described software are installed.

- Use this product as a standard user or an administrator.
- When the following functions are used, this product may not run properly.
  - Application start-up in Windows compatibility mode
  - Fast user switching
  - Remote desktop
  - Touch function
  - Client Hyper-V
  - Virtual desktop
  - Tablet mode
  - Unified Write Filter
    - Text cursor indicator
- In the following cases, the screen of this product may not work properly.
  - The size of the text and/or other items on the screen are other than default 100%.
  - The resolution of the screen is changed in operation.
  - Windows theme is changed in operation.
  - The multi-display is set.
- Surrogate pair characters and environment dependent characters are not available in MELSEC-A/QnA → MELSEC iQ-R Conversion Support Tool.

### 2. Installation

#### 2.1 Confirm before installation.

- Log on to the personal computer as an administrator.
- Close all running applications before installation. If the product is installed while other applications are running, it may not operate normally.

#### 2.2 Procedure

- Unzip the compressed folder.
- Double-click “setup.exe” in the unzipped folder to start installation.
- Select or enter the necessary information by following the on-screen instructions.

### 3. Uninstallation

Uninstall MELSEC-A/QnA → MELSEC iQ-R Conversion Support Tool from the control panel of Windows.

Acrobat Reader is either a registered trademark or trademark of Adobe Systems Incorporated in the United States and/or other countries.

Google Chrome is either a registered trademark or a trademark of Google LLC. Intel is either a registered trademark or a trademark of Intel Corporation in the United States and/or other countries.

Microsoft, Windows, and Microsoft Edge are trademarks of the Microsoft group of companies.

The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as ™ or ® are not specified in this manual.

#### 三菱電機株式会社

〒100-8310 東京都千代田区丸の内2-7-3(東京ビル)

**MITSUBISHI ELECTRIC CORPORATION**  
HEAD OFFICE: TOKYO BLDG. 2-7-3, MARUNOUCHI, CHYODOKU, TOKYO 100-8310, JAPAN  
NAGOYA WORKS: 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA 461-8670, JAPAN