

<b>MELSOFT</b>
IB(NA)-0800651-A(2010)

## ユーザWebページ作画ツールインストール手順書

## ご使用前にお読みください

ご使用になる前に、本資料をお読みください。お読みになった後は、いつでも使用できるように大切に保管してください。また、本製品のユーザが代わる場合も、必ず最終ユーザのお手元に届くようお願いいたします。使用時の注意事項については、下記を参照してください。
 ユーザWebページ作画ツールオペレーティングマニュアル[SH-082314]

### 本書に関するご注意

- 本書の内容の一部または全部を当社に断りなく、いかなる形式でも転載または複製することは、固くお断りします。
- 本書の記述内容はソフトウェア、ハードウェアの改訂に追従するように努力しておりますが、やむなく同期できない場合も生じます。
- 本書に記載されている内容はお断りなしに変更することがありますのでご了承ください。

### 1. 動作環境

#### 1.1 作画ツールの動作環境

作画ツールの動作環境を示します。

項目	内容
パソコン本体	Microsoft® Windows®が動作するパーソナルコンピュータ
CPU	Intel® Core® i3 2GHz以上推奨
必要メモリ	8GB以上推奨
ハードディスク空き容量	400MB以上
ディスプレイ	解像度1280×1024ドット以上
OS(64ビット版) (日本語版、英語版、中国語版(簡体字)) <sup>1)</sup>	Windows 10(Home, Pro, Enterprise, Education)

<sup>1)</sup> 作画ツールの表示言語は、日本語、英語、中国語(簡体字)をサポートします。ただし、選択ボタン表示などは、OSの言語に依存するため上記言語以外の表示がされる場合があります。

- Windows 10では、.NET Framework 4.5が無効化されている場合、有効化する必要があります。テクノカルニュースNo.FA-D-0207を参照してください。
- 下記の機能を使用した場合、本製品は正常に動作しない可能性があります。
  - Windows互換モードでのアプリケーション起動
  - ユーザ簡易切替え
  - リモートデスクトップ
  - Windows XP Mode
  - Windowsタッチまたはタッチ
  - Modern UI
  - クライアントHyper-V
  - タブレットモード
  - 仮想デスクトップ
- 下記の場合、本製品の画面が正常に動作しない可能性があります。
  - 画面上のテキストやその他の項目のサイズを既定値(96 DPI、100％、9ptなど)以外に変更した場合
  - 動作中に画面の解像度を変更した場合
  - マルチディスプレイに設定した場合
- 「管理者」で使用してください。
- 本製品では小数点を表す記号としてピリオド(.)を使用します。コントロールパネルの「小数点の記号」の設定にかかわらず、小数点を入力するときはピリオドを入力してください。

#### 1.2 クライアントの動作環境

HTML5、CSS3、JavaScriptに対応したWebブラウザを使用してください。弊社で動作確認済みのクライアントは、下記を参照してください。
 ユーザWebページ作画ツールオペレーティングマニュアル[SH-082314]

### 2. ソフトウェアライセンス

作画ツールは、複数のソフトウェアコンポーネントで構成されています。それぞれ当社または第三者の著作権が存在します。ソフトウェアライセンスの詳細については、下記を参照してください。
 ユーザWebページ作画ツールオペレーティングマニュアル[SH-082314]

### 3. インストール手順

#### 3.1 インストール前に確認してください。

- パソコンへは、「管理者」または「Administrator」のユーザとしてログインしてください。
- インストールを行う前に、動作させているすべてのアプリケーションを終了させてください。他のアプリケーションが動作している状態でインストールすると、製品が正常に動作しない場合があります。
- 入手した圧縮ファイルを解凍します。
- 解凍されたフォルダ内の「setup.exe」をダブルクリックし、インストーラを起動します。
- 画面の指示に従って必要事項を選択または入力します。

#### 3.2 対応バージョン

対応するCPUユニットのバージョンについては、下記を参照してください。
 ユーザWebページ作画ツールオペレーティングマニュアル[SH-082314]

### 4. アンインストール手順

- インストールされたフォルダ内の「uninstall.exe」をダブルクリックし、アンインストーラを起動します。
- 画面の指示に従って必要事項を選択または入力します。

MicrosoftおよびWindowsは、米国Microsoft Corporationの米国およびその他の国における登録商標または商標です。Intelは、米国およびその他の国におけるIntel Corporationの登録商標または商標です。OracleおよびJavaScriptは、Oracle Corporationおよびその子会社、関連会社の、米国およびその他の国における登録商標です。本文中における会社名、システム名、製品名などは、一般に各社の登録商標または商標です。本文中で、商標記号(™、®)は明記していません場合があります。

## User Web Page Design Tool Installation Instructions

## Before Using the Product

Please read this document before use. Keep the document in a safe place for future reference. Make sure that the end users read the document.

For the precautions on using User Web Page Design Tool, refer to the following manuals.

User Web Page Design Tool Operating Manual [SH-082315ENG]

### Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.

## 1. Operating Environment

### 1.1 Operating environment of the design tool

This section describes the design tool's operating environment.

Item	Contents
Personal computer	A personal computer on which Microsoft® Windows® operates
CPU	Intel® Core® i3 2 GHz or more recommended
Required memory	8 GB or more recommended
Available hard disk capacity	400 MB or more
Monitor	Resolution 1280 × 1024 pixels or higher
OS (64-bit version) (Japanese version, English version, Chinese version (simplified characters)) <sup>1)</sup>	Windows 10 (Home, Pro, Enterprise, Education)

<sup>1)</sup> English, Japanese, and Chinese (simplified characters) are supported as the design tool's display languages. However, selection button displays, etc. depend on an OS's language, and therefore they may be displayed in one other than those languages above.

- For Windows 10, if .NET Framework 4.5 is invalid, it needs to be valid. Refer to TECHNICAL BULLETIN No. FA-A-0207.
- When the following functions are used, this product may not run properly.
  - Application start-up in Windows compatibility mode
  - Fast user switching
  - Remote desktop
  - Windows XP Mode
  - Windows Touch or Touch
  - Modern UI
  - Client Hyper-V
  - Tablet mode
  - Virtual Desktops
- In the following cases, the screen of this product may not work properly.
  - The size of the text and/or other items on the screen are changed to values other than default values (such as 96 DPI, 100%, and 9 pt).
  - The resolution of the screen is changed in operation.
  - The multi-display is set.
- Use the product as an administrator.
- In this product, the period (.) is used as the symbol of the decimal point. Regardless of the setting of "Decimal symbol" on the control panel, use the period when entering the decimal point.

#### 1.2 Operating environment of the client

Use a web browser that supports HTML5, CSS3, and JavaScript. For clients whose operability have been confirmed by Mitsubishi Electric Corporation, refer to the following.
 User Web Page Design Tool Operating Manual [SH-082315ENG]

## 2. Software License

The design tool is composed of multiple software components. There are copyrights of our company and third parties to those individual software components. For details of the software licenses, refer to the following.
 User Web Page Design Tool Operating Manual [SH-082315ENG]

## 用户网页绘图工具 安装步骤说明书

## 使用前请务必阅读

使用前请务必阅读本资料。阅读后请妥善保管，以便随时使用。此外，本产品的用户发生变更时，请务必将本资料转交给最终用户。关于使用时的注意事项，请参照以下手册。
 用户网页绘图工具操作手册 [SH-082317CHN]

### 本书说明书相关注意事项

- 未经三菱电机株式会社许可，禁止以任何形式转载或复制本说明书的部分或全部内容。
- 本说明书的记载内容将尽力跟随软件、硬件的改版进行修订，但仍有可能无法完全同步。
- 本说明书中记载的内容可能在事先未进行告知的情况下进行修改，敬请谅解。

## 1. 运行环境

### 1.1 绘图工具的运行环境

以下为绘图工具的运行环境。

项目	内容
个人计算机	基于Microsoft® Windows®下运行的个人计算机
CPU	推荐使用Intel® Core® i3 2GHz以上。
必要内存	建议8GB以上
硬盘可用空间	400MB以上
显示器	分辨率1280×1024以上
OS(64位版) (日语版、英语版、中文版(简体字)) <sup>*1</sup>	Windows 10(Home、Pro、Enterprise、Education)

<sup>\*1</sup> 绘图工具的显示语言支持中文(简体字)、日语以及英语。但是，由于选择按钮的显示等取决于OS的语言，所以可能会显示上述语言以外的语言。

- 使用Windows 10时，.NET Framework 4.5如果被设置为无效，需要先将其置为有效。请参考技术简讯No.FA-A-0207(英语版)。
- 如果使用下述功能，有可能导致本产品无法正常运行。
  - Windows兼容模式下的应用程序启动
  - 用户简易切换
  - 远程桌面
  - Windows XP Mode
  - Windows Touch或Touch
  - Modern UI
  - 客户端Hyper-V
  - 平板模式
  - 虚拟桌面
- 下述情况下，有可能导致本产品的画面无法正常显示。
  - 将画面上的文字及其他项目的尺寸更改为默认值(96 DPI、100％、9pt等)以外时
  - 在运行中更改了画面的分辨率时
  - 设置为多屏显示时
- 请以“管理员”身份运行。
- 本产品中表示小数点的符号使用(.)。无论控制面板的“小数点”的设置如何，输入小数点时请输入(.)。

#### 1.2 客户端的运行环境

请使用支持HTML5、CSS3以及JavaScript的Web浏览器。已由本公司确认过运行的客户端请参照以下内容。
 用户网页绘图工具操作手册 [SH-082317CHN]

## 2. 软件许可证

绘图工具由多个软件组件构成。其著作权由本公司或第三方所拥有。关于软件许可证的详细，请参照以下内容。
 用户网页绘图工具操作手册 [SH-082317CHN]

## 3. 安装步骤

### 3.1 安装前请确认

- 安装至个人计算机时，请以“管理员”或“Administrator”权限的用户进行登录。
- 安装前，请结束所有运行的应用程序。如果在其他应用程序运行的状态下进行安装，有可能导致产品无法正常安装。
- 将取得的压缩文件解压缩。
- 双击解压缩的文件夹中的“setup.exe”，启动安装程序。
- 请按照画面指示选择或输入所需事项。

### 3.2 支持版本

关于支持CPU模块版本，请参照以下内容。

用户网页绘图工具操作手册 [SH-082317CHN]

## 4. 卸载步骤

- 在安装后的文件夹中双击“uninstall.exe”，启动卸载程序。
- 根据画面指示，选择或输入所需事项。

Microsoft and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Intel is either registered trademarks or trademarks of Intel Corporation in the United States and/or other countries. Oracle and JavaScript are registered trademarks of Oracle Corporation and/or its affiliates in the United States and other countries. The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as “™” or “®” are not specified in this manual.

## 3. Installation

### 3.1 Items to be checked before installation

- Log on to the personal computer as an administrator.
- Close all running applications before installation. If the product is installed while other applications are running, it may not operate normally.

- Unzip the compressed folder.
- Double-click “setup.exe” in the unzipped folder to start the installer.
- Select or enter the necessary information by following the on-screen instructions.

### 3.2 Supported version

For a supported version of a CPU module, refer to the following.
 User Web Page Design Tool Operating Manual [SH-082315ENG]

## 4. Uninstallation

- Double-click “uninstall.exe” in the installed folder, and start the uninstaller.
- Select or input essential items according to the instructions on the screen.

Microsoft and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Intel is either registered trademarks or trademarks of Intel Corporation in the United States and/or other countries. Oracle and JavaScript are registered trademarks or trademarks of Oracle Corporation and/or its affiliates in the United States and other countries. The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as “™” or “®” are not specified in this manual.