



Magnetic Contactors and Magnetic Motor Starters TECHNICAL NOTES

MS-T Series



Magnetic Motor Starter TECHNICAL NOTES

MS-T Series Magnetic Contactors and Magnetic Motor Starters

This document introduces the types, characteristics and performances (Type test results) of the magnetic motor starter, for the purpose of being generally utilized as a basic document by all the users including the administrators, designers, and those responsible for construction.

- Note a) Note that the described contents are subject to change without notice.
 - b) The described content is only for reference and it cannot be guaranteed.

The units are described in SI units.

Table of Contents

Standard Series Magnetic Motor Starter and Magnetic Contactor

Kinds and Ratings 2
Characteristics and Performance (Type test results) 5
1. Structure 5
2. Type Test
2.1 Type Tests and Test Sequences 5
2.2 Test Sequence I
2.2.1 Temperature Rise and Dielectric Properties ······ 6
2.2.2 Operating Limits ······ 7
(1) Operating Limits of the Magnetic Contactor7
(2) Operating Charateristics of Thermal Overload Relay
2.3 Test Sequence II ······ 9
2.3.1 Test of Making and Breaking Capacities
(1) Test of Making Capacity ····· 9
(2) Test of Making and Breaking Capacities
(3) The Switching Capacity and Reversibility
2.3.2 The Operating Performance ······12
(1) Non-reversing ······12
(2) Reversing ·······13
2.4 Test Sequence III ·································
2.4.1 Performance under Short-circuit Conditions14
2.5 Test Sequence IV······15
2.5.1 Ability of Contactors to Withstand Overload Currents
2.6 Test Sequence V ······ 16
2.6.1 Mechanical Properties of Terminals ······16
(1) Tests of Mechanical Strength of Terminals
(2) Flexion and Pull-out Tests 17

Special Magnetic Contactor

DC-operated Magnetic Contactor <type sd-t=""> ······2</type>	0
1. Structure ······2	0
2. Rating ······2	0
3. Type Test······2	0
3.1 Type Tests and Test Sequences ······2	0
3.2 Test Sequence I······2	1
3.2.1 Temperature Rise and Dielectric Properties2	1
3.2.2 Operating Limits ······2	2

3.3 Test Sequence II·····	23
3.3.1 Test of Making and Breaking Capacities ·····	
(1) Test of Making Capacity ······	23
(2) Test of Making and Breaking Capacities	23
(3) The Switching Capacity and Reversibility	24
3.3.2 The Operating Performance ·····	25
(1) Non-reversing ·····	
(2) Reversing	
3.4 Test Sequence III ·····	
3.4.1 Performance under Short-circuit Conditions	
3.5 Test Sequence IV·····	
3.5.1 Ability of Contactors to Withstand Overload Currents	
3.6 Test Sequence V ·····	
3.6.1 Mechanical Properties of Terminals ·····	
(1) Tests of Mechanical Strength of Terminals	
(2) Flexion and Pull-out Tests	28
Mechanical Latch Type Magnetic Contactor <type sl-t,="" sld-t=""> ·····</type>	
1. Usage ·····	
2. Rating ·····	
3. Type Test	
3.1 Type Tests and Test Sequences ······	
3.2 Test Sequence I	
3.2.1 Temperature Rise and Dielectric Properties	
3.2.2 Operating Limits ·····	
3.3 Test Sequence II ·····	
3.3.1 Test of Making and Breaking Capacities	
(1) Test of Making Capacity ·····	
(2) Test of Making and Breaking Capacities	
(3) The Switching Capacity and Reversibility	
3.3.2 The Operating Performance ······	
(1) Non-reversing ·····	
(2) Reversing	
3.4 Test Sequence III	
3.4.1 Performance under Short-circuit Conditions	
3.5 Test Sequence IV	
3.5.1 Ability of Contactors to Withstand Overload Currents	
3.6 Test Sequence V	
3.6.1 Mechanical Properties of Terminals ·····	
(1) Tests of Mechanical Strength of Terminals	
(2) Flexion and Pull-out Tests·····	36

Environmental Characteristics and Special Performance

1. Surrounding Environment of the Magnetic Starter
2. Application to the Special Environment
2.1 High Temperature ····································
2.2 Low Temperature40
3. Instantaneous Voltage Drop Tolerance41
3.1 SEMI-F47 Standard ······41
3.2 Instantaneous Power Failure Tolerance41
4. Operating Characteristics of the Thermal Relay
4.1 Operations in a Balanced Circuit (Ambient Temperature: 20°C)······42
4.2 Operations in an Unbalanced Circuit (Ambient Temperature: 20°C)······42
5. Noise Characteristics
5.1 Noise during the ON State ······43
5.2 Noise during Opening and Closing ······44
6. Impact during Opening and Closing
7. Insulation Resistance and Withstand Voltage45
8. Vibration ······45
8.1 Contact Malfunction Vibration ······45
8.2 Constant Vibration Endurance 45
9. Impact
10. Mechanical Endurance ·······46
11. Electrical Endurance 47
12. Short Time Current Overload Tolerance of the Magnetic Contactor

Standard Series Magnetic Motor Starter and Magnetic Contactor

Kinds and Ratings

Type MS-T magnetic motor starter consists of a type S-T magnetic contactor, type TH-T thermal overload relay and an outer case. Type MSO-T magnetic motor starters are also available as a unit for power distributor panels and control panels.

Table 1 Constitutional Elements of Type MS-T Magnetic Motor Starters

Non-reversing




Table 2 Kinds and Composition

		•	Туре		Constituent elements				
Frame	MS-, with	enclosure		n-out enclosure	S-, magnet	ic contactor			
Fiame	Non- reversing	Reversing	Non- reversing	Reversing	Non- reversing Reversing		Thermal overload relay		
T10	MS-T10 (KP)	-	MSO-T10 (KP)	MSO-2xT10 (KP)	S-T10	S-2xT10			
T12	MS-T12 (KP)	-	MSO-T12 (KP)	MSO-2xT12 (KP)	S-T12	S-2xT12	TH-T18(KP)		
T20	-	-	MSO-T20 (KP)	MSO-2xT20 (KP)	S-T20	S-2xT20			
T21	MS-T21 (KP)	MS-2xT21 (KP)	MSO-T21 (KP)	MSO-2xT21 (KP)	S-T21	S-2xT21	TH-T25(KP)		
T25	-	-	MSO-T25 (KP)	MSO-2xT25 (KP)	S-T25	S-2xT25	10-120(KF)		
T32	-	-	-	-	S-T32	S-2xT32	-		
T35	MS-T35(KP)		MSO-T35 (KP)	MSO-2xT35 (KP)	S-T35	S-2xT35	TH-T25(KP) (Nominal current of the heater: 22 A or less) TH-T50(KP) (Nominal current of the heater: 29 A)		
T50	MS-T50(KP)		MSO-T50 (KP)	MSO-2xT50 (KP)	S-T50	S-2xT50	TH-T25(KP) (Nominal current of the heater: 22 A or less) TH-T50(KP) (Nominal current of the heater: 29 A or higher)		
T65	MS-T65(KP)		MSO-T65 (KP)	MSO-2xT65 (KP)	S-T65	S-2xT65	TH-T65(KP)		
T80	MS-T80(KP)		MS-T80(KP)		MSO-T80 (KP)	MSO-2xT80 (KP)	S-T80	S-2xT80	TH-T65(KP) (Nominal current of the heater: 54 A or less) TH-T100(KP) (Nominal current of the heater: 67 A)
T100	MS-T100(KP)		MSO-T100 (KP)	MSO-2xT100 (KP)	S-T100	S-2xT100	TH-T65(KP) (Nominal current of the heater: 54 A or less) TH-T100(KP) (Nominal current of the heater: 67 A or higher)		

Table 3 Rated Capacity

Application			Resista	nce load			
	/ Three-phas	ategory AC-3 [k se squirrel-cage ndard responsib	motor load	Category / Three-phase motor loa respon	squirrel-cage d inching	•••	AC-1 [kW] ce, heater)
Frame	220 to 240V	380 to 440V	500V	220 to 240V	500V	220 to 240V	380 to 440V
T10	2.5	4	4	1.5	2.7(2.2)	7.5	7
T12	3.5	5.5	7.5	2.2	5.5(4)	7.5	8.5
T20	4.5	7.5	7.5	3.7	5.5	7.5	8.5
T21	5.5	11	11	3.7	5.5	12	20
T25	7.5	15	15	4.5	7.5	12	20
T32	7.5	15	15	5.5	7.5(11)	12	20
T35	11	18.5	18.5	5.5	11	20	35
T50	15	22	25	7.5	15	30	50
T65	18.5	30	37	11	22	35	65
T80	22	45	45	15	30	45	78
T100	30	55	55	19	37	55	90

Note a) Brackets () in the inching operation indicate the rating of 380V to 440V.

Table 4 Rated Operation Current

Application			Moto	Resistance load					
	Cat	egory AC- 3	[A]	Cat	egory AC- 4	- [A]	Category	Rated Continuous	
Frame	220 to 240V	380 to 440V	500V	220 to 240V	380 to 440V	500V	220 to 240V	380 to 440V	current I th [A]
T10	11	9	7	8	6	6	20	11	20
T12	13	12	9	11	9	9	20	13	20
T20	18	18	17	18	13	10	20	13	20
T21	25	23	17	18	13	10	32	32	32
T25	30(26)	30(26)	24	20	17	12	32	32	32
T32	32	32	24	26	24	17	32	32	32
T35	40	40	32	26	24	17	60	60	60
T50	55	48	38	35	32	24	80	80	80
T65	65	65	60	50	47	38	100	100	100
T80	85	85	75	65	62	45	120	120	120
T100	105	105	85	80	75	55	150	150	150

Note a) Rated operational current is the maximum applicable current that satisfies the making capacity, breaking capacity, switching frequency, and life at the rated operational voltage.

Note b) Rated Continuous current is a current that can conduct the electricity for 8 hours without raising the temperature above the stated level for all the parts, without switching the magnetic contactor.

Note c) The values of rated operational current in brackets () apply to the magnetic contactor (without thermal overload relay).

Table 5 DC rated working current

	Rated	Category DO (DC moto	C2, and DC4 r load) [A]	Catego (Resistanc	ry DC1 e load) [A]	Category DC-13 (DC coil load) [A]			
Frame	voltage DC [V]	2-pole series	3- pole series	2- pole series	3- pole series	Single pole	2- pole series	3- pole series	
	24	8	8	10	10	5	8	8	
-	48	4	6	10	10	3	4	6	
T10	110	2.5	4	6	8	0.6	2	3	
	220	0.8	2	3	8	0.2	0.3	0.8	
	24	12	12	12	12	7	12	12	
T 40	48	6	10	12	12	5	6	10	
T12	110	4	8	10	12	1.2	3	5	
	220	1.2	4	7	12	0.2	0.5	2	
	24	18	18	18	18	10	14	15	
TOO	48	15	18	18	18	5	7	12	
T20	110	8	15	13	18	1.2	3	5	
	220	2	8	8	18	0.2	0.5	2	
	24	20	20	20	20	12	20	20	
T 04	48	15	20	20	20	8	12	15	
T21	110	8	15	15	20	1.5	3	10	
	220	2	8	10	20	0.25	1.2	4	
	24	25	25	25	25	15	25	25	
TOF TOO	48	20	25	25	25	10	15	25	
T25, T32	110	10	20	25	25	1.5	4	12	
	220	3	10	12	22	0.25	1.2	4	
	24	35	35	35	35	15	35	35	
T35	48	20	30	35	35	10	15	25	
135	110	10	20	25	35	1.5	4	12	
	220	3	10	12	30	0.25	1.2	4	
	24	45	50	50	50	-	-	_	
T50	48	25	35	40	50	-	-	-	
150	110	15	30	35	50	-	-	-	
	220	3.5	12	15	40	-	-	-	
	24	45	50	50	65	-	-	-	
T65	48	25	35	40	65	-	-	-	
105	110	15	30	35	65	-	-	-	
	220	3.5	12	15	50	-	-	-	
	24	65	80	80	80	-	-	-	
T80	48	40	60	65	80	-	-	-	
100	110	20	50	50	80	-	-	-	
	220	5	20	20	60	-	-	-	
	24	93	93	93	93	-	-	-	
T100	48	60	90	93	93	-	-	-	
1100	110	40	80	80	93	-	-	-	
	220	30	50	50	70	-	-	-	


Note a) DC2, DC4, and DC1 are the gradings of JEM1038 that are to be applied for starting and stopping the DC shunt-wound motor, starting and stopping the DC series motor, and resistance load respectively. Note b) DC- 13 is the grading of IEC60947-5-1 which is to be applied to the induction (coil) load (time constant L/R =

100ms).


Note c) The Switching of the electrical switch can be done up to 500,000 times.

Note d) The closed current capacity of the DC2 and DC4 is four times of the above table while the frequency is 100 times and the breaking current capacity is four times of the above table while the frequency is 25 times.

Note e) The 2-pole series and 3-pole series connections are shown in the following diagram.



2-pole series



3-pole series

Characteristics and Performance (Type test results)

1. Structure

It is compatible with JISC8201-4-1, IEC60947-4-1, EN60947-4-1, UL60947-4-1, CSA C22.2 No.60947-4-1, and GB14048.4.

2. Type Test

 Applicable Standard
 IEC60947-1
 (2011)
 Low voltage switchgear and control gear

 Part 1: General Rule
 IEC60947-4-1
 (2012)
 Low voltage switchgear and control gear

 Part 4: Contactor and Motor Starter
 Section 1: Electro-mechanical Contactor and Motor Starter

2.1 Type Tests and Test Sequences

Test Sequences	Test Name	Test Conditions					
a) Sequence I	1) Temperature rise	According to the IEC60947-4-1	9.3.3.3 "Temperature Rise".				
	2) Operation and operating limits	According to the IEC60947-4-1	9.3.3.1 "Operation" and				
			9.3.3.2 "Operating Limits".				
	3) Dielectric properties	According to the IEC60947-4-1	9.3.3.4 "Dielectric Properties".				
b) Sequence II	 Rated making breaking capacity Switching capacity and reversibility 	According to the IEC60947-4-1 Capacity".	9.3.3.5 "Making and Breaking				
	2) Conventional operating performance	According to the IEC60947-4-1 Performance Capability".	9.3.3.6 "Operating				
c) Sequence III	1) Performance under short-circuit conditions	According to the IEC60947-4-1 Short-circuit Conditions".	9.3.4 "Performance under				
d) Sequence IV	1) Ability of contactors to withstand overload currents	According to the IEC60947-4-1 Withstand Overload Currents".	9.3.5 "Ability of Contactors to				
e) Sequence V	 Mechanical properties of terminals 	According to the IEC60947-1 of Terminals".	8.2.4 "Mechanical Properties				

Note a) Tests were conducted with the following coil designation: 200VAC (Rated voltage 200 to 240V 50Hz/60Hz)

2.2 Test Sequence I

2.2.1 Temperature Rise and Dielectric Properties

These tests were conducted according to the test conditions indicated in Table 1 and Note a) to e). The temperature rise of each part met the standard criteria of temperature rise limit. Also the operations and dielectric properties after the temperature tests met the standard criteria.

	Table 1														
Item	Item Combined Thermal Results														
\mathbb{N}	Overload Relay			les	Test Conditions Note a)										
		· · ·	S			5 2					/	0	Diele	ectric	
	lod	eat	ettl	Curre	ent [A]	Mair Wire		Tempe	erature R	lise [K]		pe		erties	
	Model Name	ter	ing	-	~	n Circ Size		-		0		Operation	· · · ·		
	Jan	des	ç	∕lai	Чих	ie rcu	Coil		ninal		tact	n	mp	NOC	
	ле	Heater designation	Settling Current	Main Circuit	Auxiliary Circuit	Main Circuit Connection Wire Size		Main Circuit	Au	Main Circuit	Au>		Impulse	Power Frequency	
		atio	nt	ircu	η	onr		n	cilia	n C	cilia		CD	-rec	
		n		Jit	Sirc	lec		lirc	Ţ	lirc	ry (luer	٦ L
					uit	lion		uit	Auxiliary Circuit	uit	Auxiliary Circuit			лсу	dgr
									üit		üit				Judgment
		[A]	[A]			[mm ²]	[Resistance								Ħ
						Note b)	method]						Note d)	Note d)	
Stan-												Ka 1	ĺ ĺ	· · ·	
dard												Three times opening and closing thermal No trip	7.3kV		
							100	65	65			osin	1.2/50	1890V	
	-	-	-	-	-	-	or less	or less	or less	Not	e c)	es o g th	μs	5 seconds	
Model												em	x5	• • • • • • • • • • • • • • • • • • • •	
Name												al	times		
MSO-T10 (KP)	TH-T18 (KP)	9	11	11	10	1.5	47	48	39	50	52	OK	OK	OK	ОК
MSO-T10 (KP)	TH-T18 (KP)	11	13	13	10	2.5	47	56	41	55	54	OK	OK	OK	OK
MSO-T20 (KP)	TH-T18 (KP)	15	18	18	10	2.5	53	58	42	72	54	OK	OK	OK	OK
MSO-T21 (KP)	TH-T25 (KP)	15	18	18	10	2.5	43	51	41	43	47	OK	OK	OK	OK
MSO-T25 (KP)	TH-T25 (KP)	22	26	26	10	6	43	53	40	57	47	OK	OK	OK	OK
MSO-T35 (KP)	TH-T50 (KP)	29	34	34	10	10	67	47	30	58	42	OK	OK	OK	OK
MSO-T50 (KP)	TH-T50 (KP)	42	50	50	10	10	67	58	30	68	43	OK	OK	OK	OK
MSO-T65 (KP)	TH-T65 (KP)	54	65	65	10	16	57	49	25	60	42	OK	OK	OK	OK
MSO-T80 (KP)	TH-T100 (KP)	67	80	80	10	25	63	58	25	75	42	OK	OK	OK	OK
MSO-T100 (KP)	TH-T100 (KP)	82	100	100	10	35	51	56	34	70	49	OK	OK	OK	OK
S-T10	-	-	-	20	10	2.5	45	46	38	71	52	-	OK	OK	OK
S-T12	-	-	-	20	10	2.5	41	55	38	76	52	-	OK	OK	OK
S-T20	-	-	-	20	10	2.5	41	55	38	75	52	-	OK	OK	OK
S-T21	-	-	-	32	10	6	31	34	30	46	47	-	OK	OK	OK
S-T25 S-T32	-	-	-	32 32	10 -	6 6	31 29	34 33	30	46 45	47	-	OK OK	OK OK	OK OK
S-132 S-T35	-	-	-	32 60	- 10	6 16	29 62	33	- 30	45 45	- 46	-	OK	OK	OK
S-T50	-	-	-	80	10	25	64	35 41	29	45 58	40	-	OK	OK	OK
S-T65	-	-	-	100	10	35	56	39	29	61	43	-	OK	OK	OK
S-T80	-	_	_	120	10	50	62	45	25	71	42	-	OK	OK	OK
S-T100	-	-	-	150	10	50	43	46	34	83	49	_	OK	OK	OK
0 1100				100					, v.			1	0.0	0.0	0

Note a) The test of temperature rise and operation was conducted by operating at an ambient temperature of 40°C, in open state with the iron plate mounted and by applying a voltage of 240V and a frequency of 60Hz to the operating coil.

Note b) The connection wire size of the auxiliary circuit: 1.5 mm²

Note c) The temperature rise of the contacts was checked at a temperature that is not harmful to the surrounding components. (In short 100K)

Note d) The application points of the impulse withstand voltage performance and the power frequency withstand voltage performance were as follows. However in the power frequency withstand voltage test, (c) was not implemented. Measurement Points: (a) Between all terminals of the main circuit and grounded metal body when the contact element was closed.

- (b) Between one pole of the main circuit and all other poles connected altogether to the grounded metal body when the contact element was closed.
- (c) Between the supply side terminals and the load side terminals of the main circuit when the contact element was opened.
- (d) Between one circuit of the operating circuit and auxiliary circuit, and all other circuits/grounded metal body.

Note e) Number of Samples: 1 per machine

2.2.2 Operating Limits

(1) Operating Limits of the Magnetic Contactor

The operating voltage (hot condition) and open-circuit voltage after the temperature test met the standard criteria by operating and opening without hindrance in the set voltage.

			Table 2			
	Item		Test Conditions and Re	esults		
		Operating Volt	Open-circuit Voltage (-5°C Cold)	Judgment		
	Standard	Operation at 85% (170V or	Operation at 110% of the	Open at 20 to 75% of the	Judgment	
Model Name		less) of the coil rated voltage	coil rated voltage Note a)	coil rated voltage Note b)		
MSO-T10 (KP)	50Hz	129	OK	90	OK	
WISO-110 (KF)	60Hz	142	OK	107	OK	
MSO-T12 (KP)	50Hz	149	OK	95	OK	
MOO-112 (NI)	60Hz	164	OK	109	OK	
MSO-T20 (KP)	50Hz	151	OK	96	OK	
MOO-120 (N)	60Hz	165	OK	112	OK	
MSO-T21 (KP)	50Hz	144	OK	104	OK	
M00-121 (N1)	60Hz	156	OK	115	OK	
MSO-T25 (KP)	50Hz	147	OK	108	OK	
100 120 (11)	60Hz	159	OK	118	OK	
MSO-T35 (KP)	50Hz	137	OK	107	OK	
	60Hz	146	OK	117	OK	
MSO-T50 (KP)	50Hz	137	OK	107	OK	
	60Hz	146	OK	117	OK	
MSO-T65 (KP)	50Hz	146	OK	85	OK	
	60Hz	148	OK	77	OK	
MSO-T80 (KP)	50Hz	146	OK	85	OK	
	60Hz	148	OK	77	OK	
MSO-T100 (KP)	50Hz	157	OK	100	OK	
	60Hz	159	OK	93	OK	
S-T10	50Hz	128	OK	89	OK	
0 1 10	60Hz	142	OK	106	OK	
S-T12	50Hz	145	OK	90	OK	
0112	60Hz	161	OK	107	OK	
S-T20	50Hz	145	OK	90	OK	
0 120	60Hz	161	OK	108	OK	
S-T21	50Hz	130	OK	103	OK	
5 · 1 ·	60Hz	141	OK	112	OK	
S-T25	50Hz	131	OK	104	OK	
0.20	60Hz	142	OK	114	OK	
S-T32	50Hz	142	OK	96	OK	
0.02	60Hz	156	OK	108	OK	
S-T35	50Hz	135	OK	107	OK	
0.00	60Hz	148	OK	117	OK	
S-T50	50Hz	135	OK	107	OK	
	60Hz	148	OK	117	OK	
S-T65	50Hz	146	OK	85	OK	
	60Hz	148	OK	77	OK	
S-T80	50Hz	146	OK	85	OK	
	60Hz	148	OK	77	OK	
S-T100	50Hz	153	OK	98	OK	
	60Hz	155	OK	91	OK	

Note a) The operation at 110% of the coil rated voltage of standard value was possible at 264V 50Hz/60Hz. Note b) The operation at 20 to 75% of the coil rated voltage of standard value was possible at 48V to 150V 50Hz/60Hz.

Note c) Number of Samples: 1 per machine

<Reference Test>

Coil characteristics	(20°C cold condition)
----------------------	-----------------------

	Input	[]//]	Con	Operating V		Coil C	urrent			Operating	Time [ms]		
Madal	input	[VA]	Con-	Operating v	ollage [v]	[mA]		(Coil ON -	`	0	Coil OFF -	→
Model Name	Instant	Usual	sumption Power [W]	Operation	Open	Instant	Usual	Main Contact ON	Auxiliary Contact a ON	Auxiliary Contact b OFF	Main Contact OFF	Auxiliary Contact a OFF	Auxiliary Contact b ON
S-T10	45	7	2.2	120 to 150	75 to 115	200	30	12 to 18	12 to 18	-	5 to 20	5 to 20	-
S-T12	45	7	2.2	120 to 150	75 to 115	200	30	12 to 18	12 to 18	9 to 16	5 to 20	5 to 20	7 to 22
S-T20	45	7	2.2	120 to 150	75 to 115	200	30	12 to 18	12 to 18	9 to 16	5 to 20	5 to 20	7 to 22
S-T21	75	7	2.4	125 to 155	80 to 115	340	30	13 to 20	13 to 20	8 to 14	5 to 15	5 to 15	8 to 18
S-T25	75	7	2.4	125 to 155	80 to 115	340	30	13 to 20	13 to 20	8 to 14	5 to 15	5 to 15	8 to 18
S-T32	55	4.5	1.8	125 to 155	80 to 115	250	20	15 to 22	-	-	5 to 15	-	-
S-T35	110	10	3.8	120 to 150	80 to 115	500	45	10 to 20	10 to 20	8 to 15	5 to 14	5 to 14	8 to 18
S-T50	110	10	3.8	120 to 150	80 to 115	500	45	10 to 20	10 to 20	8 to 15	5 to 14	5 to 14	8 to 18
S-T65	115	20	2.2	110 to 135	60 to 100	520	67	20 to 30	20 to 30	13 to 24	35 to 65	35 to 65	50 to 79
S-T80	115	20	2.2	110 to 135	60 to 100	520	67	20 to 30	20 to 30	13 to 24	35 to 65	35 to 65	50 to 79
S-T100	210	23	2.8	110 to 135	60 to 100	950	85	20 to 35	20 to 35	18 to 28	50 to 100	50 to 100	54 to 104

Note a) The above table shows the standard values of the properties of the 200VAC coil. Note b) Coil current is the average value when 220V 60Hz was applied.

7

- (2) Operating Charateristics of Thermal Overload Relay
 - 1) Operations in a Balanced Circuit (Ambient Temperature: 20°C)
 - (a) If the thermal overload relay does not function at 105% of settling current in cold conditions for more than 2 hours, the operation should be performed with 120% of the settling current for less than 2 hours after the constant temperature is maintained.
 - (b) When 150% of the settling current is passed after the settling current is passed and the constant temperature is maintained, the relay should operate within the limits shown in the table below with respect to the corresponding trip class.
 - (c) The operation should be performed within the limits shown in the table below with respect to the corresponding trip class, when 720% of the settling current is passed in cold conditions.

Trip Class	150% of the settling current	720% of the settling current
5	Less than 2 minutes	TP≦5 seconds
10A	Less than 2 minutes	2 <tp≦10 seconds<="" td=""></tp≦10>
10	Less than 4 minutes	4 <tp≦10 seconds<="" td=""></tp≦10>
20	Less than 8 minutes	6 <tp≦20 seconds<="" td=""></tp≦20>
30	Less than 12 minutes	9 <tp seconds<="" td="" ≦30=""></tp>

TP : Operating time at the time of constraint

Result: All the frames satisfy the above conditions.

- 2) Operations in an Unbalanced Circuit (Ambient Temperature: 20°C)
 - (a) If the open phase detection function does not execute when settling current is passed to all poles at thesame time for 2 hours, the operation should be performed within 2 hours when 1-pole is disconnected and 132% of settling current is passed to the other 2-pole after the constant temperature is maintained.
 - (b) If the open phase detection function does not execute when settling current is passed to 2-pole and 90% of settling current to 1 pole for 2 hours, the operation should be performed within 2 hours when 1-pole is disconnected and 115% of settling current is passed to the other 2-pole after the constant temperature is maintained.
 - (c) The operation should be performed within the limits shown in the table below with respect to the corresponding trip class, when 720% of the settling current is passed in cold conditions. Result: MSO-T□KP types satisfy the above conditions.

2.3 Test Sequence II

2.3.1 Test of Making and Breaking Capacities

(1) Test of Making Capacity

These tests were conducted according to the test conditions indicated in Table 4 and Note a) to c). No abnormalities such as welding of contacts were found, and the results met the standard criteria.

					I able 4	•				
Item	Rated Valu	ue (AC- 3)			Test Cond	itions (making)				
	Voltage Ue [V]	Current le [A]	Voltage U [V]	Current I [A]	Power Factor cosφ	Operation Cycle [Times] Note b)	ON time [seconds]	OFF time [seconds]	Results	nr
Stan- dard Model Name	-	-	1.05 x Ue	10 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	50	0.05	10	Contact Welding	Judgment
S-T10	220	11	231	110	0.45	50	0.05	10	None	OK
3-110	440	9	462	90	0.45	50	0.05	10	None	OK
S-T12	220	13	231	130	0.45	50	0.05	10	None	OK
5-112	440	12	462	120	0.45	50	0.05	10	None	OK
S-T20	220	18	231	180	0.45	50	0.05	10	None	OK
3-120	440	18	462	180	0.45	50	0.05	10	None	OK
S-T21	220	25	231	250	0.45	50	0.05	10	None	OK
5-121	440	23	462	230	0.45	50	0.05	10	None	OK
S-T25	220	30	231	300	0.45	50	0.05	10	None	OK
5-125	440	30	462	300	0.45	50	0.05	10	None	OK
S-T32	220	32	231	320	0.45	50	0.05	10	None	OK
5-132	440	32	462	320	0.45	50	0.05	10	None	OK
S-T35	220	40	231	400	0.45	50	0.05	10	None	OK
0-100	440	40	462	400	0.45	50	0.05	10	None	OK
S-T50	220	55	231	550	0.45	50	0.05	10	None	OK
5-150	440	48	462	480	0.45	50	0.05	10	None	OK
S-T65	220	65	231	650	0.45	50	0.05	10	None	OK
5-105	440	65	462	650	0.45	50	0.05	10	None	OK
S-T80	220	85	231	850	0.45	50	0.05	10	None	OK
5-100	440	85	462	850	0.45	50	0.05	10	None	OK
S-T100	220	105	231	1050	0.35	50	0.05	10	None	OK
3-1100	440	105	462	1050	0.35	50	0.05	10	None	OK

Note a) Main circuit frequency: 60Hz

Note b) Among 50 operating cycles, 110% of the rated value (264V 60Hz) was applied to the coil for 25 cycles, and 85% of the rated value (170V 60Hz) was applied to the coil for the other 25 cycles.

Note c) Number of Samples: 1 per machine

(2) Test of Making and Breaking Capacities

These tests were conducted according to the test conditions indicated in Table 5 and Note a) to c) after the making capacity test (1). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria.

					l able 5					
Item	Rated (AC	Value - 3)		Test	Conditions (mak	ing and breaking	g capacity	()	Deculto	
	Voltage Ue	Current le	Voltage Ur	Current Ic	Power Factor	Operation Cycle	ON time	OFF time	Results	1
	ſŇ	[A]	ĪŇ	[A]	cosφ	[Times]	[seconds]	[seconds]		
Stan-			[·]			[]	[]	lc≦100: 10		Judgment
dard								100 <lc≦200: 20<="" td=""><td>Contact</td><td>lĝp</td></lc≦200:>	Contact	lĝp
					le≦100A:			200 <lc≦200: 20<="" td=""><td></td><td>me</td></lc≦200:>		me
			1.05	0	0.45±0.05	-0	0.05		Welding and	nt
	-	-	1.05 x Ue	8 x le	le>100A:	50	0.05	300 <lc≦400: 40<="" td=""><td>Phase-to-</td><td></td></lc≦400:>	Phase-to-	
					0.35±0.05			400 <lc≦600: 60<="" td=""><td>phase</td><td></td></lc≦600:>	phase	
Model					0.0020.00			600 <lc≦800: 80<="" td=""><td>Short-circuits</td><td></td></lc≦800:>	Short-circuits	
Name								800 <lc≦1000: 100<="" td=""><td></td><td></td></lc≦1000:>		
S-T10	220	11	231	88	0.45	50	0.05	10	None	OK
3-110	440	9	462	72	0.45	50	0.05	10	None	OK
S-T12	220	13	231	104	0.45	50	0.05	20	None	OK
0-112	440	12	462	96	0.45	50	0.05	10	None	OK
S-T20	220	18	231	144	0.45	50	0.05	20	None	OK
0-120	440	18	462	144	0.45	50	0.05	20	None	OK
S-T21	220	25	231	200	0.45	50	0.05	20	None	OK
0-121	440	23	462	184	0.45	50	0.05	20	None	OK
S-T25	220	30	231	240	0.45	50	0.05	30	None	OK
0 120	440	30	462	240	0.45	50	0.05	30	None	OK
S-T32	220	32	231	256	0.45	50	0.05	30	None	OK
0 102	440	32	462	256	0.45	50	0.05	30	None	OK
S-T35	220	40	231	320	0.45	50	0.05	40	None	OK
0 100	440	40	462	320	0.45	50	0.05	40	None	OK
S-T50	220	55	231	440	0.45	50	0.05	60	None	OK
- 100	440	48	462	384	0.45	50	0.05	40	None	OK
S-T65	220	65	231	520	0.45	50	0.05	60	None	OK
- 100	440	65	462	520	0.45	50	0.05	60	None	OK
S-T80	220	85	231	680	0.45	50	0.05	80	None	OK
- 100	440	85	462	680	0.45	50	0.05	80	None	OK
S-T100	220	105	231	840	0.35	50	0.05	100	None	OK
	440	105	462	840	0.35	50	0.05	100	None	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying a voltage of 240V and a frequency 60Hz to the operating coil. Note c) Number of Samples: 1 per machine

(3) The Switching Capacity and Reversibility

These tests were conducted according to the test conditions indicated in Table 6, 7 and Note a) to d). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria.

					Tac	ne o				
Item	Rated (AC	Value - 4)			Test Cond	itions (making)			Desults	
\setminus	Voltage Ue	Current le	Voltage Ur	Current Ic	Power Factor	Operation Cycle	ON time	OFF time	Results	
	٢Ň٦	[A]	١٧	[A]	cosφ	[Times]	[seconds]	[seconds]		ب
Stan- dard	-	-	1.05 x Ue	12 x le	le≦100A 0.45±0.05 le>100A	50	0.05	10	Contact Welding and Phase-to- phase	Judgment
Model Name					0.35±0.05				Short-circuits	
C 2 × T10	220	8	231	96	0.45	50	0.05	10	None	OK
S-2 x T10	440	6	462	72	0.45	50	0.05	10	None	OK
S-2 x T12	220	11	231	132	0.45	50	0.05	10	None	OK
5-2 X 1 12	440	9	462	108	0.45	50	0.05	10	None	OK
S-2 x T20	220	18	231	216	0.45	50	0.05	10	None	OK
3-2 X 120	440	13	462	156	0.45	50	0.05	10	None	OK
S-2 x T21	220	18	231	216	0.45	50	0.05	10	None	OK
0-2 x 121	440	13	462	156	0.45	50	0.05	10	None	OK
S-2 x T25	220	20	231	240	0.45	50	0.05	10	None	OK
02 x 120	440	17	462	204	0.45	50	0.05	10	None	OK
S-2 x T35	220	26	231	312	0.45	50	0.05	10	None	OK
0 2 % 100	440	24	462	288	0.45	50	0.05	10	None	OK
S-2 x T50	220	35	231	420	0.45	50	0.05	10	None	OK
0 2 x 100	440	32	462	384	0.45	50	0.05	10	None	OK
S-2 x T65	220	50	231	600	0.45	50	0.05	10	None	OK
	440	47	462	564	0.45	50	0.05	10	None	OK
S-2 x T80	220	65	231	780	0.45	50	0.05	10	None	OK
	440	62	462	744	0.45	50	0.05	10	None	OK
S-2 x T100	220	80	231	960	0.45	50	0.05	10	None	OK
	440	75	462	900	0.45	50	0.05	10	None	OK


					Table 7						
Item	Rated (AC			Test (Conditions (maki	ng and	breaking	capacity))		
Stan-	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ		ion Cycle mes] Simulta- neous Excitation Test	ON time [seconds]	OFF time [seconds]	Results	Judgment
dard Model Name	-	-	1.05 x Ue	10 x le	le≦100A 0.45±0.05 le>100A 0.35±0.05	50	10	0.05	Ic≦100: 10 100 <ic≦200: 20<br="">200<ic≦300: 30<br="">300<ic≦400: 40<br="">400<ic≦600: 60<br="">600<ic≦800: 80<="" td=""><td>Contact Welding and Phase-to- phase Short-circuits</td><td>nt</td></ic≦800:></ic≦600:></ic≦400:></ic≦300:></ic≦200:>	Contact Welding and Phase-to- phase Short-circuits	nt
S-2 x T10	220	8	231	80	0.45	50	10	0.05	10	None	OK
5-2 × 110	440	6	462	60	0.45	50	10	0.05	10	None	OK
S-2 x T12	220	11	231	110	0.45	50	10	0.05	20	None	OK
5-2 × 112	440	9	462	90	0.45	50	10	0.05	10	None	OK
S-2 x T20	220	18	231	180	0.45	50	10	0.05	20	None	OK
5-2 x 120	440	13	462	130	0.45	50	10	0.05	20	None	OK
S-2 x T21	220	18	231	180	0.45	50	10	0.05	20	None	OK
5-2 x 121	440	13	462	130	0.45	50	10	0.05	20	None	OK
S-2 x T25	220	20	231	200	0.45	50	10	0.05	20	None	OK
3-2 X 125	440	17	462	170	0.45	50	10	0.05	20	None	OK
S-2 x T35	220	26	231	260	0.45	50	10	0.05	30	None	OK
3-2 X 135	440	24	462	240	0.45	50	10	0.05	30	None	OK
S-2 x T50	220	35	231	350	0.45	50	10	0.05	40	None	OK
3-2 X 100	440	32	462	320	0.45	50	10	0.05	40	None	OK
S-2 x T65	220	50	231	500	0.45	50	10	0.05	60	None	OK
3-2 X 103	440	47	462	470	0.45	50	10	0.05	60	None	OK
S-2 x T80	220	65	231	650	0.45	50	10	0.05	80	None	OK
3-2 X 100	440	62	462	620	0.45	50	10	0.05	80	None	OK
S-2 x T100	220	80	231	800	0.45	50	10	0.05	80	None	OK
3-2 X 1 100	440	75	462	750	0.45	50	10	0.05	80	None	OK

Note a) The test was conducted using reversible-type magnetic contactor.

Note b) The operation was conducted at main circuit frequency of 60Hz by applying a voltage of 240V and a frequency of 60Hz to the operating coil.

Note c) Making A → Open circuit A, then immediately making B → Open circuit B → OFF time (above table) pause →Making B → Open circuit B, then immediately making A → Open circuit A → OFF time (above table) pause, this makes 1 cycle. 50 cycles were performed in this way.

Here, (1) "A" shows the forward rotation contactor and "B" shows the reverse rotation contactor. (2) "Immediately" refers to the shortest reversible exchange time.



Note d) Number of Samples: 1 per machine

2.3.2 The Operating Performance

(1) Non-reversing

These tests were conducted according to the test conditions indicated in Table 8 and Note a) to c). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria. After the test, the withstand voltage performance was checked by applying a voltage of 1000V and a frequency of 60Hz for 5 seconds. The results were acceptable. Table 8

Itom	Rated	Value			100	le 8					
Item	(AC			Test	Conditions (m	naking and break	ing capac	ity)	Res	ults	
	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Operation Cycle [Times]	ON time [seconds]	OFF time [seconds]	Making and Breaking Capacity	Withstand Voltage	
Stan- dard Model Name	-	-	1.05 x Ue	2 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	6000	0.05	lc≦100: 10 100 <lc≦200: 20<br="">200<lc≦300: 30<="" td=""><td>Contact Welding and Phase-to-phase Short-circuit</td><td>2 x Ue provided 1000V or higher 5 seconds</td><td>Judgment</td></lc≦300:></lc≦200:>	Contact Welding and Phase-to-phase Short-circuit	2 x Ue provided 1000V or higher 5 seconds	Judgment
S-T10	220	11	231	22	0.45	6000	0.05	10	None	OK	OK
3-110	440	9	462	18	0.45	6000	0.05	10	None	OK	OK
S-T12	220	13	231	26	0.45	6000	0.05	10	None	OK	OK
0-112	440	12	462	24	0.45	6000	0.05	10	None	OK	OK
S-T20	220	18	231	36	0.45	6000	0.05	10	None	OK	OK
0.10	440	18	462	36	0.45	6000	0.05	10	None	OK	OK
S-T21	220	25	231	50	0.45	6000	0.05	10	None	OK	OK
	440	23	462	46	0.45	6000	0.05	10	None	OK	OK
S-T25	220	30	231	60	0.45	6000	0.05	10	None	OK	OK
	440	30	462	60	0.45	6000	0.05	10	None	OK	OK
S-T32	220	32	231	64	0.45	6000	0.05	10	None	OK	OK
	440	32	462	64	0.45	6000	0.05	10	None	OK	OK
S-T35	220 440	40	231	80	0.45	6000	0.05	10 10	None	OK OK	OK OK
	220	40 55	462 231	80 110	0.45 0.45	6000 6000	0.05 0.05	20	None	OK	OK
S-T50		55 48	462	96		6000		10	None	OK	OK
	440				0.45		0.05	20	None	OK	OK
S-T65	220	65	231	130	0.45	6000	0.05		None	-	_
	440 220	65 85	462 231	130 170	0.45 0.45	6000 6000	0.05 0.05	20 20	None	OK OK	OK OK
S-T80	440	85 85	462	170	0.45	6000	0.05	20	None	OK	OK
	220	85 105	462 231	210	0.45	6000	0.05	30	None None	OK	OK
S-T100	440	105	462	210	0.35	6000	0.05	30		OK	OK
L	440	105	402	210	0.35	0000	0.05	30	None	UN	UN

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying a voltage of 240V and a frequency of 60Hz to the operating coil.

Note c) Number of Samples: 1 per machine

(2) Reversing

These tests were conducted according to the test conditions indicated in Table 9 and Note a) to e). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria. After the test, the withstand voltage performance was checked by applying a voltage of 1000V and a frequency of 60Hz for 5 seconds. The results were acceptable. Table 9

Item	Rated (AC-			Test		naking and break	ing capac	ity)	Res	ults	
	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Operation Cycle [Times] Note d)	ON time [seconds]	OFF time [seconds]	Making and Breaking Capacity	Withstand Voltage	
Stan- dard Model Name	-	-	1.05 x Ue	6 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	6000	0.05	lc≦100: 10 100 <lc≦200: 20<br="">200<lc≦300: 30<br="">300<lc≦400: 40<br="">400<lc≦600: 60<="" td=""><td>Contact Welding and Phase-to-phase Short-circuit</td><td>2 x Ue Provided 1000V or higher 5 seconds</td><td>Judgment</td></lc≦600:></lc≦400:></lc≦300:></lc≦200:>	Contact Welding and Phase-to-phase Short-circuit	2 x Ue Provided 1000V or higher 5 seconds	Judgment
	220	8	231	48	0.45	6000	0.05	10	None	ОК	ОК
S-2 x T10	440	6	462	36	0.45	6000	0.05	10	None	OK	OK
	220	11	231	66	0.45	6000	0.05	10	None	OK	OK
S-2 x T12	440	9	462	54	0.45	6000	0.05	10	None	OK	OK
0.0	220	18	231	108	0.45	6000	0.05	20	None	OK	OK
S-2 x T20	440	13	462	78	0.45	6000	0.05	10	None	OK	OK
C 2 x T21	220	18	231	108	0.45	6000	0.05	20	None	OK	OK
S-2 x T21	440	13	462	78	0.45	6000	0.05	10	None	OK	OK
S-2 x T25	220	20	231	120	0.45	6000	0.05	20	None	OK	OK
3-2 X 125	440	17	462	102	0.45	6000	0.05	20	None	OK	OK
S-2 x T32	220	26	231	156	0.45	6000	0.05	20	None	OK	OK
3-2 X 132	440	24	462	144	0.45	6000	0.05	20	None	OK	OK
S-2 x T35	220	26	231	156	0.45	6000	0.05	20	None	OK	OK
3-2 X 133	440	24	462	144	0.45	6000	0.05	20	None	OK	OK
S-2 x T50	220	35	231	210	0.45	6000	0.05	30	None	OK	OK
5-2 X 150	440	32	462	192	0.45	6000	0.05	20	None	OK	OK
S-2 x T65	220	50	231	300	0.45	6000	0.05	30	None	OK	OK
3-2 x 103	440	47	462	282	0.45	6000	0.05	30	None	OK	OK
S-2 x T80	220	65	231	390	0.45	6000	0.05	40	None	OK	OK
3-2 X 100	440	62	462	372	0.45	6000	0.05	40	None	OK	OK
S-2 x T100	220	80	231	480	0.45	6000	0.05	60	None	OK	OK
3-2 X 1 100	440	75	462	450	0.45	6000	0.05	60	None	OK	OK

Note a) The test was conducted using reversible-type magnetic contactor.

Note b) Main circuit frequency: 60Hz

Note c) The operation was conducted by applying a voltage of 240V and frequency of 60Hz to the operating coil.

Note d) The operation was performed based on the cycle mentioned in Note c) of 2.3.1 (3).

Note e) Number of Samples: 1 per machine

2.4 Test Sequence III

2.4.1 Performance under Short-circuit Conditions

These tests were conducted according to the test conditions indicated in Table 10 and Note a) to d). There was no damage to the conductors and terminals. The leakage detection fuse was not melted, and the results were acceptable.

					Т	able 10						
\mathbb{N}	ltem	Rated	Rated Valu	e (AC- 3)		Test Co	nditions			Results		
Thermal Overload Relay		Current of SCPD [A] Note a)	Voltage Ue [V]	Current le [A]	Voltage [V]	Current I [kA]	Power Factor cosφ	Number of Samples	O or CO Operation	Conductor/ Terminal Damage	Melting of the Leakage Detection Fuse	Judgment
	lel Name Standard nd Nominal Current of the Heater	-	-	-	Ue	Note c)	Note d)	[machine]	Note b)	None	None	ent
MSO-T10 (KP)	TH-T18 9A	20	220/440	11/9	440	1	0.95	1	O CO	None None	None None	OK
MSO-T12 (KP)	TH-T18 11A	25	220/440	13/12	440	1	0.95	1	0 CO	None None	None None	OK
MSO-T20 (KP)	TH-T18 15A	32	220/440	18/18	440	3	0.9	1	0 C0	None	None	OK
MSO-T21 (KP)	TH-T25 15A	32	220/440	25/23	440	3	0.9	1	0 C0	None	None	OK
MSO-T25 (KP)	TH-T25 22A	50	220/440	30/30	440	3	0.9	1	0 CO	None	None	OK
MSO-T35 (KP)	TH-T50 29A	63	220/440	40/40	440	3	0.9	1	0 C0	None	None	OK
MSO-T50 (KP)	TH-T50 42A	100	220/440	55/48	440	3	0.9	1	0 C0	None	None	ОК
MSO-T65 (KP)	TH-T65 54A	100	220/440	65/65	440	5	0.7	1	0 C0	None	None	ОК
MSO-T80 (KP)	TH-T100 67A	125	220/440	85/85	440	5	0.7	1	0 C0	None	None	ОК
MSO-T100 (KP)	TH-T100 82A	160	220/440	105/105	440	5	0.7	1	0 C0	None	None	ОК
S-T10	-	40	220/440	11/9	440	1	0.95	1	0 CO	None	None	OK
S-T12	-	40	220/440	13/12	440	1	0.95	1	0 C0	None	None	OK
S-T20	-	40	220/440	18/18	440	3	0.9	1	0 C0	None	None	ОК
S-T21	-	80	220/440	25/23	440	3	0.9	1	0 CO	None	None	ОК
S-T25	-	80	220/440	30/30	440	3	0.9	1	0 C0	None	None	OK
S-T32	-	80	220/440	32/32	440	3	0.9	1	0 CO	None	None	OK
S-T35	-	100	220/440	40/40	440	3	0.9	1	0 C0	None	None	OK
S-T50	-	100	220/440	55/48	440	3	0.9	1	0 0 C0	None	None	OK
S-T65	-	100	220/440	65/65	440	5	0.7	1	0 C0	None	None	OK
S-T80	-	125	220/440	85/85	440	5	0.7	1	0 C0	None	None	OK
S-T100	-	160	220/440	105/105	440	5	0.7	1	0 C0	None None	None	OK
	1			1				· ·		10110	110110	

Note a) SCPD: Short Circuit Protection Device

Note b) O operation: Breaking of the circuit by the SCPD resulting from closing the circuit on the equipment under test which is in the closed position.

- CO operation: Breaking of the circuit by the SCPD resulting from closing the circuit by the equipment under test.
- Note c) The test current specified in the standards for rated operational current was as follows. (le indicates the maximum current applied to the motor) When 1<le≦16: 1 kA
 - When 16<le≦63: 3 kA

When 63<le≦125: 5 kA

Note d) The power factor specified in the standards for test current was as follows.

When I≦1.5 kA: 0.95±0.05

When 1.5 kA<l≦3 kA: 0.9±0.05

When 4.5 kA<I≦6 kA: 0.7±0.05

2.5 Test Sequence IV

2.5.1 Ability of Contactors to Withstand Overload Currents

The current indicated in Table 11 was applied for 10 seconds in making conditions of the magnetic contactor. All the parts met the standard criteria without abnormality.

			able 11		
Item		Test Cond	itions		
	Rated Current [A]	Current [A]	Current Passage Time [seconds]	Results	
Stan- dard Model Name	Rated Operational Current (AC-3)	le≦630A: 8 x le le>630A: 6 x le	10	Abnormality in the part	Judgment
S-T10	11	88	10	None	OK
S-T12	13	104	10	None	OK
S-T20	18	144	10	None	OK
S-T21	25	200	10	None	OK
S-T25	30	240	10	None	OK
S-T32	32	256	10	None	OK
S-T35	40	320	10	None	OK
S-T50	55	440	10	None	OK
S-T65	65	520	10	None	OK
S-T80	85	680	10	None	OK
S-T100	105	840	10	None	OK

Note a) The test was conducted only for the magnetic contactor.

Note b) Number of Samples: 1 per machine

2.6 Test Sequence V

2.6.1 Mechanical Properties of Terminals

- (1) Tests of Mechanical Strength of Terminals
- The crimp terminal indicated in Table 12 was tightened with the following tightening torques, and was tested by connection and disconnection 5 times. All the parts met the standard criteria without looseness or damage.

	_		Table 12			
Item	Position	Crimp Terminal Size	Manufacturer Standard Tightening Torque [N⋅m]	Tested Tightening Torque [N · m]	Results	bnſ
Stan- darc Model Name		Conductor of the Maximum Cross-Sectional Area	-	110% of the Manufacturer Standard Tightening Torque Note a)	Looseness or Damage to the Part	Judgment
	S-T10: 1/L1	2-3.5	0.9 to 1.5	1.65	None	OK
MSO-T10(KP)	TH-T18(KP): 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK
	S-T12: 1/L1	2-3.5	0.9 to 1.5	1.65	None	OK
MSO-T12(KP)	TH-T18(KP): 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK
MSO-T20(KP)	S-T20: 1/L1	2-3.5	0.9 to 1.5	1.65	None	OK
WISO-120(KP)	TH-T18(KP): 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK
	S-T21: 1/L1	5.5-4	1.2 to 1.9	2.09	None	OK
MSO-T21(KP)	TH-T25(KP): 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK
	S-T25: 1/L1	5.5-4	1.2 to 1.9	2.09	None	OK
MSO-T25(KP)	TH-T25(KP): 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK
	S-T35: 1/L1	22-S5	2.0 to 3.3	3.63	None	OK
MSO-T35(KP)	TH-T50(KP): 6/T3	14-5	2.0 to 3.3	3.63	None	OK
	S-T50: 1/L1	22-S5	2.0 to 3.3	3.63	None	OK
MSO-T50(KP)	TH-T50(KP): 6/T3	14-5	2.0 to 3.3	3.63	None	OK
	S-T65: 1/L1	60-S6	3.5 to 5.7	6.27	None	OK
MSO-T65(KP)	TH-T65(KP): 6/T3	22-6	3.5 to 5.7	6.27	None	OK
	S-T80: 1/L1	60-S6	3.5 to 5.7	6.27	None	OK
MSO-T80(KP)	TH-T100(KP): 6/T3	38-S6	3.5 to 5.7	6.27	None	OK
	S-T100: 1/L1	60-6	3.5 to 5.7	6.27	None	OK
MSO-T100(KP)	TH-T100(KP): 6/T3	38-S6	3.5 to 5.7	6.27	None	OK
S-T10	2/T1, 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK
S-T12	2/T1, 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK
S-T20	2/T1, 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK
S-T21	2/T1, 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK
S-T25	2/T1, 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK
S-T32	2/T1, 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK
S-T35	2/T1, 6/T3	22-S5	2.0 to 3.3	3.63	None	OK
S-T50	2/T1, 6/T3	22-S5	2.0 to 3.3	3.63	None	OK
S-T65	2/T1, 6/T3	60-S6	3.5 to 5.7	6.27	None	OK
S-T80	2/T1, 6/T3	60-S6	3.5 to 5.7	6.27	None	OK
S-T100	2/T1, 6/T3	60-6	3.5 to 5.7	6.27	None	OK

Note a) The test was conducted by applying 110% of the maximum value of the manufacturer standard tightening torque.

Note b) Number of Samples: 1 per machine

(2) Flexion and Pull-out Tests

In the flexion tests, the wire was rotated 135 times continuously by placing weight on its pointed end under the conditions (the following tightening torques were checked by using the minimum value of the manufacturer standard tightening torque) indicated in Table 13-1 and 13-2. The results met the standard criteria without pullout or breaking of the conductor. Then, the pull-out strength indicated in Table 13-1 and 13-2 was applied for 1 minute. The results met the standard criteria without pullout or breaking of the conductor. Table 13-1

							Table 13-					
Item	Target Terminal Position	Screw Size	Wire Spe Type	cifications Size	Number of Connections	Manufacturer Standard Tightening Torque [N·m]	Tested Tightening Torque [N ⋅ m]	Bushing Hole Diameter [mm]	Height [mm]	Weight [kg]	Pulling Force [N]	Judgment
Model Name	-	-	-	-	Maximum Number of Connections	-	Specified Tightening Torque	$\begin{array}{c} 0.75mm^2: 6.5\\ 1.25mm^2: 0.5\\ 2.5mm^2: 9.5\\ 4mm^2: 9.5\\ 14mm^2: 9.5\\ 14mm^2: 13.0\\ 16mm^2: 13.0\\ \phi 1.6: 9.5\\ \phi 2: 9.5\\ \phi 2: 9.5\\ \phi 3.6: 13.0\\ \end{array}$	0.75mm ² : 260 1.25mm ² : 280 2.5mm ² : 280 4mm ² : 280 6mm ² : 280 14mm ² : 300 16mm ² : 300 0fl.6: 280 0fl.6: 280 0fl.6: 280 0fl.6: 280 0fl.6: 300	$\begin{array}{c} 0.75mm^2: 0.4\\ 1.25mm^2: 0.4\\ 2.5mm^2: 0.7\\ 4mm^2: 0.9\\ 6mm^2: 1.4\\ 14mm^2: 2.9\\ 16mm^2: 2.9\\ 16mm^2: 2.9\\ \phi1.6: 0.7\\ \phi2: 0.9\\ \phi2.6: 1.4\\ \phi3.6: 2.9 \end{array}$	$\begin{array}{c} 0.75mm^2{\rm :}\;30\\ 1.25mm^2{\rm :}\;40\\ 2.5mm^2{\rm :}\;50\\ 4mm^2{\rm :}\;50\\ 4mm^2{\rm :}\;80\\ 14mm^2{\rm :}\;100\\ 16mm^2{\rm :}\;100\\ \phi1.6{\rm :}\;50\\ \phi2{\rm :}\;60\\ \phi2{\rm :}\;60\\ \phi2{\rm .}6{\rm :}\;80\\ \phi3{\rm .}6{\rm :}\;100 \end{array}$	Pullout or Breaking of Conductor
				0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
MSO-T10	2/T1 (S-T10)	M3.5	Wire Single Wire	2.5mm ² φ1.6	2	0.9 to 1.5 0.9 to 1.5	0.9 0.9	9.5 9.5	280 280	0.7	50 50	ОК ОК
(KP)	0.770			0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	ОК
	6/T3 (TH-T18	M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
	(KP))		Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
	2/T1		Stranded Wire	0.75mm ² 2.5mm ²	2	0.9 to 1.5 0.9 to 1.5	0.9 0.9	6.5 9.5	260 280	0.4	30 50	OK OK
MSO-T12	(S-T12)	M3.5	Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
(KP)	6/T3		Stranded	0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
	(TH-T18	M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
	(KP))		Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
	2/T1		Stranded Wire	0.75mm ² 2.5mm ²	2	0.9 to 1.5 0.9 to 1.5	0.9 0.9	6.5 9.5	260 280	0.4	30 50	OK OK
MSO-T20	(S-T20)	M3.5	Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
(KP)	6/T3		Stranded	0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
	(TH-T18 (KP))	M3.5	Wire Single	2.5mm ² φ1.6	2	0.9 to 1.5 0.9 to 1.5	0.9 0.9	9.5 9.5	280 280	0.7	50 50	ок ОК
	())		Wire Stranded	1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	2/T1	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	(S-T21)	1014	Single Wire	φ1.6	2	1.2 to 1.9 1.2 to 1.9	1.2	9.5	280	0.7	50 80	OK OK
MSO-T21 (KP)	0.770		Stranded	φ2.6 1.25mm ²	2	1.2 to 1.9	1.2 1.2	9.5 6.5	280 260	1.4 0.4	40	OK
、 ,	6/T3 (TH-T25	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	(KP))		Single Wire	φ1.6 φ2.6	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 9.5	280 280	0.7	50 80	OK OK
				42.0 1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	2/T1	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
MSO-T25	(S-T25)		Single Wire	φ1.6 φ2.6	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 9.5	280 280	0.7	50 80	OK OK
(KP)	6/T3		Stranded	1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	(TH-T25	M4	Wire Single	6mm ² φ1.6	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 9.5	280 280	1.4 0.7	80 50	OK OK
	(KP))		Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	0/74		Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	2/T1 (S-T35)	M5	Wire Single	16mm ² φ1.6	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	13.0 9.5	300 280	2.9 0.7	100 50	OK OK
MSO-T35	/		Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
(KP)	6/T3		Stranded Wire	4mm ² 14mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	9.5 13.0	280 300	0.9 2.9	60 100	OK OK
	(TH-T50 (KP))	M5	Single	φ2	2	2.0 to 3.3	2.0	9.5	280	0.9	60	OK
	(N <i>I</i>)		Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	2/T1		Stranded Wire	1.25mm ² 16mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	6.5 13.0	260 300	0.4 2.9	40 100	OK OK
	(S-T50)	M5	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
MSO-T50 (KP)			Wire	φ3.6 4mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	13.0 9.5	300 280	2.9 0.9	100 60	OK OK
(())	6/T3	N/5	Stranded Wire	14mm ²	2	2.0 to 3.3	2.0	9.5	300	2.9	100	OK
	(TH-T50 (KP))	M5	Single	φ2	2	2.0 to 3.3	2.0	9.5	280	0.9	60	OK
	· //		Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK

Note a) Since MSO-T65(KP) higher models cannot be connected to the unprocessed exposed conductor, this evaluation is not applicable.

Table 13-2

Item			Miro Spo	ecification	z			2				
Stan-	Target Terminal Position	Screw Size	Туре	Size	Number of Connections	Manufacturer Standard Tightening Torque [N·m]	Tested Tightening Torque [N∙m]	Bushing Hole Diameter [mm]	Height [mm]	Weight [kg]	Pulling Force [N]	Judgment
Model Name	_	-	-	-	Maximum Number of Connections	-	Specified Tightening Torque	$\begin{array}{c} 0.75mm^2: 6.5\\ 1.25mm^2: 6.5\\ 2.5mm^2: 9.5\\ 16mm^2: 13.0\\ \phi 1.6: 9.5\\ \phi 3.6: 13.0 \end{array}$	0.75mm ² : 260 1.25mm ² : 260 2.5mm ² : 280 16mm ² : 300 φ1.6: 280 φ3.6: 300	$\begin{array}{c} 0.75mm^2: 0.4\\ 1.25mm^2: 0.4\\ 2.5mm^2: 0.7\\ 16mm^2: 2.9\\ \phi 1.6: 0.7\\ \phi 3.6: 2.9 \end{array}$	0.75mm ² : 30 1.25mm ² : 40 2.5mm ² : 50 16mm ² : 100 φ1.6: 50 φ3.6: 100	Pullout or Breaking of Conductor
			Stranded		2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
	2/T1	M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
			Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
S-T10				0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
	6/T3	M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
			Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
				0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	ОК
	2/T1	M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
			Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	ОК
S-T12			Stranded	0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	ОК
	6/T3	M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.4	50	OK
	0/13	1013.5	Single	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
			Wire	0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
	0/74	N/0 5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
	2/T1	M3.5	Single	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
S-T20			Wire	•								
			Stranded Wire	0.75mm ² 2.5mm ²	2	0.9 to 1.5 0.9 to 1.5	0.9	6.5 9.5	260 280	0.4	30 50	OK OK
	6/T3	M3.5	Single	φ1.6	2	0.9 to 1.5	0.9	9.5	280		50	OK
			Wire	•						0.7		
			Stranded Wire	1.25mm ² 6mm ²	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	6.5 9.5	260 280	0.4	40 80	OK OK
	2/T1	M4	Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
S-T21			Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
3-121				1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	6/T3	M4	Wire Single	6mm ² φ1.6	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 9.5	280 280	<u>1.4</u> 0.7	80 50	OK OK
			Wire	φ1.0 φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
				1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	2/T1	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
			Single Wire	φ1.6 φ2.6	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 9.5	280 280	0.7	50 80	OK OK
S-T25				1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	6/T3	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	0/10		Single Wire	φ1.6	2	1.2 to 1.9	1.2 1.2	9.5 9.5	280	0.7	50 80	OK OK
				φ2.6 1.25mm ²	2	1.2 to 1.9 1.2 to 1.9	1.2	9.5 6.5	280 260	1.4 0.4	40	OK
	2/T1	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	2/11	1014	Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
S-T32			Wire Stranded	φ2.6 1.25mm ²	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 6.5	280 260	<u>1.4</u> 0.4	80 40	OK OK
	0/70		Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	6/T3	M4	Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
			Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
			Stranded Wire	1.25mm ² 16mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	6.5 13.0	260 300	0.4 2.9	40 100	OK OK
	2/T1	M5	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
S-T35			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
5 100				1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	6/T3	M5	Wire Single	16mm ² φ1.6	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	13.0 9.5	300 280	2.9 0.7	100 50	OK OK
			Wire	φ1.0 φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
			Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	2/T1	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
			Single Wire	φ1.6 φ3.6	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	9.5 13.0	280 300	0.7 2.9	50 100	OK OK
S-T50				43.0 1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	6/T3	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	5,10	1010	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK

Note a) Since S-T65 or higher models cannot be connected to the unprocessed exposed conductor, this evaluation is not applicable.

Special Magnetic Contactor

DC-operated Magnetic Contactor <Type SD-T>

Type SD-T DC operating magnetic contactor is used to supply DC to the electromagnetic portion of type S-T magnetic contactor.

1. Structure

Since the SD-T12 to T100 electromagnets limit the current with just the resistor of the coil by directly applying all the voltage, their operation is stable with no inrush current. The SD-T12 to T32 electromagnets are high efficiency polarized electromagnets that combine the coil and permanent magnet.

2. Rating

Contact rated value is the same as that of AC operating type S-T.

3. Type Test

Applicable Standard IEC60947-1 (2011) Low voltage switchgear and control gear Part 1: General Rule IEC60947-4-1 (2012) Low voltage switchgear and control gear Part 4: Contactor and Motor Starter Section 1: Electro-mechanical Contactor and Motor Starter

3.1 Type Tests and Test Sequences

Test Sequences	Test Name	Test Co	onditions
a) Sequence I	1) Temperature rise	According to the IEC60947-4-1	9.3.3.3 "Temperature Rise".
	2) Operation and operating limits	According to the IEC60947-4-1	9.3.3.2 "Operating Limit".
	3) Dielectric properties	According to the IEC60947-4-1	9.3.3.4 "Dielectric Properties".
b) Sequence II	 Rated making and breaking capacity Switching capacity and reversibility 	According to the IEC60947-4-1 Capacity".	9.3.3.5 "Making and Breaking
	2) Conventional operating performance	According to the IEC60947-4-1 Performance Capability".	9.3.3.6 "Operating
c) Sequence III	1) Performance under short-circuit conditions	According to the IEC60947-4-1 Short-circuit Conditions".	9.3.4 "Performance under
d) Sequence IV	1) Ability of contactors to withstand overload currents	According to the IEC60947-4-1 Withstand Overload Currents".	9.3.5 "Ability of Contactors to
e) Sequence V	1) Mechanical properties of terminals	According to the IEC60947-1 of Terminals".	8.2.4 "Mechanical Properties

Note Tests were conducted with the following coil designation:

Test Sequence I : SD-T12 to SD-T32: 24VDC, 100VDC

SD-T35 to SD-T100: 24VDC

Test Sequence II to V : 24VDC

3.2 Test Sequence I

3.2.1 Temperature Rise and Dielectric Properties

For the temperature rise, these tests were conducted according to the test conditions indicated in Table 1 and Note a) to d), and the temperature rise of each portion met the standards. The dielectric properties after the temperature test also met the standard criteria.

l able 1														
\mathbb{N}	Item		Те	st Cond	itions				F	Results	Note a)			
				Conn	ection		Maximu	m Temp	erature	Rise Va	lue [K]	Dielectric P	operties	
	\backslash	Curre	ent [A]		ire [mm²]	Coil Voltage	Coil		ninal	Cor	ntact	Impulse	Power	
		Main Circuit	Auxiliary Circuit	Main Circuit	Auxiliary Circuit	[V]	[Resistance Method]	Main Circuit	Auxiliary Circuit	Main Circuit	Auxiliary Circuit	Note c)	Frequency Note c)	Judgment
Model N	Standard Coil Nominal /alue	Thermo	oen oelectric rent	-	-	-	100 or less	65 or less	65 or less	Not	te b)	7.3kV 1.2/50 μs x5 times	1890V 5 seconds	nent
SD-T12	24VDC	20	10	2.5	1.5	24	29	52	34	77	52	OK	OK	OK
SD-T12	100VDC	20	10	2.5	1.5	100	38	52	34	77	52	OK	OK	OK
SD-T20	24VDC	20	10	2.5	1.5	24	29	43	34	65	52	OK	OK	OK
SD-T20	100VDC	20	10	2.5	1.5	100	38	43	34	65	52	OK	OK	OK
SD-T21	24VDC	32	10	6	1.5	24	27	35	27	45	46	OK	OK	OK
SD-T21	100VDC	32	10	6	1.5	100	38	35	27	45	46	OK	OK	OK
SD-T32	24VDC	32	-	6	-	24	36	31	-	40	-	OK	OK	OK
SD-T32	100VDC	32	-	6	-	100	46	31	-	40	-	OK	OK	OK
SD-T35	24VDC	60	10	16	1.5	24	67	35	30	46	45	OK	OK	OK
SD-T50	24VDC	80	10	25	1.5	24	71	40	32	55	46	OK	OK	OK
SD-T65	24VDC	100	10	35	1.5	24	63	39	28	58	43	OK	OK	OK
SD-T80	24VDC	120	10	50	1.5	24	66	54	25	68	43	OK	OK	OK
SD-T100	24VDC	150	10	50	1.5	24	62	57	46	92	59	OK	OK	OK

Note a) The test of temperature rise was conducted by operating at an ambient temperature of 40°C, in open state with the iron plate mounted.

Note b) The temperature rise of the contacts was checked at a temperature that is not harmful to the surrounding components. (In short 100K)

Note c) The application points of the impulse withstand voltage performance and the power frequency withstand voltage performance were as follows. However in the power frequency withstand voltage test, (c) was not implemented. Measurement Points: (a) Between all terminals of the main circuit and grounded metal body when the contact element was closed.

- (b) Between 1-pole of the main circuit and all other poles connected altogether to the grounded metal body when the contact element was closed.
- (c) Between the supply side terminals and the load side terminals of the main circuit when the contact element was opened.
- (d) Between one circuit of the operating circuit (control circuit) and auxiliary circuit, and all other circuits/grounded metal body.

Note d) Number of Samples: 1 per machine

3.2.2 Operating Limits

The operating voltage (hot condition) and open-circuit voltage after the temperature test met the standard criteria by operating and opening without hindrance in the set voltage.

		l able 2		
Item	-	Test Conditions and Judgme	ent	
	Operating Volta	age (40°C Hot)	Open-circuit Voltage (-5°C Cold)	
Standard Coil Model Nominal Name Value	Operation at 85% or less of the coil rated voltage	Operation at 110% of the coil rated voltage	Open at 10 to 75% of the coil rated voltage	Judgment
SD-T12 24VDC	18.6	OK	4.9	OK
SD-T12 100VDC	72	OK	20	OK
SD-T20 24VDC	18.5	OK	5.2	OK
SD-T20 100VDC	71	OK	21	OK
SD-T21 24VDC	17.1	OK	4.5	OK
SD-T21 100VDC	64	OK	18	OK
SD-T32 24VDC	18.1	OK	4.3	OK
SD-T32 100VDC	70	OK	17	OK
SD-T35 24VDC	17.8	OK	5.7	OK
SD-T50 24VDC	18.2	OK	6.1	OK
SD-T65 24VDC	19.0	OK	5.8	OK
SD-T80 24VDC	20.1	OK	6.2	OK
SD-T100 24VDC	17.5	OK	5.5	OK

Note a) Coil rated voltage is 24V when coil nominal voltage is 24VDC, and is 100V when coil nominal voltage is 100VDC.

<Reference Test> Coil characteristics (20°C cold condition)

		Coil Properties		Óper	ating	Operating Time [ms]						
Model		Con Fropenties		Volt	age		$\text{Coil ON} \rightarrow$		(Coil OFF –	→	
Name	Coil Current [A]	Consumption Power [W]	Coil Time Constant [ms]	Operation	Open	Main Contact ON	Auxiliary Contact a ON	Auxiliary Contact b OFF	Main Contact OFF	Auxiliary Contact a OFF	Auxiliary Contact b ON	
SD-T12	0.033	3.3(2.2)	40(45)	60 to 75	10 to 30	55 to 75 (75 to 95)	55 to 75 (75 to 95)	50 to 70 (70 to 90)	5 to 15	5 to 15	10 to 20	
SD-T20	0.033	3.3(2.2)	40(45)	60 to 75	10 to 30	55 to 75 (75 to 95)	55 to 75 (75 to 95)	50 to 70 (70 to 90)	5 to 15	5 to 15	10 to 20	
SD-T21	0.033	3.3(2.2)	50(40)	60 to 75	10 to 30	60 to 80 (80 to 100)	60 to 80 (80 to 100)	55 to 75 (75 to 95)	5 to 15	5 to 15	10 to 20	
SD-T32	0.033	3.3(2.2)	50(40)	60 to 75	10 to 30	65 to 85 (85 to 105)	-	-	5 to 15	-	-	
SD-T35	0.09	9	40	50 to 65	15 to 35	45 to 55	45 to 55	38 to 48	6 to 10	6 to 10	9 to 13	
SD-T50	0.09	9	40	50 to 65	15 to 35	45 to 55	45 to 55	38 to 48	6 to 10	6 to 10	9 to 13	
SD-T65	0.18	18	65	52 to 63	20 to 35	45 to 55	45 to 55	40 to 50	9 to 16	9 to 16	12 to 19	
SD-T80	0.18	18	65	52 to 63	20 to 35	45 to 55	45 to 55	40 to 50	9 to 16	9 to 16	12 to 19	
SD-T100	0.24	24	80	50 to 65	15 to 30	70 to 80	70 to 80	63 to 73	14 to 21	14 to 21	18 to 25	

Note a) The standard values of the properties of the 100VDC coil. The values in brackets () for SD-T12 to SD-T32 are property values of the 24VDC coil.

3.3 Test Sequence II

3.3.1 Test of Making and Breaking Capacities

(1) Test of Making Capacity

These tests were conducted according to the test conditions indicated in Table 3 and Note a) to c). No abnormalities such as welding of contacts were found, and the results met the standard criteria.

Table 3

	Item	Rated (AC	Value - 3)		Te	est Condition	ns (making)				
	Char	Voltage Ue [V]	Current le [A]	Voltage U [V]	Current I [A]	Power Factor cosφ	Operating Cycle [Times] Note b)		OFF time [seconds]	Results	Judgment
Model Na	Stan- dard ame	-	-	1.05 x Ue	10 x le	0.45 ±0.05	50	0.05	10	Contact Welding	r.
SD-T12	24VDC	220	13	231	130	0.45	50	0.05	10	None	OK
30-112	24000	440	12	462	120	0.45	50	0.05	10	None	OK
SD-T20	24VDC	220	18	231	180	0.45	50	0.05	10	None	OK
3D-120	24000	440	18	462	180	0.45	50	0.05	10	None	OK
SD-T21	24VDC	220	25	231	250	0.45	50	0.05	10	None	OK
00-121	24000	440	23	462	230	0.45	50	0.05	10	None	OK
SD-T32	24VDC	220	32	231	320	0.45	50	0.05	10	None	OK
00-102	24000	440	32	462	320	0.45	50	0.05	10	None	OK
SD-T35	24VDC	220	40	231	400	0.45	50	0.05	10	None	OK
30-133	24000	440	40	462	400	0.45	50	0.05	10	None	OK
SD-T50	24VDC	220	55	231	550	0.45	50	0.05	10	None	OK
00-100	24000	440	48	462	480	0.45	50	0.05	10	None	OK
SD-T65	24VDC	220	65	231	650	0.45	50	0.05	10	None	OK
00-100	24000	440	65	462	650	0.45	50	0.05	10	None	OK
SD-T80	24VDC	220	85	231	850	0.45	50	0.05	10	None	OK
30-100	24000	440	85	462	850	0.45	50	0.05	10	None	OK
SD-T100	241/00	220	105	231	1050	0.35	50	0.05	10	None	OK
30-1100	24000	440	105	462	1050	0.35	50	0.05	10	None	OK

Note a) Main circuit frequency: 60Hz

Note b) Among 50 operating cycles, 110% of the rated value (26.4V) was applied to the coil for 25 cycles, and 85% of the rated value (20.4V) was applied to the coil for the other 25 cycles.

Note c) Number of Samples: 1 per machine

(2) Test of Making and Breaking Capacities

These tests were conducted according to the test conditions indicated in Table 4 and Note a) to c) after the making capacity test (1). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria.

					l a	ible 4					
	Item	Rated (AC	Value - 3)		Test Conc	litions (ma	king and bre	eaking ca	apacity)		
		Voltage Ue [V]	Current le [A]	Voltage U [V]	Current I [A]	Power Factor cosφ	Operating Cycle [Times]	ON time [seconds]	OFF time [seconds]	Results	onf
Model Na	Standard	-	-	1.05 x Ue	8 x le	0.45 ±0.05	50	0.05	Ic≦100: 10 100 <ic≦200: 20<br="">200<ic≦300: 30<br="">300<ic≦400: 40<br="">400<ic≦600: 60<br="">600<ic≦800: 80<br="">800<ic≦1000: 100<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td></td></ic≦1000:></ic≦800:></ic≦600:></ic≦400:></ic≦300:></ic≦200:>	Contact Welding and Phase-to-phase Short-circuits	
SD-T12	24VDC	220	13	231	104	0.45	50	0.05	20	None	OK
00-112	24000	440	12	462	96	0.45	50	0.05	10	None	OK
SD-T20	24VDC	220	18	231	144	0.45	50	0.05	20	None	OK
00 120	24700	440	18	462	144	0.45	50	0.05	20	None	OK
SD-T21	24VDC	220	25	231	200	0.45	50	0.05	20	None	OK
00-121	24000	440	23	462	184	0.45	50	0.05	20	None	OK
SD-T32	24VDC	220	32	231	256	0.45	50	0.05	30	None	OK
00 102	24700	440	32	462	256	0.45	50	0.05	30	None	OK
SD-T35	24VDC	220	40	231	320	0.45	50	0.05	40	None	OK
00-100	24000	440	40	462	320	0.45	50	0.05	40	None	OK
SD-T50	24VDC	220	55	231	440	0.45	50	0.05	60	None	OK
00 100	24000	440	48	462	384	0.45	50	0.05	40	None	OK
SD-T65	24VDC	220	65	231	520	0.45	50	0.05	60	None	OK
00-100	2-1000	440	65	462	520	0.45	50	0.05	60	None	OK
SD-T80	24\/DC	220	85	231	680	0.45	50	0.05	80	None	OK
00 100	24000	440	85	462	680	0.45	50	0.05	80	None	OK
SD-T100		220	105	231	840	0.35	50	0.05	100	None	OK
55 1100		440	105	462	840	0.35	50	0.05	100	None	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying a voltage of 24V to the operating coil.

Note c) Number of Samples: 1 per machine

(3) The Switching Capacity and Reversibility

These tests were conducted according to the test conditions indicated in Table 5, 6 and Note a) to c). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria.

Item	Rated (AC	Value - 4)			Test Cond	tions (making)				
	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Operation Cycle [Times]	ON time [seconds]	OFF time [seconds]	Results	Judgment
Stan- dard Model Name	-	-	1.05 x Ue	12 x le	0.45±0.05	50	0.05	10	Contact Welding and Phase-to-phase Short-circuits	nent
SD-2 x T12	220	11	231	132	0.45	50	0.05	10	None	OK
3D-2 X 112	440	9	462	108	0.45	50	0.05	10	None	OK
SD-2 x T20	220	18	231	216	0.45	50	0.05	10	None	OK
5D-2 x 120	440	13	462	156	0.45	50	0.05	10	None	OK
SD-2 x T21	220	18	231	216	0.45	50	0.05	10	None	OK
5D-2 X 121	440	13	462	156	0.45	50	0.05	10	None	OK
SD-2 x T32	220	26	231	312	0.45	50	0.05	10	None	OK
0D-2 x 102	440	24	462	288	0.45	50	0.05	10	None	OK
SD-2 x T35	220	26	231	312	0.45	50	0.05	10	None	OK
0D-2 x 100	440	24	462	288	0.45	50	0.05	10	None	OK
SD-2 x T50	220	35	231	420	0.45	50	0.05	10	None	OK
3D-2 X 130	440	32	462	384	0.45	50	0.05	10	None	OK
SD-2 x T65	220	50	231	600	0.45	50	0.05	10	None	OK
5D-2 X 105	440	47	462	564	0.45	50	0.05	10	None	OK
SD-2 x T80	220	65	231	780	0.45	50	0.05	10	None	OK
5D-2 X 100	440	62	462	744	0.45	50	0.05	10	None	OK
SD-2 x T100	220	80	231	960	0.45	50	0.05	10	None	OK
3D-2 X 1100	440	75	462	900	0.45	50	0.05	10	None	OK

Table 5


Table 6

Item	Rated (AC			Test (Conditions (maki	ing and	breaking	capacity)			
Stan	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Ċ	eration ycle mes] Simul- taneous Excitation Test	ON time [seconds]	OFF time [seconds]	Results	Judgment
dard Model Name	-	-	1.05 x Ue	10 x le	0.45±0.05	50	10	0.05	Ic≦100: 10 100 <ic≦200: 20<br="">200<ic≦300: 30<br="">300<ic≦400: 40<br="">400<ic≦600: 60<br="">600<ic≦800: 80<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td></td></ic≦800:></ic≦600:></ic≦400:></ic≦300:></ic≦200:>	Contact Welding and Phase-to-phase Short-circuits	
SD-2 x T12	220	11	231	110	0.45	50	10	0.05	20	None	OK
00-2 x 112	440	9	462	90	0.45	50	10	0.05	10	None	OK
SD-2 x T20	220	18	231	180	0.45	50	10	0.05	20	None	OK
00 2 x 120	440	13	462	130	0.45	50	10	0.05	20	None	OK
SD-2 x T21	220	18	231	180	0.45	50	10	0.05	20	None	OK
00 2 x 121	440	13	462	130	0.45	50	10	0.05	20	None	OK
SD-2 x T32	220	26	231	260	0.45	50	10	0.05	30	None	OK
00 2 x 102	440	24	462	240	0.45	50	10	0.05	30	None	OK
SD-2 x T35	220	26	231	260	0.45	50	10	0.05	30	None	OK
05 2	440	24	462	240	0.45	50	10	0.05	30	None	OK
SD-2 x T50	220	35	231	350	0.45	50	10	0.05	40	None	OK
03 <u>2 x 100</u>	440	32	462	320	0.45	50	10	0.05	40	None	OK
SD-2 x T65	220	50	231	500	0.45	50	10	0.05	60	None	OK
02 2 % 100	440	47	462	470	0.45	50	10	0.05	60	None	OK
SD-2 x T80	220	65	231	650	0.45	50	10	0.05	80	None	OK
00 2 1 100	440	62	462	620	0.45	50	10	0.05	80	None	OK
SD-2 x T100	220	80	231	800	0.45	50	10	0.05	80	None	OK
0D-2 X 1100	440	75	462	750	0.45	50	10	0.05	80	None	OK

Note a) Main circuit frequency: 60Hz

Note b) In the operating cycle, making A open circuit A - making B - open circuit B - OFF time, makes 1 cycle. The switching from open circuit A to making B was performed in the shortest time on the control system.

Note c) Number of Samples: 1 per machine



3.3.2 The Operating Performance

(1) Non-reversing

These tests were conducted according to the test conditions indicated in Table 7 and Note a) to c). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria. After the test, the withstand voltage performance was checked by applying a voltage of 1000V and a frequency of 60Hz for 5 seconds, and the results were acceptable. Table 7

\bigvee	Item		d Value C- 3)		Test Co	onditions (making and	breaking	capacity)	Resu	ilts	
		Voltage Ue [V]	Current le [A]	Voltage U [V]	Current Ic [A]	Power Factor cosφ	Operating Cycle [Times]	ON time [seconds]	OFF time [seconds]	Making and Breaking capacity	Withstand Voltage	Judgment
Model Na	Stan- dard ume	-	-	1.05 x Ue	2 x le	0.45 ±0.05	6000	0.05	lc≦100: 10 100 <lc≦200: 20<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td>2 x Ue provided 1000V or higher 5 seconds</td><td>ment</td></lc≦200:>	Contact Welding and Phase-to-phase Short-circuits	2 x Ue provided 1000V or higher 5 seconds	ment
SD-T12	24VDC	220	13	231	26	0.45	6000	0.05	10	None	OK	OK
30-112	24000	440	12	462	24	0.45	6000	0.05	10	None	OK	OK
SD-T20	24VDC	220	18	231	36	0.45	6000	0.05	10	None	OK	OK
30-120	24000	440	18	462	36	0.45	6000	0.05	10	None	OK	OK
SD-T21	24VDC	220	25	231	50	0.45	6000	0.05	10	None	OK	OK
30-121	24000	440	23	462	46	0.45	6000	0.05	10	None	OK	OK
SD-T32	24VDC	220	32	231	64	0.45	6000	0.05	10	None	OK	OK
30-132	24000	440	32	462	64	0.45	6000	0.05	10	None	OK	OK
SD-T35	24VDC	220	40	231	80	0.45	6000	0.05	10	None	OK	OK
30-135	24000	440	40	462	80	0.45	6000	0.05	10	None	OK	OK
SD-T50	24VDC	220	55	231	110	0.45	6000	0.05	20	None	OK	OK
30-150	24000	440	48	462	96	0.45	6000	0.05	10	None	OK	OK
SD-T65	24VDC	220	65	231	130	0.45	6000	0.05	20	None	OK	OK
00-100	24000	440	65	462	130	0.45	6000	0.05	20	None	OK	OK
SD-T80	24VDC	220	85	231	170	0.45	6000	0.05	20	None	OK	OK
30-100	24000	440	85	462	170	0.45	6000	0.05	20	None	OK	OK
SD-T100	241/00	220	105	231	210	0.35	6000	0.05	20	None	OK	OK
30-1100	24000	440	105	462	210	0.35	6000	0.05	20	None	OK	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying 24VDC to the operating coil.

Note c) Number of Samples: 1 per machine

(2) Reversing

These tests were conducted according to the test conditions indicated in Table 8 and Note a) to d). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria. After the test, the withstand voltage performance was checked by applying a voltage of 1000V and a frequency of 60Hz for 5 seconds, and the results were acceptable. Т

ab	le	8	

Item	Rated (AC			Test	Conditions (ty)	Resi	ults			
	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Operation Cycle [Times] Note c)	ON time [seconds]	OFF time [seconds]	Making and Breaking capacity	Withstand Voltage	Spnr
Stan- dard Model Name	-	-	1.05 x Ue	6 x le	0.45±0.05	6000	0.05	lc≦100: 10 100 <lc≦200: 20<br="">200<lc≦300: 30<br="">300<lc≦400: 40<br="">400<lc≦600: 60<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td>2 x Ue provided 1000V or higher 5 seconds</td><td>Judgment</td></lc≦600:></lc≦400:></lc≦300:></lc≦200:>	Contact Welding and Phase-to-phase Short-circuits	2 x Ue provided 1000V or higher 5 seconds	Judgment
SD-2 x T12	220	11	231	66	0.45	6000	0.05	10	None	OK	OK
3D-2 X 1 12	440	9	462	54	0.45	6000	0.05	10	None	OK	OK
SD-2 x T20	220	18	231	108	0.45	6000	0.05	20	None	OK	OK
3D-2 X 120	440	13	462	78	0.45	6000	0.05	10	None	OK	OK
SD-2 x T21	220	18	231	108	0.45	6000	0.05	20	None	OK	OK
3D-2 X 121	440	13	462	78	0.45	6000	0.05	10	None	OK	OK
SD-2 x T32	220	26	231	156	0.45	6000	0.05	20	None	OK	OK
5D-2 X 152	440	24	462	144	0.45	6000	0.05	20	None	OK	OK
SD-2 x T35	220	26	231	156	0.45	6000	0.05	20	None	OK	OK
3D-2 X 133	440	24	462	144	0.45	6000	0.05	20	None	OK	OK
SD-2 x T50	220	35	231	210	0.45	6000	0.05	30	None	OK	OK
0D-2 x 100	440	32	462	192	0.45	6000	0.05	20	None	OK	OK
SD-2 x T65	220	50	231	300	0.45	6000	0.05	30	None	OK	OK
00-2 x 100	440	47	462	282	0.45	6000	0.05	30	None	OK	OK
SD-2 x T80	220	65	231	390	0.45	6000	0.05	40	None	OK	OK
5D-2 x 100	440	62	462	372	0.45	6000	0.05	40	None	OK	OK
SD-2 x T100	220	80	231	480	0.45	6000	0.05	60	None	OK	OK
0D-2 X 1100	440	75	462	450	0.45	6000	0.05	60	None	OK	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying 24VDC to the operating coil.

Note c) The operation was performed based on the cycle mentioned in Note b) of 3.3.1 (3).

Note d) Number of Samples: 1 per machine

3.4 Test Sequence III

3.4.1 Performance under Short-circuit Conditions

These tests were conducted according to the test conditions indicated in Table 9 and Note a) to d). There was no damage to the conductors and terminals. The leakage detection fuse was not melted, and the results were acceptable.

					Table 9					
Item	Rated	Rated Valu	e (AC- 3)	Τe	est Conditio	ns				
Stan-	Current of SCPD [A] Note a)	Voltage Ue [V]	Current le [A]	Voltage [V]	Current I [kA]	Power Factor cosφ	O or CO Operation	Conductor/ Terminal Damage	Melting of the Leakage Detection Fuse	Judgment
dard Model Name	-	-	-	Ue	Note b)	Note c)	Note d)	None	None	nent
SD-T12	40	220/440	13/12	440	1	0.95	0	None	None	ОК
3D-112	40	220/440	13/12	440	1	0.95	CO	None	None	UK
SD-T20	40	40 220/440	/440 18/18	8 440	3	0.9	0	None	None	ОК
3D-120	40					0.9	CO	None	None	UK
SD-T21	80	220/440	25/23	440	3	0.9	0	None	None	ОК
30-121	80	220/440	23/23	440	5	0.9	CO	None	None	UK
SD-T32	80	220/440	32/32	440	3	0.9	0	None	None	ОК
30-132	80	220/440	32/32	440	5	0.9	CO	None	None	UK
SD-T35	100	220/440	40/40	440	3	0.9	0	None	None	OK
30-135	100	220/440	40/40	440	3	0.9	CO	None	None	UK
SD-T50	100	220/440	55/48	440	3	0.9	0	None	None	ОК
30-150	100	220/440	55/46	440	3	0.9	CO	None	None	UK
SD-T65	100	220/440	65/65	440	5	0.7	0	None	None	ОК
3D-105	100	220/440	05/05	440	5	0.7	CO	None	None	UK
SD-T80	125	220/440	85/85	440	5	0.7	0	None	None	OK
30-100	125	220/440	03/03	440	5	0.7	CO	None	None	OK
SD-T100	160	220/440	105/105	440	5	0.7	0	None	None	OK
30-1100	100	220/440	105/105	440	5	0.7	CO	None	None	UK

Note a) SCPD: Short Circuit Protection Device

Note b) The test currents of specified standards for rated operational current were as follows. (le indicates the maximum current to be applied to the motor.)

In the case of 1<le≦16: 1 kA In the case of 16<le≦63: 3 kA In the case of 63<le≦125: 5 kA Note c) The power factors of specified standards for test current are as follows.

In the case of l≦1.5 kA: 0.95±0.05 In the case of 1.5 kA<l≦3 kA: 0.9±0.05 In the case of 4.5 kA<l≦6 kA: 0.7±0.05
 Note d) O operation: Breaking of the circuit by the SCPD resulting from closing the circuit on the equipment under test which is in the closed position.

CO operation: Breaking of the circuit by the SCPD resulting from closing the circuit by the equipment under test.

3.5 Test Sequence IV

3.5.1 Ability of Contactors to Withstand Overload Currents

The current indicated in Table 10 was applied for 10 seconds in making conditions of the contactor. All the parts met the standard criteria without abnormality.

			Table 10			
Item		Test	Conditions			
Standard	200 to 220V Rated Current [A]	Current [A]	Current Passage Time [seconds]	Results	Judgment	
Model Name	le (AC-3)	le x 8	10	Abnormality in the part	-	
SD-T12	13	104	10	None	OK	
SD-T20	18	144	10	None	OK	
SD-T21	25	200	10	None	OK	
SD-T32	32	256	10	None	OK	
SD-T35	40	320	10	None	OK	
SD-T50	55	440	10	None	OK	
SD-T65	65	520	10	None	OK	
SD-T80	85	680	10	None	OK	
SD-T100	105	840	10	None	OK	

Note a) Number of Samples: 1 per machine

3.6 Test Sequence V

3.6.1 Mechanical Properties of Terminals

- (1) Tests of Mechanical Strength of Terminals
- The crimp terminals described in Table 11 were tightened using the following tightening torques and tested by connection and disconnection 5 times. All the parts met the standard criteria without looseness or damage.

Item	Target Terminal Position	Crimp Terminal Size	Manufacturer Standard Tightening Torque [N·m]	Tested Tightening Torque [N·m]	Results	Ju	
Stan- dard Model Name	-	Conductor of the Maximum Cross-Sectional Area	-	110% of the Manufacturer Standard Tightening Torque	Looseness or Damage to the Part	Judgment	
SD-T12	2/T1, 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK	
SD-T20	2/T1, 6/T3	2-3.5	0.9 to 1.5	1.65	None	OK	
SD-T21	2/T1, 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK	
SD-T32	2/T1, 6/T3	5.5-4	1.2 to 1.9	2.09	None	OK	
SD-T35	2/T1, 6/T3	22-S5	2.0 to 3.3	3.63	None	OK	
SD-T50	2/T1, 6/T3	22-S5	2.0 to 3.3	3.63	None	OK	
SD-T65	2/T1, 6/T3	60-S6	3.5 to 5.7	6.27	None	OK	
SD-T80	2/T1, 6/T3	60-S6	3.5 to 5.7	6.27	None	OK	
SD-T100	2/T1, 6/T3	60-6	3.5 to 5.7	6.27	None	OK	

Note a) The test was conducted by applying 110% of the maximum value of the manufacturer standard tightening torque

Note b) Number of Samples: 1 per machine

(2) Flexion and Pull-out Tests

In the flexion tests, the wire was rotated 135 times continuously by placing weight on its pointed end under the conditions (the following tightening torques were checked by using the minimum value of the manufacturer standard tightening torque) indicated in Table 12. The results met the standard criteria without pullout or breaking of the conductor. Then, the pull-out strength indicated in Table 12 was applied for 1 minute. The results met the standard criteria without pullout or breaking of the conductor. Table 12

							Table 12					
Item	Target Terminal	Screw Size	Wire Spe	cifications Size	Number of Connections	Manufacturer Standard Tightening	Tested Tightening Torque	Diameter of the Bushing Hole	Height [mm]	Weight [kg]	Pulling Force	Judgment
	Position				nections	Torque [N∙m]	[N · m]	[mm]		. 0.	[N]	
Model Name	-	-	-	-	Maximum Number of Connections	-	Specified Tightening Torque	$\begin{array}{c} 0.75 mm^2: 6.5\\ 1.25 mm^2: 9.5\\ 4mm^2: 9.5\\ 6mm^2: 9.5\\ 14mm^2: 13.0\\ 16mm^2: 13.0\\ \phi 1.6: 9.5\\ \phi 2: 9.5\\ \phi 2: 9.5\\ \phi 3.6: 13.0\\ \end{array}$	$\begin{array}{l} 0.75mm^2:260\\ 1.25mm^2:280\\ 4mm^2:280\\ 6mm^2:280\\ 6mm^2:280\\ 14mm^2:300\\ 16mm^2:300\\ \phi 1.6:280\\ \phi 2.:280\\ \phi 2.6:280\\ \phi 3.6:300\\ \end{array}$	$\begin{array}{c} 0.75mm^2: 0.4\\ 1.25mm^2: 0.4\\ 2.5mm^2: 0.9\\ 6mm^2: 1.4\\ 14mm^2: 2.9\\ 16mm^2: 2.9\\ \phi 1.6: 0.7\\ \phi 2: 0.9\\ \phi 2.6: 1.4\\ \phi 3.6: 2.9 \end{array}$	0.75mm ² : 30 1.25mm ² : 40 2.5mm ² : 50 4mm ² : 60 6mm ² : 80 14mm ² : 100 φ1.6: 50 φ2: 60 φ2.6: 80 φ3.6: 100	Pullout or Breaking of Conductor
			Stranded	0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	OK
	2/T1	M3.5	Wire Single	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
SD-T12			Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
-			Stranded Wire	0.75mm ² 2.5mm ²	2	0.9 to 1.5 0.9 to 1.5	0.9	6.5 9.5	260 280	0.4	30 50	OK OK
	6/T3	M3.5	Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
			Stranded	0.75mm ²	2	0.9 to 1.5	0.9	6.5	260	0.4	30	ОК
	2/T1	1 M3.5	Wire	2.5mm ²	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
SD-T20	2/11		Single Wire	φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	ОК
00 120			Stranded	0.75mm ²	2	0.9 to 1.5 0.9 to 1.5	0.9	6.5 9.5	260 280	0.4 0.7	30 50	OK OK
	6/T3	M3.5	Wire Single Wire	2.5mm ² φ1.6	2	0.9 to 1.5	0.9	9.5	280	0.7	50	OK
		M4	Stranded	1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	ОК
	2/T1		Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
			Single Wire	φ1.6 φ2.6	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 9.5	280 280	0.7	50 80	OK OK
SD-T21		M4	Stranded	ψ2.0 1.25mm ²	2	1.2 to 1.9	1.2	<u>9.5</u> 6.5	260	0.4	40	OK
	6/T3		Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	0/13		Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
			Wire Stranded	φ2.6 1.25mm ²	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	9.5 6.5	280 260	1.4 0.4	80 40	OK OK
	0.774	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	2/T1		Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
SD-T32			Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
			Stranded Wire	1.25mm ² 6mm ²	2	1.2 to 1.9 1.2 to 1.9	1.2 1.2	6.5 9.5	260 280	0.4	40 80	OK OK
	6/T3	M4	Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
			Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
			Stranded Wire	1.25mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	2/T1	M5	Single	16mm ² φ1.6	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	13.0 9.5	300 280	2.9 0.7	100 50	OK OK
00 705			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
SD-T35			Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	6/T3	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
			Single Wire	φ1.6 φ3.6	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	9.5 13.0	280 300	0.7 2.9	50 100	OK OK
			Stranded	43.0 1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	2/T1	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	2,	1010	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
SD-T50	<u> </u>		Wire Stranded	φ3.6 1.25mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0 2.0	13.0 6.5	300 260	2.9 0.4	100 40	OK OK
			Wire	1.25mm ²	2	2.0 to 3.3 2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	6/T3	M5	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK

Note a) Since SD-T65 or higher models cannot be connected to the unprocessed exposed conductor, this evaluation is not applicable.

Mechanical Latch Type Magnetic Contactor <Type SL-T, SLD-T>

Type SL-T, SLD-T mechanical latch type magnetic contactors are type S-T magnetic contactors with mechanical latch feature. This instant excitation type magnetic contactor is composed of a closing coil and tripping coil. At the time of closing, the closing coil is energized and the ON state is mechanically held. At the time of opening, the tripping coil is energized to remove the joining element of the latch.

1. Usage

- Can be used as a memory circuit in which the contactor maintains the making state at the time of power failure, instantaneous power failure or voltage drop.
- The switchboard can be used as a circuit in facilities sensitive to noise (hospitals, buildings etc.).
- The circuit can be used for long time power supply such as road lighting.
- The switching frequency is done less often resulting in saving the continuous power consumption of coil.

Rated operating current of AC			t of AC- 3 [A]	Open	Auxiliary Contact			Life	
Model Name	220 to 240V	380 to 440V	500V	Thermoelectric Current I th [A]	Valid	For Self-Demagn etization	Switching Frequency	Mechanical	Electrical
SL-T21 SLD-T21	25	23	17	32	2a2b	1a1b	1200 time/hour	500000 times	500000 times
SL-T35 SLD-T35	40	40	32	60	2a2b	1a1b	1200 time/hour	500000 times	500000 times
SL-T50 SLD-T50	55	48	38	80	2a2b	1a1b	1200 time/hour	250000 times	250000 times
SL-T65 SLD-T65	65	65	60	100	2a2b	1a1b	1200 time/hour	250000 times	250000 times
SL-T100 SLD-T100	105	105	85	150	2a2b	1a1b	1200 time/hour	250000 times	250000 times

2. Rating

3. Type Test

Applicable Standard IEC60947-1 (2011)

Low voltage switchgear and control gear Part 1: General Rule IEC60947-4-1 (2012) Low voltage switchgear and control gear Part 4: Contactor and Motor Starter Section 1: Electro-mechanical Contactor and Motor Starter

3.1 Type Tests and Test Sequences

Test Sequences	Test Name	Test Conditions				
a) Sequence I	1) Temperature rise	According to the IEC60947-4-1	9.3.3.3 "Temperature Rise".			
	2) Operation and operating limits	According to the IEC60947-4-1	9.3.3.1 "Operation" and			
			9.3.3.2 "Operating limit".			
	3) Dielectric properties	According to the IEC60947-4-1 Properties".	9.3.3.4 "Dielectric			
b) Sequence II	 Rated making and breaking capacity 	According to the IEC60947-4-1 Breaking Capacity".	9.3.3.5 "Making and			
	2) Conventional operating performance	According to the IEC60947-4-1 Performance Capability".	9.3.3.6 "Operating			
c) Sequence III	1) Performance under short-circuit conditions	According to the IEC60947-4-1 Short-circuit Conditions".	9.3.4 "Performance under			
d) Sequence IV	 Ability of contactors to withstand overload currents 	According to the IEC60947-4-1 Withstand Overload Currents".	9.3.5 "Ability of Contactors to			
e) Sequence V	1) Mechanical properties of terminals	According to the IEC60947-1 of Terminals".	8.2.4 "Mechanical Properties			

Note a) As only the operating coils differ in type SL-T and type SLD-T (AC operation coil for type SL-T and DC operation coil for type SLD-T), the items that do not affect the operation were carried out with type SL-T.

Note b) For type SL-T, the coil with nominal voltage 200VAC (200-240V, 50Hz/60Hz) was used. For type SLD-T, the coil with nominal voltage 100VDC (Rated voltage 100-110V) was used.

3.2 Test Sequence I

3.2.1 Temperature Rise and Dielectric Properties

These tests were conducted according to the test conditions indicated in Table 1 and Note a) to f), the temperature rise of each part met the standard criteria of temperature rise limit. Also the operations, dielectric properties, and insulation resistances after the temperature tests met the standard criteria. Cabla 1

				l able	91					
Item	٦	Fest Condition	ons	Results Note a)						
	Curre	ent [A]	Connection	Maxim	um Tempera	ture Rise	Value [K]	Dielectric I	Properties	
	Curre	ant [A]	Wire Size	Ter	minal	Co	ntact	Impulse	Power	Juc
	Main	Auxiliary	[mm ²]	Main	Auxiliary	Main	Auxiliary	Note e)	Frequency	Judgment
Stan-	Circuit	Circuit	Note b)	Circuit	Circuit	Circuit	Circuit	11010 0)	Note e)	ler
Model Name	Open Thermoelectric Current		-	65 or less	65 or less	Note d)		7.3kV 1.2/50 µs x5 times	1890V 5 seconds	nt
SL-T21	32	10	6	27	30	36	36	OK	OK	OK
SL-T35	60	10	16	35	30	45	46	OK	OK	OK
SL-T50	80	10	25	41	29	58	45	OK	OK	OK
SL-T65	100	10	35	39	25	61	42	OK	OK	OK
SL-T85	120	10	50	45	25	71	42	OK	OK	OK
SL-T100	150	10	50	46	34	83	49	OK	OK	OK

Note a) The test of temperature rise was conducted by operating at an ambient temperature of 40°C, in open state with the iron plate mounted.

Note b)

The connection wire size of the auxiliary circuit: 1.5 mm² The operating coils were not measured because they are instant excitation type. Note c)

Note d) The temperature rise of the contacts was checked at a temperature that is not harmful to the surrounding components. (In short 100K)

Note e) The application points of the impulse withstand voltage performance and the power frequency withstand voltage performance were as follows. However in the power frequency withstand voltage test, (c) was not implemented. Measurement Points: (a) Between all terminals of the main circuit and grounded metal body when the contact

- element was closed. (b) Between 1- pole of the main circuit and all other poles connected altogether to the
- grounded metal body when the contact element was closed. Between the supply side terminals and the load side terminals of the main circuit (c) when the contact element was opened.
- Between one circuit of the operating circuit and auxiliary circuit, and all other (d) circuits/grounded metal body.

Note f) Number of Samples: 1 per machine

3.2.2 Operating Limits

The input voltage and trip voltage after the temperature test met the standard criteria by operating without hindrance in the set voltage.

			Table 2						
	Item Test Conditions and Judgment								
		Input Voltage	e (40°C Cold)	Trip Voltage (-5°C Cold)	Judgment				
	Standard	Operation at 85% or less of the	Operation at 110% of the Coil	Operation at 85% or less of the	Judgment				
Model Name		Coil Rated Voltage Note a)	Rated Voltage Note b)	Coil Rated Voltage Note a)					
SL-T21	50Hz	131	OK	90	OK				
SL-121	60Hz	157	OK	105	OK				
SL-T35	50Hz	113	OK	83	OK				
SL-135	60Hz	136	OK	99	OK				
SL-T50	50Hz	113	OK	83	OK				
SL-150	60Hz	136	OK	99	OK				
SL-T65	50Hz	120	OK	68	OK				
SL-105	60Hz	125	OK	82	OK				
SL-T85	50Hz	120	OK	68	OK				
SL-100	60Hz	125	OK	82	OK				
SL-T100	50Hz	118	OK	67	OK				
SL-1100	60Hz	125	OK	88	OK				
SLD-T21	-	68.5	OK	52	OK				
SLD-T35	-	56	OK	63	OK				
SLD-T50	-	56	OK	63	OK				
SLD-T65	-	66	OK	47	OK				
SLD-T80	-	66	OK	47	OK				
SLD-T100	-	64	OK	45	OK				

Note a) The operation at 85% or less of the coil rated voltage of standard value was possible at 170V 50Hz/60Hz for SL-T21. The operation was also possible at 85VDC for SLD-T21.

Note b) The operation at 110% of the coil rated voltage of standard value was possible at 264V 50Hz/60Hz for SL-T21. The operation was also possible at 121VDC for SLD-T21.

3.3 Test Sequence II

3.3.1 Test of Making and Breaking Capacities

(1) Test of Making Capacity

These tests were conducted according to the test conditions indicated in Table 3 and Note a) to c). No abnormalities such as welding of contacts were found, and the results met the standard criteria.

 	\mathbf{a}
 ab	_≺.
 av	J

					10010 0					
Item		Value 2-3)			Test Conditions (n	naking)				
Star	Voltage Current Ue le [V] [A]		Voltage U [V]	Current I [A]	Operating Power Factor Cycle cosφ [Times] Note b)		ON time OFF time [seconds] [seconds]		Results	Judgment
Model Name	-	-	1.05 x Ue	10 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	50	0.05	10	Contact Welding	
SL-T21	220	25	231	250	0.45	50	0.05	10	None	OK
SL-121	440	23	462	230	0.45	50	0.05	10	None	OK
SL-T35	220	40	231	400	0.45	50	0.05	10	None	OK
SL-135	440	40	462	400	0.45	50	0.05	10	None	OK
SL-T50	220	55	231	550	0.45	50	0.05	10	None	OK
SL-150	440	48	462	480	0.45	50	0.05	10	None	OK
SL-T65	220	65	231	650	0.45	50	0.05	10	None	OK
SL-105	440	65	462	650	0.45	50	0.05	10	None	OK
SL-T80	220	85	231	850	0.45	50	0.05	10	None	OK
SL-100	440	85	462	850	0.45	50	0.05	10	None	OK
CL T100	220	105	231	1050	0.35	50	0.05	10	None	OK
SL-T100	440	105	462	1050	0.35	50	0.05	10	None	OK

Note a) Main circuit frequency: 60Hz Note b) Among 50 operating cycles, 110% of the rated value (264V 60Hz) was applied to the coil for 25 cycles, and 85% of the rated value (170V 60Hz) was applied to the coil for the other 25 cycles.

Note c) Number of Samples: 1 per machine

(2) Test of Making and Breaking Capacities

These tests were conducted according to the test conditions indicated in Table 4 and Note a) to c). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria.

Table 4

					Table 4					
Item	Rated (AC	Value 2-3)		Те	st Conditions (making		0 1	,		
	Voltage Current Ue le [V] [A]		Voltage U [V]	Current I [A]	Power Factor cosφ	Operating Cycle [Times]	ON time [seconds]	OFF time [seconds]	Results	6pn r
Standard Standard	-	-	1.05 x Ue	8 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	50	0.05	lc≦100: 10 100 <lc≦200: 20<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td>Judgment</td></lc≦200:>	Contact Welding and Phase-to-phase Short-circuits	Judgment
01 704	220	25	231	200	0.45	50	0.05	20	None	OK
SL-T21	440	23	462	184	0.45	50	0.05	20	None	OK
	220	40	231	320	0.45	50	0.05	40	None	OK
SL-T35	440	40	462	320	0.45	50	0.05	40	None	OK
	220	55	231	440	0.45	50	0.05	60	None	OK
SL-T50	440	48	462	384	0.45	50	0.05	40	None	OK
	220	65	231	520	0.45	50	0.05	60	None	OK
SL-T65	440	65	462	520	0.45	50	0.05	60	None	OK
CL T00	220	85	231	680	0.45	50	0.05	80	None	OK
SL-T80	440	85	462	680	0.45	50	0.05	80	None	OK
CL T100	220	105	231	840	0.35	50	0.05	100	None	OK
SL-T100	440	105	462	840	0.35	50	0.05	100	None	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying a voltage of 240V and a frequency of 60Hz to the operating coil.

Note c) Number of Samples: 1 per machine

(3) The Switching Capacity and Reversibility

These tests were conducted according to the test conditions indicated in Table 5, 6 and Note a) to c). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria.


					l able 5					
Item		Value C-4)			Test Cond	itions (making)				
Stan-	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Operation Cycle [Times]	ON time [seconds]	OFF time [seconds]	Results	Judgment
dard Model Name	-	-	1.05 x Ue	12 x le	le≦100A 0.45±0.05 le>100A 0.35±0.05	50	0.05	10	Contact Welding and Phase-to-phase Short-circuits	ent
01.0	220	18	231	216	0.45	50	0.05	10	None	OK
SL-2 x T21	440	13	462	156	0.45	50	0.05	10	None	OK
	220	26	231	312	0.45	50	0.05	10	None	OK
SL-2 x T35	440	24	462	288	0.45	50	0.05	10	None	OK
	220	35	231	420	0.45	50	0.05	10	None	OK
SL-2 x T50	440	32	462	384	0.45	50	0.05	10	None	OK
	220	50	231	600	0.45	50	0.05	10	None	OK
SL-2 x T65	440	47	462	564	0.45	50	0.05	10	None	OK
	220	65	231	780	0.45	50	0.05	10	None	OK
SL-2 x T80	440	62	462	744	0.45	50	0.05	10	None	OK
SL 2 x T100	220	80	231	960	0.45	50	0.05	10	None	OK
SL-2 x T100	440	75	462	900	0.45	50	0.05	10	None	OK


\$					Table 6						
Item	Rated (AC	Value 2-4)			Test Conditions (ma	king an	d breaking c	apacity)			
Stan-	Voltage Ue [V]	Current le [A]	Voltage Ur [V]				Operation Cycle [Times] Simultaneous Excitation Test		OFF time [seconds]	Results	Judgment
dard Model Name	-	-	1.05 x Ue	10 x le	le≦100A 0.45±0.05 le>100A 0.35±0.05	50	10	0.05	lc≦100: 10 100 <lc≦200: 20<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td>nt</td></lc≦200:>	Contact Welding and Phase-to-phase Short-circuits	nt
SL-2 x T21	220	18	231	180	0.45	50	10	0.05	20	None	OK
3L-2 X 121	440	13	462	130	0.45	50	10	0.05	20	None	OK
SL-2 x T35	220	26	231	260	0.45	50	10	0.05	20	None	OK
SL-2 X 155	440	24	462	240	0.45	50	10	0.05	20	None	OK
SL-2 x T50	220	35	231	350	0.45	50	10	0.05	20	None	OK
SL-2 X 150	440	32	462	320	0.45	50	10	0.05	20	None	OK
SL-2 x T65	220	50	231	500	0.45	50	10	0.05	20	None	OK
SL-2 X 100	440	47	462	470	0.45	50	10	0.05	20	None	OK
	220	65	231	650	0.45	50	10	0.05	20	None	OK
SL-2 x T80	440	62	462	620	0.45	50	10	0.05	20	None	OK
SL-2 x T100	220	80	231	800	0.45	50	10	0.05	20	None	OK
3L-2 X 1 100	440	75	462	750	0.45	50	10	0.05	20	None	OK

Note a) Main circuit frequency: 60Hz

Note b) In the operating cycle, making A - open circuit A - making B - open circuit B - OFF time, makes 1 cycle.

The switching from open circuit A to making B was performed in the shortest time on the control system.





The snap switches were switched in the sequence of SW A \rightarrow SW B \rightarrow SW C \rightarrow SW B \rightarrow SW C \rightarrow

Note c) Number of Samples: 1 per machine

3.3.2 The Operating Performance

(1) Non-reversing

These tests were conducted according to the test conditions indicated in Table 7 and Note a) to c). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria. After the test, the withstand voltage performance was checked by applying a voltage of 1000V and a frequency of 60Hz for 5 seconds, and the results were acceptable. Table 7

Item	Rated (AC			Те	st Conditions (making	and breakir	ng capac	ity)	Resul	ts	
	Voltage Ue [V]	Current le [A]	Voltage U [V]	Current I [A]	Power Factor cosφ	Operating Cycle [Times]	ON time [seconds]	OFF time [seconds]	Making and Breaking capacity	Withstand Voltage	Judgment
Stan- dard Model Name	-	-	1.05 x Ue	2 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	6000	0.05	lc≦100: 10	Contact Welding and Phase-to-phase Short-circuits	2 x Ue provided 1000V or higher 5 seconds	nent
SL-T21	220	25	231	50	0.45	6000	0.05	10	None	OK	OK
3L-121	440	23	462	46	0.45	6000	0.05	10	None	OK	OK
SL-T35	220	40	231	80	0.45	6000	0.05	10	None	OK	OK
3L-135	440	40	462	80	0.45	6000	0.05	10	None	OK	OK
SL-T50	220	55	231	110	0.45	6000	0.05	20	None	OK	OK
3L-130	440	48	462	96	0.45	6000	0.05	10	None	OK	OK
SL-T65	220	65	231	130	0.45	6000	0.05	20	None	OK	OK
SL-105	440	65	462	130	0.45	6000	0.05	20	None	OK	OK
SI T90	220	85	231	170	0.45	6000	0.05	20	None	OK	OK
SL-T80	440	85	462	170	0.45	6000	0.05	20	None	OK	OK
SL T100	220	105	231	210	0.45	6000	0.05	30	None	OK	OK
SL-T100	440	105	462	210	0.45	6000	0.05	30	None	OK	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying a voltage of 240V and a frequency 60Hz to the operating coil.

Note c) Number of Samples: 1 per machine

(2) Reversing

These tests were conducted according to the test conditions indicated in Table 8 and Note a) to d). No abnormalities such as welding of contacts and phase-to-phase short circuits were found, and the results met the standard criteria. After the test, the withstand voltage performance was checked by applying a voltage of 1000V and a frequency of 60Hz for 5 seconds, and the results were acceptable. Table 8

					1 UL						
Item	Rated (AC			-	Test Conditions (making	ng and brea	king capa	acity)	Re	sults	
	Voltage Ue [V]	Current le [A]	Voltage Ur [V]	Current Ic [A]	Power Factor cosφ	Operating Cycle [Times] Note c)	ON time [seconds]	OFF time [seconds]	Making and Breaking capacity	Withstand Voltage	Judgment
Stan- dard Model Name	-	-	1.05 x Ue	6 x le	le≦100A: 0.45±0.05 le>100A: 0.35±0.05	6000	0.05	lc≦100: 10 100 <lc≦200: 20<="" td=""><td>Contact Welding and Phase-to-phase Short-circuits</td><td>2 x Ue provided 1000V or higher 5 seconds</td><td>ent</td></lc≦200:>	Contact Welding and Phase-to-phase Short-circuits	2 x Ue provided 1000V or higher 5 seconds	ent
	220	18	231	108	0.45	6000	0.05	20	None	OK	OK
SL-2 x T21	440	13	462	78	0.45	6000	0.05	10	None	OK	OK
SL-2 x T35	220	26	231	156	0.45	6000	0.05	20	None	OK	OK
3L-2 X 133	440	24	462	144	0.45	6000	0.05	20	None	OK	OK
SL-2 x T50	220	35	231	210	0.45	6000	0.05	30	None	OK	OK
3L-2 X 150	440	32	462	192	0.45	6000	0.05	20	None	OK	OK
SL-2 x T65	220	50	231	300	0.45	6000	0.05	30	None	OK	OK
3L-2 X 105	440	47	462	282	0.45	6000	0.05	30	None	OK	OK
SL-2 x T80	220	65	231	390	0.45	6000	0.05	40	None	OK	OK
3L-2 X 100	440	62	462	372	0.45	6000	0.05	40	None	OK	OK
SL-2 x T100	220	80	231	480	0.45	6000	0.05	60	None	OK	OK
3L-2 X 1 100	440	75	462	450	0.45	6000	0.05	60	None	OK	OK

Note a) Main circuit frequency: 60Hz

Note b) The operation was conducted by applying a voltage of 240V and a frequency 60Hz to the operating coil.

Note c) The operation was performed based on the cycle mentioned in Note b) of 3.3.1 (3).

Note d) Number of Samples: 1 per machine

3.4 Test Sequence III

3.4.1 Performance under Short-circuit Conditions

These tests were conducted according to the test conditions indicated in Table 9 and Note a) to d). There was no damage to the conductors and terminals. The leakage detection fuse was not melted, and the results met the standard criteria.

					Table 9					
Item	Rated	Rated Valu	ie (AC-3)	Te	est Conditio	ns		Results		
	Current of SCPD [A] Note a)	Voltage Ue [V]	Current le [A]	Voltage [V]	Current I [kA]	Power Factor cosφ	O or CO Operation	Conductor/ Terminal Damage	Melting of the Leakage Detection Fuse	Judgment
Stan- dard Name	-	-	-	Ue	-	Note b)	Note c)	None	None	nent
SL-T21	80	220/440	25/23	440	3	0.9	0	None	None	ок
3L-121	50	220/440	25/25	440	5	0.9	CO	None	None	ON
SL-T35	100	220/440	40/40	440	3	0.9	0	None	None	OK
3L-133	100	220/440	40/40	440	5	0.5	CO	None	None	OI
SL-T50	100	220/440	55/48	440	3	0.9	0	None	None	ок
02 100	100		00/40		Ũ	0.0	CO	None	None	•
SL-T65	100	220/440	65/65	440	5	0.7	0	None	None	ОК
02.100	100		00,00		Ű	0.1	CO	None	None	•
SL-T80	125	220/440	85/85	440	5	0.7	0	None	None	ОК
02.00	0		00.00			0.1	CO	None	None	
SL-T100	160	220/440	105/105	440	5	0.7	0	None	None	OK
				-	-		CO	None	None	

Note a) SCPD: Short Circuit Protection Device

Note b) The test currents of specified standards for rated operating current were as follows. (le indicates the maximum current to be applied to the motor.) In the case of 16<le≦63: 3 kA

Note c) The power factors of specified standards for test current were as follows. In the case of 1.5 kA<l≦3 kA: 0.9±0.05

Note d) O operation: Breaking of the circuit by the SCPD resulting from closing the circuit on the equipment under test which is in the closed position. CO operation: Breaking of the circuit by the SCPD resulting from closing the circuit by the equipment under test.

3.5 Test Sequence IV

3.5.1 Ability of Contactors to Withstand Overload Currents

The current indicated in Table 10 was applied for 10 seconds in making conditions of the contactor. All the parts met the standard criteria without abnormality.

		Table	10		
Item	220 to 240V	Test Co	nditions		
	Rated Current [A]	Current [A]	Current Passage Time [seconds]	Results	Judgment
Standard Model Name	Rated Operational Current Ie (AC-3)	le≦630A: 8 x le le>630A: 6 x le	10	Abnormality in the part	Judgment
SL-T21	25	200	10	None	OK
SL-T35	40	320	10	None	OK
SL-T50	55	440	10	None	OK
SL-T65	65	520	10	None	OK
SL-T80	85	680	10	None	OK
SL-T100	105	840	10	None	OK

Note a) Number of Samples: 1 per machine

3.6 Test Sequence V

3.6.1 Mechanical Properties of Terminals

- (1) Tests of Mechanical Strength of Terminals
- The crimp terminals described in Table 11 were tightened using the following tightening torques and tested by connection and disconnection 5 times. All the parts met the standard criteria without looseness or damage.

Item	Target Terminal Position	Crimp Terminal Size	Manufacturer Standard Tightening Torque [N·m]	Tested Tightening Torque [N ⋅ m]	Results	þnr
Standard Model Name	-	Conductor of the Maximum Cross-Sectional Area	-	110% of the Manufacturer Standard Tightening Torque	Looseness or Damage to the Part	Judgment
SL-T21	2/T1, 6/T3	5.5-4	1.2 to 1.9	2.09 (110% of the maximum value)	None	OK
SL-T35	2/T1, 6/T3	22-S5	2.0 to 3.3	3.63	None	OK
SL-T50	2/T1, 6/T3	22-S5	2.0 to 3.3	3.63	None	OK
SL-T65	2/T1, 6/T3	60-S6	3.5 to 5.7	6.27	None	OK
SL-T80	2/T1, 6/T3	60-S6	3.5 to 5.7	6.27	None	OK
SL-T100	2/T1, 6/T3	60-6	3.5 to 5.7	6.27	None	OK

(2) Flexion and Pull-out Tests

In the flexion tests, the wire was rotated 135 times continuously by placing weight on its pointed end under the conditions (the following tightening torques were checked by using the minimum value of the manufacturer standard tightening torque) indicated in Table 12. The results met the standard criteria without pullout or breaking of the conductor. Then, the pull-out strength indicated in Table 12 was applied for 1 minute. The results met the standard criteria without pullout or breaking of the conductor.

							Table 12					
Item	Target Terminal Position	Screw Size	Wire Spe Type	cifications Size	Number of Connections	Manufacturer Standard Tightening Torque [N·m]	Tested Tightening Torque [N · m]	Diameter of the Bushing Hole [mm]	Height [mm]	Weight [kg]	Pulling Force [N]	Judgment
Standard Model Name	-	-	-	-	Maximum Number of Connections	-	Specified Tightening Torque	$\begin{array}{l} 1.25mm^2: 6.5\\ 6mm^2: 9.5\\ \phi 1.6: 9.5\\ \phi 2.6: 9.5\end{array}$	1.25mm ² : 260 6mm ² : 280 φ1.6: 280 φ2.6: 280	1.25mm ² : 0.4 6mm ² : 1.4 φ1.6: 0.7 φ2.6: 1.4	1.25mm ² : 40 6mm ² : 80 φ1.6: 50 φ2.6: 80	Pullout or Breaking of Conductor
			Stranded	1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK
	2/T1	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	2/11	1014	Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
SL-T21			Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
3L-121		Stranded	1.25mm ²	2	1.2 to 1.9	1.2	6.5	260	0.4	40	OK	
	6/T3	M4	Wire	6mm ²	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
	0/13	1014	Single	φ1.6	2	1.2 to 1.9	1.2	9.5	280	0.7	50	OK
			Wire	φ2.6	2	1.2 to 1.9	1.2	9.5	280	1.4	80	OK
			Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	2/T1	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	2/11	1VIO	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
SL-T35			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
SE-135			Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	6/T3	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	0/10	WIO	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
			Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK
	2/T1	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	2/11 IVI5	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK	
SL-T50			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
01-100		Stranded	1.25mm ²	2	2.0 to 3.3	2.0	6.5	260	0.4	40	OK	
	6/T3	M5	Wire	16mm ²	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK
	5/15	IVIO	Single	φ1.6	2	2.0 to 3.3	2.0	9.5	280	0.7	50	OK
			Wire	φ3.6	2	2.0 to 3.3	2.0	13.0	300	2.9	100	OK

Environmental Characteristics and Special Performance

1. Surrounding Environment of the Magnetic Starter

There are various environmental conditions that can affect the use of a magnetic starter. It is necessary to clarify these conditions because they greatly affect the performance of the magnetic starter. Generally, performance validation tests performed by the manufacturer are under the standard usage condition. Therefore, performance is guaranteed in the standard usage conditions. The standard usage conditions refer to the following conditions. The magnetic starter may fail if it is used under environmental or atmospheric conditions other than those described below.

- a. Ambient Temperature : Standard 20°C, range of usage ambient temperature: -10°C to 40°C (Maximum average temperature during a day: 35°C, Maximum average temperature for a year: 25°C)
- b. Maximum temperature inside the control panel

	 : 55°C. For boxed MS type, the ambient temperature should be 40°C (the annual average temperature in the panel should be 40°C or less) It is necessary to pay attention to the ambient temperature as it influences the operational properties of the magnetic contactor and the thermal relay. The insulation will proceed to degrade even in normal usage. Especially if the ambient temperature rises, the life span of the insulation shortens. Generally, whenever the ambient temperature rises by 6 to 10°C, the life span of the insulation halves. (Arrhenius law)
c. Relative Humidity	: 45 to 85% RH, provided that there should be no condensation or freezing.
d. Altitude	: 2000m or less
e. Oscillation	: 10 to 55Hz 19.6m/s ² or less
f. Impact	: 49m/s ² or less
g. Atmosphere	: Must not contain too much water vapor, oil vapor, dust, smoke, corrosive gases or salt.
	Contact can be interrupted if the magnetic starter is used consecutively for a long time in an airtight environment.
	Never use this magnetic starter in places where there is a possibility of generation of combustible gases.

h. Storage Temperature : -30°C to 65°C, provided that there should be no condensation or freezing.

The summarized temperature range applicable to the MS-T series is shown in Table 1.

Та	ble	1	

	Temperature	Usage Temperature	Storage Temperature
Specification		[°C]	[°C]
Standard	Boxed MS-T type	-10 to 40	-30 to 65
Models	Open MSO-T type	-10 to 55	-30 to 65

Note a) Storage temperature is the ambient temperature during transportation and storage, and it must be within the specified range of usage temperature at the time of commencement of usage.

Note b) Set the conditions such that there is no condensation or freezing due to sudden temperature change.

2. Application to the Special Environment

2.1 High Temperature

If the magnetic starter is used at high ambient temperature, the temperature is mainly determined by the life span of the operating coil (continuous current life span) and the gradual change of the molding. According to the standard, the temperature rise of the operating coil is specified as follows: 125°C or less for A type insulation and 140°C or less for E type insulation including the ambient temperature. However, to facilitate long term usage for MSO-T and S-T series at 55°C temperature in the panel, the temperature rise using E type insulation or higher is limited to values lower than A type insulation. In order to estimate the continuous current life span of the operating coil, an acceleration test of

continuous current on the electromagnet was performed as indicated below. As a result, there was no abnormality, such as burnout. Thermostatic Premises Temperature : 80°C

Thermostatic Premises Temperature	:	80
Voltage Applied to Operating Coil	:	11(
Continuous Current Passage Time	:	50
Number of Test Items	:	5υ
Test Results	:	No

0% of rated voltage (60Hz) 000 hours units of operating electromagnets for each frame o occurrence of burnout, no abnormality in surge comparison test

The continuous current life span of the operating coil is determined by the degradation of the winding material, and it is as shown in Figure 1 according to Arrhenius law. From this result, we can assume that the insulation lifespan of the operating coil is the average ambient temperature + temperature rise of the coil, but it generally has a life span of 10 years.




Figure 1: Magnet Wire Heat-resistance Life Span Curve (according to the Technical Report of The Institute of Electrical Engineers of Japan)

To investigate the gradual change of the molding, an acceleration test is implemented at 120°C after having a surplus of 105°C over the ambient temperature 40°C and a rated value 65°C of the temperature rise at the terminal. The test time is set to 300 hours because the molding (mainly phenol raisin) requires to be saturated at 120°C for 300 hours for gradual change to occur.

The results of the heating test of 300 hours at 120°C are shown in Table 1. This result indicates that there was no problem with the gradual changes due to temperature with respect to the MS-T series.

Table 1: Heating test results for MSO-1 type						
Time		0			300	
Proper- ties Model Name	Operating Voltage [V 60Hz]	Open Voltage [V 60Hz]	Open Time [ms]	Operating Voltage [V 60Hz]	Open Voltage [V 60Hz]	Open Time [ms]
MSO-T10	139	88	14	142	87	13
MSO-T12	139	95	12	140	90	12
MSO-T20	139	106	12	140	104	12
MSO-T21	145	90	9	145	88	9
MSO-T25	145	90	9	146	88	9
MSO-T35	146	115	9	151	120	9
MSO-T50	146	115	9	151	120	9
MSO-T65	120	65	48	123	63	45
MSO-T80	120	65	48	123	63	45
MSO-T100	121	75	74	124	72	70

Table 1: Heating test results for MSO-T type

Note a) A nominal value of 200VAC was used for the rated value of the operating coil.

2.2 Low Temperature

The magnetic starter and the magnetic contactor that are installed in a panel may be transported to a cold area or be used in intense cold conditions such as in a cold area or freezing machine. In this case, the cold resistance will be a problem, but the standard S-T type magnetic contactors can be used in low temperatures.

• Storage Temperature -60°C or more

There was no abnormality found in any part when a shelf test was performed at -70° C for 1 month. Therefore, it can be considered that the products can withstand storage at -60° C or more. Also, the panels transported to cold areas are usually waterproof, and packed against moisture, and when panels packed in warm areas reach cold areas, it is necessary to take into account the potential damage to the utensil due to condensation or freezing. Therefore it is vital to pay attention to the dehumidification inside the packaging, and it is advisable to use silica gel as a drying agent in the amount of 3kg per $1m^2$.

Usage Temperature -50°C or more

Mechanical durability test was performed according to the following conditions.

Temperature	: -50°C
Voltage Applied to Coil and Frequency	: 240V and 60Hz for 200VAC coil
Switching Frequency	: 120 times per hour
Usage Factor	: 0.66%
Usage Frequency	: 3 months (250000 times)
Since there was no damage to the parts durin	a or after the test the products can be us

Since there was no damage to the parts during or after the test, the products can be used at temperatures higher than -50°C.

During usage at cold temperatures or storage, if the temperature suddenly returns to 0°C or higher, condensation occurs, and if the temperature returns to the low temperature again, condensation or freezing occurs. Therefore, it should be noted that an operational failure or contact failure may occur if condensation or freezing forms on the sliding parts of moving components or the contact surface.

3. Instantaneous Voltage Drop Tolerance

The guaranteed range of the operating voltage of the magnetic starter and the magnetic contactor is 85 to 110% of the rated voltage of the operating coil. However, according to the voltage drop during the first current supplied to the motor, the attraction force of the electromagnet drops from the time when the contact surface is touched as shown in Figure 1, and if the attraction force falls below the opposing force, the contact floats, repeating close circuit \rightarrow voltage recovery \rightarrow reclosing \rightarrow voltage drop \rightarrow open circuit at high frequency (2), and contact welding or contact element fusing may occur.(1) is the state after contact chattering is controlled and contact welding tolerance is improved, by balancing the attraction force and opposing force for enduring as much as possible in such conditions for MS-T series.





Figure 1: Attraction force property of the electromagnet due to the voltage drop when the motor is started

3.1 SEMI-F47 Standard

The magnetic contactor is not directly based on the SEMI standard because this standard demands an instantaneous voltage drop tolerance for the semiconductor equipment. However, the instantaneous voltage drop tolerance (that is tolerance when the contact is not turned off even after instantaneous voltage drop occurs in the coil excitation state) test was conducted for the S-T type and SD-T type magnetic contactors under SEMI-F47 standard. The AC-operated magnetic contactor is applicable in a certain range. The DC-operated magnetic contactor is applicable to the SEMI-F47 standard.



3.2 Instantaneous Power Failure Tolerance

The following table shows the maximum instantaneous power failure time during instantaneous power failure of the MS-T series.

Model Name	Maximum Instantaneous Power Failure Time [ms]
S-T10	2
S-T12, T20	2
S-T21, T25	2
S-T32	2

Model Name	Maximum Instantaneous Power Failure Time [ms]
S-T35, T50	2
S-T65, T80	40
S-T100	30

Note. This table shows the maximum instantaneous power failure time when self-maintenance (Auxiliary contact a) is functioning properly.

4. Operating Characteristics of the Thermal Relay

4.1 Operations in a Balanced Circuit (Ambient Temperature: 20°C)

- (a) If the thermal relay does not function at 105% of settling current in cold conditions for more than 2 hours, the operation should be performed with 120% of the settling current for less than 2 hours after the constant temperature is maintained.
- (b) When 150% of the settling current is passed after the settling current is passed and the constant temperature is maintained, the relay should operate within the limits shown in the table below with respect to the corresponding trip class.
- (c) The operation should be performed within the limits shown in the table below with respect to the corresponding trip class, when 720% of the settling current is passed in cold conditions.

Trip Class	150% of the settling	720% of the settling	
•	current	current	
5	Less than 2 minutes	T⊧≦5 seconds	
10A	Less than 2 minutes	2 <t⊵≦10 seconds<="" td=""></t⊵≦10>	
10	Less than 4 minutes	4 <t⊵≦10 seconds<="" td=""></t⊵≦10>	
20	Less than 8 minutes	6 <t⊵≦20 seconds<="" td=""></t⊵≦20>	
30	Less than 12 minutes	9 <t<sub>P ≦30 seconds</t<sub>	


TP : Operating time at the time of constraint


4.2 Operations in an Unbalanced Circuit (Ambient Temperature: 20°C)

- (a) If the open phase detection function does not execute when settling current is passed to all poles at the same time for 2 hours, the operation should be performed within 2 hours when one pole is disconnected and 132% of settling current is passed to the other two poles after the constant temperature is maintained.
- (b) If the open phase detection function does not execute when settling current is passed to 2 poles and 90% of settling current to 1 pole for 2 hours, the operation should be performed within 2 hours when one pole is disconnected and 115% of settling current is passed to the other two poles after the constant temperature is maintained.

Result: The whole frame satisfies the above condition.

Operational property curve is shown below.






5. Noise Characteristics

The S-T10 to T50 type magnetic contactors use the optimum design of the electromagnet and oscillation insulation, while the S-T65 to T100 type magnetic contactors use AC-operated and DC excitation electromagnets. Thus, the measures to control the whining sound of core are implemented for a silent series.

5.1 Noise during the ON State



Test Conditions: Operating Coil Rated Value 200VAC Background noise in a soundproof room: 30 dB Measurement after every 30 cycles in A-weighting characteristic Fast.

Table 1: Noise during the ON state [dB,	A-weighting Characteristic Fast]
---	----------------------------------

Voltage Applied to Coil	170V 60Hz	200V 60Hz	240V 60Hz
Model Name	Average Value	Average Value	Average Value
S-T10/T12/T20	33	33	35
S-T21/T25	30	31	32
S-T32	30	31	30
S-T35	32	32	33
S-T50	32	32	33

Note a) Indicates the average value of every 10 machines.

5.2 Noise during Opening and Closing

Table 2 shows the results when noise during opening and closing at 240V and 60Hz was measured from a distance of 10cm (other measurement conditions are the same as that of section 5.1).

Madel Neme	No	ise
Model Name	When closed	When opened
S-T10/T12/T20	88	87
S-T21/T25	94	92
S-T32	91	90
S-T35	94	91
S-T50	94	91
S-T65	98	98
S-T80	98	98
S-T100	98	98

Table 2: Noise during opening and closing [dB, A-weighting Characteristic Fast]

Note a) Indicates the average value of every 4 machines.

6. Impact during Opening and Closing

When the magnetic starter/magnetic contactor is installed in the control panel and opened and closed, the kinetic energy at the stop position of the movable part is converted into impact energy, and the control panel vibrates. These vibrations are transmitted to the other controllers installed on the control panel, causing a malfunction. The magnitude of these vibrations (acceleration, frequency) differs according to the magnitude of the opening-closing impact of the magnetic contactor or specifications of the control panel (hardness, number of the installed fixtures, position of installation, etc.). The existence of malfunction cannot be determined unless the measurement is performed for each case. Therefore, the test was conducted for impact acceleration and relay contact malfunctions on the standard panel of the MS-T series as shown in

Figure 1.

Model Name	240V 50Hz
S-T10	14.7 to 19.6
S-T12/T20	14.7 to 19.6
S-T21/T25	14.7 to 19.6
S-T32	14.7 to 19.6
S-T35	14.7 to 24.5
S-T50	14.7 to 24.5
S-T65	14.7 to 24.5
S-T80	14.7 to 24.5
S-T100	24.5 to 39.2

Open-close impact values (acceleration [m/s²] at a frequency of 0 to 2000Hz)

Contact malfunction due to open-close impact of the installed plate

Impact making	S-T10 to T100 (by applying voltage of 240V
body	and frequency of 50Hz to the 200VAC coil)
Impact receiving body	SR-T9 5a4b
Results	The contact b did not malfunction.




Figure 1: Standard panel for the open and close impact test

7. Insulation Resistance and Withstand Voltage

	Reference Value	Results	Measurement Locations
Insulation Resistance	$5M\Omega$ or more	$100M\Omega$ or more for all frames	 (a) Between conducting part and grounded metal body as well as the operating circuit (grounded) when the contact element was closed. (b) Between all poles when the contact element was closed. (c) Between conducting part and grounded metal body as well as the operating circuit (grounded) when the contact element was opened.
Withstand Voltage	Endurance for 1 minute at 2500V and 50Hz or 60Hz	No abnormality for 1 minute at 2500V and 60Hz for all the frames	 (d) Between the supply side terminals and the load side terminals when the contact element was opened. (e) Between the conducting part of the operating circuit and the grounded metal body. (f) Between one circuit of the operating circuit, and all other circuits (grounded).

8. Vibration

8.1 Contact Malfunction Vibration

Investigation of resonance point existence and contact malfunction existence by slowly increasing the frequency from 10Hz to 55Hz, and then slowly decreasing it from 55Hz to 10Hz according to the following conditions. Conditions

Conditions		
Acceleration	: Constant at 19.6m/s ²	
Vibration Direction	: Front-Back, Right-Left,	Up-Down
Frequency Variable Spe	ed: 2Hz per second	
Check Items	•	ence, contact malfunction existence (contact malfunction check ng points)
	Magnetic Contactor	: The existence of contact b malfunction was checked when the operating coil was OFF.
		The existence of main or auxiliary contact a malfunction was checked when the operating coil was ON (applying 85% of the rated voltage).
	Thermal Relay	: The existence of contact a malfunction was checked when there was no current trip state.
		The existence of contact b malfunction was checked after the smallest current of the scale was passed, and the temperature was saturated.
Judgment Conditions		
Resonance Point	: Should be none	
Contact Malfunction		eft open for more than 1ms

Jı

Contact Malfunction : Contact should not be left open for more than 1ms

Results

There was no malfunction in the resonance point or contact of S-T10 to T100 type and TH-T18 to T100 type.

8.2 Constant Vibration Endurance

One-hour test was conducted in each state and in each direction for a total of six hours according to the following conditions to check for change in properties, damage, and looseness before and after the test.


Conditions

Conditions		
Frequency	: 16.7Hz	
Double Amplitude	: 4mm	
Vibration Direction	: Front-Back, Right-Left,	Up-Down
Check items	: The existence of change	e in properties, damage to the parts, loose screws, or contact Ifunction check according to the following points)
	Magnetic Contactor	: The existence of contact b malfunction was checked when the operating coil was OFF.
		The existence of main or auxiliary contact a malfunction was checked when the operating coil was ON (applying 85% of the rated voltage).
	Thermal Relay	: The existence of contact a malfunction was checked when there was no current trip state. The existence of contact b malfunction was checked after the
		smallest current of the scale was passed, and the temperature was saturated.
Screw Tightening Torque	e: Tightening at 80% of the	reference torque
Judgment Conditions		
Change in Property	. .	g voltage of the magnetic contactor should be ±2% or less ng current) change of the thermal relay should be within 5%
Damage	: No part should be dam	
Looseness	: No screw should be loo	bse
Contact Malfunction	: Contact should not be	left open for more than 1ms
Results		•
For S-T10 to T100 type	and TH-T18 to T100 type,	there was no contact malfunction, or damage to any parts, or

۶ye אעי looseness of the screws and the property change was within the reference value.

9. Impact

Investigation of contact malfunction or damage by applying the sine wave pulse impact. Impact Waveform: Figure on right side Impact Count: 5 times per direction (3 times when the operating coil was OFF, and 2 times when it was ON) Judgment conditions: Contact malfunction: 49m/s² or more Damage to parts: 490m/s² or more



		Test Co	nditions			Results	
Model	Therma	al Relay	Operating Coil		Testing		-50115
Name	Nominal Value [A]	Passage of Current [A]	Voltage [V]	Frequency [Hz]	Machine	49m/s ²	490m/s ²
MSO-T10	9	7	170	60	Pendulum	No contact malfunction	No damage
MSO-T12	11	9	170	60	Pendulum	No contact malfunction	No damage
MSO-T20	15	12	170	60	Pendulum	No contact malfunction	No damage
MSO-T21	15	12	170	60	Pendulum	No contact malfunction	No damage
MSO-T25	22	18	170	60	Pendulum	No contact malfunction	No damage
MSO-T35	29	24	170	60	Pendulum	No contact malfunction	No damage
MSO-T50	42	34	170	60	Pendulum	No contact malfunction	No damage
MSO-T65	54	43	170	60	Pendulum	No contact malfunction	No damage
MSO-T80	67	54	170	60	Pendulum	No contact malfunction	No damage
MSO-T100	82	65	170	60	Pendulum	No contact malfunction	No damage

Note a) A nominal value of 200VAC was used for the rated value of the operating coil.


Note b) The coil was switched on 1 hour after the start of current passage.

10. Mechanical Endurance

In the test conditions indicated in Table 1, the operation was performed specified number of times. As a result, there was no damage to the parts, etc. There was no abnormality in the operation even after the test, meeting the standard criteria.


Table 1									
	Test Conditions			Results					
Model Name	Operating Circuit	Frequency [Hz]	Switching Frequency [times per hour]	Number of Switching Times [10000 times]	Damage to Parts	Looseness of tightened parts	Operating Test after Number of Switching Times		
	Voltage [V]						Operating Voltage [V]	Open Voltage [V]	
Standard	Rated Voltage	Rated Frequency	-	-	None	None	85% or less of the Coil Rated Voltage	20 to 75% (S-T50 or less) 10 to 75% (S-T65 or more) of Coil Rated Voltage	
S-T10	240	60	14400	1000	None	None	140 to 150	108 to 120	
S-T12	240	60	14400	1000	None	None	144 to 155	107 to 130	
S-T20	240	60	14400	1000	None	None	144 to 155	107 to 130	
S-T21	240	60	14400	1000	None	None	148 to 151	109 to 120	
S-T25	240	60	14400	1000	None	None	148 to 151	109 to 120	
S-T32	240	60	14400	1000	None	None	147 to 154	100 to 104	
S-T35	240	60	14400	1000	None	None	138 to 149	110 to 118	
S-T50	240	60	14400	1000	None	None	138 to 149	110 to 118	
S-T65	240	60	7200	500	None	None	108 to 118	35 to 50	
S-T80	240	60	7200	500	None	None	108 to 118	35 to 50	
S-T100	240	60	7200	500	None	None	106 to 122	55 to 85	

11. Electrical Endurance



2000/4400							
Item		Те	st Conditions	Number of	Insulation	Withstand	
Stan-	Voltage Ur [3φ, V]	Current Ie [A]	Power Factor [Delay]	Switching Frequency [times per hour]	Tests [10000 times]	Resistance [MΩ]	Voltage [VAC 1 minute]
dard Model Name	*1	*2	le≦17A : 0.65 le≥17A : 0.35	-	-	-	2 x Ue
S-T10	220 440	11 7	0.65 ″	1800 ″	200 ″	100 or more	2500 OK
S-T12	220 440	13 9	0.65 ″	1800 ″	200 "	11	11
S-T20	220 440	18 18	0.35 ″	1800 ″	200 100	11	11
S-T21	220 440	20 20	0.35 ″	1800 "	200 "	11	11
S-T25	220 440	26 25	0.35 ″	1800 "	200 //	11	11
S-T32	220 440	32 32	0.35 ″	1800 "	200 //	11	11
S-T35	220 440	35 32	0.35 ″	1800 ″	200 "	11	11
S-T50	220 440	50 48	0.35 ″	1200 ″	200 "	11	11
S-T65	220 440	65 65	0.35 ″	1200 "	200 "	11	11
S-T80	220 440	80 80	0.35 ″	1200 "	100 "	11	11
S-T100	220 440	100 93	0.35 ″	1200 "	100 "	11	11

Note a) *1 Closed circuit voltage: Rated applicable voltage (Ue), break-time voltage: Ue x 0.17 times *2 Closed circuit current: Rated applicable current (le) x 6 times, break-time current: le




Switching Frequency In case of 300 times per hour

200V/440V		125	In case of 300 time	es per hour			
Item		Те	st Conditions	Number of	Inculation	Withstand	
Stan-	Voltage Ur [3φ, V]	Current le [A]	Power Factor [Delay]	Switching Frequency [times per hour]	Number of Tests [10000 times]	Insulation Resistance [MΩ]	Withstand Voltage [VAC 1 minute]
dard Model Name	*3	*4	le≦17A : 0.65 le≥17A : 0.35	-	-	-	2 x Ue
S-T10	220 440	8 6	0.65 ″	300 ″	3	100 or more	2500 OK
S-T12	220 440	11 9	0.65 ″	300 "	3 //	11	11
S-T20	220 440	18 13	0.35 0.65	300 ″	1.5 ″	11	11
S-T21	220 440	18 13	0.35 0.65	300 ″	3 //	11	"
S-T25	220 440	20 17	0.35 0.65	300 ″	3 "	11	11
S-T32	220 440	26 24	0.35 ″	300 "	3 "	11	11
S-T35	220 440	26 24	0.35 ″	300 "	3 1.5	11	11
S-T50	220 440	35 32	0.35 ″	300 ″	3 1.5	11	11
S-T65	220 440	50 47	0.35 ″	300 "	3 1.5	11	11
S-T80	220 440	65 62	0.35 ″	300 "	3 1.5	11	11
S-T100	220 440	80 75	0.35 ″	300 "	3 1.5	11	"

Note a) *3 Closed circuit voltage: Rated applicable voltage (Ue), break-time voltage: Ue

*4 Closed circuit current: Rated applicable current (le) x 6 times, break-time current: le x 6 times



Note a) Indicates the relationship between the time and the passage of current up to a certain temperature at which the temperature rise value of the contact element of the magnetic contactor will not cause hindrance to the continuous use of the contactor.

Mitsubishi Electric Corporation Nagoya Works is a factory certified for ISO14001 (standards for environmental management systems) and ISO9001(standards for quality assurance management systems)



To ensure proper use of the products listed in this catalog, please be sure to read the instruction manual prior to use.

MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE: TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN www.MitsubishiElectric.co.jp/melfansweb

14001 14001 CONTROLOGY CONT

