



Numerical Protection Relay

*MELPRO*™-D Series

Modbus Register Map  
for TYPE CMP1-A41D1

Attachment-1 MODBUS Address Map

Coil Map

Address Range (1 to 9999)

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks	
0	15	0001	Forced DO action setting DO1	Activate	x	0	1	No Unit	Digital Value	With a "Forced DO control setting" request from the master station as Function Code: 15, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 0001+16*i • Number of access points = 16*j • i+j<=2 (i=0 to 1, j=1 to 2) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.  • Reserved is fixed as 0. This is a usage prohibited area when adding models. (If a value other than 0 arrives, it will not be reflected.)	
1		0002	Forced DO action setting DO2	Activate	x	0	1	No Unit	Digital Value		
2		0003	Forced DO action setting DO3	Activate	x	0	1	No Unit	Digital Value		
3		0004	Forced DO action setting DO4	Activate	x	0	1	No Unit	Digital Value		
4		0005	Forced DO action setting DO5	Activate	x	0	1	No Unit	Digital Value		
5		0006	Forced DO action setting DO6	Activate	x	0	1	No Unit	Digital Value		
6		0007	Forced DO action setting DO7	Activate	x	0	1	No Unit	Digital Value		
7		0008	Forced DO action setting DO8	Activate	x	0	1	No Unit	Digital Value		
8		0009	(Reserved)				0	0			
9		0010	(Reserved)				0	0			
10		0011	(Reserved)				0	0			
11		0012	(Reserved)				0	0			
12		0013	(Reserved)				0	0			
13		0014	(Reserved)				0	0			
14		0015	(Reserved)				0	0			
15		0016	(Reserved)				0	0			
16		0017	(Reserved)				0	0			
17		0018	(Reserved)				0	0			
18		0019	(Reserved)				0	0			
19		0020	(Reserved)				0	0			
20		0021	(Reserved)				0	0			
21		0022	(Reserved)				0	0			
22		0023	(Reserved)				0	0			
23		0024	(Reserved)				0	0			
24		0025	(Reserved)				0	0			
25		0026	(Reserved)				0	0			
26		0027	(Reserved)				0	0			
27		0028	(Reserved)				0	0			
28		0029	(Reserved)				0	0			
29		0030	(Reserved)				0	0			
30		0031	(Reserved)				0	0			
31		0032	(Reserved)				0	0			
32	15	0033	Start forced DO action operation DO1	Activate	x	0	1	No Unit	Digital Value	With a "Start forced action operation" request from the master station as Function Code: 15, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 0033+16*i • Number of access points = 16*j • i+j<=2 (i=0 to 1, j=1 to 2) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.  • Reserved is fixed as 0. This is a usage prohibited area when adding models. (If a value other than 0 arrives, it will not be reflected.)	
33		0034	Start forced DO action operation DO2	Activate	x	0	1	No Unit	Digital Value		
34		0035	Start forced DO action operation DO3	Activate	x	0	1	No Unit	Digital Value		
35		0036	Start forced DO action operation DO4	Activate	x	0	1	No Unit	Digital Value		
36		0037	Start forced DO action operation DO5	Activate	x	0	1	No Unit	Digital Value		
37		0038	Start forced DO action operation DO6	Activate	x	0	1	No Unit	Digital Value		
38		0039	Start forced DO action operation DO7	Activate	x	0	1	No Unit	Digital Value		
39		0040	Start forced DO action operation DO8	Activate	x	0	1	No Unit	Digital Value		
40		0041	(Reserved)				0	0			
41		0042	(Reserved)				0	0			
42		0043	(Reserved)				0	0			
43		0044	(Reserved)				0	0			
44		0045	(Reserved)				0	0			
45		0046	(Reserved)				0	0			
46		0047	(Reserved)				0	0			
47		0048	(Reserved)				0	0			
48		0049	(Reserved)				0	0			
49		0050	(Reserved)				0	0			
50		0051	(Reserved)				0	0			
51		0052	(Reserved)				0	0			
52		0053	(Reserved)				0	0			
53		0054	(Reserved)				0	0			
54		0055	(Reserved)				0	0			
55		0056	(Reserved)				0	0			
56		0057	(Reserved)				0	0			
57		0058	(Reserved)				0	0			
58		0059	(Reserved)				0	0			
59		0060	(Reserved)				0	0			
60		0061	(Reserved)				0	0			
61		0062	(Reserved)				0	0			
62		0063	(Reserved)				0	0			
63		0064	(Reserved)				0	0			
64	15	0065	Test mode setting 1 monitor lock	On	Off	0	1	No Unit	Digital Value	With a "Test mode setting" request from the master station as Function Code: 15, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 0065+16*i • Number of access points = 16*j • i+j<=4 (i=0 to 4, j=1 to 4) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.  • Reserved is fixed as 0. (If a value other than 0 arrives, it will not be reflected.)	
65		0066	Test mode setting 2 UC phase A lock	On	Off	0	1	No Unit	Digital Value		
66		0067	Test mode setting 3 UC phase B lock	On	Off	0	1	No Unit	Digital Value		
67		0068	Test mode setting 4 UC phase C lock	On	Off	0	1	No Unit	Digital Value		
68		0069	Test mode setting 5 UV phase A lock	On	Off	0	1	No Unit	Digital Value		
69		0070	Test mode setting 6 UV phase B lock	On	Off	0	1	No Unit	Digital Value		
70		0071	Test mode setting 7 UV phase C lock	On	Off	0	1	No Unit	Digital Value		
71		0072	Test mode setting 8 OV phase A lock	On	Off	0	1	No Unit	Digital Value		
72		0073	Test mode setting 9 OV phase B lock	On	Off	0	1	No Unit	Digital Value		
73		0074	Test mode setting 10 OV phase C lock	On	Off	0	1	No Unit	Digital Value		
74		0075	Test mode setting 11 trip counter lock	On	Off	0	1	No Unit	Digital Value		
75		0076	Test mode setting 12 OCNEG3 test	On	Off	0	1	No Unit	Digital Value		
76		0077	Test mode setting 13 THOL test	On	Off	0	1	No Unit	Digital Value		
77		0078	Test mode setting 14 MST1 & 2 test	On	Off	0	1	No Unit	Digital Value		
78		0079	(Reserved)				0	0			
79		0080	(Reserved)				0	0			
80		0081	(Reserved)				0	0			
81		0082	(Reserved)				0	0			
82		0083	(Reserved)				0	0			
83		0084	(Reserved)				0	0			
84		0085	(Reserved)				0	0			
85		0086	(Reserved)				0	0			
86		0087	(Reserved)				0	0			
87		0088	(Reserved)				0	0			
88		0089	(Reserved)				0	0			
89		0090	(Reserved)				0	0			
90		0091	(Reserved)				0	0			
91		0092	(Reserved)				0	0			
92		0093	(Reserved)				0	0			
93		0094	(Reserved)				0	0			
94		0095	(Reserved)				0	0			
95		0096	(Reserved)				0	0			
96		0097	(Reserved)				0	0			
97		0098	(Reserved)				0	0			
98		0099	(Reserved)				0	0			
99		0100	(Reserved)				0	0			
100		0101	(Reserved)				0	0			
101		0102	(Reserved)				0	0			
102		0103	(Reserved)				0	0			
103		0104	(Reserved)				0	0			
104		0105	(Reserved)				0	0			
105		0106	(Reserved)				0	0			
106		0107	(Reserved)				0	0			
107		0108	(Reserved)				0	0			
108		0109	(Reserved)				0	0			
109		0110	(Reserved)				0	0			
110		0111	(Reserved)				0	0			
111		0112	(Reserved)				0	0			
112		0113	(Reserved)				0	0			
113		0114	(Reserved)				0	0			
114		0115	(Reserved)				0	0			
115		0116	(Reserved)				0	0			
116		0117	(Reserved)				0	0			
117		0118	(Reserved)				0	0			
118		0119	(Reserved)				0	0			
119		0120	(Reserved)				0	0			
120		0121	(Reserved)				0	0			
121		0122	(Reserved)				0	0			
122		0123	(Reserved)				0	0			
123		0124	(Reserved)				0	0			
124		0125	(Reserved)				0	0			
125		0126	(Reserved)				0	0			
126		0127	(Reserved)				0	0			
127		0128	(Reserved)				0	0			

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
128	15	0129	Start test mode operation 1: Monitor lock	On	Off	0	1	No Unit	Digital Value	With a "Start test mode operation" request from the master station as Function Code: 15, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 0129+16*i • Number of access points = 16*j • i+j<=4 (i=0 to 3, j=1 to 4) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.  • Reserved is fixed as 0. (If a value other than 0 arrives, it will not be reflected.)
129		0130	Start test mode operation 2: UC phase A lock	On	Off	0	1	No Unit	Digital Value	
130		0131	Start test mode operation 3: UC phase B lock	On	Off	0	1	No Unit	Digital Value	
131		0132	Start test mode operation 4: UC phase C lock	On	Off	0	1	No Unit	Digital Value	
132		0133	Start test mode operation 5: UV phase A lock	On	Off	0	1	No Unit	Digital Value	
133		0134	Start test mode operation 6: UV phase B lock	On	Off	0	1	No Unit	Digital Value	
134		0135	Start test mode operation 7: UV phase C lock	On	Off	0	1	No Unit	Digital Value	
135		0136	Start test mode operation 8: OV phase A lock	On	Off	0	1	No Unit	Digital Value	
136		0137	Start test mode operation 9: OV phase B lock	On	Off	0	1	No Unit	Digital Value	
137		0138	Start test mode operation 10: OV phase C lock	On	Off	0	1	No Unit	Digital Value	
138		0139	Start test mode operation 11: Trip counter lock	On	Off	0	1	No Unit	Digital Value	
139		0140	(Reserved)			0	0			
140		0141	(Reserved)			0	0			
141		0142	(Reserved)			0	0			
142		0143	(Reserved)			0	0			
143		0144	(Reserved)			0	0			
144		0145	(Reserved)			0	0			
145		0146	(Reserved)			0	0			
146		0147	(Reserved)			0	0			
147	0148	(Reserved)			0	0				
148	0149	(Reserved)			0	0				
149	0150	(Reserved)			0	0				
150	0151	(Reserved)			0	0				
151	0152	(Reserved)			0	0				
152	0153	(Reserved)			0	0				
153	0154	(Reserved)			0	0				
154	0155	(Reserved)			0	0				
155	0156	(Reserved)			0	0				
156	0157	(Reserved)			0	0				
157	0158	(Reserved)			0	0				
158	0159	(Reserved)			0	0				
159	0160	(Reserved)			0	0				
160	0161	(Reserved)			0	0				
161	0162	(Reserved)			0	0				
162	0163	(Reserved)			0	0				
163	0164	(Reserved)			0	0				
164	0165	(Reserved)			0	0				
165	0166	(Reserved)			0	0				
166	0167	(Reserved)			0	0				
167	0168	(Reserved)			0	0				
168	0169	(Reserved)			0	0				
169	0170	(Reserved)			0	0				
170	0171	(Reserved)			0	0				
171	0172	(Reserved)			0	0				
172	0173	(Reserved)			0	0				
173	0174	(Reserved)			0	0				
174	0175	(Reserved)			0	0				
175	0176	(Reserved)			0	0				
176	0177	(Reserved)			0	0				
177	0178	(Reserved)			0	0				
178	0179	(Reserved)			0	0				
179	0180	(Reserved)			0	0				
180	0181	(Reserved)			0	0				
181	0182	(Reserved)			0	0				
182	0183	(Reserved)			0	0				
183	0184	(Reserved)			0	0				
184	0185	(Reserved)			0	0				
185	0186	(Reserved)			0	0				
186	0187	(Reserved)			0	0				
187	0188	(Reserved)			0	0				
188	0189	(Reserved)			0	0				
189	0190	(Reserved)			0	0				
190	0191	(Reserved)			0	0				
191	0192	(Reserved)			0	0				
192	0193	(Reserved)								
193	0194	(Reserved)								
194	0195	(Reserved)								
195	0196	(Reserved)								
196	0197	(Reserved)								
197	0198	(Reserved)								
198	0199	(Reserved)								
199	0200	(Reserved)								
200	0201	(Reserved)								
201	0202	(Reserved)								
202	0203	(Reserved)								
203	0204	(Reserved)								
204	0205	(Reserved)								
205	0206	(Reserved)								
206	0207	(Reserved)								
207	0208	(Reserved)								
208	0209	(Reserved)								
209	0210	(Reserved)								
210	0211	(Reserved)								
211	0212	(Reserved)								
212	0213	(Reserved)								
213	0214	(Reserved)								
214	0215	(Reserved)								
215	0216	(Reserved)								
216	0217	(Reserved)								
217	0218	(Reserved)								
218	0219	(Reserved)								
219	0220	(Reserved)								
220	0221	(Reserved)								
221	0222	(Reserved)								
222	0223	(Reserved)								
223	0224	(Reserved)								
224	0225	(Reserved)								
225	0226	(Reserved)								
226	0227	(Reserved)								
227	0228	(Reserved)								
228	0229	(Reserved)								
229	0230	(Reserved)								
230	0231	(Reserved)								
231	0232	(Reserved)								
232	0233	(Reserved)								
233	0234	(Reserved)								
234	0235	(Reserved)								
235	0236	(Reserved)								
236	0237	(Reserved)								
237	0238	(Reserved)								
238	0239	(Reserved)								
239	0240	(Reserved)								
240	0241	(Reserved)								
241	0242	(Reserved)								
242	0243	(Reserved)								
243	0244	(Reserved)								
244	0245	(Reserved)								
245	0246	(Reserved)								
246	0247	(Reserved)								
247	0248	(Reserved)								
248	0249	(Reserved)								
249	0250	(Reserved)								
250	0251	(Reserved)								
251	0252	(Reserved)								
252	0253	(Reserved)								
253	0254	(Reserved)								
254	0255	(Reserved)								
255	0256	(Reserved)								

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
256		0257	(Reserved)							
257		0258	(Reserved)							
258		0259	(Reserved)							
259		0260	(Reserved)							
260		0261	(Reserved)							
261		0262	(Reserved)							
262		0263	(Reserved)							
263		0264	(Reserved)							
264		0265	(Reserved)							
265		0266	(Reserved)							
266		0267	(Reserved)							
267		0268	(Reserved)							
268		0269	(Reserved)							
269		0270	(Reserved)							
270		0271	(Reserved)							
271		0272	(Reserved)							
272		0273	(Reserved)							
273		0274	(Reserved)							
274		0275	(Reserved)							
275		0276	(Reserved)							
276		0277	(Reserved)							
277		0278	(Reserved)							
278		0279	(Reserved)							
279		0280	(Reserved)							
280		0281	(Reserved)							
281		0282	(Reserved)							
282		0283	(Reserved)							
283		0284	(Reserved)							
284		0285	(Reserved)							
285		0286	(Reserved)							
286		0287	(Reserved)							
287		0288	(Reserved)							
288		0289	(Reserved)							
289		0290	(Reserved)							
290		0291	(Reserved)							
291		0292	(Reserved)							
292		0293	(Reserved)							
293		0294	(Reserved)							
294		0295	(Reserved)							
295		0296	(Reserved)							
296		0297	(Reserved)							
297		0298	(Reserved)							
298		0299	(Reserved)							
299		0300	(Reserved)							
300		0301	(Reserved)							
301		0302	(Reserved)							
302		0303	(Reserved)							
303		0304	(Reserved)							
304		0305	(Reserved)							
305		0306	(Reserved)							
306		0307	(Reserved)							
307		0308	(Reserved)							
308		0309	(Reserved)							
309		0310	(Reserved)							
310		0311	(Reserved)							
311		0312	(Reserved)							
312		0313	(Reserved)							
313		0314	(Reserved)							
314		0315	(Reserved)							
315		0316	(Reserved)							
316		0317	(Reserved)							
317		0318	(Reserved)							
318		0319	(Reserved)							
319		0320	(Reserved)							
320		0321	(Reserved)							
321		0322	(Reserved)							
322		0323	(Reserved)							
323		0324	(Reserved)							
324		0325	(Reserved)							
325		0326	(Reserved)							
326		0327	(Reserved)							
327		0328	(Reserved)							
328		0329	(Reserved)							
329		0330	(Reserved)							
330		0331	(Reserved)							
331		0332	(Reserved)							
332		0333	(Reserved)							
333		0334	(Reserved)							
334		0335	(Reserved)							
335		0336	(Reserved)							
336		0337	(Reserved)							
337		0338	(Reserved)							
338		0339	(Reserved)							
339		0340	(Reserved)							
340		0341	(Reserved)							
341		0342	(Reserved)							
342		0343	(Reserved)							
343		0344	(Reserved)							
344		0345	(Reserved)							
345		0346	(Reserved)							
346		0347	(Reserved)							
347		0348	(Reserved)							
348		0349	(Reserved)							
349		0350	(Reserved)							
350		0351	(Reserved)							
351		0352	(Reserved)							
352		0353	(Reserved)							
353		0354	(Reserved)							
354		0355	(Reserved)							
355		0356	(Reserved)							
356		0357	(Reserved)							
357		0358	(Reserved)							
358		0359	(Reserved)							
359		0360	(Reserved)							
360		0361	(Reserved)							
361		0362	(Reserved)							
362		0363	(Reserved)							
363		0364	(Reserved)							
364		0365	(Reserved)							
365		0366	(Reserved)							
366		0367	(Reserved)							
367		0368	(Reserved)							
368		0369	(Reserved)							
369		0370	(Reserved)							
370		0371	(Reserved)							
371		0372	(Reserved)							
372		0373	(Reserved)							
373		0374	(Reserved)							
374		0375	(Reserved)							
375		0376	(Reserved)							
376		0377	(Reserved)							
377		0378	(Reserved)							
378		0379	(Reserved)							
379		0380	(Reserved)							
380		0381	(Reserved)							
381		0382	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
382	15	0383	(Reserved)							
383		0384	(Reserved)							
384		0385	LED reset setting	Activate	x	0	1	No Unit	Digital Value	(Note 1)
385		0386	Erase event records setting	Activate	x	0	1	No Unit	Digital Value	(Note 1)
386		0387	Erase monitoring error data setting	Activate	x	0	1	No Unit	Digital Value	(Note 1)
387		0388	(Reserved)							
388		0389	Erase accident records setting	Activate	x	0	1	No Unit	Digital Value	(Note 1)
389		0390	(Reserved)							
390		0391	Get event records	Activate	x	0	1	No Unit	Digital Value	(Note 2)
391		0392	Get monitoring error records	Activate	x	0	1	No Unit	Digital Value	(Note 2)
392		0393	Get access records	Activate	x	0	1	No Unit	Digital Value	(Note 2)
393		0394	Get accident records	Activate	x	0	1	No Unit	Digital Value	(Note 3)
394		0395	CB close control setting	Activate	x	0	1	No Unit	Digital Value	
395		0396	CB open control setting	Activate	x	0	1	No Unit	Digital Value	
396		0397	CB close control operation	Activate	x	0	1	No Unit	Digital Value	
397		0398	CB open control operation	Activate	x	0	1	No Unit	Digital Value	

## Note 1:

With a request from the master station as Function Code: 15, the slave will respond with (MODBUS send) 05: ACKNOWLEDGE(ACK).

## On MODBUS:

- Start address = Each address
- Number of access points = 1

→ When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.

If another request comes from the master after the "Start operation" request has been issued but before the relay's response has completed, the slave will respond with (MODBUS send) 07: NEGATIVE ACKNOWLEDGE.

## Note 2:

With a request from the master station as Function Code: 15, the slave will respond with (MODBUS send) 05: ACKNOWLEDGE(ACK).

## On MODBUS:

- Start address = Each address
- Number of access points = 1

Fixed value.

→ When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.

If another request comes from the master after a request has been issued but before the relay's response has completed, the slave will respond with (MODBUS send) 07: NEGATIVE ACKNOWLEDGE.  
If an error has occurred (recording) when the request was issued, return the error status with check get request for each record.

## Note 3:

With a request from the master station as Function Code: 15, the slave will respond with (MODBUS send) 05: ACKNOWLEDGE(ACK).

## On MODBUS:

- Start address = 0394
- Number of access points = 1

Fixed value.

→ When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.

If another request comes from the master after a request has been issued but before the relay's response has completed, the slave will respond with (MODBUS send) 07: NEGATIVE ACKNOWLEDGE.  
If an error has occurred (tripped) when the request was issued, return the error status with check accident record get request (address 39813).

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
0	2	10001	For exclusive use of manufacturer							With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
1		10002	For exclusive use of manufacturer							
2		10003	For exclusive use of manufacturer							
3		10004	For exclusive use of manufacturer							
4		10005	For exclusive use of manufacturer							
5		10006	For exclusive use of manufacturer							
6		10007	For exclusive use of manufacturer							
7		10008	For exclusive use of manufacturer							
8		10009	For exclusive use of manufacturer							
9		10010	For exclusive use of manufacturer							
10		10011	For exclusive use of manufacturer							
11		10012	For exclusive use of manufacturer							
12		10013	For exclusive use of manufacturer							
13		10014	For exclusive use of manufacturer							
14		10015	For exclusive use of manufacturer							
15		10016	For exclusive use of manufacturer							
16		10017	For exclusive use of manufacturer							
17		10018	For exclusive use of manufacturer							
18		10019	For exclusive use of manufacturer							
19		10020	For exclusive use of manufacturer							
20		10021	For exclusive use of manufacturer							
21		10022	For exclusive use of manufacturer							
22		10023	For exclusive use of manufacturer							
23		10024	For exclusive use of manufacturer							
24		10025	For exclusive use of manufacturer							
25		10026	For exclusive use of manufacturer							
26		10027	For exclusive use of manufacturer							
27		10028	For exclusive use of manufacturer							
28		10029	For exclusive use of manufacturer							
29		10030	For exclusive use of manufacturer							
30		10031	For exclusive use of manufacturer							
31		10032	For exclusive use of manufacturer							
32		10033	For exclusive use of manufacturer							
33		10034	For exclusive use of manufacturer							
34		10035	For exclusive use of manufacturer							
35		10036	For exclusive use of manufacturer							
36		10037	For exclusive use of manufacturer							
37		10038	For exclusive use of manufacturer							
38		10039	For exclusive use of manufacturer							
39		10040	For exclusive use of manufacturer							
40		10041	For exclusive use of manufacturer							
41		10042	For exclusive use of manufacturer							
42		10043	For exclusive use of manufacturer							
43		10044	For exclusive use of manufacturer							
44		10045	For exclusive use of manufacturer							
45		10046	For exclusive use of manufacturer							
46		10047	For exclusive use of manufacturer							
47		10048	For exclusive use of manufacturer							
48		10049	For exclusive use of manufacturer							
49		10050	For exclusive use of manufacturer							
50		10051	For exclusive use of manufacturer							
51		10052	For exclusive use of manufacturer							
52		10053	For exclusive use of manufacturer							
53		10054	For exclusive use of manufacturer							
54		10055	For exclusive use of manufacturer							
55		10056	For exclusive use of manufacturer							
56		10057	For exclusive use of manufacturer							
57		10058	For exclusive use of manufacturer							
58		10059	For exclusive use of manufacturer							
59		10060	For exclusive use of manufacturer							
60		10061	For exclusive use of manufacturer							
61		10062	For exclusive use of manufacturer							
62		10063	For exclusive use of manufacturer							
63		10064	For exclusive use of manufacturer							
64		10065	For exclusive use of manufacturer							
65		10066	For exclusive use of manufacturer							
66		10067	For exclusive use of manufacturer							
67		10068	For exclusive use of manufacturer							
68		10069	For exclusive use of manufacturer							
69		10070	For exclusive use of manufacturer							
70		10071	For exclusive use of manufacturer							
71		10072	For exclusive use of manufacturer							
72		10073	For exclusive use of manufacturer							
73		10074	For exclusive use of manufacturer							
74		10075	For exclusive use of manufacturer							
75		10076	For exclusive use of manufacturer							
76		10077	For exclusive use of manufacturer							
77		10078	For exclusive use of manufacturer							
78		10079	For exclusive use of manufacturer							
79		10080	For exclusive use of manufacturer							
80		10081	For exclusive use of manufacturer							
81		10082	For exclusive use of manufacturer							
82		10083	For exclusive use of manufacturer							
83		10084	For exclusive use of manufacturer							
84		10085	For exclusive use of manufacturer							
85		10086	For exclusive use of manufacturer							
86		10087	For exclusive use of manufacturer							
87		10088	For exclusive use of manufacturer							
88		10089	For exclusive use of manufacturer							
89		10090	For exclusive use of manufacturer							
90		10091	For exclusive use of manufacturer							
91		10092	For exclusive use of manufacturer							
92		10093	For exclusive use of manufacturer							
93		10094	For exclusive use of manufacturer							
94		10095	For exclusive use of manufacturer							
95		10096	For exclusive use of manufacturer							
96		10097	For exclusive use of manufacturer							
97		10098	For exclusive use of manufacturer							
98		10099	For exclusive use of manufacturer							
99		10100	For exclusive use of manufacturer							
100		10101	For exclusive use of manufacturer							
101		10102	For exclusive use of manufacturer							
102		10103	For exclusive use of manufacturer							
103		10104	For exclusive use of manufacturer							
104		10105	For exclusive use of manufacturer							
105		10106	For exclusive use of manufacturer							
106		10107	For exclusive use of manufacturer							
107		10108	For exclusive use of manufacturer							
108		10109	For exclusive use of manufacturer							
109		10110	For exclusive use of manufacturer							
110		10111	For exclusive use of manufacturer							
111		10112	For exclusive use of manufacturer							
112		10113	For exclusive use of manufacturer							
113		10114	For exclusive use of manufacturer							
114		10115	For exclusive use of manufacturer							
115		10116	For exclusive use of manufacturer							
116		10117	For exclusive use of manufacturer							
117		10118	For exclusive use of manufacturer							
118		10119	For exclusive use of manufacturer							
119		10120	For exclusive use of manufacturer							
120		10121	For exclusive use of manufacturer							
121		10122	For exclusive use of manufacturer							
122		10123	For exclusive use of manufacturer							
123		10124	For exclusive use of manufacturer							
124		10125	For exclusive use of manufacturer							
125	10126	For exclusive use of manufacturer								

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
126	2	10127	For exclusive use of manufacturer							With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
127		10128	For exclusive use of manufacturer							
128		10129	DI1 status	On	Off	0	1	ON/OFF	Digital Input	
129		10130	DI2 status	On	Off	0	1	ON/OFF	Digital Input	
130		10131	DI3 status	On	Off	0	1	ON/OFF	Digital Input	
131		10132	DI4 status	On	Off	0	1	ON/OFF	Digital Input	
132		10133	DI5 status	On	Off	0	1	ON/OFF	Digital Input	
133		10134	DI6 status	On	Off	0	1	ON/OFF	Digital Input	
134		10135	DI7 status	On	Off	0	1	ON/OFF	Digital Input	
135		10136	DI8 status	On	Off	0	1	ON/OFF	Digital Input	
136		10137	For exclusive use of manufacturer							
137		10138	For exclusive use of manufacturer							
138		10139	For exclusive use of manufacturer							
139		10140	For exclusive use of manufacturer							
140		10141	For exclusive use of manufacturer							
141		10142	For exclusive use of manufacturer							
142		10143	For exclusive use of manufacturer							
143	10144	(Reserved)								
144	10145	(Reserved)								
145	10146	(Reserved)								
146	10147	(Reserved)								
147	10148	(Reserved)								
148	10149	(Reserved)								
149	10150	(Reserved)								
150	10151	(Reserved)								
151	10152	(Reserved)								
152	10153	(Reserved)								
153	10154	(Reserved)								
154	10155	(Reserved)								
155	10156	(Reserved)								
156	10157	(Reserved)								
157	10158	(Reserved)								
158	10159	(Reserved)								
159	10160	(Reserved)								
160	10161	(Reserved)								
161	10162	(Reserved)								
162	10163	(Reserved)								
163	10164	(Reserved)								
164	10165	(Reserved)								
165	10166	(Reserved)								
166	10167	(Reserved)								
167	10168	(Reserved)								
168	10169	(Reserved)								
169	10170	(Reserved)								
170	10171	(Reserved)								
171	10172	(Reserved)								
172	10173	(Reserved)								
173	10174	(Reserved)								
174	10175	(Reserved)								
175	10176	(Reserved)								
176	10177	(Reserved)								
177	10178	(Reserved)								
178	10179	(Reserved)								
179	10180	(Reserved)								
180	10181	(Reserved)								
181	10182	(Reserved)								
182	10183	(Reserved)								
183	10184	(Reserved)								
184	10185	(Reserved)								
185	10186	(Reserved)								
186	10187	(Reserved)								
187	10188	(Reserved)								
188	10189	(Reserved)								
189	10190	(Reserved)								
190	10191	(Reserved)								
191	10192	(Reserved)								
192	10193	DO1 status	On	Off	0	1	ON/OFF	Digital Input		
193	10194	DO2 status	On	Off	0	1	ON/OFF	Digital Input		
194	10195	DO3 status	On	Off	0	1	ON/OFF	Digital Input		
195	10196	DO4 status	On	Off	0	1	ON/OFF	Digital Input		
196	10197	DO5 status	On	Off	0	1	ON/OFF	Digital Input		
197	10198	DO6 status	On	Off	0	1	ON/OFF	Digital Input		
198	10199	DO7 status	On	Off	0	1	ON/OFF	Digital Input		
199	10200	DO8 status	On	Off	0	1	ON/OFF	Digital Input		
200	10201	(Reserved)								
201	10202	(Reserved)								
202	10203	(Reserved)								
203	10204	(Reserved)								
204	10205	(Reserved)								
205	10206	(Reserved)								
206	10207	(Reserved)								
207	10208	All DO OR	On	Off	0	1	ON/OFF	Digital Input		
208	10209	(Reserved)								
209	10210	(Reserved)								
210	10211	(Reserved)								
211	10212	(Reserved)								
212	10213	(Reserved)								
213	10214	(Reserved)								
214	10215	(Reserved)								
215	10216	(Reserved)								
216	10217	(Reserved)								
217	10218	(Reserved)								
218	10219	(Reserved)								
219	10220	(Reserved)								
220	10221	(Reserved)								
221	10222	(Reserved)								
222	10223	(Reserved)								
223	10224	(Reserved)								
224	10225	(Reserved)								
225	10226	(Reserved)								
226	10227	(Reserved)								
227	10228	(Reserved)								
228	10229	(Reserved)								
229	10230	(Reserved)								
230	10231	(Reserved)								
231	10232	(Reserved)								
232	10233	(Reserved)								
233	10234	(Reserved)								
234	10235	(Reserved)								
235	10236	(Reserved)								
236	10237	(Reserved)								
237	10238	(Reserved)								
238	10239	(Reserved)								
239	10240	(Reserved)								
240	10241	(Reserved)								
241	10242	(Reserved)								
242	10243	(Reserved)								
243	10244	(Reserved)								
244	10245	(Reserved)								
245	10246	(Reserved)								
246	10247	(Reserved)								
247	10248	(Reserved)								
248	10249	(Reserved)								
249	10250	(Reserved)								
250	10251	(Reserved)								
251	10252	(Reserved)								
252	10253	(Reserved)								
253	10254	(Reserved)								
254	10255	(Reserved)								
255	10256	(Reserved)								

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
256	2	10257	(Reserved)							With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
257		10258	(Reserved)							
258		10259	(Reserved)							
259		10260	(Reserved)							
260		10261	(Reserved)							
261		10262	(Reserved)							
262		10263	(Reserved)							
263		10264	(Reserved)							
264		10265	(Reserved)							
265		10266	(Reserved)							
266		10267	(Reserved)							
267		10268	(Reserved)							
268		10269	(Reserved)							
269		10270	(Reserved)							
270		10271	(Reserved)							
271		10272	(Reserved)							
272		10273	(Reserved)							
273		10274	(Reserved)							
274		10275	(Reserved)							
275		10276	(Reserved)							
276		10277	(Reserved)							
277		10278	(Reserved)							
278		10279	(Reserved)							
279		10280	(Reserved)							
280		10281	(Reserved)							
281		10282	(Reserved)							
282		10283	(Reserved)							
283		10284	(Reserved)							
284		10285	(Reserved)							
285		10286	(Reserved)							
286	10287	(Reserved)								
287	10288	(Reserved)								
288	10289	(Reserved)								
289	10290	(Reserved)								
290	10291	(Reserved)								
291	10292	(Reserved)								
292	10293	(Reserved)								
293	10294	(Reserved)								
294	10295	(Reserved)								
295	10296	(Reserved)								
296	10297	(Reserved)								
297	10298	(Reserved)								
298	10299	(Reserved)								
299	10300	(Reserved)								
300	10301	(Reserved)								
301	10302	(Reserved)								
302	10303	(Reserved)								
303	10304	(Reserved)								
304	10305	(Reserved)								
305	10306	(Reserved)								
306	10307	(Reserved)								
307	10308	(Reserved)								
308	10309	(Reserved)								
309	10310	(Reserved)								
310	10311	(Reserved)								
311	10312	(Reserved)								
312	10313	(Reserved)								
313	10314	(Reserved)								
314	10315	(Reserved)								
315	10316	(Reserved)								
316	10317	(Reserved)								
317	10318	(Reserved)								
318	10319	(Reserved)								
319	10320	(Reserved)								
320	10321	For exclusive use of manufacturer								
321	10322	For exclusive use of manufacturer								
322	10323	For exclusive use of manufacturer								
323	10324	For exclusive use of manufacturer								
324	10325	For exclusive use of manufacturer								
325	10326	For exclusive use of manufacturer								
326	10327	For exclusive use of manufacturer								
327	10328	For exclusive use of manufacturer								
328	10329	For exclusive use of manufacturer								
329	10330	For exclusive use of manufacturer								
330	10331	For exclusive use of manufacturer								
331	10332	For exclusive use of manufacturer								
332	10333	For exclusive use of manufacturer								
333	10334	For exclusive use of manufacturer								
334	10335	For exclusive use of manufacturer								
335	10336	For exclusive use of manufacturer								
336	10337	For exclusive use of manufacturer								
337	10338	For exclusive use of manufacturer								
338	10339	For exclusive use of manufacturer								
339	10340	For exclusive use of manufacturer								
340	10341	For exclusive use of manufacturer								
341	10342	For exclusive use of manufacturer								
342	10343	For exclusive use of manufacturer								
343	10344	For exclusive use of manufacturer								
344	10345	For exclusive use of manufacturer								
345	10346	For exclusive use of manufacturer								
346	10347	For exclusive use of manufacturer								
347	10348	For exclusive use of manufacturer								
348	10349	For exclusive use of manufacturer								
349	10350	For exclusive use of manufacturer								
350	10351	For exclusive use of manufacturer								
351	10352	For exclusive use of manufacturer								
352	10353	RUN status		On	Off	0	1	ON/OFF	Digital Input	
353	10354	ALARM status		On	Off	0	1	ON/OFF	Digital Input	
354	10355	Fixed red LED: Status of stage 4 left LED		On	Off	0	1	ON/OFF	Digital Input	
355	10356	Fixed red LED: Status of stage 4 middle LED		On	Off	0	1	ON/OFF	Digital Input	
356	10357	Fixed red LED: Status of stage 4 right LED		On	Off	0	1	ON/OFF	Digital Input	
357	10358	Variable (R) LED: Status of stage 1 left LED		On	Off	0	1	ON/OFF	Digital Input	
358	10359	Variable (G) LED: Status of stage 1 left LED		On	Off	0	1	ON/OFF	Digital Input	
359	10360	For exclusive use of manufacturer								
360	10361	Variable (R) LED: Status of stage 1 middle LED		On	Off	0	1	ON/OFF	Digital Input	
361	10362	Variable (G) LED: Status of stage 1 middle LED		On	Off	0	1	ON/OFF	Digital Input	
362	10363	Variable (R) LED: Status of stage 1 right LED		On	Off	0	1	ON/OFF	Digital Input	
363	10364	Variable (G) LED: Status of stage 1 right LED		On	Off	0	1	ON/OFF	Digital Input	
364	10365	Variable (R) LED: Status of stage 2 left LED		On	Off	0	1	ON/OFF	Digital Input	
365	10366	Variable (G) LED: Status of stage 2 left LED		On	Off	0	1	ON/OFF	Digital Input	
366	10367	Variable (R) LED: Status of stage 2 middle LED		On	Off	0	1	ON/OFF	Digital Input	
367	10368	Variable (G) LED: Status of stage 2 middle LED		On	Off	0	1	ON/OFF	Digital Input	
368	10369	Variable (R) LED: Status of stage 2 right LED		On	Off	0	1	ON/OFF	Digital Input	
369	10370	Variable (G) LED: Status of stage 2 right LED		On	Off	0	1	ON/OFF	Digital Input	
370	10371	Variable (R) LED: Status of stage 3 left LED		On	Off	0	1	ON/OFF	Digital Input	
371	10372	Variable (G) LED: Status of stage 3 left LED		On	Off	0	1	ON/OFF	Digital Input	
372	10373	Variable (R) LED: Status of stage 3 middle LED		On	Off	0	1	ON/OFF	Digital Input	
373	10374	Variable (G) LED: Status of stage 3 middle LED		On	Off	0	1	ON/OFF	Digital Input	
374	10375	Variable (R) LED: Status of stage 3 right LED		On	Off	0	1	ON/OFF	Digital Input	
375	10376	Variable (G) LED: Status of stage 3 right LED		On	Off	0	1	ON/OFF	Digital Input	
376	10377	For exclusive use of manufacturer								
377	10378	For exclusive use of manufacturer								
378	10379	For exclusive use of manufacturer								
379	10380	For exclusive use of manufacturer								
380	10381	For exclusive use of manufacturer								
381	10382	For exclusive use of manufacturer								
382	10383	For exclusive use of manufacturer								
383	10384	For exclusive use of manufacturer								



Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
384	2	10385	Overcurrent time limit (51) element: Stage 1: Phase A confirmation	On	Off	0	1	ON/OFF	Digital Input	With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
385		10386	Overcurrent time limit (51) element: Stage 1: Phase B confirmation	On	Off	0	1	ON/OFF	Digital Input	
386		10387	Overcurrent time limit (51) element: Stage 1: Phase C confirmation	On	Off	0	1	ON/OFF	Digital Input	
387		10388	Overcurrent instantaneous (50) element: Stage 1: Zero phase confirmation	On	Off	0	1	ON/OFF	Digital Input	
388		10389	Overcurrent time limit (51) element: Stage 2: Phase A confirmation	On	Off	0	1	ON/OFF	Digital Input	
389		10390	Overcurrent time limit (51) element: Stage 2: Phase B confirmation	On	Off	0	1	ON/OFF	Digital Input	
390		10391	Overcurrent time limit (51) element: Stage 2: Phase C confirmation	On	Off	0	1	ON/OFF	Digital Input	
391		10392	Overcurrent instantaneous (50) element: Stage 2: Zero phase confirmation	On	Off	0	1	ON/OFF	Digital Input	
392		10393	Overcurrent instantaneous (50) element: Stage 3: Phase A confirmation	On	Off	0	1	ON/OFF	Digital Input	
393		10394	Overcurrent instantaneous (50) element: Stage 3: Phase B confirmation	On	Off	0	1	ON/OFF	Digital Input	
394		10395	Overcurrent instantaneous (50) element: Stage 3: Phase C confirmation	On	Off	0	1	ON/OFF	Digital Input	
395		10396	Negative phase overcurrent (46) element: Stage 1 confirmation	On	Off	0	1	ON/OFF	Digital Input	
396		10397	Negative phase overcurrent (46) element: Stage 2 confirmation	On	Off	0	1	ON/OFF	Digital Input	
397		10398	Negative phase overcurrent (single-phase open phase) element: Stage 3 confirmation	On	Off	0	1	ON/OFF	Digital Input	
398		10399	Undercurrent (37) element: Stage 1: Phase A	On	Off	0	1	ON/OFF	Digital Input	
399		10400	Undercurrent (37) element: Stage 1: Phase B	On	Off	0	1	ON/OFF	Digital Input	
400		10401	Undercurrent (37) element: Stage 1: Phase C	On	Off	0	1	ON/OFF	Digital Input	
401		10402	Undercurrent (37) element: Stage 2: Phase A	On	Off	0	1	ON/OFF	Digital Input	
402		10403	Undercurrent (37) element: Stage 2: Phase B	On	Off	0	1	ON/OFF	Digital Input	
403		10404	Undercurrent (37) element: Stage 2: Phase C	On	Off	0	1	ON/OFF	Digital Input	
404		10405	Overcurrent (50BF) element for CBF detection: Phase A confirmation	On	Off	0	1	ON/OFF	Digital Input	
405		10406	Overcurrent (50BF) element for CBF detection: Phase B confirmation	On	Off	0	1	ON/OFF	Digital Input	
406		10407	Overcurrent (50BF) element for CBF detection: Phase C confirmation	On	Off	0	1	ON/OFF	Digital Input	
407		10408	Overcurrent (50BF) element for CBF detection: G phase confirmation	On	Off	0	1	ON/OFF	Digital Input	
408		10409	Overload (49) element: Confirmation	On	Off	0	1	ON/OFF	Digital Input	
409		10410	Ground directional instantaneous (67G) element: Stage 1 confirmation	On	Off	0	1	ON/OFF	Digital Input	
410		10411	Ground directional instantaneous (67G) element: Stage 2 confirmation	On	Off	0	1	ON/OFF	Digital Input	
411		10412	Underpower (37P) element: Stage 1 confirmation	On	Off	0	1	ON/OFF	Digital Input	
412		10413	Underpower (37P) element: Stage 2 confirmation	On	Off	0	1	ON/OFF	Digital Input	
413		10414	Undervoltage (27) element: Stage 1: Phase A (phase AB) confirmation	On	Off	0	1	ON/OFF	Digital Input	
414		10415	Undervoltage (27) element: Stage 1: Phase B (phase BC) confirmation	On	Off	0	1	ON/OFF	Digital Input	
415		10416	Undervoltage (27) element: Stage 1: Phase C (phase CA) confirmation	On	Off	0	1	ON/OFF	Digital Input	
416		10417	Undervoltage (27) element: Stage 2: Phase A (phase AB) confirmation	On	Off	0	1	ON/OFF	Digital Input	
417		10418	Undervoltage (27) element: Stage 2: Phase B (phase BC) confirmation	On	Off	0	1	ON/OFF	Digital Input	
418		10419	Undervoltage (27) element: Stage 2: Phase C (phase CA) confirmation	On	Off	0	1	ON/OFF	Digital Input	
419		10420	Overvoltage (59) element: Stage 1: Phase A (phase AB) confirmation	On	Off	0	1	ON/OFF	Digital Input	
420		10421	Overvoltage (59) element: Stage 1: Phase B (phase BC) confirmation	On	Off	0	1	ON/OFF	Digital Input	
421		10422	Overvoltage (59) element: Stage 1: Phase C (phase CA) confirmation	On	Off	0	1	ON/OFF	Digital Input	
422		10423	Overvoltage (59) element: Stage 2: Phase A (phase AB) confirmation	On	Off	0	1	ON/OFF	Digital Input	
423		10424	Overvoltage (59) element: Stage 2: Phase B (phase BC) confirmation	On	Off	0	1	ON/OFF	Digital Input	
424		10425	Overvoltage (59) element: Stage 2: Phase C (phase CA) confirmation	On	Off	0	1	ON/OFF	Digital Input	
425		10426	Ground overvoltage (64G) element: Stage 1	On	Off	0	1	ON/OFF	Digital Input	
426		10427	Ground overvoltage (64G) element: Stage 2	On	Off	0	1	ON/OFF	Digital Input	
427		10428	Negative phase overvoltage (47) element: Stage 1 confirmation	On	Off	0	1	ON/OFF	Digital Input	
428		10429	Negative phase overvoltage (47) element: Stage 2 confirmation	On	Off	0	1	ON/OFF	Digital Input	
429		10430	Frequency (81) element UV element for locking	On	Off	0	1	ON/OFF	Digital Input	
430	10431	Frequency decrease detection (81UF) element: Stage 1 confirmation	On	Off	0	1	ON/OFF	Digital Input		
431	10432	Frequency decrease detection (81UF) element: Stage 2 confirmation	On	Off	0	1	ON/OFF	Digital Input		
432	10433	Frequency decrease detection (81UF) element: Stage 3 confirmation	On	Off	0	1	ON/OFF	Digital Input		
433	10434	Frequency increase detection (81OF) element: Stage 1 confirmation	On	Off	0	1	ON/OFF	Digital Input		
434	10435	Frequency increase detection (81OF) element: Stage 2 confirmation	On	Off	0	1	ON/OFF	Digital Input		
435	10436	Frequency increase detection (81OF) element: Stage 3 confirmation	On	Off	0	1	ON/OFF	Digital Input		
436	10437	Starting count limitation (66) element: Stage 1	On	Off	0	1	ON/OFF	Digital Input		
437	10438	Starting count limitation (66) element: Stage 2	On	Off	0	1	ON/OFF	Digital Input		
438	10439	(Reserved)								
439	10440	(Reserved)								
440	10441	(Reserved)								
441	10442	VTF element: Confirmation	On	Off	0	1	ON/OFF	Digital Input		
442	10443	For exclusive use of manufacturer								
443	10444	For exclusive use of manufacturer								
444	10445	For exclusive use of manufacturer								
445	10446	For exclusive use of manufacturer								
446	10447	For exclusive use of manufacturer								
447	10448	For exclusive use of manufacturer								
448	10449	Trip counter ALARM	On	Off	0	1	ON/OFF	Digital Input		
449	10450	For exclusive use of manufacturer								
450	10451	Zero phase voltage monitor: Confirmation	On	Off	0	1	ON/OFF	Digital Input		
451	10452	Zero phase current monitor: Confirmation (if residual type)	On	Off	0	1	ON/OFF	Digital Input		
452	10453	(Reserved)								
453	10454	(Reserved)								
454	10455	(Reserved)								
455	10456	(Reserved)								
456	10457	(Reserved)								
457	10458	(Reserved)								
458	10459	(Reserved)								
459	10460	(Reserved)								
460	10461	Motor operating time ALARM	On	Off	0	1	ON/OFF	Digital Input		
461	10462	(Reserved)								
462	10463	(Reserved)								
463	10464	(Reserved)								
464	10465	For exclusive use of manufacturer								
465	10466	For exclusive use of manufacturer								
466	10467	For exclusive use of manufacturer								
467	10468	For exclusive use of manufacturer								

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
468	2	10469	For exclusive use of manufacturer							
469		10470	For exclusive use of manufacturer							
470		10471	For exclusive use of manufacturer							
471		10472	For exclusive use of manufacturer							
472		10473	For exclusive use of manufacturer							
473		10474	For exclusive use of manufacturer							
474		10475	For exclusive use of manufacturer							
475		10476	For exclusive use of manufacturer							
476		10477	For exclusive use of manufacturer							
477		10478	For exclusive use of manufacturer							
478		10479	For exclusive use of manufacturer							
479		10480	For exclusive use of manufacturer							
480		10481	(Reserved)							
481		10482	(Reserved)							
482		10483	(Reserved)							
483		10484	(Reserved)							
484		10485	(Reserved)							
485		10486	(Reserved)							
486		10487	(Reserved)							
487		10488	(Reserved)							
488		10489	(Reserved)							
489		10490	(Reserved)							
490		10491	(Reserved)							
491		10492	(Reserved)							
492		10493	(Reserved)							
493		10494	(Reserved)							
494		10495	(Reserved)							
495		10496	(Reserved)							
496		10497	(Reserved)							
497		10498	For exclusive use of manufacturer							
498		10499	For exclusive use of manufacturer							
499		10500	For exclusive use of manufacturer							
500		10501	For exclusive use of manufacturer							
501		10502	For exclusive use of manufacturer							
502		10503	For exclusive use of manufacturer							
503		10504	For exclusive use of manufacturer							
504		10505	For exclusive use of manufacturer							
505		10506	For exclusive use of manufacturer							
506		10507	For exclusive use of manufacturer							
507		10508	For exclusive use of manufacturer							
508		10509	For exclusive use of manufacturer							
509		10510	For exclusive use of manufacturer							
510		10511	For exclusive use of manufacturer							
511		10512	For exclusive use of manufacturer							
512		10513	For exclusive use of manufacturer							
513		10514	For exclusive use of manufacturer							
514		10515	For exclusive use of manufacturer							
515		10516	For exclusive use of manufacturer							
516		10517	For exclusive use of manufacturer							
517		10518	For exclusive use of manufacturer							
518		10519	For exclusive use of manufacturer							
519		10520	For exclusive use of manufacturer							
520		10521	For exclusive use of manufacturer							
521		10522	For exclusive use of manufacturer							
522		10523	For exclusive use of manufacturer							
523		10524	For exclusive use of manufacturer							
524		10525	For exclusive use of manufacturer							
525		10526	For exclusive use of manufacturer							
526		10527	For exclusive use of manufacturer							
527		10528	(Reserved)							
528		10529	(Reserved)							
529		10530	(Reserved)							
530		10531	(Reserved)							
531		10532	(Reserved)							
532		10533	(Reserved)							
533		10534	(Reserved)							
534		10535	(Reserved)							
535		10536	(Reserved)							
536		10537	(Reserved)							
537		10538	(Reserved)							
538		10539	(Reserved)							
539		10540	(Reserved)							
540		10541	(Reserved)							
541		10542	(Reserved)							
542		10543	(Reserved)							
543		10544	(Reserved)							
544		10545	For exclusive use of manufacturer							
545		10546	For exclusive use of manufacturer							
546		10547	For exclusive use of manufacturer							
547		10548	For exclusive use of manufacturer							
548		10549	For exclusive use of manufacturer							
549		10550	For exclusive use of manufacturer							
550		10551	For exclusive use of manufacturer							
551		10552	For exclusive use of manufacturer							
552		10553	For exclusive use of manufacturer							
553		10554	For exclusive use of manufacturer							
554		10555	For exclusive use of manufacturer							
555		10556	For exclusive use of manufacturer							
556		10557	For exclusive use of manufacturer							
557		10558	For exclusive use of manufacturer							
558		10559	For exclusive use of manufacturer							
559		10560	For exclusive use of manufacturer							
560		10561	For exclusive use of manufacturer							
561		10562	For exclusive use of manufacturer							
562		10563	For exclusive use of manufacturer							
563		10564	For exclusive use of manufacturer							
564		10565	For exclusive use of manufacturer							
565		10566	For exclusive use of manufacturer							
566		10567	For exclusive use of manufacturer							
567		10568	For exclusive use of manufacturer							
568		10569	For exclusive use of manufacturer							
569		10570	For exclusive use of manufacturer							
570		10571	For exclusive use of manufacturer							
571		10572	For exclusive use of manufacturer							
572		10573	For exclusive use of manufacturer							
573		10574	For exclusive use of manufacturer							
574		10575	For exclusive use of manufacturer							
575		10576	For exclusive use of manufacturer							
576		10577	For exclusive use of manufacturer							
577		10578	For exclusive use of manufacturer							
578		10579	For exclusive use of manufacturer							
579		10580	For exclusive use of manufacturer							
580		10581	For exclusive use of manufacturer							
581		10582	For exclusive use of manufacturer							
582		10583	For exclusive use of manufacturer							
583		10584	For exclusive use of manufacturer							
584		10585	For exclusive use of manufacturer							
585		10586	For exclusive use of manufacturer							
586		10587	For exclusive use of manufacturer							
587		10588	For exclusive use of manufacturer							
588		10589	For exclusive use of manufacturer							
589		10590	For exclusive use of manufacturer							
590		10591	For exclusive use of manufacturer							
591		10592	For exclusive use of manufacturer							
592		10593	For exclusive use of manufacturer							
593		10594	For exclusive use of manufacturer							
594		10595	For exclusive use of manufacturer							
595		10596	For exclusive use of manufacturer							
596		10597	For exclusive use of manufacturer							
597		10598	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
598	2	10599	(Reserved)							
599		10600	(Reserved)							
600		10601	For exclusive use of manufacturer							
601		10602	(Reserved)							
602		10603	(Reserved)							
603		10604	(Reserved)							
604		10605	(Reserved)							
605		10606	(Reserved)							
606		10607	(Reserved)							
607		10608	For exclusive use of manufacturer							
608		10609	For exclusive use of manufacturer							
609		10610	For exclusive use of manufacturer							
610		10611	For exclusive use of manufacturer							
611		10612	For exclusive use of manufacturer							
612		10613	For exclusive use of manufacturer							
613		10614	(Reserved)							
614		10615	(Reserved)							
615		10616	(Reserved)							
616		10617	(Reserved)							
617		10618	(Reserved)							
618		10619	(Reserved)							
619		10620	(Reserved)							
620		10621	(Reserved)							
621		10622	(Reserved)							
622		10623	(Reserved)							
623		10624	(Reserved)							
624		10625	For exclusive use of manufacturer							
625		10626	For exclusive use of manufacturer							
626		10627	(Reserved)							
627		10628	(Reserved)							
628		10629	(Reserved)							
629		10630	(Reserved)							
630		10631	(Reserved)							
631		10632	(Reserved)							
632		10633	(Reserved)							
633		10634	(Reserved)							
634		10635	(Reserved)							
635		10636	(Reserved)							
636		10637	(Reserved)							
637		10638	(Reserved)							
638		10639	(Reserved)							
639		10640	(Reserved)							
640		10641	For exclusive use of manufacturer							
641		10642	(Reserved)							
642		10643	(Reserved)							
643		10644	(Reserved)							
644		10645	(Reserved)							
645		10646	(Reserved)							
646		10647	(Reserved)							
647		10648	(Reserved)							
648		10649	(Reserved)							
649		10650	(Reserved)							
650		10651	(Reserved)							
651		10652	(Reserved)							
652		10653	(Reserved)							
653		10654	(Reserved)							
654		10655	(Reserved)							
655		10656	(Reserved)							
656		10657	(Reserved)							
657		10658	(Reserved)							
658		10659	(Reserved)							
659		10660	(Reserved)							
660		10661	For exclusive use of manufacturer							
661		10662	For exclusive use of manufacturer							
662		10663	For exclusive use of manufacturer							
663		10664	(Reserved)							
664		10665	(Reserved)							
665		10666	(Reserved)							
666		10667	(Reserved)							
667		10668	(Reserved)							
668		10669	For exclusive use of manufacturer							
669		10670	(Reserved)							
670		10671	(Reserved)							
671		10672	(Reserved)							
672		10673	For exclusive use of manufacturer							
673		10674	For exclusive use of manufacturer							
674		10675	For exclusive use of manufacturer							
675		10676	For exclusive use of manufacturer							
676		10677	For exclusive use of manufacturer							
677		10678	For exclusive use of manufacturer							
678		10679	For exclusive use of manufacturer							
679		10680	For exclusive use of manufacturer							
680		10681	For exclusive use of manufacturer							
681		10682	For exclusive use of manufacturer							
682		10683	For exclusive use of manufacturer							
683		10684	For exclusive use of manufacturer							
684		10685	For exclusive use of manufacturer							
685		10686	For exclusive use of manufacturer							
686		10687	For exclusive use of manufacturer							
687		10688	(Reserved)							
688		10689	(Reserved)							
689		10690	(Reserved)							
690		10691	(Reserved)							
691		10692	(Reserved)							
692		10693	(Reserved)							
693		10694	(Reserved)							
694		10695	(Reserved)							
695		10696	(Reserved)							
696		10697	(Reserved)							
697		10698	(Reserved)							
698		10699	(Reserved)							
699		10700	(Reserved)							
700		10701	(Reserved)							
701		10702	(Reserved)							
702		10703	(Reserved)							
703		10704	(Reserved)							
704		10705	For exclusive use of manufacturer							
705		10706	For exclusive use of manufacturer							
706		10707	For exclusive use of manufacturer							
707		10708	For exclusive use of manufacturer							
708		10709	For exclusive use of manufacturer							
709		10710	For exclusive use of manufacturer							
710		10711	For exclusive use of manufacturer							
711		10712	For exclusive use of manufacturer							
712		10713	For exclusive use of manufacturer							
713		10714	For exclusive use of manufacturer							
714		10715	For exclusive use of manufacturer							
715		10716	For exclusive use of manufacturer							
716		10717	For exclusive use of manufacturer							
717		10718	(Reserved)							
718		10719	(Reserved)							
719		10720	(Reserved)							
720		10721	(Reserved)							
721		10722	(Reserved)							
722		10723	(Reserved)							
723		10724	(Reserved)							
724		10725	(Reserved)							
725		10726	(Reserved)							
726		10727	(Reserved)							
727		10728	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
728	2	10729	(Reserved)							
729		10730	(Reserved)							
730		10731	(Reserved)							
731		10732	(Reserved)							
732		10733	(Reserved)							
733		10734	(Reserved)							
734		10735	(Reserved)							
735		10736	(Reserved)							
736		10737	(Reserved)							
737		10738	(Reserved)							
738		10739	(Reserved)							
739		10740	(Reserved)							
740		10741	(Reserved)							
741		10742	(Reserved)							
742		10743	(Reserved)							
743		10744	(Reserved)							
744		10745	(Reserved)							
745		10746	(Reserved)							
746		10747	(Reserved)							
747		10748	(Reserved)							
748		10749	(Reserved)							
749		10750	(Reserved)							
750		10751	(Reserved)							
751		10752	(Reserved)							
752		10753	(Reserved)							
753		10754	(Reserved)							
754		10755	(Reserved)							
755		10756	(Reserved)							
756		10757	(Reserved)							
757		10758	(Reserved)							
758		10759	(Reserved)							
759		10760	(Reserved)							
760		10761	(Reserved)							
761		10762	(Reserved)							
762		10763	(Reserved)							
763		10764	(Reserved)							
764		10765	(Reserved)							
765		10766	(Reserved)							
766		10767	(Reserved)							
767		10768	(Reserved)							
768		10769	(Reserved)							
769		10770	(Reserved)							
770		10771	(Reserved)							
771		10772	(Reserved)							
772		10773	(Reserved)							
773		10774	(Reserved)							
774		10775	(Reserved)							
775		10776	(Reserved)							
776		10777	(Reserved)							
777		10778	(Reserved)							
778		10779	(Reserved)							
779		10780	(Reserved)							
780		10781	(Reserved)							
781		10782	(Reserved)							
782		10783	(Reserved)							
783		10784	(Reserved)							
784		10785	For exclusive use of manufacturer							
785		10786	For exclusive use of manufacturer							
786		10787	For exclusive use of manufacturer							
787		10788	For exclusive use of manufacturer							
788		10789	For exclusive use of manufacturer							
789		10790	For exclusive use of manufacturer							
790		10791	For exclusive use of manufacturer							
791		10792	For exclusive use of manufacturer							
792		10793	(Reserved)							
793		10794	(Reserved)							
794		10795	(Reserved)							
795		10796	(Reserved)							
796		10797	(Reserved)							
797		10798	(Reserved)							
798		10799	(Reserved)							
799		10800	(Reserved)							
800		10801	For exclusive use of manufacturer							
801		10802	For exclusive use of manufacturer							
802		10803	For exclusive use of manufacturer							
803		10804	For exclusive use of manufacturer							
804		10805	For exclusive use of manufacturer							
805		10806	For exclusive use of manufacturer							
806		10807	For exclusive use of manufacturer							
807		10808	For exclusive use of manufacturer							
808		10809	For exclusive use of manufacturer							
809		10810	For exclusive use of manufacturer							
810		10811	For exclusive use of manufacturer							
811		10812	For exclusive use of manufacturer							
812		10813	For exclusive use of manufacturer							
813		10814	For exclusive use of manufacturer							
814		10815	For exclusive use of manufacturer							
815		10816	For exclusive use of manufacturer							
816		10817	For exclusive use of manufacturer							
817		10818	For exclusive use of manufacturer							
818		10819	For exclusive use of manufacturer							
819		10820	For exclusive use of manufacturer							
820		10821	For exclusive use of manufacturer							
821		10822	For exclusive use of manufacturer							
822		10823	For exclusive use of manufacturer							
823		10824	For exclusive use of manufacturer							
824		10825	For exclusive use of manufacturer							
825		10826	For exclusive use of manufacturer							
826		10827	For exclusive use of manufacturer							
827		10828	For exclusive use of manufacturer							
828		10829	For exclusive use of manufacturer							
829		10830	For exclusive use of manufacturer							
830		10831	For exclusive use of manufacturer							
831		10832	For exclusive use of manufacturer							
832		10833	For exclusive use of manufacturer							
833		10834	For exclusive use of manufacturer							
834		10835	For exclusive use of manufacturer							
835		10836	For exclusive use of manufacturer							
836		10837	For exclusive use of manufacturer							
837		10838	For exclusive use of manufacturer							
838		10839	For exclusive use of manufacturer							
839		10840	For exclusive use of manufacturer							
840		10841	For exclusive use of manufacturer							
841		10842	For exclusive use of manufacturer							
842		10843	For exclusive use of manufacturer							
843		10844	For exclusive use of manufacturer							
844		10845	For exclusive use of manufacturer							
845		10846	For exclusive use of manufacturer							
846		10847	For exclusive use of manufacturer							
847		10848	(Reserved)							
848		10849	(Reserved)							
849		10850	(Reserved)							
850		10851	(Reserved)							
851		10852	(Reserved)							
852		10853	(Reserved)							
853		10854	(Reserved)							
854		10855	(Reserved)							
855		10856	(Reserved)							
856		10857	(Reserved)							
857		10858	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
858	2	10859	(Reserved)							
859		10860	(Reserved)							
860		10861	(Reserved)							
861		10862	(Reserved)							
862		10863	(Reserved)							
863		10864	(Reserved)							
864		10865	(Reserved)							
865		10866	(Reserved)							
866		10867	(Reserved)							
867		10868	(Reserved)							
868		10869	(Reserved)							
869		10870	(Reserved)							
870		10871	(Reserved)							
871		10872	(Reserved)							
872		10873	(Reserved)							
873		10874	(Reserved)							
874		10875	(Reserved)							
875		10876	(Reserved)							
876		10877	(Reserved)							
877		10878	(Reserved)							
878		10879	(Reserved)							
879		10880	(Reserved)							
880		10881	(Reserved)							
881		10882	(Reserved)							
882		10883	(Reserved)							
883		10884	(Reserved)							
884		10885	(Reserved)							
885		10886	(Reserved)							
886		10887	(Reserved)							
887		10888	(Reserved)							
888		10889	(Reserved)							
889		10890	(Reserved)							
890		10891	(Reserved)							
891		10892	(Reserved)							
892		10893	(Reserved)							
893		10894	(Reserved)							
894		10895	(Reserved)							
895		10896	(Reserved)							
896		10897	For exclusive use of manufacturer							
897		10898	For exclusive use of manufacturer							
898		10899	For exclusive use of manufacturer							
899		10900	For exclusive use of manufacturer							
900		10901	For exclusive use of manufacturer							
901		10902	For exclusive use of manufacturer							
902		10903	For exclusive use of manufacturer							
903		10904	For exclusive use of manufacturer							
904		10905	For exclusive use of manufacturer							
905		10906	For exclusive use of manufacturer							
906		10907	For exclusive use of manufacturer							
907		10908	For exclusive use of manufacturer							
908		10909	For exclusive use of manufacturer							
909		10910	For exclusive use of manufacturer							
910		10911	For exclusive use of manufacturer							
911		10912	For exclusive use of manufacturer							
912		10913	For exclusive use of manufacturer							
913		10914	For exclusive use of manufacturer							
914		10915	For exclusive use of manufacturer							
915		10916	For exclusive use of manufacturer							
916		10917	For exclusive use of manufacturer							
917		10918	For exclusive use of manufacturer							
918		10919	For exclusive use of manufacturer							
919		10920	For exclusive use of manufacturer							
920		10921	For exclusive use of manufacturer							
921		10922	For exclusive use of manufacturer							
922		10923	For exclusive use of manufacturer							
923		10924	For exclusive use of manufacturer							
924		10925	For exclusive use of manufacturer							
925		10926	For exclusive use of manufacturer							
926		10927	For exclusive use of manufacturer							
927		10928	For exclusive use of manufacturer							
928		10929	For exclusive use of manufacturer							
929		10930	For exclusive use of manufacturer							
930		10931	For exclusive use of manufacturer							
931		10932	For exclusive use of manufacturer							
932		10933	For exclusive use of manufacturer							
933		10934	For exclusive use of manufacturer							
934		10935	For exclusive use of manufacturer							
935		10936	For exclusive use of manufacturer							
936		10937	For exclusive use of manufacturer							
937		10938	For exclusive use of manufacturer							
938		10939	For exclusive use of manufacturer							
939		10940	(Reserved)							
940		10941	(Reserved)							
941		10942	(Reserved)							
942		10943	(Reserved)							
943		10944	For exclusive use of manufacturer							
944		10945	For exclusive use of manufacturer							
945		10946	For exclusive use of manufacturer							
946		10947	For exclusive use of manufacturer							
947		10948	For exclusive use of manufacturer							
948		10949	For exclusive use of manufacturer							
949		10950	For exclusive use of manufacturer							
950		10951	For exclusive use of manufacturer							
951		10952	For exclusive use of manufacturer							
952		10953	For exclusive use of manufacturer							
953		10954	For exclusive use of manufacturer							
954		10955	For exclusive use of manufacturer							
955		10956	For exclusive use of manufacturer							
956		10957	For exclusive use of manufacturer							
957		10958	For exclusive use of manufacturer							
958		10959	For exclusive use of manufacturer							
959		10960	For exclusive use of manufacturer							
960		10961	For exclusive use of manufacturer							
961		10962	For exclusive use of manufacturer							
962		10963	For exclusive use of manufacturer							
963		10964	For exclusive use of manufacturer							
964		10965	For exclusive use of manufacturer							
965		10966	For exclusive use of manufacturer							
966		10967	For exclusive use of manufacturer							
967		10968	For exclusive use of manufacturer							
968		10969	For exclusive use of manufacturer							
969		10970	For exclusive use of manufacturer							
970		10971	For exclusive use of manufacturer							
971		10972	For exclusive use of manufacturer							
972		10973	For exclusive use of manufacturer							
973		10974	For exclusive use of manufacturer							
974		10975	For exclusive use of manufacturer							
975		10976	For exclusive use of manufacturer							
976		10977	For exclusive use of manufacturer							
977		10978	For exclusive use of manufacturer							
978		10979	For exclusive use of manufacturer							
979		10980	(Reserved)							
980		10981	(Reserved)							
981		10982	(Reserved)							
982		10983	(Reserved)							
983		10984	(Reserved)							
984		10985	(Reserved)							
985		10986	(Reserved)							
986		10987	(Reserved)							
987		10988	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
988	2	10989	(Reserved)							
989		10990	(Reserved)							
990		10991	(Reserved)							
991		10992	For exclusive use of manufacturer							
992		10993	(Reserved)							
993		10994	(Reserved)							
994		10995	(Reserved)							
995		10996	(Reserved)							
996		10997	(Reserved)							
997		10998	(Reserved)							
998		10999	(Reserved)							
999		11000	(Reserved)							
1000		11001	(Reserved)							
1001		11002	(Reserved)							
1002		11003	(Reserved)							
1003		11004	(Reserved)							
1004		11005	(Reserved)							
1005		11006	(Reserved)							
1006		11007	(Reserved)							
1007		11008	(Reserved)							
1008		11009	For exclusive use of manufacturer							
1009		11010	For exclusive use of manufacturer							
1010		11011	For exclusive use of manufacturer							
1011		11012	For exclusive use of manufacturer							
1012		11013	For exclusive use of manufacturer							
1013		11014	For exclusive use of manufacturer							
1014		11015	(Reserved)							
1015		11016	(Reserved)							
1016		11017	(Reserved)							
1017		11018	(Reserved)							
1018		11019	(Reserved)							
1019		11020	(Reserved)							
1020		11021	(Reserved)							
1021		11022	(Reserved)							
1022		11023	(Reserved)							
1023		11024	(Reserved)							
1024		11025	For exclusive use of manufacturer							
1025		11026	For exclusive use of manufacturer							
1026		11027	For exclusive use of manufacturer							
1027		11028	For exclusive use of manufacturer							
1028		11029	For exclusive use of manufacturer							
1029		11030	For exclusive use of manufacturer							
1030		11031	(Reserved)							
1031		11032	(Reserved)							
1032		11033	(Reserved)							
1033		11034	(Reserved)							
1034		11035	(Reserved)							
1035		11036	(Reserved)							
1036		11037	(Reserved)							
1037		11038	(Reserved)							
1038		11039	(Reserved)							
1039		11040	(Reserved)							
1040		11041	(Reserved)							
1041		11042	(Reserved)							
1042		11043	(Reserved)							
1043		11044	(Reserved)							
1044		11045	(Reserved)							
1045		11046	(Reserved)							
1046		11047	(Reserved)							
1047		11048	(Reserved)							
1048		11049	(Reserved)							
1049		11050	(Reserved)							
1050		11051	(Reserved)							
1051		11052	(Reserved)							
1052		11053	(Reserved)							
1053		11054	(Reserved)							
1054		11055	(Reserved)							
1055		11056	(Reserved)							
1056		11057	(Reserved)							
1057		11058	(Reserved)							
1058		11059	(Reserved)							
1059		11060	(Reserved)							
1060		11061	(Reserved)							
1061		11062	(Reserved)							
1062		11063	(Reserved)							
1063		11064	(Reserved)							
1064		11065	(Reserved)							
1065		11066	(Reserved)							
1066		11067	(Reserved)							
1067		11068	(Reserved)							
1068		11069	(Reserved)							
1069		11070	(Reserved)							
1070		11071	(Reserved)							
1071		11072	(Reserved)							
1072		11073	(Reserved)							
1073		11074	(Reserved)							
1074		11075	(Reserved)							
1075		11076	(Reserved)							
1076		11077	(Reserved)							
1077		11078	(Reserved)							
1078		11079	(Reserved)							
1079		11080	(Reserved)							
1080		11081	(Reserved)							
1081		11082	(Reserved)							
1082		11083	(Reserved)							
1083		11084	(Reserved)							
1084		11085	(Reserved)							
1085		11086	(Reserved)							
1086		11087	(Reserved)							
1087		11088	(Reserved)							
1088		11089	(Reserved)							
1089		11090	(Reserved)							
1090		11091	(Reserved)							
1091		11092	(Reserved)							
1092		11093	(Reserved)							
1093		11094	(Reserved)							
1094		11095	(Reserved)							
1095		11096	(Reserved)							
1096		11097	(Reserved)							
1097		11098	(Reserved)							
1098		11099	(Reserved)							
1099		11100	(Reserved)							
1100		11101	(Reserved)							
1101		11102	(Reserved)							
1102		11103	(Reserved)							
1103		11104	(Reserved)							
1104		11105	(Reserved)							
1105		11106	(Reserved)							
1106		11107	(Reserved)							
1107		11108	(Reserved)							
1108		11109	(Reserved)							
1109		11110	(Reserved)							
1110		11111	(Reserved)							
1111		11112	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1112	2	11113	(Reserved)							
1113		11114	(Reserved)							
1114		11115	(Reserved)							
1115		11116	(Reserved)							
1116		11117	(Reserved)							
1117		11118	(Reserved)							
1118		11119	(Reserved)							
1119		11120	(Reserved)							
1120		11121	(Reserved)							
1121		11122	(Reserved)							
1122		11123	(Reserved)							
1123		11124	(Reserved)							
1124		11125	(Reserved)							
1125		11126	(Reserved)							
1126		11127	(Reserved)							
1127		11128	(Reserved)							
1128		11129	(Reserved)							
1129		11130	(Reserved)							
1130		11131	(Reserved)							
1131		11132	(Reserved)							
1132		11133	(Reserved)							
1133		11134	(Reserved)							
1134		11135	(Reserved)							
1135		11136	(Reserved)							
1136		11137	(Reserved)							
1137		11138	(Reserved)							
1138		11139	(Reserved)							
1139		11140	(Reserved)							
1140		11141	(Reserved)							
1141		11142	(Reserved)							
1142		11143	(Reserved)							
1143		11144	(Reserved)							
1144		11145	(Reserved)							
1145		11146	(Reserved)							
1146		11147	(Reserved)							
1147		11148	(Reserved)							
1148		11149	(Reserved)							
1149		11150	(Reserved)							
1150		11151	(Reserved)							
1151		11152	(Reserved)							
1152		11153	(Reserved)							
1153		11154	(Reserved)							
1154		11155	(Reserved)							
1155		11156	(Reserved)							
1156		11157	(Reserved)							
1157		11158	(Reserved)							
1158		11159	(Reserved)							
1159		11160	(Reserved)							
1160		11161	(Reserved)							
1161		11162	(Reserved)							
1162		11163	(Reserved)							
1163		11164	(Reserved)							
1164		11165	(Reserved)							
1165		11166	(Reserved)							
1166		11167	(Reserved)							
1167		11168	(Reserved)							
1168		11169	(Reserved)							
1169		11170	(Reserved)							
1170		11171	(Reserved)							
1171		11172	(Reserved)							
1172		11173	(Reserved)							
1173		11174	(Reserved)							
1174		11175	(Reserved)							
1175		11176	(Reserved)							
1176		11177	(Reserved)							
1177		11178	(Reserved)							
1178		11179	(Reserved)							
1179		11180	(Reserved)							
1180		11181	(Reserved)							
1181		11182	(Reserved)							
1182		11183	(Reserved)							
1183		11184	(Reserved)							
1184		11185	(Reserved)							
1185		11186	(Reserved)							
1186		11187	(Reserved)							
1187		11188	(Reserved)							
1188		11189	(Reserved)							
1189		11190	(Reserved)							
1190		11191	(Reserved)							
1191		11192	(Reserved)							
1192		11193	(Reserved)							
1193		11194	(Reserved)							
1194		11195	(Reserved)							
1195		11196	(Reserved)							
1196		11197	(Reserved)							
1197		11198	(Reserved)							
1198		11199	(Reserved)							
1199		11200	(Reserved)							
1200		11201	For exclusive use of manufacturer							
1201		11202	For exclusive use of manufacturer							
1202		11203	For exclusive use of manufacturer							
1203		11204	For exclusive use of manufacturer							
1204		11205	For exclusive use of manufacturer							
1205		11206	For exclusive use of manufacturer							
1206		11207	For exclusive use of manufacturer							
1207		11208	For exclusive use of manufacturer							
1208		11209	For exclusive use of manufacturer							
1209		11210	(Reserved)							
1210		11211	For exclusive use of manufacturer							
1211		11212	(Reserved)							
1212		11213	(Reserved)							
1213		11214	(Reserved)							
1214		11215	(Reserved)							
1215		11216	(Reserved)							
1216		11217	For exclusive use of manufacturer							
1217		11218	For exclusive use of manufacturer							
1218		11219	For exclusive use of manufacturer							
1219		11220	For exclusive use of manufacturer							
1220		11221	For exclusive use of manufacturer							
1221		11222	For exclusive use of manufacturer							
1222		11223	For exclusive use of manufacturer							
1223		11224	For exclusive use of manufacturer							
1224		11225	For exclusive use of manufacturer							
1225		11226	For exclusive use of manufacturer							
1226		11227	For exclusive use of manufacturer							
1227		11228	For exclusive use of manufacturer							
1228		11229	For exclusive use of manufacturer							
1229		11230	For exclusive use of manufacturer							
1230		11231	For exclusive use of manufacturer							
1231		11232	For exclusive use of manufacturer							
1232		11233	For exclusive use of manufacturer							
1233		11234	For exclusive use of manufacturer							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1234	2	11235	For exclusive use of manufacturer							With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
1235		11236	For exclusive use of manufacturer							
1236		11237	For exclusive use of manufacturer							
1237		11238	For exclusive use of manufacturer							
1238		11239	For exclusive use of manufacturer							
1239		11240	For exclusive use of manufacturer							
1240		11241	For exclusive use of manufacturer							
1241		11242	For exclusive use of manufacturer							
1242		11243	For exclusive use of manufacturer							
1243		11244	For exclusive use of manufacturer							
1244		11245	For exclusive use of manufacturer							
1245		11246	For exclusive use of manufacturer							
1246		11247	For exclusive use of manufacturer							
1247		11248	For exclusive use of manufacturer							
1248		11249	For exclusive use of manufacturer							
1249		11250	For exclusive use of manufacturer							
1250		11251	For exclusive use of manufacturer							
1251		11252	For exclusive use of manufacturer							
1252		11253	For exclusive use of manufacturer							
1253		11254	For exclusive use of manufacturer							
1254		11255	For exclusive use of manufacturer							
1255		11256	For exclusive use of manufacturer							
1256		11257	(Reserved)							
1257		11258	(Reserved)							
1258		11259	(Reserved)							
1259		11260	(Reserved)							
1260		11261	(Reserved)							
1261		11262	(Reserved)							
1262		11263	(Reserved)							
1263		11264	(Reserved)							
1264		11265	For exclusive use of manufacturer							
1265		11266	For exclusive use of manufacturer							
1266		11267	For exclusive use of manufacturer							
1267		11268	For exclusive use of manufacturer							
1268		11269	For exclusive use of manufacturer							
1269		11270	For exclusive use of manufacturer							
1270		11271	For exclusive use of manufacturer							
1271		11272	For exclusive use of manufacturer							
1272		11273	For exclusive use of manufacturer							
1273		11274	For exclusive use of manufacturer							
1274		11275	For exclusive use of manufacturer							
1275		11276	For exclusive use of manufacturer							
1276		11277	For exclusive use of manufacturer							
1277		11278	For exclusive use of manufacturer							
1278		11279	For exclusive use of manufacturer							
1279		11280	For exclusive use of manufacturer							
1280		11281	For exclusive use of manufacturer							
1281		11282	For exclusive use of manufacturer							
1282		11283	For exclusive use of manufacturer							
1283		11284	For exclusive use of manufacturer							
1284		11285	For exclusive use of manufacturer							
1285		11286	For exclusive use of manufacturer							
1286		11287	For exclusive use of manufacturer							
1287		11288	For exclusive use of manufacturer							
1288		11289	For exclusive use of manufacturer							
1289		11290	For exclusive use of manufacturer							
1290		11291	For exclusive use of manufacturer							
1291		11292	For exclusive use of manufacturer							
1292		11293	For exclusive use of manufacturer							
1293		11294	For exclusive use of manufacturer							
1294		11295	For exclusive use of manufacturer							
1295		11296	For exclusive use of manufacturer							
1296		11297	OC1 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1297		11298	OC1 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1298		11299	OC1 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1299		11300	OC1 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1300		11301	OC1 zero phase: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1301		11302	OC2 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1302		11303	OC2 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1303		11304	OC2 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1304		11305	OC2 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1305		11306	OC2 zero phase: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1306		11307	OC3 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1307		11308	OC3 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1308		11309	OC3 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1309		11310	OC3 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1310		11311	OCNEG1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1311		11312	OCNEG2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1312		11313	OCNEG3: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1313		11314	UC1 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1314		11315	UC1 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1315		11316	UC1 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1316		11317	UC1 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1317		11318	UC2 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1318		11319	UC2 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1319		11320	UC2 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1320		11321	UC2 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1321		11322	CBF phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1322		11323	CBF phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1323		11324	CBF phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1324		11325	CBF three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1325		11326	CBF zero phase: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1326		11327	TOL: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1327		11328	DIRG1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1328		11329	DIRG2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1329		11330	UP1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1330		11331	UP2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1331		11332	UV1 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1332		11333	UV1 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1333		11334	UV1 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1334		11335	UV1 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1335		11336	UV2 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1336		11337	UV2 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1337		11338	UV2 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1338		11339	UV2 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1339		11340	OV1 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1340		11341	OV1 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1341		11342	OV1 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1342		11343	OV1 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1343		11344	OV2 phase A: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1344		11345	OV2 phase B: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1345		11346	OV2 phase C: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1346		11347	OV2 three-phase OR: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1347		11348	OVG1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1348		11349	OVG2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1349		11350	OVNEG1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1350		11351	OVNEG2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1351		11352	UF1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1352		11353	UF2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1353		11354	UF3: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1354		11355	OF1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1355		11356	OF2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	



Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1356	2	11357	OF3: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
1357		11358	MST1: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1358		11359	MST2: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1359		11360	VTF: Confirmation forced control	On	Off	x	x	ON/OFF	Digital Input	
1360		11361	For exclusive use of manufacturer							
1361		11362	For exclusive use of manufacturer							
1362		11363	For exclusive use of manufacturer							
1363		11364	For exclusive use of manufacturer							
1364		11365	For exclusive use of manufacturer							
1365		11366	For exclusive use of manufacturer							
1366		11367	For exclusive use of manufacturer							
1367		11368	For exclusive use of manufacturer							
1368		11369	(Reserved)							
1369		11370	(Reserved)							
1370		11371	(Reserved)							
1371		11372	(Reserved)							
1372		11373	(Reserved)							
1373	11374	(Reserved)								
1374	11375	(Reserved)								
1375	11376	(Reserved)								
1376	11377	(Reserved)								
1377	11378	(Reserved)								
1378	11379	(Reserved)								
1379	11380	(Reserved)								
1380	11381	(Reserved)								
1381	11382	(Reserved)								
1382	11383	(Reserved)								
1383	11384	(Reserved)								
1384	11385	(Reserved)								
1385	11386	(Reserved)								
1386	11387	(Reserved)								
1387	11388	(Reserved)								
1388	11389	(Reserved)								
1389	11390	(Reserved)								
1390	11391	(Reserved)								
1391	11392	(Reserved)								
1392	11393	(Reserved)								
1393	11394	(Reserved)								
1394	11395	(Reserved)								
1395	11396	(Reserved)								
1396	11397	(Reserved)								
1397	11398	(Reserved)								
1398	11399	(Reserved)								
1399	11400	(Reserved)								
1400	11401	(Reserved)								
1401	11402	(Reserved)								
1402	11403	(Reserved)								
1403	11404	(Reserved)								
1404	11405	(Reserved)								
1405	11406	(Reserved)								
1406	11407	(Reserved)								
1407	11408	(Reserved)								
1408	11409	(Reserved)								
1409	11410	(Reserved)								
1410	11411	(Reserved)								
1411	11412	(Reserved)								
1412	11413	(Reserved)								
1413	11414	(Reserved)								
1414	11415	(Reserved)								
1415	11416	(Reserved)								
1416	11417	(Reserved)								
1417	11418	(Reserved)								
1418	11419	(Reserved)								
1419	11420	(Reserved)								
1420	11421	(Reserved)								
1421	11422	(Reserved)								
1422	11423	(Reserved)								
1423	11424	(Reserved)								
1424	11425	(Reserved)								
1425	11426	(Reserved)								
1426	11427	(Reserved)								
1427	11428	(Reserved)								
1428	11429	(Reserved)								
1429	11430	(Reserved)								
1430	11431	(Reserved)								
1431	11432	(Reserved)								
1432	11433	(Reserved)								
1433	11434	(Reserved)								
1434	11435	(Reserved)								
1435	11436	(Reserved)								
1436	11437	(Reserved)								
1437	11438	(Reserved)								
1438	11439	(Reserved)								
1439	11440	(Reserved)								
1440	11441	(Reserved)								
1441	11442	(Reserved)								
1442	11443	(Reserved)								
1443	11444	(Reserved)								
1444	11445	(Reserved)								
1445	11446	(Reserved)								
1446	11447	(Reserved)								
1447	11448	(Reserved)								
1448	11449	(Reserved)								
1449	11450	(Reserved)								
1450	11451	(Reserved)								
1451	11452	(Reserved)								
1452	11453	(Reserved)								
1453	11454	(Reserved)								
1454	11455	(Reserved)								
1455	11456	(Reserved)								
1456	11457	(Reserved)								
1457	11458	(Reserved)								
1458	11459	(Reserved)								
1459	11460	(Reserved)								
1460	11461	(Reserved)								
1461	11462	(Reserved)								
1462	11463	(Reserved)								
1463	11464	(Reserved)								
1464	11465	(Reserved)								
1465	11466	(Reserved)								
1466	11467	(Reserved)								
1467	11468	(Reserved)								
1468	11469	(Reserved)								
1469	11470	(Reserved)								
1470	11471	(Reserved)								
1471	11472	(Reserved)								
1472	11473	(Reserved)								
1473	11474	(Reserved)								
1474	11475	(Reserved)								
1475	11476	(Reserved)								
1476	11477	(Reserved)								
1477	11478	(Reserved)								

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1478	2	11479	(Reserved)							With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
1479		11480	(Reserved)							
1480		11481	(Reserved)							
1481		11482	(Reserved)							
1482		11483	(Reserved)							
1483		11484	(Reserved)							
1484		11485	(Reserved)							
1485		11486	(Reserved)							
1486		11487	(Reserved)							
1487		11488	(Reserved)							
1488		11489	(Reserved)							
1489		11490	(Reserved)							
1490		11491	(Reserved)							
1491		11492	(Reserved)							
1492		11493	(Reserved)							
1493		11494	(Reserved)							
1494		11495	(Reserved)							
1495		11496	(Reserved)							
1496		11497	(Reserved)							
1497		11498	(Reserved)							
1498		11499	(Reserved)							
1499		11500	(Reserved)							
1500		11501	(Reserved)							
1501		11502	(Reserved)							
1502		11503	(Reserved)							
1503		11504	(Reserved)							
1504		11505	(Reserved)							
1505		11506	(Reserved)							
1506		11507	(Reserved)							
1507		11508	(Reserved)							
1508		11509	(Reserved)							
1509		11510	(Reserved)							
1510		11511	(Reserved)							
1511		11512	(Reserved)							
1512		11513	(Reserved)							
1513		11514	(Reserved)							
1514		11515	(Reserved)							
1515		11516	(Reserved)							
1516		11517	(Reserved)							
1517		11518	(Reserved)							
1518		11519	(Reserved)							
1519		11520	(Reserved)							
1520		11521	(Reserved)							
1521		11522	(Reserved)							
1522		11523	(Reserved)							
1523		11524	(Reserved)							
1524		11525	(Reserved)							
1525		11526	(Reserved)							
1526		11527	(Reserved)							
1527		11528	(Reserved)							
1528	11529	(Reserved)								
1529	11530	(Reserved)								
1530	11531	(Reserved)								
1531	11532	(Reserved)								
1532	11533	(Reserved)								
1533	11534	(Reserved)								
1534	11535	(Reserved)								
1535	11536	(Reserved)								
1536	11537	(Reserved)								
1537	11538	(Reserved)								
1538	11539	(Reserved)								
1539	11540	(Reserved)								
1540	11541	(Reserved)								
1541	11542	(Reserved)								
1542	11543	(Reserved)								
1543	11544	(Reserved)								
1544	11545	(Reserved)								
1545	11546	(Reserved)								
1546	11547	(Reserved)								
1547	11548	(Reserved)								
1548	11549	(Reserved)								
1549	11550	(Reserved)								
1550	11551	(Reserved)								
1551	11552	(Reserved)								
1552	11553	OC1 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1553	11554	OC1 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1554	11555	OC1 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1555	11556	OC1 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1556	11557	OC1 zero phase: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1557	11558	OC2 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1558	11559	OC2 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1559	11560	OC2 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1560	11561	OC2 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1561	11562	OC2 zero phase: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1562	11563	OC3 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1563	11564	OC3 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1564	11565	OC3 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1565	11566	OC3 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1566	11567	OCNEG1: Confirmation & forced relay control signal	On	Off	x	x	ON/OFF	Digital Input		
1567	11568	OCNEG2: Confirmation & forced relay control signal	On	Off	x	x	ON/OFF	Digital Input		
1568	11569	OCNEG3: Confirmation & forced relay control signal	On	Off	x	x	ON/OFF	Digital Input		
1569	11570	UC1 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1570	11571	UC1 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1571	11572	UC1 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1572	11573	UC1 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1573	11574	UC2 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1574	11575	UC2 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1575	11576	UC2 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1576	11577	UC2 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1577	11578	CBF phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1578	11579	CBF phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1579	11580	CBF phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1580	11581	CBF three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1581	11582	CBF zero phase: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1582	11583	TOL: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1583	11584	DIRG1: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1584	11585	DIRG2: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1585	11586	UP1: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1586	11587	UP2: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1587	11588	UV1 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1588	11589	UV1 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1589	11590	UV1 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks	
1590	2	11591	UV1 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input	With a "DIGITAL I/O" request from the master station as Function Code: 2, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 10001+16*i • Number of access points = 16*j • i+j<=125 (i=0 to 124, j=1 to 125) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.	
1591		11592	UV2 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1592		11593	UV2 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1593		11594	UV2 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1594		11595	UV2 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1595		11596	OV1 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1596		11597	OV1 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1597		11598	OV1 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1598		11599	OV1 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1599		11600	OV2 phase A: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1600		11601	OV2 phase B: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1601		11602	OV2 phase C: Confirmation & forced relay control	On	Off	x	x	ON/OFF	Digital Input		
1602		11603	OV2 three-phase OR: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1603		11604	OVG1: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1604		11605	OVG2: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1605		11606	OVNEG1: Confirmation & forced relay control signal	On	Off	x	x	ON/OFF	Digital Input		
1606		11607	OVNEG2: Confirmation & forced relay control signal	On	Off	x	x	ON/OFF	Digital Input		
1607		11608	UF1: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1608		11609	UF2: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1609		11610	UF3: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1610		11611	OF1: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1611		11612	OF2: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1612		11613	OF3: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1613		11614	MST1: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1614		11615	MST2: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1615		11616	VTF: Confirmation & forced relay control signal OR	On	Off	x	x	ON/OFF	Digital Input		
1616		11617	For exclusive use of manufacturer								
1617		11618	For exclusive use of manufacturer								
1618	11619	For exclusive use of manufacturer									
1619	11620	For exclusive use of manufacturer									
1620	11621	For exclusive use of manufacturer									
1621	11622	For exclusive use of manufacturer									
1622	11623	For exclusive use of manufacturer									
1623	11624	For exclusive use of manufacturer									
1624	11625	(Reserved)									
1625	11626	(Reserved)									
1626	11627	(Reserved)									
1627	11628	(Reserved)									
1628	11629	(Reserved)									
1629	11630	(Reserved)									
1630	11631	(Reserved)									
1631	11632	(Reserved)									
1632	11633	(Reserved)									
1633	11634	(Reserved)									
1634	11635	(Reserved)									
1635	11636	(Reserved)									
1636	11637	(Reserved)									
1637	11638	(Reserved)									
1638	11639	(Reserved)									
1639	11640	(Reserved)									
1640	11641	(Reserved)									
1641	11642	(Reserved)									
1642	11643	(Reserved)									
1643	11644	(Reserved)									
1644	11645	(Reserved)									
1645	11646	(Reserved)									
1646	11647	(Reserved)									
1647	11648	(Reserved)									
1648	11649	(Reserved)									
1649	11650	(Reserved)									
1650	11651	(Reserved)									
1651	11652	(Reserved)									
1652	11653	(Reserved)									
1653	11654	(Reserved)									
1654	11655	(Reserved)									
1655	11656	(Reserved)									
1656	11657	(Reserved)									
1657	11658	(Reserved)									
1658	11659	(Reserved)									
1659	11660	(Reserved)									
1660	11661	(Reserved)									
1661	11662	(Reserved)									
1662	11663	(Reserved)									
1663	11664	(Reserved)									
1664	11665	(Reserved)									
1665	11666	(Reserved)									
1666	11667	(Reserved)									
1667	11668	(Reserved)									
1668	11669	(Reserved)									
1669	11670	(Reserved)									
1670	11671	(Reserved)									
1671	11672	(Reserved)									
1672	11673	(Reserved)									
1673	11674	(Reserved)									
1674	11675	(Reserved)									
1675	11676	(Reserved)									
1676	11677	(Reserved)									
1677	11678	(Reserved)									
1678	11679	(Reserved)									
1679	11680	(Reserved)									
1680	11681	(Reserved)									
1681	11682	(Reserved)									
1682	11683	(Reserved)									
1683	11684	(Reserved)									
1684	11685	(Reserved)									
1685	11686	(Reserved)									
1686	11687	(Reserved)									
1687	11688	(Reserved)									
1688	11689	(Reserved)									
1689	11690	(Reserved)									
1690	11691	(Reserved)									
1691	11692	(Reserved)									
1692	11693	(Reserved)									
1693	11694	(Reserved)									
1694	11695	(Reserved)									
1695	11696	(Reserved)									
1696	11697	(Reserved)									
1697	11698	(Reserved)									
1698	11699	(Reserved)									
1699	11700	(Reserved)									
1700	11701	(Reserved)									
1701	11702	(Reserved)									
1702	11703	(Reserved)									
1703	11704	(Reserved)									
1704	11705	(Reserved)									
1705	11706	(Reserved)									
1706	11707	(Reserved)									
1707	11708	(Reserved)									

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1708	2	11709	(Reserved)							
1709		11710	(Reserved)							
1710		11711	(Reserved)							
1711		11712	(Reserved)							
1712		11713	(Reserved)							
1713		11714	(Reserved)							
1714		11715	(Reserved)							
1715		11716	(Reserved)							
1716		11717	(Reserved)							
1717		11718	(Reserved)							
1718		11719	(Reserved)							
1719		11720	(Reserved)							
1720		11721	(Reserved)							
1721		11722	(Reserved)							
1722		11723	(Reserved)							
1723		11724	(Reserved)							
1724		11725	(Reserved)							
1725		11726	(Reserved)							
1726		11727	(Reserved)							
1727		11728	(Reserved)							
1728		11729	(Reserved)							
1729		11730	(Reserved)							
1730		11731	(Reserved)							
1731		11732	(Reserved)							
1732		11733	(Reserved)							
1733		11734	(Reserved)							
1734		11735	(Reserved)							
1735		11736	(Reserved)							
1736		11737	(Reserved)							
1737		11738	(Reserved)							
1738		11739	(Reserved)							
1739		11740	(Reserved)							
1740		11741	(Reserved)							
1741		11742	(Reserved)							
1742		11743	(Reserved)							
1743		11744	(Reserved)							
1744		11745	(Reserved)							
1745		11746	(Reserved)							
1746		11747	(Reserved)							
1747		11748	(Reserved)							
1748		11749	(Reserved)							
1749		11750	(Reserved)							
1750		11751	(Reserved)							
1751		11752	(Reserved)							
1752		11753	(Reserved)							
1753		11754	(Reserved)							
1754		11755	(Reserved)							
1755		11756	(Reserved)							
1756		11757	(Reserved)							
1757		11758	(Reserved)							
1758		11759	(Reserved)							
1759		11760	(Reserved)							
1760		11761	(Reserved)							
1761		11762	(Reserved)							
1762		11763	(Reserved)							
1763		11764	(Reserved)							
1764		11765	(Reserved)							
1765		11766	(Reserved)							
1766		11767	(Reserved)							
1767		11768	(Reserved)							
1768		11769	(Reserved)							
1769		11770	(Reserved)							
1770		11771	(Reserved)							
1771		11772	(Reserved)							
1772		11773	(Reserved)							
1773		11774	(Reserved)							
1774		11775	(Reserved)							
1775		11776	(Reserved)							
1776		11777	(Reserved)							
1777		11778	(Reserved)							
1778		11779	(Reserved)							
1779		11780	(Reserved)							
1780		11781	(Reserved)							
1781		11782	(Reserved)							
1782		11783	(Reserved)							
1783		11784	(Reserved)							
1784		11785	(Reserved)							
1785		11786	(Reserved)							
1786		11787	(Reserved)							
1787		11788	(Reserved)							
1788		11789	(Reserved)							
1789		11790	(Reserved)							
1790		11791	(Reserved)							
1791		11792	(Reserved)							
1792		11793	(Reserved)							
1793		11794	(Reserved)							
1794		11795	(Reserved)							
1795		11796	(Reserved)							
1796		11797	(Reserved)							
1797		11798	(Reserved)							
1798		11799	(Reserved)							
1799		11800	(Reserved)							
1800		11801	(Reserved)							
1801		11802	(Reserved)							
1802		11803	(Reserved)							
1803		11804	(Reserved)							
1804		11805	(Reserved)							
1805		11806	(Reserved)							
1806		11807	(Reserved)							
1807		11808	(Reserved)							
1808		11809	For exclusive use of manufacturer							
1809		11810	For exclusive use of manufacturer							
1810		11811	For exclusive use of manufacturer							
1811		11812	For exclusive use of manufacturer							
1812		11813	For exclusive use of manufacturer							
1813		11814	For exclusive use of manufacturer							
1814		11815	For exclusive use of manufacturer							
1815		11816	For exclusive use of manufacturer							
1816		11817	For exclusive use of manufacturer							
1817		11818	For exclusive use of manufacturer							
1818		11819	For exclusive use of manufacturer							
1819		11820	For exclusive use of manufacturer							
1820		11821	For exclusive use of manufacturer							
1821		11822	For exclusive use of manufacturer							
1822		11823	For exclusive use of manufacturer							
1823		11824	For exclusive use of manufacturer							
1824		11825	For exclusive use of manufacturer							
1825		11826	For exclusive use of manufacturer							
1826		11827	For exclusive use of manufacturer							
1827		11828	For exclusive use of manufacturer							
1828		11829	For exclusive use of manufacturer							
1829		11830	For exclusive use of manufacturer							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1830	2	11831	For exclusive use of manufacturer							
1831		11832	For exclusive use of manufacturer							
1832		11833	For exclusive use of manufacturer							
1833		11834	For exclusive use of manufacturer							
1834		11835	For exclusive use of manufacturer							
1835		11836	For exclusive use of manufacturer							
1836		11837	For exclusive use of manufacturer							
1837		11838	For exclusive use of manufacturer							
1838		11839	For exclusive use of manufacturer							
1839		11840	For exclusive use of manufacturer							
1840		11841	(Reserved)							
1841		11842	(Reserved)							
1842		11843	(Reserved)							
1843		11844	(Reserved)							
1844		11845	(Reserved)							
1845		11846	(Reserved)							
1846		11847	(Reserved)							
1847		11848	(Reserved)							
1848		11849	(Reserved)							
1849		11850	(Reserved)							
1850		11851	(Reserved)							
1851		11852	(Reserved)							
1852		11853	(Reserved)							
1853		11854	(Reserved)							
1854		11855	(Reserved)							
1855		11856	(Reserved)							
1856		11857	(Reserved)							
1857		11858	(Reserved)							
1858		11859	(Reserved)							
1859		11860	(Reserved)							
1860		11861	(Reserved)							
1861		11862	(Reserved)							
1862		11863	(Reserved)							
1863		11864	(Reserved)							
1864		11865	(Reserved)							
1865		11866	(Reserved)							
1866		11867	(Reserved)							
1867		11868	(Reserved)							
1868		11869	(Reserved)							
1869		11870	(Reserved)							
1870		11871	(Reserved)							
1871		11872	(Reserved)							
1872		11873	(Reserved)							
1873		11874	(Reserved)							
1874		11875	(Reserved)							
1875		11876	(Reserved)							
1876		11877	(Reserved)							
1877		11878	(Reserved)							
1878		11879	(Reserved)							
1879		11880	(Reserved)							
1880		11881	(Reserved)							
1881		11882	(Reserved)							
1882		11883	(Reserved)							
1883		11884	(Reserved)							
1884		11885	(Reserved)							
1885		11886	(Reserved)							
1886		11887	(Reserved)							
1887		11888	(Reserved)							
1888		11889	(Reserved)							
1889		11890	(Reserved)							
1890		11891	(Reserved)							
1891		11892	(Reserved)							
1892		11893	(Reserved)							
1893		11894	(Reserved)							
1894		11895	(Reserved)							
1895		11896	(Reserved)							
1896		11897	(Reserved)							
1897		11898	(Reserved)							
1898		11899	(Reserved)							
1899		11900	(Reserved)							
1900		11901	(Reserved)							
1901		11902	(Reserved)							
1902		11903	(Reserved)							
1903		11904	(Reserved)							
1904		11905	(Reserved)							
1905		11906	(Reserved)							
1906		11907	(Reserved)							
1907		11908	(Reserved)							
1908		11909	(Reserved)							
1909		11910	(Reserved)							
1910		11911	(Reserved)							
1911		11912	(Reserved)							
1912		11913	(Reserved)							
1913		11914	(Reserved)							
1914		11915	(Reserved)							
1915		11916	(Reserved)							
1916		11917	(Reserved)							
1917		11918	(Reserved)							
1918		11919	(Reserved)							
1919		11920	(Reserved)							
1920		11921	(Reserved)							
1921		11922	(Reserved)							
1922		11923	(Reserved)							
1923		11924	(Reserved)							
1924		11925	(Reserved)							
1925		11926	(Reserved)							
1926		11927	(Reserved)							
1927		11928	(Reserved)							
1928		11929	(Reserved)							
1929		11930	(Reserved)							
1930		11931	(Reserved)							
1931		11932	(Reserved)							
1932		11933	(Reserved)							
1933		11934	(Reserved)							
1934		11935	(Reserved)							
1935		11936	(Reserved)							
1936		11937	(Reserved)							
1937		11938	(Reserved)							
1938		11939	(Reserved)							
1939		11940	(Reserved)							
1940		11941	(Reserved)							
1941		11942	(Reserved)							
1942		11943	(Reserved)							
1943		11944	(Reserved)							
1944		11945	(Reserved)							
1945		11946	(Reserved)							
1946		11947	(Reserved)							
1947		11948	(Reserved)							
1948		11949	(Reserved)							
1949		11950	(Reserved)							
1950		11951	(Reserved)							
1951		11952	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Signal Type	Remarks
1952	2	11953	(Reserved)							
1953		11954	(Reserved)							
1954		11955	(Reserved)							
1955		11956	(Reserved)							
1956		11957	(Reserved)							
1957		11958	(Reserved)							
1958		11959	(Reserved)							
1959		11960	(Reserved)							
1960		11961	(Reserved)							
1961		11962	(Reserved)							
1962		11963	(Reserved)							
1963		11964	(Reserved)							
1964		11965	(Reserved)							
1965		11966	(Reserved)							
1966		11967	(Reserved)							
1967		11968	(Reserved)							
1968		11969	(Reserved)							
1969		11970	(Reserved)							
1970		11971	(Reserved)							
1971		11972	(Reserved)							
1972		11973	(Reserved)							
1973		11974	(Reserved)							
1974		11975	(Reserved)							
1975		11976	(Reserved)							
1976		11977	(Reserved)							
1977		11978	(Reserved)							
1978		11979	(Reserved)							
1979		11980	(Reserved)							
1980		11981	(Reserved)							
1981		11982	(Reserved)							
1982		11983	(Reserved)							
1983		11984	(Reserved)							
1984		11985	(Reserved)							
1985		11986	(Reserved)							
1986		11987	(Reserved)							
1987		11988	(Reserved)							
1988		11989	(Reserved)							
1989		11990	(Reserved)							
1990		11991	(Reserved)							
1991		11992	(Reserved)							
1992		11993	(Reserved)							
1993		11994	(Reserved)							
1994		11995	(Reserved)							
1995		11996	(Reserved)							
1996		11997	(Reserved)							
1997		11998	(Reserved)							
1998		11999	(Reserved)							
1999		12000	(Reserved)							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks	
0	4	30001	Get measured value 1 (H): Phase A voltage	x	x	0	1500	V	1	Analog Input	With a "Measured value" request from the master station as Function Code: 4, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 30001+2*i • Number of access points = 2*j • i+j<=60 (i=0 to 59, j=1 to 60) → When an error occurs, the slave will respond with 02: ILLEGAL DATA ADDRESS.  * The displayed value depending on the zero-sequence current type. *1: ZCT Type *2: 5A Type	
1		30002	Get measured value 1 (L): Phase A voltage									
2		30003	Get measured value 2 (H): Phase B voltage	x	x	0	1500	V	1	Analog Input		
3		30004	Get measured value 2 (L): Phase B voltage									
4		30005	Get measured value 3 (H): Phase C voltage	x	x	0	1500	V	1	Analog Input		
5		30006	Get measured value 3 (L): Phase C voltage									
6		30007	Get measured value 4 (H): Phase AB voltage	x	x	0	2600	V	1	Analog Input		
7		30008	Get measured value 4 (L): Phase AB voltage									
8		30009	Get measured value 5 (H): Phase BC voltage	x	x	0	2600	V	1	Analog Input		
9		30010	Get measured value 5 (L): Phase BC voltage									
10		30011	Get measured value 6 (H): Phase CA voltage	x	x	0	2600	V	1	Analog Input		
11		30012	Get measured value 6 (L): Phase CA voltage									
12		30013	Get measured value 7 (H): Zero phase voltage	x	x	0	2600	V	1	Analog Input		
13		30014	Get measured value 7 (L): Zero phase voltage									
14		30015	Get measured value 8 (H): Zero phase voltage	x	x	0	2470	V	1	Analog Input		
15		30016	Get measured value 8 (L): Zero phase voltage									
16		30017	Get measured value 9 (H): Positive phase voltage	x	x	0	1500	V	1	Analog Input		
17		30018	Get measured value 9 (L): Positive phase voltage									
18		30019	Get measured value 10 (H): Negative phase voltage	x	x	0	1500	V	1	Analog Input		
19		30020	Get measured value 10 (L): Negative phase voltage									
20		30021	Get measured value 11 (H): Phase A current	x	x	0	1000	A	2	Analog Input		
21		30022	Get measured value 11 (L): Phase A current									
22		30023	Get measured value 12 (H): Phase B current	x	x	0	1000	A	2	Analog Input		
23		30024	Get measured value 12 (L): Phase B current									
24		30025	Get measured value 13 (H): Phase C current	x	x	0	1000	A	2	Analog Input		
25		30026	Get measured value 13 (L): Phase C current									
26		30027	Get measured value 14 (H): Zero phase current *	x	x	0	9999 *1	mA *1	1 *1	Analog Input		
27		30028	Get measured value 14 (L): Zero phase current *				1000 *2	A *2	2 *2			
28		30029	For exclusive use of manufacturer (not displayed on									
29		30030	For exclusive use of manufacturer (not displayed on									
30		30031	Get measured value 16 (H): Positive phase current	x	x	0	1000	A	2	Analog Input		
31		30032	Get measured value 16 (L): Positive phase current									
32		30033	Get measured value 17 (H): Negative phase current	x	x	0	1000	A	2	Analog Input		
33		30034	Get measured value 17 (L): Negative phase current									
34		30035	For exclusive use of manufacturer (not displayed on									
35		30036	For exclusive use of manufacturer (not displayed on									
36		30037	For exclusive use of manufacturer (not displayed on									
37		30038	For exclusive use of manufacturer (not displayed on									
38		30039	For exclusive use of manufacturer (not displayed on									
39		30040	For exclusive use of manufacturer (not displayed on									
40		30041	For exclusive use of manufacturer (not displayed on									
41		30042	For exclusive use of manufacturer (not displayed on									
42		30043	For exclusive use of manufacturer (not displayed on									
43		30044	For exclusive use of manufacturer (not displayed on									
44		30045	For exclusive use of manufacturer (not displayed on									
45		30046	For exclusive use of manufacturer (not displayed on									
46		30047	For exclusive use of manufacturer (not displayed on									
47		30048	For exclusive use of manufacturer (not displayed on									
48		30049	For exclusive use of manufacturer (not displayed on									
49		30050	For exclusive use of manufacturer (not displayed on									
50		30051	Get measured value 18 (H): Phase A voltage phase	x	x	0	3599	°LAG	1	Analog Input		
51		30052	Get measured value 18 (L): Phase A voltage phase									
52		30053	Get measured value 19 (H): Phase B voltage phase	x	x	0	3599	°LAG	1	Analog Input		
53		30054	Get measured value 19 (L): Phase B voltage phase									
54		30055	Get measured value 20 (H): Phase C voltage phase	x	x	0	3599	°LAG	1	Analog Input		
55		30056	Get measured value 20 (L): Phase C voltage phase									
56		30057	Get measured value 21 (H): Phase AB voltage phase	x	x	0	3599	°LAG	1	Analog Input		
57		30058	Get measured value 21 (L): Phase AB voltage phase									
58		30059	Get measured value 22 (H): Phase BC voltage phase	x	x	0	3599	°LAG	1	Analog Input		
59		30060	Get measured value 22 (L): Phase BC voltage phase									
60		30061	Get measured value 23 (H): Phase CA voltage phase	x	x	0	3599	°LAG	1	Analog Input		
61		30062	Get measured value 23 (L): Phase CA voltage phase									
62		30063	Get measured value 24 (H): Zero phase voltage	x	x	0	3599	°LAG	1	Analog Input		
63		30064	Get measured value 24 (L): Zero phase voltage phase									
64		30065	Get measured value 25 (H): Phase A current phase	x	x	0	3599	°LAG	1	Analog Input		
65		30066	Get measured value 25 (L): Phase A current phase									
66		30067	Get measured value 26 (H): Phase B current phase	x	x	0	3599	°LAG	1	Analog Input		
67		30068	Get measured value 26 (L): Phase B current phase									
68		30069	Get measured value 27 (H): Phase C current phase	x	x	0	3599	°LAG	1	Analog Input		
69		30070	Get measured value 27 (L): Phase C current phase									
70		30071	Get measured value 28 (H): Zero phase current phase	x	x	0	3599	°LAG	1	Analog Input		
71		30072	Get measured value 28 (L): Zero phase current phase									
72		30073	For exclusive use of manufacturer (not displayed on									
73		30074	For exclusive use of manufacturer (not displayed on									
74		30075	For exclusive use of manufacturer (not displayed on									
75		30076	For exclusive use of manufacturer (not displayed on									
76		30077	For exclusive use of manufacturer (not displayed on									
77		30078	For exclusive use of manufacturer (not displayed on									
78		30079	For exclusive use of manufacturer (not displayed on									
79		30080	For exclusive use of manufacturer (not displayed on									
80		30081	For exclusive use of manufacturer (not displayed on									
81		30082	For exclusive use of manufacturer (not displayed on									
82		30083	For exclusive use of manufacturer (not displayed on									
83		30084	For exclusive use of manufacturer (not displayed on									
84		30085	For exclusive use of manufacturer (not displayed on									
85		30086	For exclusive use of manufacturer (not displayed on									
86		30087	For exclusive use of manufacturer (not displayed on									
87		30088	For exclusive use of manufacturer (not displayed on									
88		30089	Get measured value 29 (H): Active power +P	x	x	0	9999	MW	1	Analog Input		
89		30090	Get measured value 29 (L): Active power +P									
90		30091	Get measured value 30 (H): Active power -P	x	x	0	9999	MW	1	Analog Input		
91		30092	Get measured value 30 (L): Active power -P									
92		30093	Get measured value 31 (H): Reactive power +Q	x	x	0	9999	MVar	1	Analog Input		
93		30094	Get measured value 31 (L): Reactive power +Q									
94		30095	Get measured value 32 (H): Reactive power -Q	x	x	0	9999	MVar	1	Analog Input		
95		30096	Get measured value 32 (L): Reactive power -Q									
96		30097	Get measured value 31 (H): Apparent power	x	x	0	9999	MVA	1	Analog Input		
97		30098	Get measured value 31 (L): Apparent power									
98		30099	Get measured value 32 (H): Power factor	x	x	-100	100	No Unit	2	Analog Input		
99		30100	Get measured value 32 (L): Power factor									
100		30101	Get measured value 33 (H): Frequency	x	x	450	650	Hz	1	Analog Input		
101		30102	Get measured value 33 (L): Frequency									
102		30103	Get measured value 34 (H): Active power amount (incoming direction)	x	x	0	999999999	kWh	0	Analog Input		
103		30104	Get measured value 34 (L): Active power amount (incoming direction)									
104		30105	Get measured value 35 (H): Active power amount (outgoing direction)	x	x	0	999999999	kWh	0	Analog Input		
105		30106	Get measured value 35 (L): Active power amount (outgoing direction)									
106		30107	Get measured value 36 (H): Reactive power amount (incoming direction)	x	x	0	999999999	kVarh	0	Analog Input		
107		30108	Get measured value 36 (L): Reactive power amount (incoming direction)									
108		30109	Get measured value 37 (H): Reactive power amount (outgoing direction)	x	x	0	999999999	kVarh	0	Analog Input		
109		30110	Get measured value 37 (L): Reactive power amount (outgoing direction)									
110		30111	(Reserved)									
111		30112	(Reserved)									
112		30113	(Reserved)									
113		30114	(Reserved)									
114		30115	(Reserved)									
115	30116	(Reserved)										

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks	
116	4	30117	(Reserved)									
117		30118										
118		30119										
119		30120	(Reserved)									
149	4	30150	Number of acquired event records	x	x	0	256	No Unit		Analog Input	With an "Event record" request from the master station as Function Code: 4, the slave will respond with (MODBUS send) the response data.  On MODBUS: • Start address = 30150+i • Number of access points = j • i+j<=2049 (i=0 to 2048, j=1 to 125)  → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.  "0" will be stored for the data portion with no event record. (Example: If "Number of acquired event records" is "1", trip data #2 through #256 will be "0")  The internal data will be erased with "Start erase event records operation".  (Note 2)	
150		30151	Event record #001: Event item number	x	x	1	256	No Unit		Analog Input		
151		30152	Event record #001: Event status	x	x	0	1	No Unit		Analog Input		
152		30153	Event record #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input		
153		30154	Event record #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x0101	0x1231	No Unit		Analog Input		
154		30155	Event record #001: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input		
155		30156	Event record #001: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x5900	No Unit		Analog Input		
156		30157	Event record #001: Time of occurrence (BCD time millisecond)	x	x	0x0000	0x0999	No Unit		Analog Input		
157		30158	Event record #001: Time type	x	x	1	4	No Unit		Analog Input		
158		30159	Event record #002									
159		30160										
160		30161										
161		30162										
162		30163										
163		30164										
164		30165										
165		30166										
166		30167	Event record #003									
167		30168										
168		30169										
169		30170										
170		30171										
171		30172										
172		30173										
173		30174										
2190	32191	Event record #256										
2191	32192											
2192	32193											
2193	32194											
2194	32195											
2195	32196											
2196	32197											
2197	32198											
2460	4	32461	Number of acquired monitoring errors	x	x	0	200	No Unit		Analog Input	When start address=32461 ("Number of items of acquired monitoring error data") is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data. (When (start address=32462 or greater) is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data.)  On MODBUS: • Start address = 32461+i • Number of access points = j • i+j<=2801 (i=0 to 2800, j=1 to 125)  "0" will be stored for the data portion with no monitoring error data. (Example: If "Number of items of acquired monitoring data" is "1", monitoring error #2 through #200 will be "0")  The internal data will be erased with "Start erase monitoring error data operation".  → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.	
2461		32462	Monitoring error #001: Error code	x	x			No Unit		Analog Input		
2462		32463	Monitoring error #001: Detailed error code	x	x			No Unit		Analog Input		
2463		32464	Monitoring error #001: Detailed error code	x	x			No Unit		Analog Input		
2464		32465	Monitoring error #001: Detailed error code	x	x			No Unit		Analog Input		
2465		32466	Monitoring error #001: Detailed error code	x	x			No Unit		Analog Input		
2466		32467	Monitoring error #001: Detailed error code	x	x			No Unit		Analog Input		
2467		32468	Monitoring error #001: Detailed error code	x	x			No Unit		Analog Input		
2468		32469	Monitoring error #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input		
2469		32470	Monitoring error #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x0101	0x1231	No Unit		Analog Input		
2470		32471	Monitoring error #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x0000	0x2359	No Unit		Analog Input		
2471		32472	Monitoring error #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x0000	0x5900	No Unit		Analog Input		
2472		32473	Monitoring error #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x0000	0x0999	No Unit		Analog Input		
2473		32474	Monitoring error #001: Time type	x	x	1	4	No Unit		Analog Input		
2474		32475	Monitoring error #001: CPU ID	x	x	?	?	No Unit		Analog Input		
2475		32476	Monitoring error #002									
2476		32477										
2477		32478										
2478		32479										
2479		32480										
2480		32481										
2481		32482										
2482		32483										
2483		32484										
2484		32485										
2485	32486											
2486	32487											
2487	32488											
2488	32489											
2489	32490	Monitoring error #003										
2490	32491											
2491	32492											
2492	32493											
2493	32494											
2494	32495											
2495	32496											
2496	32497											
2497	32498											
2498	32499											
2499	32500											
2500	32501											
2501	32502											
2502	32503											
5247	35248	Monitoring error #200										
5248	35249											
5249	35250											
5250	35251											
5251	35252											
5252	35253											
5253	35254											
5254	35255											
5255	35256											
5256	35257											
5257	35258											
5258	35259											
5259	35260											
5260	35261											
5470	4	35471	Number of acquired access records	x	x	0	128	No Unit		Analog Input	When (start address=35471 ("Number of items of acquired access record data")) is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data. (When (start address=35472 or greater) is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data.)  On MODBUS: • Start address = 35471+i • Number of access points = j • i+j<=1025 (i=0 to 1024, j=1 to 125)  "0" will be stored for the data portion with no monitoring error data. (Example: If "Number of items of acquired access record data" is "1", monitoring error #2 through #128 will be "0")  → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.	
5471		35472	Access record #001: Access item number	x	x	0	0x65535	No Unit		Analog Input		
5472		35473	Access record #001: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input		
5473		35474	Access record #001: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input		
5474		35475	Access record #001: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input		
5475		35476	Access record #001: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input		
5476		35477	Access record #001: Time of occurrence (BCD time millisecond)	x	x	0x0000	0x0999	No Unit		Analog Input		
5477		35478	Access record #001: Time type	x	x	1	4	No Unit		Analog Input		
5478		35479	Access record #001: Access source	x	x	0	3	No Unit		Analog Input		
5479		35480	Access record #002									
5480		35481										
5481		35482										
5482		35483										
5483		35484										
5484		35485										
5485		35486										
5486		35487										
5487		35488	Access record #003									
5488		35489										
5489		35490										
5490		35491										
5491		35492										
5492		35493										
5493		35494										
5494		35495										



Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks
6487	4	36488	Access record #128								
6488		36489									
6489		36490									
6490		36491									
6491		36492									
6492		36493									
6493		36494									
6494		36495									
6630	4	36631	Number of acquired accident records	x	x	0	5	No Unit		Analog Input	When (start address=36631 ("Number of acquired accident records")) is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the records. (When (start address=36632 or greater) is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data.)  On MODBUS: • Start address = 36631+i • Number of access points = j • i+j<=341 (i=0 to 340, j=1 to 125)  "0" will be stored for the data portion with no accident record. (Example: If "Number of acquired accident records" is "1", monitoring error #2 through #5 will be "0")  → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.  If the residual type, zero phase current (combination) will be allocated to measured value 15, and measured values 15 to 27 listed to the left will be allocated to measured values 16 to 28.  * The displayed value depending on the zero-sequence current type. *1: ZCT Type *2: 5A Type
6631		36632	Accident record #1: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input	
6632		36633	Accident record #1: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input	
6633		36634	Accident record #1: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input	
6634		36635	Accident record #1: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input	
6635		36636	Accident record #1: Time of occurrence (BCD time milliseconds)	x	x	0x0000	0x0999	No Unit		Analog Input	
6636		36637	Accident record #1: Time type	x	x	1	4	No Unit		Analog Input	
6637		36638	Accident record #1: Trip cause (H)	x	x	Accident record cause		No Unit		Analog Input	
6638		36639	Accident record #1: Trip cause (L)	x	x	index bit information		No Unit		Analog Input	
6639		36640	Accident record #1: Measured value 1 (H): Phase A	x	x	0	1500	V	1	Analog Input	
6640		36641	Accident record #1: Measured value 1 (L): Phase A								
6641		36642	Accident record #1: Measured value 2 (H): Phase B	x	x	0	1500	V	1	Analog Input	
6642		36643	Accident record #1: Measured value 2 (L): Phase B								
6643		36644	Accident record #1: Measured value 3 (H): Phase C	x	x	0	1500	V	1	Analog Input	
6644		36645	Accident record #1: Measured value 3 (L): Phase C								
6645		36646	Accident record #1: Measured value 4 (H): Phase AB	x	x	0	2600	V	1	Analog Input	
6646		36647	Accident record #1: Measured value 4 (L): Phase AB								
6647		36648	Accident record #1: Measured value 5 (H): Phase BC	x	x	0	2600	V	1	Analog Input	
6648		36649	Accident record #1: Measured value 5 (L): Phase BC								
6649		36650	Accident record #1: Measured value 6 (H): Phase CA	x	x	0	2600	V	1	Analog Input	
6650		36651	Accident record #1: Measured value 6 (L): Phase CA								
6651		36652	Accident record #1: Measured value 7 (H): Zero phase voltage	x	x	0	2470	V	1	Analog Input	
6652		36653	Accident record #1: Measured value 7 (L): Zero phase voltage								
6653		36654	Accident record #1: Measured value 8 (H): Zero phase voltage (combination)	x	x	0	2470	V	1	Analog Input	
6654		36655	Accident record #1: Measured value 8 (L): Zero phase voltage (combination)								
6655		36656	Accident record #1: Measured value 9 (H): Positive phase voltage	x	x	0	1500	V	1	Analog Input	
6656		36657	Accident record #1: Measured value 9 (L): Positive phase voltage								
6657		36658	Accident record #1: Measured value 10 (H): Negative phase voltage	x	x	0	1500	V	1	Analog Input	
6658		36659	Accident record #1: Measured value 10 (L): Negative phase voltage								
6659		36660	Accident record #1: Measured value 11 (H): Phase A	x	x	0	1000	A	2	Analog Input	
6660		36661	Accident record #1: Measured value 11 (L): Phase A								
6661		36662	Accident record #1: Measured value 12 (H): Phase B	x	x	0	1000	A	2	Analog Input	
6662		36663	Accident record #1: Measured value 12 (L): Phase B								
6663		36664	Accident record #1: Measured value 13 (H): Phase C	x	x	0	1000	A	2	Analog Input	
6664		36665	Accident record #1: Measured value 13 (L): Phase C								
6665		36666	Accident record #1: Measured value 14 (H): Zero phase current *	x	x	0	9999 *1 1000 *2	mA *1 A *2	1 *1 2 *2	Analog Input	
6666		36667	Accident record #1: Measured value 14 (L): Zero phase current *								
6667		36668	Accident record #1: Measured value 15 (H): Positive phase current	x	x	0	1000	A	2	Analog Input	
6668		36669	Accident record #1: Measured value 15 (L): Positive phase current								
6669		36670	Accident record #1: Measured value 16 (H): Negative phase current	x	x	0	1000	A	2	Analog Input	
6670		36671	Accident record #1: Measured value 16 (L): Negative phase current								
6671		36672	Accident record #1: Measured value 17 (H): Phase A voltage phase	x	x	0	3599	°LAG	1	Analog Input	
6672		36673	Accident record #1: Measured value 17 (L): Phase A voltage phase								
6673		36674	Accident record #1: Measured value 18 (H): Phase B voltage phase	x	x	0	3599	°LAG	1	Analog Input	
6674		36675	Accident record #1: Measured value 18 (L): Phase B voltage phase								
6675		36676	Accident record #1: Measured value 19 (H): Phase C voltage phase	x	x	0	3599	°LAG	1	Analog Input	
6676		36677	Accident record #1: Measured value 19 (L): Phase C voltage phase								
6677		36678	Accident record #1: Measured value 20 (H): Phase AB voltage phase	x	x	0	3599	°LAG	1	Analog Input	
6678	36679	Accident record #1: Measured value 20 (L): Phase AB voltage phase									
6679	36680	Accident record #1: Measured value 21 (H): Phase BC voltage phase	x	x	0	3599	°LAG	1	Analog Input		
6680	36681	Accident record #1: Measured value 21 (L): Phase BC voltage phase									
6681	36682	Accident record #1: Measured value 22 (H): Phase CA voltage phase	x	x	0	3599	°LAG	1	Analog Input		
6682	36683	Accident record #1: Measured value 22 (L): Phase CA voltage phase									
6683	36684	Accident record #1: Measured value 23 (H): Zero phase voltage phase	x	x	0	3599	°LAG	1	Analog Input		
6684	36685	Accident record #1: Measured value 23 (L): Zero phase voltage phase									
6685	36686	Accident record #1: Measured value 24 (H): Phase A current phase	x	x	0	3599	°LAG	1	Analog Input		
6686	36687	Accident record #1: Measured value 24 (L): Phase A current phase									
6687	36688	Accident record #1: Measured value 25 (H): Phase B current phase	x	x	0	3599	°LAG	1	Analog Input		
6688	36689	Accident record #1: Measured value 25 (L): Phase B current phase									
6689	36690	Accident record #1: Measured value 26 (H): Phase C current phase	x	x	0	3599	°LAG	1	Analog Input		
6690	36691	Accident record #1: Measured value 26 (L): Phase C current phase									
6691	36692	Accident record #1: Measured value 27 (H): Zero phase current phase	x	x	0	3599	°LAG	1	Analog Input		
6692	36693	Accident record #1: Measured value 27 (L): Zero phase current phase									
6693	36694	(Reserved)	x	x							
6694	36695	(Reserved)									
6695	36696	(Reserved)	x	x							
6696	36697	(Reserved)									
6697	36698	(Reserved)	x	x							
6698	36699	(Reserved)									

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks
6903	4	36904	Accident record #5								
6904		36905									
6905		36906									
6906		36907									
6907		36908									
6908		36909									
6909		36910									
6910		36911									
6911		36912									
6912		36913									
6913		36914									
6914		36915									
6915		36916									
6916		36917									
6917		36918									
6918		36919									
6919		36920									
6920		36921									
6921		36922									
6922		36923									
6923		36924									
6924		36925									
6925		36926									
6926		36927									
6927		36928									
6928		36929									
6929		36930									
6930		36931									
6931		36932									
6932		36933									
6933		36934									
6934		36935									
6935		36936									
6936		36937									
6937		36938									
6938		36939									
6939		36940									
6940		36941									
6941		36942									
6942		36943									
6943		36944									
6944		36945									
6945		36946									
6946		36947									
6947		36948									
6948		36949									
6949		36950									
6950		36951									
6951	36952										
6952	36953										
6953	36954										
6954	36955										
6955	36956										
6956	36957										
6957	36958										
6958	36959										
6959	36960										
6960	36961										
6961	36962										
6962	36963										
6963	36964										
6964	36965										
6965	36966										
6966	36967										
6967	36968										
6968	36969										
6969	36970										
6970	36971										
7130	4	37131	Number of acquired items in trip data list	x	x	0	5	No Unit		Analog Input	When (start address=37131 ("Number of acquired items in trip data list") is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data.  If an error (a trip) has occurred when "Get trip data list" is requested, the slave will respond with 07: NEGATIVE ACKNOWLEDGE.  When (start address=37132 or greater) is received as Function Code: 4, the slave will respond with (MODBUS send) the size of the data.  "0" will be stored for the data portion with no trip data. (Example: If "Number of acquired items in trip data list" is "1", trip data #2 through #5 will be "0")  The internal data will be erased with "Start erase accident records operation".  On MODBUS: • Start address = 37132+i • Number of access points = j • i+j<=55 (i=0 to 54, j=1 to 55)  When an error occurs, the slave will respond with 02: ILLEGAL DATA ADDRESS.)
7131		37132	Trip data #1: Phenomenon number (H)	x	x	0x00000000	0x3B9ACA0	No Unit		Analog Input	
7132		37133	Trip data #1: Phenomenon number (L)	x	x	0	0	No Unit		Analog Input	
7133		37134	Trip data #1: Storage block number	x	x	1	10	No Unit		Analog Input	
7134		37135	Trip data #1: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input	
7135		37136	Trip data #1: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input	
7136		37137	Trip data #1: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input	
7137		37138	Trip data #1: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input	
7138		37139	Trip data #1: Time of occurrence (BCD time	x	x	0x0000	0x0999	No Unit		Analog Input	
7139		37140	Trip data #1: Time type	x	x	1	4	No Unit		Analog Input	
7140		37141	Trip data #2: Phenomenon number (H)	x	x	0x00000000	0x3B9ACA0	No Unit		Analog Input	
7141		37142	Trip data #2: Phenomenon number (L)	x	x	0	0	No Unit		Analog Input	
7142		37143	Trip data #2: Storage block number	x	x	1	10	No Unit		Analog Input	
7143		37144	Trip data #2: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input	
7144		37145	Trip data #2: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input	
7145		37146	Trip data #2: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input	
7146		37147	Trip data #2: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input	
7147		37148	Trip data #2: Time of occurrence (BCD time	x	x	0x0000	0x0999	No Unit		Analog Input	
7148		37149	Trip data #2: Time type	x	x	1	4	No Unit		Analog Input	
7149		37150	Trip data #3: Phenomenon number (H)	x	x	0x00000000	0x3B9ACA0	No Unit		Analog Input	
7150		37151	Trip data #3: Phenomenon number (L)	x	x	0	0	No Unit		Analog Input	
7151		37152	Trip data #3: Storage block number	x	x	1	10	No Unit		Analog Input	
7152		37153	Trip data #3: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input	
7153		37154	Trip data #3: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input	
7154		37155	Trip data #3: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input	
7155		37156	Trip data #3: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input	
7156		37157	Trip data #3: Time of occurrence (BCD time	x	x	0x0000	0x0999	No Unit		Analog Input	
7157		37158	Trip data #3: Time type	x	x	1	4	No Unit		Analog Input	
7158		37159	Trip data #4: Phenomenon number (H)	x	x	0x00000000	0x3B9ACA0	No Unit		Analog Input	
7159		37160	Trip data #4: Phenomenon number (L)	x	x	0	0	No Unit		Analog Input	
7160		37161	Trip data #4: Storage block number	x	x	1	10	No Unit		Analog Input	
7161		37162	Trip data #4: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input	
7162		37163	Trip data #4: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input	
7163		37164	Trip data #4: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input	
7164		37165	Trip data #4: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input	
7165		37166	Trip data #4: Time of occurrence (BCD time	x	x	0x0000	0x0999	No Unit		Analog Input	
7166		37167	Trip data #4: Time type	x	x	1	4	No Unit		Analog Input	
7167		37168	Trip data #5: Phenomenon number (H)	x	x	0x00000000	0x3B9ACA0	No Unit		Analog Input	
7168		37169	Trip data #5: Phenomenon number (L)	x	x	0	0	No Unit		Analog Input	
7169		37170	Trip data #5: Storage block number	x	x	1	10	No Unit		Analog Input	
7170		37171	Trip data #5: Time of occurrence (BCD time year/month/day (H))	x	x	0x1970	0x2069	No Unit		Analog Input	

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks
7171	4	37172	Trip data #5: Time of occurrence (BCD time year/month/day (L))	x	x	0x0101	0x1231	No Unit		Analog Input	
7172		37173	Trip data #5: Time of occurrence (BCD time hour/minute/second (H))	x	x	0x0000	0x2359	No Unit		Analog Input	
7173		37174	Trip data #5: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x5900	No Unit		Analog Input	
7174		37175	Trip data #5: Time of occurrence (BCD time hour/minute/second (L))	x	x	0x0000	0x0999	No Unit		Analog Input	
7175		37176	Trip data #5: Time type	x	x	1	4	No Unit		Analog Input	
7176		37177									
7177		37178									
7178		37179									
7179		37180									
7180		37181									
7181		37182									
7182		37183									
7183		37184									
7184		37185									
7185		37186									
7186		37187									
7187		37188									
7188		37189									
7189		37190									
7190		37191									
7191		37192									
7192		37193									
7193		37194									
7194		37195									
7195		37196									
7196		37197									
7197		37198									
7198		37199									
7199		37200									
7200		37201									
7201		37202									
7202		37203									
7203		37204									
7204		37205									
7205		37206									
7206		37207									
7207		37208									
7208		37209									
7209		37210									
7210		37211									
7211		37212									
7212		37213									
7213		37214									
7214		37215									
7215		37216									
7216		37217									
7217		37218									
7218		37219									
7219		37220									
7220		37221									
7221		37222									
7222		37223									
7223		37224									
7224		37225									
7225		37226									
7226		37227									
7227		37228									
7228		37229									
7229		37230									

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks	
7230	4	37231	Get trip data (trip header/model-specific data) phenomenon number (H)	x	x	1	10^9	No Unit		Analog Input	This memory stores the results of the get trip data (trip header/model-specific data) request (a request as Function Code: 16 to Holding Register 44101 to 44103). This memory is entirely "0" if no get trip data (trip header/model-specific data) request has been made.  On MODBUS: • Start address = 37231+i • Number of access points = j • i+j<=63 (i=0 to 62, j=1 to 63)  → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.	
7231		37232	Get trip data (trip header/model-specific data) phenomenon number (L)	x	x			No Unit		Analog Input		
7232		37233	Get trip data (trip header/model-specific data) block	x	x	1	10	No Unit		Analog Input		
7233		37234	Same as above: CT secondary processing value 1 (phase A or AB voltage)	x	x	Fixed value		No Unit		Analog Input		
7234		37235	Same as above: CT secondary processing value 2 (phase B or BC voltage)	x	x	Fixed value		No Unit		Analog Input		
7235		37236	Same as above: CT secondary processing value 3 (phase C or CA voltage)	x	x	Fixed value		No Unit		Analog Input		
7236		37237	Same as above: CT secondary processing value 4 (zero phase voltage)	x	x	Fixed value		No Unit		Analog Input		
7237		37238	Same as above: CT secondary processing value 5 (phase A current)	x	x	Fixed value		No Unit		Analog Input		
7238		37239	Same as above: CT secondary processing value 6 (phase B current)	x	x	Fixed value		No Unit		Analog Input		
7239		37240	Same as above: CT secondary processing value 7 (phase C current)	x	x	Fixed value		No Unit		Analog Input		
7240		37241	Same as above: CT secondary processing value 8 (zero phase current)	x	x	Fixed value		No Unit		Analog Input		
7241		37242	(Reserved)									
7242		37243	(Reserved)									
7243		37244	(Reserved)									
7244		37245	(Reserved)									
7245		37246	(Reserved)									
7246		37247	(Reserved)									
7247		37248	(Reserved)									
7248		37249	(Reserved)									
7249		37250	(Reserved)									
7250	37251	(Reserved)										
7251	37252	(Reserved)										
7252	37253	(Reserved)										
7253	37254	(Reserved)										
7254	37255	(Reserved)										
7255	37256	(Reserved)										
7256	37257	(Reserved)										
7257	37258	(Reserved)										
7258	37259	(Reserved)										
7259	37260	(Reserved)										
7260	37261	(Reserved)										
7261	37262	(Reserved)										
7262	37263	(Reserved)										
7263	37264	(Reserved)										
7264	37265	(Reserved)										
7265	37266	(Reserved)										
7266	37267	(Reserved)										
7267	37268	(Reserved)										
7268	37269	(Reserved)										
7269	37270	(Reserved)										
7270	37271	(Reserved)										
7271	37272	(Reserved)										
7272	37273	(Reserved)										
7273	37274	(Reserved)										
7274	37275	(Reserved)										
7275	37276	(Reserved)										
7276	37277	(Reserved)										
7277	37278	(Reserved)										
7278	37279	(Reserved)										
7279	37280	(Reserved)										
7280	37281	(Reserved)										
7281	37282	(Reserved)										
7282	37283	(Reserved)										
7283	37284	(Reserved)										
7284	37285	(Reserved)										
7285	37286	(Reserved)										
7286	37287	(Reserved)										
7287	37288	(Reserved)										
7288	37289	(Reserved)										
7289	37290	Same as above: 30° analog data word count	x	x	0	56	No Unit			Analog Input		
7290	37291	Same as above: 30° flag data word count	x	x	0	56	No Unit			Analog Input		
7291	37292	Same as above: Number of items of history data (saved IT count)	x	x	0	14549	No Unit			Analog Input		
7292	37293	Same as above: AI sampling cycle	x	x	15	30	No Unit			Analog Input		
7293	37294	Get trip data (analog/digital data/model-specific data) phenomenon number (H)	x	x	1	10^9	No Unit		Analog Input	This memory stores the results of the get trip data (analog/digital data) request (a request as Function Code: 16 to Holding Register 44104 to 7). This memory is entirely "0" if no get trip data (analog/digital data) request has been made.  On MODBUS: • Start address = 37294+i • Number of access points = j • i+j<=60 (i=0 to 59, j=1 to 60)  → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.		
7294		37295	Get trip data (analog/digital data/model-specific data) phenomenon number (L)	x			x	No Unit			Analog Input	
7295	37296	Get trip data (analog/digital data) block number	x	x	1	10	No Unit		Analog Input			
7296	37297	Same as above: Record number	x	x	0	Saved IT count-1	No Unit		Analog Input			
7297	37298	Same as above: Analog data (Va/Vab)	x	x	-32767	32767	No Unit		Analog Input			
7298	37299	Same as above: Analog data (Vb/Vbc)	x	x	-32767	32767	No Unit		Analog Input			
7299	37300	Same as above: Analog data (Vc/Vca)	x	x	-32767	32767	No Unit		Analog Input			
7300	37301	Same as above: Analog data (Vn)	x	x	-32767	32767	No Unit		Analog Input			
7301	37302	Same as above: Analog data (Ia)	x	x	-32767	32767	No Unit		Analog Input			
7302	37303	Same as above: Analog data (Ib)	x	x	-32767	32767	No Unit		Analog Input			
7303	37304	Same as above: Analog data (Ic)	x	x	-32767	32767	No Unit		Analog Input			
7304	37305	Same as above: Analog data (In)	x	x	-32767	32767	No Unit		Analog Input			
7305	37306	Same as above: Digital data 1	x	x	Refer to (Note 5)		No Unit		Digital Input			
7306	37307	Same as above: Digital data 2	x	x			No Unit		Digital Input			
7307	37308	Same as above: Digital data 3	x	x			No Unit		Digital Input			
7308	37309	Same as above: Digital data 4	x	x			No Unit		Digital Input			
7309	37310	Same as above: Digital data 5	x	x			No Unit		Digital Input			
7310	37311	Same as above: Digital data 6	x	x			No Unit		Digital Input			
7311	37312	Same as above: Digital data 7	x	x			No Unit		Digital Input			
7312	37313	Same as above: Digital data 8	x	x			No Unit		Digital Input			
7313	37314	Same as above: Digital data 9	x	x			No Unit		Digital Input			
7314	37315	Same as above: Digital data 10	x	x			No Unit		Digital Input			
7315	37316	Same as above: Digital data 11	x	x			No Unit		Digital Input			
7316	37317	Same as above: Digital data 12	x	x			No Unit		Digital Input			
7317	37318	(Reserved)										
7318	37319	(Reserved)										
7319	37320	(Reserved)										
7320	37321	(Reserved)										
7321	37322	(Reserved)										
7322	37323	(Reserved)										
7323	37324	(Reserved)										
7324	37325	(Reserved)										
7325	37326	(Reserved)										
7326	37327	(Reserved)										
7327	37328	(Reserved)										
7328	37329	(Reserved)										
7329	37330	(Reserved)										
7330	37331	(Reserved)										
7331	37332	(Reserved)										
7332	37333	(Reserved)										
7333	37334	(Reserved)										
7334	37335	(Reserved)										
7335	37336	(Reserved)										
7336	37337	(Reserved)										
7337	37338	(Reserved)										
7338	37339	(Reserved)										
7339	37340	(Reserved)										
7340	37341	(Reserved)										
7341	37342	(Reserved)										

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks
7342		37343	(Reserved)								
7343	4	37344	(Reserved)								
7344		37345	(Reserved)								
7345		37346	(Reserved)								
7346		37347	(Reserved)								
7347		37348	(Reserved)								
7348		37349	(Reserved)								
7349		37350	(Reserved)								
7350		37351	(Reserved)								
7351		37352	(Reserved)								
7352		37353	(Reserved)								
7374		4	37375	Monitoring data 1 (trip counter (H))	x	x	0	10000	time(s)	0	Digital Input
7375	37376		Monitoring data 2 (trip counter (L))	x	x					Digital Input	
7376	37377		Monitoring data 3 (trip counter ALARM (H))	x	x	1	10000	time(s)	0	Digital Input	
7377	37378		Monitoring data 4 (trip counter ALARM (L))	x	x					Digital Input	
7378	37379		Monitoring data 5 (motor operating time (H))	x	x	0	199999	h	0	Digital Input	
7379	37380		Monitoring data 6 (motor operating time (L))	x	x					Digital Input	
7380	37381		Monitoring data 7 (motor operating time ALARM (H))	x	x	1	199999	h	0	Digital Input	
7381	37382		Monitoring data 8 (motor operating time ALARM (L))	x	x					Digital Input	
7382	37383		Monitoring data 9 (MST1 counter value (H))	x	x	0	999999	s	0	Digital Input	
7383	37384		Monitoring data 10 (MST1 counter value (L))	x	x					Digital Input	
7384	37385		Monitoring data 11 (MST1 ALARM (H))	x	x	0	999999	s	0	Digital Input	
7385	37386		Monitoring data 12 (MST1 ALARM (L))	x	x					Digital Input	
7386	37387		Monitoring data 13 (MST2 counter value (H))	x	x	0	999999	h	0	Digital Input	
7387	37388		Monitoring data 14 (MST2 counter value (L))	x	x					Digital Input	
7388	37389		Monitoring data 15 (MST2 ALARM (H))	x	x	0	999999	h	0	Digital Input	
7389	37390		Monitoring data 16 (MST2 ALARM (L))	x	x					Digital Input	
7390	37391		Monitoring data 17 (THOL counter value (H))	x	x	0	999999	%	0	Digital Input	
7391	37392		Monitoring data 18 (THOL counter value (L))	x	x					Digital Input	
7392	37393		Monitoring data 19 (THOL ALARM (H))	x	x	0	999999	%	0	Digital Input	
7393	37394		Monitoring data 20 (THOL ALARM (L))	x	x					Digital Input	
7394		37395	(Reserved)								
7395		37396	(Reserved)								
7396		37397	(Reserved)								
7397		37398	(Reserved)								
7398		37399	(Reserved)								
7399		37400	(Reserved)								
7400		37401	(Reserved)								
7401		37402	(Reserved)								
7402		37403	(Reserved)								
7403		37404	(Reserved)								
7404		37405	(Reserved)								
7405		37406	(Reserved)								
7406		37407	(Reserved)								
7407		37408	(Reserved)								
7408		37409	(Reserved)								
7409		37410	(Reserved)								
7410		37411	(Reserved)								
7411		37412	(Reserved)								
7412		37413	(Reserved)								
7413		37414	(Reserved)								
7414		37415	(Reserved)								
7415		37416	(Reserved)								
7416		37417	(Reserved)								
7417		37418	(Reserved)								
7418		37419	(Reserved)								
7419		37420	(Reserved)								
7420		37421	(Reserved)								
7421		37422	(Reserved)								
7422		37423	(Reserved)								
7423		37424	(Reserved)								
7424		37425	(Reserved)								
7425		37426	(Reserved)								
7426		37427	(Reserved)								
7427		37428	(Reserved)								
7428		37429	(Reserved)								
7429		37430	(Reserved)								
7430		37431	(Reserved)								
7431		37432	(Reserved)								
7432		37433	(Reserved)								
7433		37434	(Reserved)								
7434		37435	(Reserved)								
7435		37436	(Reserved)								
7436		37437	(Reserved)								
7437		37438	(Reserved)								
7438		37439	(Reserved)								
7439		37440	(Reserved)								
7440		37441	(Reserved)								
7441		37442	(Reserved)								
7442		37443	(Reserved)								
7443		37444	(Reserved)								
7444		37445	(Reserved)								
7445		37446	(Reserved)								
7446		37447	(Reserved)								
7447		37448	(Reserved)								
7448		37449	(Reserved)								
7449		37450	(Reserved)								
7450		37451	(Reserved)								
7451		37452	(Reserved)								
7452		37453	(Reserved)								
7453		37454	(Reserved)								
7454		37455	(Reserved)								
7455		37456	(Reserved)								
7456		37457	(Reserved)								
7457		37458	(Reserved)								
7458		37459	(Reserved)								
7459		37460	(Reserved)								
7460		37461	(Reserved)								
7461		37462	(Reserved)								
7462		37463	(Reserved)								
7463		37464	(Reserved)								
7464		37465	(Reserved)								
7465		37466	(Reserved)								
7466		37467	(Reserved)								
7467		37468	(Reserved)								
7468		37469	(Reserved)								
7469		37470	(Reserved)								
7470		37471	(Reserved)								
7471		37472	(Reserved)								
7472		37473	(Reserved)								
7473		37474	(Reserved)								

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.)	Range (Max.)	Engineering Unit	Scale	Signal Type	Remarks
9800	4	39801	Check LED reset	x	x			No Unit		Digital Input	• Start address = 39801 • Number of access points = 1 (Note 1)
9801		39802	Check event record erasure	x	x			No Unit		Digital Input	• Start address = 39802 • Number of access points = 1 (Note 1)
9802		39803	Check monitoring error erasure	x	x			No Unit		Digital Input	• Start address = 39803 • Number of access points = 1 (Note 1)
9803		39804	Check access record erasure	x	x			No Unit		Digital Input	• Start address = 39804 • Number of access points = 1 (Note 1)
9804		39805	Check accident record erasure	x	x			No Unit		Digital Input	• Start address = 39805 • Number of access points = 1 (Note 1)
9805		39806	Check active group writing	x	x			No Unit		Digital Input	• Start address = 39806 • Number of access points = 1 (Note 1)
9806		39807	Check group 1 setting value data writing	x	x			No Unit		Digital Input	• Start address = 39807 • Number of access points = 1 (Note 1)
9807		39808	Check group 2 setting value data writing	x	x			No Unit		Digital Input	• Start address = 39808 • Number of access points = 1 (Note 1)
9808		39809	Check common setting value data writing	x	x			No Unit		Digital Input	• Start address = 39809 • Number of access points = 1 (Note 1)
9809		39810	Check get event record request	x	x			No Unit		Digital Input	• Start address = 39810 • Number of access points = 1 (Note 1)
9810		39811	Check get monitoring error record request	x	x			No Unit		Digital Input	• Start address = 39811 • Number of access points = 1 (Note 1)
9811		39812	Check get access record request	x	x			No Unit		Digital Input	• Start address = 39812 • Number of access points = 1 (Note 1)
9812		39813	Check get accident record request	x	x			No Unit		Digital Input	• Start address = 39813 • Number of access points = 1 (Note 1)
9813		39814	Check CB status	x	x			No Unit		Digital Input	• Start address = 39814 • Number of access points = 1 (Note 1)
9814		39815	Check open interlock status	x	x			No Unit		Digital Input	• Start address = 39815 • Number of access points = 1 (Note 1)
9815		39816	Check CB open control availability conditions	x	x			No Unit		Digital Input	• Start address = 39816 • Number of access points = 1 (Note 1)
9816		39817	Check close interlock status	x	x			No Unit		Digital Input	• Start address = 39817 • Number of access points = 1 (Note 1)
9817		39818	Check CB close control availability conditions	x	x			No Unit		Digital Input	• Start address = 39818 • Number of access points = 1 (Note 1)
9818		39819	Check CB open control completion	x	x			No Unit		Digital Input	• Start address = 39819 • Number of access points = 1 (Note 1)
9819		39820	Check CB close control completion	x	x			No Unit		Digital Input	• Start address = 39820 • Number of access points = 1 (Note 1)
9820		39821	Check test mode	x	x			No Unit		Digital Input	• Start address = 39821 • Number of access points = 1 (Note 1)
9821		39822	Check test mode setter	x	x			No Unit		Digital Input	• Start address = 39822 • Number of access points = 1 (Note 1)

## Response data list (Note 1)

Address	Data
39801	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39802	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39803	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39804	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39805	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39806	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39807	0: Not completed, 1: Normally completed, 10: Range step, AAAA: Timeout, Other: Abnormal completion
39808	0: Not completed, 1: Normally completed, 10: Range step, AAAA: Timeout, Other: Abnormal completion
39809	0: Not completed, 1: Normally completed, 11: Range step, AAAA: Timeout, Other: Abnormal completion
39810	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39811	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39812	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39813	0: Not completed, 1: Normally completed, AAAA: Timeout, Other: Abnormal completion
39814	0: Closed, 1: Opened
39815	0: Interlock disabled (controllable), 1: Interlock enabled (not controllable)
39816	0: Not controllable, 1: Controllable
39817	0: Interlock disabled (controllable), 1: Interlock enabled (not controllable)
39818	0: Not controllable, 1: Controllable
39819	0: Being controlled, 1: Control completed, 2: No control request, 3: Control failure (timeout), 4: Control failure (same direction control), 5: Control failure (interlock failure), 6: Control failure (no control rights), 7: Control failure (DI starting)
39820	0: Being controlled, 1: Control completed, 2: No control request, 3: Control failure (timeout), 4: Control failure (same direction control), 5: Control failure (interlock failure), 6: Control failure (no control rights), 7: Control failure (DI starting)
39821	0: Normal operation, 1: Test mode
39822	0: Normal operation, 1: Panel, 2: GRIFFIN, 3: MODBUS

(Note 2) Event record item numbers

Item number	Event details
1	DI1 status
2	DI2 status
3	DI3 status
4	DI4 status
5	DI5 status
6	DI6 status
7	DI7 status
8	DI8 status
9	Reserved
10	Reserved
11	Reserved
12	Reserved
13	Reserved
14	DO1 status
15	DO2 status
16	DO3 status
17	DO4 status
18	DO5 status
19	DO6 status
20	DO7 status
21	DO8 status
22	Reserved
23	Reserved
24	Reserved
25	Reserved
26	Reserved
27	Trip counter ALARM
28	Reserved
29	Zero phase voltage monitor: Confirmation
30	Reserved
31	Motor operating time ALARM
32	CB status
33	INTERLOCK signal (OPEN)
34	INTERLOCK signal (CLOSE)
35	CB open controllable
36	CB close controllable
37	CB control successful
38	CB control failed
39	CB OPEN control (local)
40	CB CLOSE control (local)
41	CB CLOSE command
42	CB OPEN command
43	Local/remote
44	
45	
46	
47	Open operation prohibited setting status
48	Close operation prohibited setting status
49	Interlock used/not used setting status
50	Improper selection
51	Control successful
52	No control rights/operation prohibited
53	Same directional control
54	Interlock conditions not satisfied
55	Timeout
56	Close control command
57	Open control command
58	Close-side interlock
59	Open-side interlock
60	CB control DI starting
61	
62	Overcurrent instantaneous (50) element: Stage 1: Zero phase detection
63	Overcurrent instantaneous (50) element: Stage 2: Zero phase detection
64	Negative phase overcurrent (46) element: Stage 1 detection
65	Negative phase overcurrent (46) element: Stage 2 detection
66	Negative phase overcurrent (single-phase open phase) element: Stage 3
67	Overcurrent (50BF) element for CBF detection: G phase detection
68	Overload (49) element: Detection
69	Ground directional instantaneous (67G) element: Stage 1 detection
70	Ground directional instantaneous (67G) element: Stage 2 detection
71	Underpower (37P) element: Stage 1 detection
72	Underpower (37P) element: Stage 2 detection
73	Ground overvoltage (64G) element: Stage 1 detection
74	Ground overvoltage (64G) element: Stage 2 detection
75	Negative phase overvoltage (47) element: Stage 1 detection
76	Negative phase overvoltage (47) element: Stage 2 detection
77	Frequency decrease detection (81UF) element: Stage 1 detection
78	Frequency decrease detection (81UF) element: Stage 2 detection
79	Frequency decrease detection (81UF) element: Stage 3 detection
80	Frequency increase detection (81OF) element: Stage 1 detection
81	Frequency increase detection (81OF) element: Stage 2 detection
82	Frequency increase detection (81OF) element: Stage 3 detection
83	Starting count limitation (66) element: Stage 1 detection
84	Starting count limitation (66) element: Stage 2 detection
85	VTF element: Detection
86	Monitoring error (serious fault) confirmation
87	Monitoring error (minor fault) confirmation
88	Relay lock
89	Monitoring lock
90	UC phase A lock
91	UC phase B lock
92	UC phase C lock
93	UV phase A lock
94	UV phase B lock
95	UV phase C lock
96	OV phase A lock
97	OV phase B lock
98	OV phase C lock
99	Trip counter lock
100	OCNEG3 test
101	THOL test
102	MST1 & 2 test
103	Communication
104	Communication
105	Communication
106	Communication
107	Communication
108	Communication
109	Communication
110	Communication
111	Detect either OC1 phase A, B, or C (Detection OR)
112	Detect either OC2 phase A, B, or C (Detection OR)
113	Detect either OC3 phase A, B, or C (Detection OR)
114	Detect either UC1 phase A, B, or C (Detection OR)
115	Detect either UC2 phase A, B, or C (Detection OR)
116	Detect either CBF phase A, B, or C (Detection OR)
117	Detect either UV1 phase A (AB), B (BC), or C (CA) (Detection OR)
118	Detect either UV2 phase A (AB), B (BC), or C (CA) (Detection OR)
119	Detect either OV1 phase A (AB), B (BC), or C (CA) (Detection OR)
120	Detect either OV2 phase A (AB), B (BC), or C (CA) (Detection OR)
121	Reserved
122	Reserved
123	All elements confirmation OR
124	Pulse signal from the start of saving data until it has completed (excluding the time before the accident)
125	GOOSE1
126	GOOSE2
127	GOOSE3
128	GOOSE4

Item number	Event details
129	GOOSE5
130	GOOSE6
131	GOOSE7
132	GOOSE8
133	GOOSE9
134	GOOSE10
135	GOOSE11
136	GOOSE12
137	GOOSE13
138	GOOSE14
139	GOOSE15
140	GOOSE16
141	GOOSE17
142	GOOSE18
143	GOOSE19
144	GOOSE20
145	GOOSE21
146	GOOSE22
147	GOOSE23
148	GOOSE24
149	GOOSE25
150	GOOSE26
151	GOOSE27
152	GOOSE28
153	GOOSE29
154	GOOSE30
155	GOOSE31
156	GOOSE32
157	GOOSE33
158	GOOSE34
159	GOOSE35
160	GOOSE36
161	GOOSE37
162	CBF/CBFG action conditions (trip signal for other relays)
163	CBF/CBFG action conditions (trip signal for other relays)
164	CBF/CBFG action conditions (trip signal for other relays)
165	OC1 phase A: Confirmation & forced relay control signal OR
166	OC1 phase B: Confirmation & forced relay control signal OR
167	OC1 phase C: Confirmation & forced relay control signal OR
168	OC1 three-phase OR: Confirmation & forced relay control signal OR
169	OC1 zero phase: Confirmation & forced relay control signal OR
170	OC2 phase A: Confirmation & forced relay control signal OR
171	OC2 phase B: Confirmation & forced relay control signal OR
172	OC2 phase C: Confirmation & forced relay control signal OR
173	OC2 three-phase OR: Confirmation & forced relay control signal OR
174	OC2 zero phase: Confirmation & forced relay control signal OR
175	OC3 phase A: Confirmation & forced relay control signal OR
176	OC3 phase B: Confirmation & forced relay control signal OR
177	OC3 phase C: Confirmation & forced relay control signal OR
178	OC3 three-phase OR: Confirmation & forced relay control signal OR
179	OCNEG1: Confirmation & forced relay control signal OR
180	OCNEG2: Confirmation & forced relay control signal OR
181	OCNEG3: Confirmation & forced relay control signal OR
182	UC1 phase A: Confirmation & forced relay control signal OR
183	UC1 phase B: Confirmation & forced relay control signal OR
184	UC1 phase C: Confirmation & forced relay control signal OR
185	UC1 three-phase OR: Confirmation & forced relay control signal OR
186	UC2 phase A: Confirmation & forced relay control signal OR
187	UC2 phase B: Confirmation & forced relay control signal OR
188	UC2 phase C: Confirmation & forced relay control signal OR
189	UC2 three-phase OR: Confirmation & forced relay control signal OR
190	CBF phase A: Confirmation & forced relay control signal OR
191	CBF phase B: Confirmation & forced relay control signal OR
192	CBF phase C: Confirmation & forced relay control signal OR
193	CBF three-phase OR: Confirmation & forced relay control signal OR
194	CBF zero phase: Confirmation & forced relay control signal OR
195	TOL: Confirmation & forced relay control signal OR
196	DIRG1: Confirmation & forced relay control signal OR
197	DIRG2: Confirmation & forced relay control signal OR
198	UP1: Confirmation & forced relay control signal OR
199	UP2: Confirmation & forced relay control signal OR
200	UV1 phase A: Confirmation & forced relay control signal OR
201	UV1 phase B: Confirmation & forced relay control signal OR
202	UV1 phase C: Confirmation & forced relay control signal OR
203	UV1 three-phase OR: Confirmation & forced relay control signal OR
204	UV2 phase A: Confirmation & forced relay control signal OR
205	UV2 phase B: Confirmation & forced relay control signal OR
206	UV2 phase C: Confirmation & forced relay control signal OR
207	UV2 three-phase OR: Confirmation & forced relay control signal OR
208	OV1 phase A: Confirmation & forced relay control signal OR
209	OV1 phase B: Confirmation & forced relay control signal OR
210	OV1 phase C: Confirmation & forced relay control signal OR
211	OV1 three-phase OR: Confirmation & forced relay control signal OR
212	OV2 phase A: Confirmation & forced relay control signal OR
213	OV2 phase B: Confirmation & forced relay control signal OR
214	OV2 phase C: Confirmation & forced relay control signal OR
215	OV2 three-phase OR: Confirmation & forced relay control signal OR
216	OVG1: Confirmation & forced relay control signal OR
217	OVG2: Confirmation & forced relay control signal OR
218	OVNEG1: Confirmation & forced relay control signal OR
219	OVNEG2: Confirmation & forced relay control signal OR
220	UF1: Confirmation & forced relay control signal OR
221	UF2: Confirmation & forced relay control signal OR
222	UF3: Confirmation & forced relay control signal OR
223	OF1: Confirmation & forced relay control signal OR
224	OF2: Confirmation & forced relay control signal OR
225	OF3: Confirmation & forced relay control signal OR
226	MST1: Confirmation & forced relay control signal OR
227	MST2: Confirmation & forced relay control signal OR
228	VTF: Confirmation & forced relay control signal OR
229	Reserved
230	Reserved
231	Reserved
232	Reserved
233	Reserved
234	Reserved
235	Reserved
236	Reserved
237	
238	
239	
240	
241	
242	
243	
244	
245	
246	
247	
248	
249	
250	
251	
252	
253	
254	
255	
256	

**(Note 3) Access record access codes**

Access code	Access details
0001	When group was set
0003	When setting DI detection voltage
0004	When setting data save
0005	When setting password usage
0006	When setting the password
0007	When setting the destination USB connection
0008	When setting the VFD brightness
0009	When setting the trip counter
000A	When setting the motor operation time
000B	When configuring communications (Modbus)
000C	When configuring communications (CC-Link)
000D	When configuring communications (IEC-61850)
0010	When setting the device name
0011	When setting a measured value
0012	When setting the electrical energy
0013	When setting the time information
0014	When setting the control mode
0015	When setting forced DO control
0016	When configuring SNTP
001D	When configuring the PLC
001E	When setting relay setting values
0200	When erasing an accident record
0210	When erasing an error record
0220	When erasing an event record
0240	When setting the time
0300	When starting test settings
0310	When ending test settings
0320	When resetting the LEDs (LED recovery, ALARM recovery, operation)
0340	Starting forced control
0350	Canceling forced control
0360	Monitoring lock ON
0370	Monitoring lock OFF
0380	Starting forced relay control
0390	Canceling forced relay control
0520	When performing a CB open/close control operation

Access source codes	Source of operation
0001	Front panel
0002	PC-HMI
0003	Modbus
0004	IEC61850
0005	CC-Link
0006	Device-side auto clear

**(Note 4) Accident record cause index bit information**

Bit	Modbus address 36638 bit allocation details
0	Either OC1 phase A, B, or C is confirmed (OR confirmation)
1	Overcurrent instantaneous (50) element: Stage 1: Zero phase confirmation
2	Either OC2 phase A, B, or C is confirmed (OR confirmation)
3	Overcurrent instantaneous (50) element: Stage 2: Zero phase confirmation
4	Either OC3 phase A, B, or C is confirmed (OR confirmation)
5	Negative phase overcurrent (46) element: Stage 1 confirmation
6	OCNEG2 and 3 confirmation OR
7	Either UC1 phase A, B, or C is confirmed (Confirmation OR)
8	Either UC2 phase A, B, or C is confirmed (Confirmation OR)
9	Either CBF phase A, B, or C is confirmed (Confirmation OR)
10	Overcurrent (50BF) element for CBF detection: G phase confirmation
11	Overload (49) element: Confirmation
12	Ground directional instantaneous (67G) element: Stage 1 confirmation
13	Ground directional instantaneous (67G) element: Stage 2 confirmation
14	UP1 to UP2 confirmation OR
15	Either UV1 phase A (AB), B (BC), or C (CA) is confirmed (Confirmation OR)

Bit	Modbus address 36639 bit allocation details
0	Either UV2 phase A (AB), B (BC), or C (CA) is confirmed (Confirmation OR)
1	Either OV1 phase A (AB), B (BC), or C (CA) is confirmed (Confirmation OR)
2	Either OV2 phase A (AB), B (BC), or C (CA) is confirmed (Confirmation OR)
3	Ground overvoltage (64G) element: Stage 1 confirmation
4	Ground overvoltage (64G) element: Stage 2 confirmation
5	Negative phase overvoltage (47) element: Stage 1 confirmation
6	Negative phase overvoltage (47) element: Stage 2 confirmation
7	Frequency decrease detection (81UF) element: Stage 1 confirmation
8	Frequency decrease detection (81UF) element: Stage 2 confirmation
9	Frequency decrease detection (81UF) element: Stage 3 confirmation
10	Frequency increase detection (81OF) element: Stage 1 confirmation
11	Frequency increase detection (81OF) element: Stage 2 confirmation
12	Frequency increase detection (81OF) element: Stage 3 confirmation
13	MST1 and 2 confirmation OR
14	VTF element: Confirmation
15	



**(Note 5) Trip data (digital data 1 to 12)**

Bit	Modbus address 37306 bit allocation details
0	DO1 status
1	DO2 status
2	DO3 status
3	DO4 status
4	DO5 status
5	DO6 status
6	DO7 status
7	DO8 status
8	Reserved
9	Reserved
10	Reserved
11	Reserved
12	Reserved
13	-
14	-
15	-

Bit	Modbus address 37307 bit allocation details
0	DI1 status
1	DI2 status
2	DI3 status
3	DI4 status
4	DI5 status
5	DI6 status
6	DI7 status
7	DI8 status
8	Reserved
9	Reserved
10	Reserved
11	Reserved
12	Reserved
13	Reserved
14	Reserved
15	-

Bit	Modbus address 37308 bit allocation details
0	Overcurrent time limit (51) element: Stage 1: Phase A confirmation
1	Overcurrent time limit (51) element: Stage 1: Phase B confirmation
2	Overcurrent time limit (51) element: Stage 1: Phase C confirmation
3	Overcurrent instantaneous (50) element: Stage 1: Zero phase confirmation
4	Overcurrent time limit (51) element: Stage 2: Phase A confirmation
5	Overcurrent time limit (51) element: Stage 2: Phase B confirmation
6	Overcurrent time limit (51) element: Stage 2: Phase C confirmation
7	Overcurrent instantaneous (50) element: Stage 2: Zero phase confirmation
8	Overcurrent instantaneous (50) element: Stage 3: Phase A confirmation
9	Overcurrent instantaneous (50) element: Stage 3: Phase B confirmation
10	Overcurrent instantaneous (50) element: Stage 3: Phase C confirmation
11	Negative phase overcurrent (46) element: Stage 1 confirmation
12	Negative phase overcurrent (46) element: Stage 2 confirmation
13	Negative phase overcurrent (single-phase open phase) element: Stage 3 confirmation
14	Undercurrent (37) element: Stage 1: Phase A confirmation
15	Undercurrent (37) element: Stage 1: Phase B confirmation

Bit	Modbus address 37309 bit allocation details
0	Undercurrent (37) element: Stage 1: Phase C confirmation
1	Undercurrent (37) element: Stage 2: Phase A confirmation
2	Undercurrent (37) element: Stage 2: Phase B confirmation
3	Undercurrent (37) element: Stage 2: Phase C confirmation
4	Overcurrent (50BF) element for CBF detection: Phase A confirmation
5	Overcurrent (50BF) element for CBF detection: Phase B confirmation
6	Overcurrent (50BF) element for CBF detection: Phase C confirmation
7	Overcurrent (50BF) element for CBF detection: G phase confirmation
8	Overload (49) element: Confirmation
9	Ground directional instantaneous (67G) element: Stage 1 confirmation
10	Ground directional instantaneous (67G) element: Stage 2 confirmation
11	Underpower (37P) element: Stage 1 confirmation
12	Underpower (37P) element: Stage 2 confirmation
13	Undervoltage (27) element: Stage 1: Phase A (phase AB) confirmation
14	Undervoltage (27) element: Stage 1: Phase B (phase BC) confirmation
15	Undervoltage (27) element: Stage 1: Phase C (phase CA) confirmation

Bit	Modbus address 37310 bit allocation details
0	Undervoltage (27) element: Stage 2: Phase A (phase AB) confirmation
1	Undervoltage (27) element: Stage 2: Phase B (phase BC) confirmation
2	Undervoltage (27) element: Stage 2: Phase C (phase CA) confirmation
3	Overvoltage (59) element: Stage 1: Phase A (phase AB) confirmation
4	Overvoltage (59) element: Stage 1: Phase B (phase BC) confirmation
5	Overvoltage (59) element: Stage 1: Phase C (phase CA) confirmation
6	Overvoltage (59) element: Stage 2: Phase A (phase AB) confirmation
7	Overvoltage (59) element: Stage 2: Phase B (phase BC) confirmation
8	Overvoltage (59) element: Stage 2: Phase C (phase CA) confirmation
9	Ground overvoltage (64G) element: Stage 1 confirmation
10	Ground overvoltage (64G) element: Stage 2 confirmation
11	Negative phase overvoltage (47) element: Stage 1 confirmation
12	Negative phase overvoltage (47) element: Stage 2 confirmation
13	Frequency (81) element UV element for locking
14	Frequency decrease detection (81UF) element: Stage 1 confirmation
15	Frequency decrease detection (81UF) element: Stage 2 confirmation

Bit	Modbus address 37311 bit allocation details
0	Frequency decrease detection (81UF) element: Stage 3 confirmation
1	Frequency increase detection (81OF) element: Stage 1 confirmation
2	Frequency increase detection (81OF) element: Stage 2 confirmation
3	Frequency increase detection (81OF) element: Stage 3 confirmation
4	Starting count limitation (66) element: Stage 1 confirmation
5	Starting count limitation (66) element: Stage 2 confirmation
6	-
7	-
8	-
9	VTF element: Confirmation
10	Reserved
11	Reserved
12	Reserved
13	Reserved
14	Reserved
15	Reserved

Bit	Modbus address 37312 bit allocation details
0	Trip counter ALARM
1	Reserved
2	Zero phase voltage monitor: Confirmation
3	Zero phase current monitor (if residual type)
4	-
5	-
6	-
7	-
8	-
9	-
10	-
11	-
12	Motor operating time ALARM
13	-
14	-
15	-

Bit	Modbus address 37313 bit allocation details
0	Overcurrent instantaneous (50) element: Stage 1: Phase A detection
1	Overcurrent instantaneous (50) element: Stage 1: Phase B detection
2	Overcurrent instantaneous (50) element: Stage 1: Phase C detection
3	Overcurrent instantaneous (50) element: Stage 1: Zero phase detection
4	Overcurrent instantaneous (50) element: Stage 2: Phase A detection
5	Overcurrent instantaneous (50) element: Stage 2: Phase B detection
6	Overcurrent instantaneous (50) element: Stage 2: Phase C detection
7	Overcurrent instantaneous (50) element: Stage 2: Zero phase detection
8	Overcurrent instantaneous (50) element: Stage 3: Phase A detection
9	Overcurrent instantaneous (50) element: Stage 3: Phase B detection
10	Overcurrent instantaneous (50) element: Stage 3: Phase C detection
11	Negative phase overcurrent (46) element: Stage 1 detection
12	Negative phase overcurrent (46) element: Stage 2 detection
13	Negative phase overcurrent (single-phase open phase) element: Stage 3 detection
14	Undercurrent (37) element: Stage 1: Phase A detection
15	Undercurrent (37) element: Stage 1: Phase B detection

Bit	Modbus address 37314 bit allocation details
0	Undercurrent (37) element: Stage 1: Phase C detection
1	Undercurrent (37) element: Stage 2: Phase A detection
2	Undercurrent (37) element: Stage 2: Phase B detection
3	Undercurrent (37) element: Stage 2: Phase C detection
4	Overcurrent (50BF) element for CBF detection: Phase A detection
5	Overcurrent (50BF) element for CBF detection: Phase B detection
6	Overcurrent (50BF) element for CBF detection: Phase C detection
7	Overcurrent (50BF) element for CBF detection: G phase detection
8	Overload (49) element: Detection
9	Ground directional instantaneous (67G) element: Stage 1 detection
10	Ground directional instantaneous (67G) element: Stage 2 detection
11	Underpower (37P) element: Stage 1 detection
12	Underpower (37P) element: Stage 2 detection
13	Undervoltage (27) element: Stage 1: Phase A (phase AB) detection
14	Undervoltage (27) element: Stage 1: Phase B (phase BC) detection
15	Undervoltage (27) element: Stage 1: Phase C (phase CA) detection

Bit	Modbus address 37315 bit allocation details
0	Undervoltage (27) element: Stage 2: Phase A (phase AB) detection
1	Undervoltage (27) element: Stage 2: Phase B (phase BC) detection
2	Undervoltage (27) element: Stage 2: Phase C (phase CA) detection
3	Overvoltage (59) element: Stage 1: Phase A (phase AB) detection
4	Overvoltage (59) element: Stage 1: Phase B (phase BC) detection
5	Overvoltage (59) element: Stage 1: Phase C (phase CA) detection
6	Overvoltage (59) element: Stage 2: Phase A (phase AB) detection
7	Overvoltage (59) element: Stage 2: Phase B (phase BC) detection
8	Overvoltage (59) element: Stage 2: Phase C (phase CA) detection
9	Ground overvoltage (64G) element: Stage 1 detection
10	Ground overvoltage (64G) element: Stage 2 detection
11	Negative phase overvoltage (47) element: Stage 1 detection
12	Negative phase overvoltage (47) element: Stage 2 detection
13	Frequency decrease detection (81UF) element: Stage 1 detection
14	Frequency decrease detection (81UF) element: Stage 2 detection
15	Frequency decrease detection (81UF) element: Stage 3 detection

Bit	Modbus address 37316 bit allocation details
0	Frequency increase detection (81OF) element: Stage 1 detection
1	Frequency increase detection (81OF) element: Stage 2 detection
2	Frequency increase detection (81OF) element: Stage 3 detection
3	Starting count limitation (66) element: Stage 1 detection
4	Starting count limitation (66) element: Stage 2 detection
5	-
6	-
7	-
8	VTF element: Detection
9	Reserved
10	Reserved
11	Reserved
12	Reserved
13	Reserved
14	Reserved
15	-

Bit	Modbus address 37317 bit allocation details
0	Monitoring error (serious fault) confirmation
1	Monitoring error (minor fault) confirmation
2	-
3	-
4	-
5	-
6	-
7	-
8	-
9	-
10	-
11	-
12	-
13	-
14	-
15	-

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
0	16	3	40001 Group 1 set/get: Rated motor current	x	x	100	500	5	A	2	Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data.
1			40002 Group 1 set/get: Motor start starting current	x	x	130	180	1	%	0	Analog Value	
2			40003 Group 1 set/get: Motor start completion current	x	x	100	130	1	%	0	Analog Value	
3			40004 Group 1 set/get: Motor operation completion current	x	x	5	50	1	%	0	Analog Value	
4			40005 Group 1 set/get: Rated motor voltage	x	x	1000	1250	1	V	1	Analog Value	
5			40006 Group 1 set/get: Number of current averaging cycles	x	x	1	32	1	No Unit	0	Analog Value	
6			40007 Group 1 set/get: OC1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
7			40008 Group 1 set/get: OC1 OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	
8			40009 Group 1 set/get: OC1 operating current	x	x	200	2000	2	%	0	Analog Value	
9			40010 Group 1 set/get: OC1 operating time scaling factor	x	x	4	240	1	No Unit	0	Analog Value	
10			40011 Group 1 set/get: OC1 operating characteristic	x	x	0	1	1	No Unit	0	Analog Value	
11			40012 Group 1 set/get: OC1 IEC characteristics OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
12			40013 Group 1 set/get: OCG1 use/do not use	x	x	0	1	x	No Unit	0	Analog Value	
13			40014 Group 1 set/get: OCG1 operating current *	x	x	10 *1 1 *2	1000	5 *1 1 *2	mA *1 A *2	1	Analog Value	On MODBUS: • Start address = 40001+1*j • Number of access points = 1*j • i+j<=256 (i=0 to 255, j=1 to 256)
14			40015 Group 1 set/get: OCG1 operating time	x	x	0	1000	1	s	2	Analog Value	→ When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
15			40016 Group 1 set/get: OC2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
16			40017 Group 1 set/get: OC2 OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	For exclusive use of manufacturer: Items that are applicable to the VFD and not applicable to Modbus in the items list are fixed as 0 when read. They also cannot be written.
17			40018 Group 1 set/get: OC2 operating current	x	x	200	2000	2	%	0	Analog Value	
18			40019 Group 1 set/get: OC2 operating time scaling factor	x	x	4	240	1	No Unit	0	Analog Value	
19			40020 Group 1 set/get: OC2 operating characteristic	x	x	0	1	1	No Unit	0	Analog Value	
20			40021 Group 1 set/get: OC2 IEC characteristics OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
21			40022 Group 1 set/get: OCG2 use/do not use	x	x	0	1	x	No Unit	0	Analog Value	
22			40023 Group 1 set/get: OCG2 operating current *	x	x	10 *1 1 *2	1000	5 *1 1 *2	mA *1 A *2	1	Analog Value	
23			40024 Group 1 set/get: OCG2 operating time	x	x	0	1000	1	s	2	Analog Value	
24			40025 Group 1 set/get: OC3 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
25			40026 Group 1 set/get: OC3 OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	
26			40027 Group 1 set/get: OC3 operating current	x	x	50	2000	1	%	0	Analog Value	
27			40028 Group 1 set/get: OC3 operating time	x	x	0	1000	1	s	2	Analog Value	
28			40029 Group 1 set/get: OCN1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
29			40030 Group 1 set/get: OCN1 operating current	x	x	25	100	1	%	0	Analog Value	
30			40031 Group 1 set/get: OCN1 operating time	x	x	0	100	1	s	1	Analog Value	
31			40032 Group 1 set/get: OCN2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
32			40033 Group 1 set/get: OCN2 operating current	x	x	25	100	1	%	0	Analog Value	
33			40034 Group 1 set/get: OCN2 operating time	x	x	0	100	1	s	1	Analog Value	
34			40035 Group 1 set/get: OCN3 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
35			40036 Group 1 set/get: OCN3 load current	x	x	20	100	1	%	0	Analog Value	
36			40037 Group 1 set/get: OCN3 open phase current	x	x	10	50	1	%	0	Analog Value	
37			40038 Group 1 set/get: UC1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
38			40039 Group 1 set/get: UC1 output three-phase OR/AND selection	x	x	0	1	x	No Unit	0	Analog Value	
39			40040 Group 1 set/get: UC1 UC detection method Pick1/Pick2	x	x	0	1	x	No Unit	0	Analog Value	
40			40041 Group 1 set/get: UC1 operating current	x	x	25	100	1	%	0	Analog Value	
41			40042 Group 1 set/get: UC1 minimum current sensitivity	x	x	25	100	1	%	0	Analog Value	
42			40043 Group 1 set/get: UC1 operating time	x	x	0	6000	1	s	1	Analog Value	
43			40044 Group 1 set/get: UC2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
44			40045 Group 1 set/get: UC2 output three-phase OR/AND selection	x	x	0	1	x	No Unit	0	Analog Value	
45			40046 Group 1 set/get: UC2 UC detection method Pick1/Pick2	x	x	0	1	x	No Unit	0	Analog Value	
46			40047 Group 1 set/get: UC2 operating current	x	x	25	100	1	%	0	Analog Value	
47			40048 Group 1 set/get: UC2 minimum current sensitivity	x	x	25	100	1	%	0	Analog Value	
48			40049 Group 1 set/get: UC2 operating time	x	x	0	6000	1	s	1	Analog Value	
49			40050 Group 1 set/get: CBF OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
50			40051 Group 1 set/get: CBF OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
51			40052 Group 1 set/get: CBF operating current	x	x	15	200	1	%	0	Analog Value	
52			40053 Group 1 set/get: CBF operating time	x	x	10	1000	5	mA	1	Analog Value	
53			40054 Group 1 set/get: CBF operating time	x	x	0	1000	1	s	2	Analog Value	
54			40055 Group 1 set/get: THOL OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
55			40056 Group 1 set/get: THOL COLD/HOT characteristic selection	x	x	0	1	x	No Unit	0	Analog Value	
56			40057 Group 1 set/get: THOL OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	
57			40058 Group 1 set/get: THOL operating current	x	x	105	150	1	%	0	Analog Value	
58			40059 Group 1 set/get: THOL operating time scaling factor	x	x	8	24	1	No Unit	0	Analog Value	
59			40060 Group 1 set/get: THOL negative phase heat multiplying factor	x	x	1	10	1	No Unit	0	Analog Value	
60			40061 Group 1 set/get: DIRG maximum sensitivity angle	x	x	0	359	1	°LAG	0	Analog Value	
61			40062 Group 1 set/get: DIRG1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
62			40063 Group 1 set/get: DIRG1 operating voltage	x	x	20	1000	1	V	1	Analog Value	
63			40064 Group 1 set/get: DIRG1 operating current *	x	x	10 *1 1 *2	1000	5 *1 1 *2	mA *1 A *2	1	Analog Value	
64			40065 Group 1 set/get: DIRG1 operating time	x	x	0	1000	1	s	2	Analog Value	
65			40066 Group 1 set/get: DIRG2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
66			40067 Group 1 set/get: DIRG2 operating voltage	x	x	20	1000	1	V	1	Analog Value	
67			40068 Group 1 set/get: DIRG2 operating current *	x	x	10 *1 1 *2	1000	5 *1 1 *2	mA *1 A *2	1	Analog Value	
68			40069 Group 1 set/get: DIRG2 operating time	x	x	0	1000	1	s	2	Analog Value	
69			40070 Group 1 set/get: UP1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
70			40071 Group 1 set/get: UP1 operating current	x	x	1	30	1	%	0	Analog Value	
71			40072 Group 1 set/get: UP1 operating time	x	x	0	100	1	s	1	Analog Value	
72			40073 Group 1 set/get: UP2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
73			40074 Group 1 set/get: UP2 operating current	x	x	1	30	1	%	0	Analog Value	
74			40075 Group 1 set/get: UP2 operating time	x	x	0	100	1	s	1	Analog Value	
75			40076 Group 1 set/get: UV1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
76			40077 Group 1 set/get: UV1 USP (phase voltage)/UVS (line voltage) selection	x	x	0	1	x	No Unit	0	Analog Value	
77			40078 Group 1 set/get: UV1 output three-phase OR/AND selection	x	x	0	1	x	No Unit	0	Analog Value	
78			40079 Group 1 set/get: UV1 operating voltage	x	x	200	1200	1	V	1	Analog Value	
79			40080 Group 1 set/get: UV1 operating time	x	x	0	1000	1	s	2	Analog Value	
80			40081 Group 1 set/get: UV2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
81			40082 Group 1 set/get: UV2 USP (phase voltage)/UVS (line voltage) selection	x	x	0	1	x	No Unit	0	Analog Value	
82			40083 Group 1 set/get: UV2 output three-phase OR/AND selection	x	x	0	1	x	No Unit	0	Analog Value	
83			40084 Group 1 set/get: UV2 operating voltage	x	x	200	1200	1	V	1	Analog Value	
84			40085 Group 1 set/get: UV2 operating time	x	x	0	1000	1	s	2	Analog Value	
85			40086 Group 1 set/get: OV1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
86			40087 Group 1 set/get: OV1 OVP (phase voltage)/OVS (line voltage) selection	x	x	0	1	x	No Unit	0	Analog Value	
87			40088 Group 1 set/get: OV1 operating voltage	x	x	200	2000	1	V	1	Analog Value	
88			40089 Group 1 set/get: OV1 operating time	x	x	0	1000	1	s	2	Analog Value	
89			40090 Group 1 set/get: OV2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
90			40091 Group 1 set/get: OV2 OVP (phase voltage)/OVS (line voltage) selection	x	x	0	1	x	No Unit	0	Analog Value	
91			40092 Group 1 set/get: OV2 operating voltage	x	x	200	2000	1	V	1	Analog Value	
92			40093 Group 1 set/get: OV2 operating time	x	x	0	1000	1	s	2	Analog Value	
93			40094 Group 1 set/get: OVG1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
94			40095 Group 1 set/get: OVG1 operating voltage	x	x	20	1000	1	V	1	Analog Value	
95			40096 Group 1 set/get: OVG1 operating time	x	x	0	1000	1	s	2	Analog Value	
96			40097 Group 1 set/get: OVG2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
97			40098 Group 1 set/get: OVG2 operating voltage	x	x	20	1000	1	V	1	Analog Value	
98			40099 Group 1 set/get: OVG2 operating time	x	x	0	1000	1	s	2	Analog Value	
99			40100 Group 1 set/get: OVNEG1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
100			40101 Group 1 set/get: OVNEG1 operating voltage	x	x	20	1000	1	V	1	Analog Value	
101			40102 Group 1 set/get: OVNEG1 operating time	x	x	0	100	1	s	1	Analog Value	
102			40103 Group 1 set/get: OVNEG2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
103			40104 Group 1 set/get: OVNEG2 operating voltage	x	x	20	1000	1	V	1	Analog Value	
104			40105 Group 1 set/get: OVNEG2 operating time	x	x	0	100	1	s	1	Analog Value	
105			40106 For exclusive use of manufacturer									
106			40107 Group 1 set/get: UF1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
107			40108 Group 1 set/get: UF1 operating frequency (difference from rated frequency)	x	x	-50	-5	1	Hz	1	Analog Value	
108			40109 Group 1 set/get: UF1 operating time	x	x	1	600	1	s	1	Analog Value	
109			40110 Group 1 set/get: UF2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
110			40111 Group 1 set/get: UF2 operating frequency (difference from rated frequency)	x	x	-50	-5	1	Hz	1	Analog Value	
111			40112 Group 1 set/get: UF2 operating time	x	x	1	600	1	s	1	Analog Value	
112			40113 Group 1 set/get: UF3 OFF: Do not use, ON: Use	x	x	0						

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
154		40155	(Reserved)									
155		40156	Group 1 set/get: Voltage reading method 0: Line, 1: Phase	x	x	0	1	1	No Unit	0	Analog Value	
156		40157	Group 1 set/get: VT input 0: Three-phase, 1: Two-phase	x	x	0	1	1	No Unit	0	Analog Value	
157		40158	(Reserved)									
158	16 3	40159	(Reserved)									
159		40160	(Reserved)									
160		40161	(Reserved)									
161		40162	(Reserved)									
162		40163	(Reserved)									
163		40164	(Reserved)									
164		40165	(Reserved)									
165		40166	(Reserved)									
166		40167	(Reserved)									
167		40168	(Reserved)									
168		40169	(Reserved)									
169		40170	(Reserved)									
170		40171	(Reserved)									
171		40172	(Reserved)									
172		40173	(Reserved)									
173		40174	(Reserved)									
174		40175	(Reserved)									
175		40176	(Reserved)									
176		40177	(Reserved)									
177		40178	(Reserved)									
178		40179	(Reserved)									
179		40180	(Reserved)									
180		40181	(Reserved)									
181		40182	(Reserved)									
182		40183	(Reserved)									
183		40184	(Reserved)									
184		40185	(Reserved)									
185		40186	(Reserved)									
186		40187	(Reserved)									
187		40188	(Reserved)									
188		40189	(Reserved)									
189		40190	(Reserved)									
190		40191	(Reserved)									
191		40192	(Reserved)									
192		40193	(Reserved)									
193		40194	(Reserved)									
194		40195	(Reserved)									
195		40196	(Reserved)									
196		40197	(Reserved)									
197		40198	(Reserved)									
198		40199	(Reserved)									
199		40200	(Reserved)									
200		40201	(Reserved)									
201		40202	(Reserved)									
202		40203	(Reserved)									
203		40204	(Reserved)									
204		40205	(Reserved)									
205		40206	(Reserved)									
206		40207	(Reserved)									
207		40208	(Reserved)									
208		40209	(Reserved)									
209		40210	(Reserved)									
210		40211	(Reserved)									
211		40212	(Reserved)									
212		40213	(Reserved)									
213		40214	(Reserved)									
214		40215	(Reserved)									
215		40216	(Reserved)									
216		40217	(Reserved)									
217		40218	(Reserved)									
218		40219	(Reserved)									
219		40220	(Reserved)									
220		40221	(Reserved)									
221		40222	(Reserved)									
222		40223	(Reserved)									
223		40224	(Reserved)									
224		40225	(Reserved)									
225		40226	(Reserved)									
226		40227	(Reserved)									
227		40228	(Reserved)									
228		40229	(Reserved)									
229		40230	(Reserved)									
230		40231	(Reserved)									
231		40232	(Reserved)									
232		40233	(Reserved)									
233		40234	(Reserved)									
234		40235	(Reserved)									
235		40236	(Reserved)									
236		40237	(Reserved)									
237		40238	(Reserved)									
238		40239	(Reserved)									
239		40240	(Reserved)									
240		40241	(Reserved)									
241		40242	(Reserved)									
242		40243	(Reserved)									
243		40244	(Reserved)									
244		40245	(Reserved)									
245		40246	(Reserved)									
246		40247	(Reserved)									
247		40248	(Reserved)									
248		40249	(Reserved)									
249		40250	(Reserved)									
250		40251	(Reserved)									
251		40252	(Reserved)									
252		40253	(Reserved)									
253		40254	(Reserved)									
254		40255	(Reserved)									
255		40256	(Reserved)									
500	16 3	40501	Group 2 set/get: Rated motor current	x	x	100	500	5	A	2	Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data.
501		40502	Group 2 set/get: Motor start starting current	x	x	130	180	1	%	0	Analog Value	With a "Set setting value" request from the master station as Function Code: 16, the slave will respond with (MODBUS send) the response data.
502		40503	Group 2 set/get: Motor start completion current	x	x	100	130	1	%	0	Analog Value	On MODBUS: • Start address = 40501+1*i • Number of access points = 1*j • i+j<=256 (i=0 to 255, j=1 to 256)
503		40504	Group 2 set/get: Motor operation completion current	x	x	5	50	1	%	0	Analog Value	→ When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
504		40505	Group 2 set/get: Rated motor voltage	x	x	1000	1250	1	V	1	Analog Value	For exclusive use of manufacturer: Items that are applicable to the VFD and not applicable to Modbus in the items list are fixed as 0 when read. They also cannot be written.
505		40506	Group 2 set/get: Number of current averaging cycles	x	x	1	32	1	No Unit	0	Analog Value	* The setting value depending on the zero-sequence current type.
506		40507	Group 2 set/get: OC1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	*1: ZCT Type
507		40508	Group 2 set/get: OC1 OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	*2: 5A Type
508		40509	Group 2 set/get: OC1 operating current	x	x	200	2000	2	%	0	Analog Value	
509		40510	Group 2 set/get: OC1 operating time scaling factor	x	x	4	240	1	No Unit	0	Analog Value	
510		40511	Group 2 set/get: OC1 operating characteristic	x	x	0	1	1	No Unit	0	Analog Value	
511		40512	Group 2 set/get: OC1 IEC characteristics OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
512		40513	Group 2 set/get: OCG1 use/do not use	x	x	0	1	x	No Unit	0	Analog Value	
513		40514	Group 2 set/get: OCG1 operating current *	x	x	10 *1 1 *2	1000	5 *1 1 *2	mA *1 A *2	1	Analog Value	
514		40515	Group 2 set/get: OCG1 operating time	x	x	0	1000	1	s	2	Analog Value	
515		40516	Group 2 set/get: OC2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
516		40517	Group 2 set/get: OC2 OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	
517		40518	Group 2 set/get: OC2 operating current	x	x	200	2000	2	%	0	Analog Value	
518		40519	Group 2 set/get: OC2 operating time scaling factor	x	x	4	240	1	No Unit	0	Analog Value	
519		40520	Group 2 set/get: OC2 operating characteristic	x	x	0	1	1	No Unit	0	Analog Value	
520		40521	Group 2 set/get: OC2 IEC characteristics OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
521		40522	Group 2 set/get: OCG2 use/do not use	x	x	0	1	x	No Unit	0	Analog Value	
522		40523	Group 2 set/get: OCG2 operating current *	x	x	10 *1 1 *2	1000	5 *1 1 *2	mA *1 A *2	1	Analog Value	
523		40524	Group 2 set/get: OCG2 operating time	x	x	0	1000	1	s	2	Analog Value	
524		40525	Group 2 set/get: OC3 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
525		40526	Group 2 set/get: OC3 OFF: Averaging OFF, ON: Averaging ON	x	x	0	1	x	No Unit	0	Analog Value	
526		40527	Group 2 set/get: OC3 operating current	x	x	50	2000	1	%	0	Analog Value	
527		40528	Group 2 set/get: OC3 operating time	x	x	0	1000	1	s	2	Analog Value	
528		40529	Group 2 set/get: OCNEG1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
529		40530	Group 2 set/get: OCNEG1 operating current	x	x	25	100	1	%	0	Analog Value	
530		40531	Group 2 set/get: OCNEG1 operating time	x	x	0	100	1	s	1	Analog Value	
531		40532	Group 2 set/get: OCNEG2 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
532		40533	Group 2 set/get: OCNEG2 operating current	x	x	25	100	1	%	0	Analog Value	
533		40534	Group 2 set/get: OCNEG2 operating time	x	x	0	100	1	s	1	Analog Value	
534		40535	Group 2 set/get: OCNEG3 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
535		40536	Group 2 set/get: OCNEG3 load current	x	x	20	100	1	%	0	Analog Value	
536		40537	Group 2 set/get: OCNEG3 open phase current	x	x	10	50	1	%	0	Analog Value	
537		40538	Group 2 set/get: UC1 OFF: Do not use, ON: Use	x	x	0	1	x	No Unit	0	Analog Value	
538		40539	Group 2 set/get: UC1 output three-phase OR/AND selection	x	x	0	1	x	No Unit	0	Analog Value	
539		40540	Group 2 set/get: UC1 UC detection method Pick1/Pick2	x	x	0	1	x	No Unit	0	Analog Value	
540		40541	Group 2 set/get: UC1 operating current	x	x	25	100	1	%	0	Analog Value	
541		40542	Group 2 set/get: UC1 minimum current sensitivity	x	x	25	100	1	%	0	Analog Value	



Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
686		40687	(Reserved)									
687		40688	(Reserved)									
688		40689	(Reserved)									
689		40690	(Reserved)									
690		40691	(Reserved)									
691		40692	(Reserved)									
692		40693	(Reserved)									
693		40694	(Reserved)									
694	16	3	40695 (Reserved)									
695		40696	(Reserved)									
696		40697	(Reserved)									
697		40698	(Reserved)									
698		40699	(Reserved)									
699		40700	(Reserved)									
700		40701	(Reserved)									
701		40702	(Reserved)									
702		40703	(Reserved)									
703		40704	(Reserved)									
704		40705	(Reserved)									
705		40706	(Reserved)									
706		40707	(Reserved)									
707		40708	(Reserved)									
708		40709	(Reserved)									
709		40710	(Reserved)									
710		40711	(Reserved)									
711		40712	(Reserved)									
712		40713	(Reserved)									
713		40714	(Reserved)									
714		40715	(Reserved)									
715		40716	(Reserved)									
716		40717	(Reserved)									
717		40718	(Reserved)									
718		40719	(Reserved)									
719		40720	(Reserved)									
720		40721	(Reserved)									
721		40722	(Reserved)									
722		40723	(Reserved)									
723		40724	(Reserved)									
724		40725	(Reserved)									
725		40726	(Reserved)									
726		40727	(Reserved)									
727		40728	(Reserved)									
728		40729	(Reserved)									
729		40730	(Reserved)									
730		40731	(Reserved)									
731		40732	(Reserved)									
732		40733	(Reserved)									
733		40734	(Reserved)									
734		40735	(Reserved)									
735		40736	(Reserved)									
736		40737	(Reserved)									
737		40738	(Reserved)									
738		40739	(Reserved)									
739		40740	(Reserved)									
740		40741	(Reserved)									
741		40742	(Reserved)									
742		40743	(Reserved)									
743		40744	(Reserved)									
744		40745	(Reserved)									
745		40746	(Reserved)									
746		40747	(Reserved)									
747		40748	(Reserved)									
748		40749	(Reserved)									
749		40750	(Reserved)									
750		40751	(Reserved)									
751		40752	(Reserved)									
752		40753	(Reserved)									
753		40754	(Reserved)									
754		40755	(Reserved)									
755		40756	(Reserved)									
1000	16	3	41001 Group 1 start operation: Rated motor current	x	x				Same as group 1 set/get setting value.		Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data. With a "Set setting value" request from the master station as Function Code: 16, the slave will respond with (MODBUS send) the response data. On MODBUS: • Start address = 41001+1* • Number of access points = 1* • i+j<=256 (i=0 to 255, j=1 to 256) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS. If out of range or out of step, the slave will respond with an error status with the 39807 completion check. When start operation for a setting value is received, the slave will respond (MODBUS send) with 05 ACKNOWLEDGE. • When any kind of data is received in a reserved area, the slave will notify the master of the error with the check group 1 setting value data writing processing. For exclusive use of manufacturer: Items that are applicable to the VFD and not applicable to Modbus in the items list are fixed as 0 when read. They also cannot be written.
1001			41002 Group 1 start operation: Motor start starting current	x	x				Same as group 1 set/get setting value.		Analog Value	
1002			41003 Group 1 start operation: Motor start completion current	x	x				Same as group 1 set/get setting value.		Analog Value	
1003			41004 Group 1 start operation: Motor operation completion current	x	x				Same as group 1 set/get setting value.		Analog Value	
1004			41005 Group 1 start operation: Rated motor voltage	x	x				Same as group 1 set/get setting value.		Analog Value	
1005			41006 Group 1 start operation: Number of current averaging cycles	x	x				Same as group 1 set/get setting value.		Analog Value	
1006			41007 Group 1 start operation: OC1 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1007			41008 Group 1 start operation: OC1 OFF: Averaging OFF, ON: Averaging ON	x	x				Same as group 1 set/get setting value.		Analog Value	
1008			41009 Group 1 start operation: OC1 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1009			41010 Group 1 start operation: OC1 operating time scaling factor	x	x				Same as group 1 set/get setting value.		Analog Value	
1010			41011 Group 1 start operation: OC1 operating characteristic	x	x				Same as group 1 set/get setting value.		Analog Value	
1011			41012 Group 1 start operation: OC1 IEC characteristics OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1012			41013 Group 1 start operation: OCG1 use/do not use	x	x				Same as group 1 set/get setting value.		Analog Value	
1013			41014 Group 1 start operation: OCG1 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1014			41015 Group 1 start operation: OCG1 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1015			41016 Group 1 start operation: OC2 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1016			41017 Group 1 start operation: OC2 OFF: Averaging OFF, ON: Averaging ON	x	x				Same as group 1 set/get setting value.		Analog Value	
1017			41018 Group 1 start operation: OC2 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1018			41019 Group 1 start operation: OC2 operating time scaling factor	x	x				Same as group 1 set/get setting value.		Analog Value	
1019			41020 Group 1 start operation: OC2 operating characteristic	x	x				Same as group 1 set/get setting value.		Analog Value	
1020			41021 Group 1 start operation: OC2 IEC characteristics OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1021			41022 Group 1 start operation: OCG2 use/do not use	x	x				Same as group 1 set/get setting value.		Analog Value	
1022			41023 Group 1 start operation: OCG2 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1023			41024 Group 1 start operation: OCG2 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1024			41025 Group 1 start operation: OC3 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1025			41026 Group 1 start operation: OC3 OFF: Averaging OFF, ON: Averaging ON	x	x				Same as group 1 set/get setting value.		Analog Value	
1026			41027 Group 1 start operation: OC3 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1027			41028 Group 1 start operation: OC3 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1028			41029 Group 1 start operation: OCNEG1 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1029			41030 Group 1 start operation: OCNEG1 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1030			41031 Group 1 start operation: OCNEG1 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1031			41032 Group 1 start operation: OCNEG2 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1032			41033 Group 1 start operation: OCNEG2 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1033			41034 Group 1 start operation: OCNEG2 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1034			41035 Group 1 start operation: OCNEG3 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1035			41036 Group 1 start operation: OCNEG3 load current	x	x				Same as group 1 set/get setting value.		Analog Value	
1036			41037 Group 1 start operation: OCNEG3 open phase current	x	x				Same as group 1 set/get setting value.		Analog Value	
1037			41038 Group 1 start operation: UC1 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1038			41039 Group 1 start operation: UC1 output three-phase OR/AND selection	x	x				Same as group 1 set/get setting value.		Analog Value	
1039			41040 Group 1 start operation: UC1 UC detection method Pick1/Pick2	x	x				Same as group 1 set/get setting value.		Analog Value	
1040			41041 Group 1 start operation: UC1 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1041			41042 Group 1 start operation: UC1 minimum current sensitivity	x	x				Same as group 1 set/get setting value.		Analog Value	
1042			41043 Group 1 start operation: UC1 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1043			41044 Group 1 start operation: UC2 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1044			41045 Group 1 start operation: UC2 output three-phase OR/AND selection	x	x				Same as group 1 set/get setting value.		Analog Value	
1045			41046 Group 1 start operation: UC2 UC detection method Pick1/Pick2	x	x				Same as group 1 set/get setting value.		Analog Value	
1046			41047 Group 1 start operation: UC2 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1047			41048 Group 1 start operation: UC2 minimum current sensitivity	x	x				Same as group 1 set/get setting value.		Analog Value	
1048			41049 Group 1 start operation: UC2 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1049			41050 Group 1 start operation: CBF OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1050			41051 Group 1 start operation: CBF OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1051			41052 Group 1 start operation: CBF operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1052			41053 Group 1 start operation: CBF operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1053			41054 Group 1 start operation: CBF operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1054			41055 Group 1 start operation: THOL OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1055			41056 Group 1 start operation: THOL COLD/HOT characteristic selection	x	x				Same as group 1 set/get setting value.		Analog Value	
1056			41057 Group 1 start operation: THOL OFF: Averaging OFF, ON: Averaging ON	x	x				Same as group 1 set/get setting value.		Analog Value	
1057			41058 Group 1 start operation: THOL operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1058			41059 Group 1 start operation: THOL operating time scaling factor	x	x				Same as group 1 set/get setting value.		Analog Value	
1059			41060 Group 1 start operation: THOL negative phase heat multiplying factor	x	x				Same as group 1 set/get setting value.		Analog Value	
1060			41061 Group 1 start operation: DIRG maximum sensitivity angle	x	x				Same as group 1 set/get setting value.		Analog Value	
1061			41062 Group 1 start operation: DIRG1 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1062			41063 Group 1 start operation: DIRG1 operating voltage	x	x				Same as group 1 set/get setting value.		Analog Value	
1063			41064 Group 1 start operation: DIRG1 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1064			41065 Group 1 start operation: DIRG1 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1065			41066 Group 1 start operation: DIRG2 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1066			41067 Group 1 start operation: DIRG2 operating voltage	x	x				Same as group 1 set/get setting value.		Analog Value	
1067			41068 Group 1 start operation: DIRG2 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1068			41069 Group 1 start operation: DIRG2 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1069			41070 Group 1 start operation: UP1 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1070			41071 Group 1 start operation: UP1 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1071			41072 Group 1 start operation: UP1 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1072			41073 Group 1 start operation: UP2 OFF: Do not use, ON: Use	x	x				Same as group 1 set/get setting value.		Analog Value	
1073			41074 Group 1 start operation: UP2 operating current	x	x				Same as group 1 set/get setting value.		Analog Value	
1074			41075 Group 1 start operation: UP2 operating time	x	x				Same as group 1 set/get setting value.		Analog Value	
1075			41076 Group 1 start operation: UV1 OFF: Do not use, ON: Use	x	x							

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
1082		41083	Group 1 start operation: UV2 output three-phase OR/AND selection	x	x						Analog Value	
1083		41084	Group 1 start operation: UV2 operating voltage	x	x						Analog Value	
1084		41085	Group 1 start operation: UV2 operating time	x	x						Analog Value	
1085		41086	Group 1 start operation: OV1 OFF: Do not use, ON: Use	x	x						Analog Value	
1086		41087	Group 1 start operation: OV1 OVP (phase voltage)/OVS (line voltage) selection	x	x						Analog Value	
1087		41088	Group 1 start operation: OV1 operating voltage	x	x						Analog Value	
1088		41089	Group 1 start operation: OV1 operating time	x	x						Analog Value	
1089		41090	Group 1 start operation: OV2 OFF: Do not use, ON: Use	x	x						Analog Value	
1090	16 3	41091	Group 1 start operation: OV2 OVP (phase voltage)/OVS (line voltage) selection	x	x						Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data.
1091		41092	Group 1 start operation: OV2 operating voltage	x	x						Analog Value	
1092		41093	Group 1 start operation: OV2 operating time	x	x						Analog Value	
1093		41094	Group 1 start operation: OVG1 OFF: Do not use, ON: Use	x	x						Analog Value	
1094		41095	Group 1 start operation: OVG1 operating voltage	x	x						Analog Value	
1095		41096	Group 1 start operation: OVG1 operating time	x	x						Analog Value	
1096		41097	Group 1 start operation: OVG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1097		41098	Group 1 start operation: OVG2 operating voltage	x	x						Analog Value	
1098		41099	Group 1 start operation: OVG2 operating time	x	x						Analog Value	
1099		41100	Group 1 start operation: OVNEG1 OFF: Do not use, ON: Use	x	x						Analog Value	
1100		41101	Group 1 start operation: OVNEG1 operating voltage	x	x						Analog Value	
1101		41102	Group 1 start operation: OVNEG1 operating time	x	x						Analog Value	
1102		41103	Group 1 start operation: OVNEG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1103		41104	Group 1 start operation: OVNEG2 operating voltage	x	x						Analog Value	
1104		41105	Group 1 start operation: OVNEG2 operating time	x	x						Analog Value	
1105		41106	For exclusive use of manufacturer									
1106		41107	Group 1 start operation: UF1 OFF: Do not use, ON: Use	x	x						Analog Value	On MODBUS: • Start address = 41001+1* • Number of access points = 1* • i+j<=256 (i=0 to 255, j=1 to 256)
1107		41108	Group 1 start operation: UF1 operating frequency (difference from rated frequency)	x	x						Analog Value	
1108		41109	Group 1 start operation: UF1 operating time	x	x						Analog Value	
1109		41110	Group 1 start operation: UF2 OFF: Do not use, ON: Use	x	x						Analog Value	
1110		41111	Group 1 start operation: UF2 operating frequency (difference from rated frequency)	x	x						Analog Value	
1111		41112	Group 1 start operation: UF2 operating time	x	x						Analog Value	
1112		41113	Group 1 start operation: UF3 OFF: Do not use, ON: Use	x	x						Analog Value	
1113		41114	Group 1 start operation: UF3 operating frequency (difference from rated frequency)	x	x						Analog Value	
1114		41115	Group 1 start operation: UF3 operating time	x	x						Analog Value	
1115		41116	Group 1 start operation: OF1 OFF: Do not use, ON: Use	x	x						Analog Value	
1116		41117	Group 1 start operation: OF1 operating frequency (difference from rated frequency)	x	x						Analog Value	
1117		41118	Group 1 start operation: OF1 operating time	x	x						Analog Value	
1118		41119	Group 1 start operation: OF2 OFF: Do not use, ON: Use	x	x						Analog Value	
1119		41120	Group 1 start operation: OF2 operating frequency (difference from rated frequency)	x	x						Analog Value	
1120		41121	Group 1 start operation: OF2 operating time	x	x						Analog Value	
1121		41122	Group 1 start operation: OF3 OFF: Do not use, ON: Use	x	x						Analog Value	
1122		41123	Group 1 start operation: OF3 operating frequency (difference from rated frequency)	x	x						Analog Value	
1123		41124	Group 1 start operation: OF3 operating time	x	x						Analog Value	
1124		41125	Group 1 start operation: MST1 OFF: Do not use, ON: Use	x	x						Analog Value	
1125		41126	Group 1 start operation: MST1 starting count	x	x						Analog Value	
1126		41127	Group 1 start operation: MST1 starting time	x	x						Analog Value	
1127		41128	Group 1 start operation: MST1 decrease rate	x	x						Analog Value	
1128		41129	Group 1 start operation: MST2 OFF: Do not use, ON: Use	x	x						Analog Value	
1129		41130	Group 1 start operation: MST2 starting count	x	x						Analog Value	
1130		41131	Group 1 start operation: MST2 recovery time	x	x						Analog Value	
1131		41132	Group 1 start operation: VTF OFF: Do not use, ON: Use	x	x						Analog Value	
1132		41133	Group 1 start operation: VTF operating voltage	x	x						Analog Value	
1133		41134	Group 1 start operation: VTF operating current	x	x						Analog Value	
1134		41135	For exclusive use of manufacturer									
1135		41136	Group 1 start operation: VTF operating current	x	x						Analog Value	
1136		41137	(Reserved)								Analog Value	
1137		41138	(Reserved)								Analog Value	
1138		41139	(Reserved)								Analog Value	
1139		41140	(Reserved)								Analog Value	
1140		41141	(Reserved)								Analog Value	
1141		41142	(Reserved)								Analog Value	
1142		41143	(Reserved)								Analog Value	
1143		41144	(Reserved)								Analog Value	
1144		41145	(Reserved)								Analog Value	
1145		41146	(Reserved)								Analog Value	
1146		41147	(Reserved)								Analog Value	
1147		41148	(Reserved)								Analog Value	
1148		41149	(Reserved)								Analog Value	
1149		41150	Group 1 start operation: Zero phase difference voltage monitoring OFF: Do not use,	x	x						Analog Value	When start operation for a setting value is received, the slave will respond (MODBUS send) with 05 ACKNOWLEDGE.
1150		41151	Group 1 start operation: Zero phase difference voltage monitoring: Detection time	x	x						Analog Value	
1151		41152	(Reserved)								Analog Value	
1152		41153	(Reserved)								Analog Value	
1153		41154	Group 1 start operation: V0 input method 0: Use VG input terminal, 1: V0S/W	x	x						Analog Value	
1154		41155	(Reserved)								Analog Value	
1155		41156	Group 1 start operation: Voltage reading method 0: Line, 1: Phase	x	x						Analog Value	
1156		41157	Group 1 start operation: VT input 0: Three-phase, 1: Two-phase	x	x						Analog Value	
1157		41158	(Reserved)	x	x						Analog Value	
1158		41159	(Reserved)	x	x						Analog Value	
1159		41160	(Reserved)	x	x						Analog Value	

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
1160	16	3	41161 (Reserved)	x	x						Analog Value	
1161			41162 (Reserved)	x	x						Analog Value	
1162			41163 (Reserved)	x	x						Analog Value	
1163			41164 (Reserved)	x	x						Analog Value	
1164			41165 (Reserved)	x	x						Analog Value	
1165			41166 (Reserved)	x	x						Analog Value	
1166			41167 (Reserved)	x	x						Analog Value	
1167			41168 (Reserved)	x	x						Analog Value	
1168			41169 (Reserved)	x	x						Analog Value	
1169			41170 (Reserved)	x	x						Analog Value	
1170			41171 (Reserved)	x	x						Analog Value	
1171			41172 (Reserved)	x	x						Analog Value	
1172			41173 (Reserved)	x	x						Analog Value	
1173			41174 (Reserved)	x	x						Analog Value	
1174			41175 (Reserved)	x	x						Analog Value	
1175			41176 (Reserved)	x	x						Analog Value	
1176			41177 (Reserved)	x	x						Analog Value	
1177			41178 (Reserved)	x	x						Analog Value	
1178			41179 (Reserved)	x	x						Analog Value	
1179			41180 (Reserved)	x	x						Analog Value	
1180			41181 (Reserved)	x	x						Analog Value	
1181			41182 (Reserved)	x	x						Analog Value	
1182			41183 (Reserved)	x	x						Analog Value	
1183			41184 (Reserved)	x	x						Analog Value	
1184			41185 (Reserved)	x	x						Analog Value	
1185			41186 (Reserved)	x	x						Analog Value	
1186			41187 (Reserved)	x	x						Analog Value	
1187			41188 (Reserved)	x	x						Analog Value	
1188			41189 (Reserved)	x	x						Analog Value	
1189			41190 (Reserved)	x	x						Analog Value	
1190			41191 (Reserved)	x	x						Analog Value	
1191			41192 (Reserved)	x	x						Analog Value	
1192			41193 (Reserved)	x	x						Analog Value	
1193			41194 (Reserved)	x	x						Analog Value	
1194			41195 (Reserved)	x	x						Analog Value	
1195			41196 (Reserved)	x	x						Analog Value	
1196			41197 (Reserved)	x	x						Analog Value	
1197			41198 (Reserved)	x	x						Analog Value	
1198			41199 (Reserved)	x	x						Analog Value	
1199			41200 (Reserved)	x	x						Analog Value	
1200			41201 (Reserved)	x	x						Analog Value	
1201			41202 (Reserved)	x	x						Analog Value	
1202			41203 (Reserved)	x	x						Analog Value	
1203			41204 (Reserved)	x	x						Analog Value	
1204			41205 (Reserved)	x	x						Analog Value	
1205			41206 (Reserved)	x	x						Analog Value	
1206			41207 (Reserved)	x	x						Analog Value	
1207			41208 (Reserved)	x	x						Analog Value	
1208			41209 (Reserved)	x	x						Analog Value	
1209			41210 (Reserved)	x	x						Analog Value	
1210			41211 (Reserved)	x	x						Analog Value	
1211			41212 (Reserved)	x	x						Analog Value	
1212			41213 (Reserved)	x	x						Analog Value	
1213			41214 (Reserved)	x	x						Analog Value	
1214			41215 (Reserved)	x	x						Analog Value	
1215			41216 (Reserved)	x	x						Analog Value	
1216			41217 (Reserved)	x	x						Analog Value	
1217			41218 (Reserved)	x	x						Analog Value	
1218			41219 (Reserved)	x	x						Analog Value	
1219			41220 (Reserved)	x	x						Analog Value	
1220			41221 (Reserved)	x	x						Analog Value	
1221			41222 (Reserved)	x	x						Analog Value	
1222			41223 (Reserved)	x	x						Analog Value	
1223			41224 (Reserved)	x	x						Analog Value	
1224			41225 (Reserved)	x	x						Analog Value	
1225			41226 (Reserved)	x	x						Analog Value	
1226			41227 (Reserved)	x	x						Analog Value	
1227			41228 (Reserved)	x	x						Analog Value	
1228			41229 (Reserved)	x	x						Analog Value	
1229			41230 (Reserved)	x	x						Analog Value	
1230			41231 (Reserved)	x	x						Analog Value	
1231			41232 (Reserved)	x	x						Analog Value	
1232			41233 (Reserved)	x	x						Analog Value	
1233			41234 (Reserved)	x	x						Analog Value	
1234			41235 (Reserved)	x	x						Analog Value	
1235			41236 (Reserved)	x	x						Analog Value	
1236			41237 (Reserved)	x	x						Analog Value	
1237			41238 (Reserved)	x	x						Analog Value	
1238			41239 (Reserved)	x	x						Analog Value	
1239			41240 (Reserved)	x	x						Analog Value	
1240			41241 (Reserved)	x	x						Analog Value	
1241			41242 (Reserved)	x	x						Analog Value	
1242			41243 (Reserved)	x	x						Analog Value	
1243			41244 (Reserved)	x	x						Analog Value	
1244			41245 (Reserved)	x	x						Analog Value	
1245			41246 (Reserved)	x	x						Analog Value	
1246			41247 (Reserved)	x	x						Analog Value	
1247			41248 (Reserved)	x	x						Analog Value	
1248			41249 (Reserved)	x	x						Analog Value	
1249			41250 (Reserved)	x	x						Analog Value	
1250			41251 (Reserved)	x	x						Analog Value	
1251			41252 (Reserved)	x	x						Analog Value	
1252			41253 (Reserved)	x	x						Analog Value	
1253			41254 (Reserved)	x	x						Analog Value	
1254			41255 (Reserved)	x	x						Analog Value	
1255			41256 (Reserved)	x	x						Analog Value	
1500	16	3	41501 Group 2 start operation: Rated motor current	x	x						Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data. With a "Set setting value" request from the master station as Function Code: 16, the slave will respond with (MODBUS send) the response data. On MODBUS: • Start address = 41501+1* • Number of access points = 1* • i+j<=256 (i=0 to 255, j=1 to 256) → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS. If out of range or out of step, the slave will respond with an error status with the 39808 completion check. When start operation for a setting value is received, the slave will respond (MODBUS send) with 05 ACKNOWLEDGE. • When any kind of data is received in a reserved area, the slave will notify the master of the error with the check group 2 setting value data writing processing. For exclusive use of manufacturer: Items that are applicable to the VFD and not applicable to Modbus in the items list are fixed as 0 when read. They also cannot be written.
1501			41502 Group 2 start operation: Motor start starting current	x	x						Analog Value	
1502			41503 Group 2 start operation: Motor start completion current	x	x						Analog Value	
1503			41504 Group 2 start operation: Motor operation completion current	x	x						Analog Value	
1504			41505 Group 2 start operation: Rated motor voltage	x	x						Analog Value	
1505			41506 Group 2 start operation: Number of current averaging cycles	x	x						Analog Value	
1506			41507 Group 2 start operation: OC1 OFF: Do not use, ON: Use	x	x						Analog Value	
1507			41508 Group 2 start operation: OC1 OFF: Averaging OFF, ON: Averaging ON	x	x						Analog Value	
1508			41509 Group 2 start operation: OC1 operating current	x	x						Analog Value	
1509			41510 Group 2 start operation: OC1 operating time scaling factor	x	x						Analog Value	
1510			41511 Group 2 start operation: OC1 operating characteristic	x	x						Analog Value	
1511			41512 Group 2 start operation: OC1 IEC characteristics OFF: Do not use, ON: Use	x	x						Analog Value	
1512			41513 Group 2 start operation: OCG1 use/do not use	x	x						Analog Value	
1513			41514 Group 2 start operation: OCG1 operating current	x	x						Analog Value	
1514			41515 Group 2 start operation: OCG1 operating time	x	x						Analog Value	
1515			41516 Group 2 start operation: OC2 OFF: Do not use, ON: Use	x	x						Analog Value	
1516			41517 Group 2 start operation: OC2 OFF: Averaging OFF, ON: Averaging ON	x	x						Analog Value	
1517			41518 Group 2 start operation: OC2 operating current	x	x						Analog Value	
1518			41519 Group 2 start operation: OC2 operating time scaling factor	x	x						Analog Value	
1519			41520 Group 2 start operation: OC2 operating characteristic	x	x						Analog Value	
1520			41521 Group 2 start operation: OC2 IEC characteristics OFF: Do not use, ON: Use	x	x						Analog Value	
1521			41522 Group 2 start operation: OCG2 use/do not use	x	x						Analog Value	
1522			41523 Group 2 start operation: OCG2 operating current	x	x						Analog Value	
1523			41524 Group 2 start operation: OCG2 operating time	x	x						Analog Value	
1524			41525 Group 2 start operation: OC3 OFF: Do not use, ON: Use	x	x						Analog Value	
1525			41526 Group 2 start operation: OC3 OFF: Averaging OFF, ON: Averaging ON	x	x						Analog Value	
1526			41527 Group 2 start operation: OC3 operating current	x	x						Analog Value	
1527			41528 Group 2 start operation: OC3 operating time	x	x						Analog Value	
1528			41529 Group 2 start operation: OCNEG1 OFF: Do not use, ON: Use	x	x						Analog Value	
1529			41530 Group 2 start operation: OCNEG1 operating current	x	x						Analog Value	
1530			41531 Group 2 start operation: OCNEG1 operating time	x	x						Analog Value	
1531			41532 Group 2 start operation: OCNEG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1532			41533 Group 2 start operation: OCNEG2 operating current	x	x						Analog Value	
1533			41534 Group 2 start operation: OCNEG2 operating time	x	x						Analog Value	
1534			41535 Group 2 start operation: OCNEG3 OFF: Do not use, ON: Use	x	x						Analog Value	
1535			41536 Group 2 start operation: OCNEG3 load current	x	x						Analog Value	
1536			41537 Group 2 start operation: OCNEG3 open phase current	x	x						Analog Value	
1537			41538 Group 2 start operation: UC1 OFF: Do not use, ON: Use	x	x						Analog Value	
1538			41539 Group 2 start operation: UC1 output three-phase OR/AND selection	x	x						Analog Value	
1539			41540 Group 2 start operation: UC1 UC detection method Pick1/Pick2	x	x						Analog Value	
1540			41541 Group 2 start operation: UC1 operating current	x	x						Analog Value	
1541			41542 Group 2 start operation: UC1 minimum current sensitivity	x	x						Analog Value	
1542			41543 Group 2 start operation: UC1 operating time	x	x						Analog Value	
1543			41544 Group 2 start operation: UC2 OFF: Do not use, ON: Use	x	x						Analog Value	
1544			41545 Group 2 start operation: UC2 output three-phase OR/AND selection	x	x						Analog Value	
1545			41546 Group 2 start operation: UC2 UC detection method Pick1/Pick2	x	x						Analog Value	
1546			41547 Group 2 start operation: UC2 operating current	x	x						Analog Value	
1547			41548 Group 2 start operation: UC2 minimum current sensitivity	x	x						Analog Value	
1548			41549 Group 2 start operation: UC2 operating time	x	x						Analog Value	
1549			41550 Group 2 start operation: CBF OFF: Do not use, ON: Use	x	x						Analog Value	

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
1550	16	3	41551 Group 2 start operation: CBF OFF: Do not use, ON: Use	x	x						Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data.
1551			41552 Group 2 start operation: CBF operating current	x	x						Analog Value	
1552			41553 Group 2 start operation: CBF operating current	x	x						Analog Value	
1553			41554 Group 2 start operation: CBF operating time	x	x						Analog Value	
1554			41555 Group 2 start operation: THOL OFF: Do not use, ON: Use	x	x						Analog Value	
1555			41556 Group 2 start operation: THOL COLD/HOT characteristic selection	x	x						Analog Value	
1556			41557 Group 2 start operation: THOL OFF: Averaging OFF, ON: Averaging ON	x	x						Analog Value	
1557			41558 Group 2 start operation: THOL operating current	x	x						Analog Value	
1558			41559 Group 2 start operation: THOL operating time scaling factor	x	x						Analog Value	
1559			41560 Group 2 start operation: THOL negative phase heat multiplying factor	x	x						Analog Value	
1560			41561 Group 2 start operation: DIRG maximum sensitivity angle	x	x						Analog Value	On MODBUS: • Start address = 41501+1* • Number of access points = 1*j • i+j<=256 (i=0 to 255, j=1 to 256)
1561			41562 Group 2 start operation: DIRG1 OFF: Do not use, ON: Use	x	x						Analog Value	
1562			41563 Group 2 start operation: DIRG1 operating voltage	x	x						Analog Value	
1563			41564 Group 2 start operation: DIRG1 operating current	x	x						Analog Value	
1564			41565 Group 2 start operation: DIRG1 operating time	x	x						Analog Value	
1565			41566 Group 2 start operation: DIRG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1566			41567 Group 2 start operation: DIRG2 operating voltage	x	x						Analog Value	
1567			41568 Group 2 start operation: DIRG2 operating current	x	x						Analog Value	
1568			41569 Group 2 start operation: DIRG2 operating time	x	x						Analog Value	
1569			41570 Group 2 start operation: DIRG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1570			41571 Group 2 start operation: UP1 operating current	x	x						Analog Value	If out of range or out of step, the slave will respond with an error status with the 39808 completion check.
1571			41572 Group 2 start operation: UP1 operating time	x	x						Analog Value	
1572			41573 Group 2 start operation: UP2 OFF: Do not use, ON: Use	x	x						Analog Value	
1573			41574 Group 2 start operation: UP2 operating current	x	x						Analog Value	
1574			41575 Group 2 start operation: UP2 operating time	x	x						Analog Value	
1575			41576 Group 2 start operation: UV1 OFF: Do not use, ON: Use	x	x						Analog Value	
1576			41577 Group 2 start operation: UV1 USP (phase voltage)/UVS (line voltage) selection	x	x						Analog Value	
1577			41578 Group 2 start operation: UV1 output three-phase OR/AND selection	x	x						Analog Value	
1578			41579 Group 2 start operation: UV1 operating voltage	x	x						Analog Value	
1579			41580 Group 2 start operation: UV1 operating time	x	x						Analog Value	
1580			41581 Group 2 start operation: UV2 OFF: Do not use, ON: Use	x	x						Analog Value	When start operation for a setting value is received, the slave will respond (MODBUS send) with 05 ACKNOWLEDGE.  • When any kind of data is received in a reserved area, the slave will notify the master of the error with the check group 2 setting value data writing processing.
1581			41582 Group 2 start operation: UV2 USP (phase voltage)/UVS (line voltage) selection	x	x						Analog Value	
1582			41583 Group 2 start operation: UV2 output three-phase OR/AND selection	x	x						Analog Value	
1583			41584 Group 2 start operation: UV2 operating voltage	x	x						Analog Value	
1584			41585 Group 2 start operation: UV2 operating time	x	x						Analog Value	
1585			41586 Group 2 start operation: OV1 OFF: Do not use, ON: Use	x	x						Analog Value	
1586			41587 Group 2 start operation: OV1 OVP (phase voltage)/OVS (line voltage) selection	x	x						Analog Value	
1587			41588 Group 2 start operation: OV1 operating voltage	x	x						Analog Value	
1588			41589 Group 2 start operation: OV1 operating time	x	x						Analog Value	
1589			41590 Group 2 start operation: OV2 OFF: Do not use, ON: Use	x	x						Analog Value	
1590			41591 Group 2 start operation: OV2 OVP (phase voltage)/OVS (line voltage) selection	x	x						Analog Value	
1591			41592 Group 2 start operation: OV2 operating voltage	x	x						Analog Value	For exclusive use of manufacturer: Items that are applicable to the VFD and not applicable to Modbus in the items list are fixed as 0 when read. They also cannot be written.
1592			41593 Group 2 start operation: OV2 operating time	x	x						Analog Value	
1593			41594 Group 2 start operation: OVG1 OFF: Do not use, ON: Use	x	x						Analog Value	
1594			41595 Group 2 start operation: OVG1 operating voltage	x	x						Analog Value	
1595			41596 Group 2 start operation: OVG1 operating time	x	x						Analog Value	
1596			41597 Group 2 start operation: OVG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1597			41598 Group 2 start operation: OVG2 operating voltage	x	x						Analog Value	
1598			41599 Group 2 start operation: OVG2 operating time	x	x						Analog Value	
1599			41600 Group 2 start operation: OVNEG1 OFF: Do not use, ON: Use	x	x						Analog Value	
1600			41601 Group 2 start operation: OVNEG1 operating voltage	x	x						Analog Value	
1601			41602 Group 2 start operation: OVNEG1 operating time	x	x						Analog Value	
1602			41603 Group 2 start operation: OVNEG2 OFF: Do not use, ON: Use	x	x						Analog Value	
1603			41604 Group 2 start operation: OVNEG2 operating voltage	x	x						Analog Value	
1604			41605 Group 2 start operation: OVNEG2 operating time	x	x						Analog Value	
1605			41606 For exclusive use of manufacturer									
1606			41607 Group 2 start operation: UF1 OFF: Do not use, ON: Use	x	x						Analog Value	
1607			41608 Group 2 start operation: UF1 operating frequency (difference from rated frequency)	x	x						Analog Value	
1608			41609 Group 2 start operation: UF1 operating time	x	x						Analog Value	
1609			41610 Group 2 start operation: UF2 OFF: Do not use, ON: Use	x	x						Analog Value	
1610			41611 Group 2 start operation: UF2 operating frequency (difference from rated frequency)	x	x						Analog Value	
1611			41612 Group 2 start operation: UF2 operating time	x	x						Analog Value	
1612			41613 Group 2 start operation: UF3 OFF: Do not use, ON: Use	x	x						Analog Value	
1613			41614 Group 2 start operation: UF3 operating frequency (difference from rated frequency)	x	x						Analog Value	
1614			41615 Group 2 start operation: UF3 operating time	x	x						Analog Value	
1615			41616 Group 2 start operation: OF1 OFF: Do not use, ON: Use	x	x						Analog Value	
1616			41617 Group 2 start operation: OF1 operating frequency (difference from rated frequency)	x	x						Analog Value	
1617			41618 Group 2 start operation: OF1 operating time	x	x						Analog Value	
1618			41619 Group 2 start operation: OF2 OFF: Do not use, ON: Use	x	x						Analog Value	
1619			41620 Group 2 start operation: OF2 operating frequency (difference from rated frequency)	x	x						Analog Value	
1620			41621 Group 2 start operation: OF2 operating time	x	x						Analog Value	
1621			41622 Group 2 start operation: OF3 OFF: Do not use, ON: Use	x	x						Analog Value	
1622			41623 Group 2 start operation: OF3 operating frequency (difference from rated frequency)	x	x						Analog Value	
1623			41624 Group 2 start operation: OF3 operating time	x	x						Analog Value	
1624			41625 Group 2 start operation: MST1 OFF: Do not use, ON: Use	x	x						Analog Value	
1625			41626 Group 2 start operation: MST1 starting count	x	x						Analog Value	
1626			41627 Group 2 start operation: MST1 starting time	x	x						Analog Value	
1627			41628 Group 2 start operation: MST1 decrease rate	x	x						Analog Value	
1628			41629 Group 2 start operation: MST2 OFF: Do not use, ON: Use	x	x						Analog Value	
1629			41630 Group 2 start operation: MST2 starting count	x	x						Analog Value	
1630			41631 Group 2 start operation: MST2 recovery time	x	x						Analog Value	
1631			41632 Group 2 start operation: VTF OFF: Do not use, ON: Use	x	x						Analog Value	
1632			41633 Group 2 start operation: VTF operating voltage	x	x						Analog Value	
1633			41634 Group 2 start operation: VTF operating current	x	x						Analog Value	
1634			41635 For exclusive use of manufacturer									
1635			41636 Group 2 start operation: VTF operating current	x	x						Analog Value	
1636			41637 (Reserved)								Analog Value	
1637			41638 (Reserved)								Analog Value	
1638			41639 (Reserved)								Analog Value	
1639			41640 (Reserved)								Analog Value	
1640			41641 (Reserved)								Analog Value	
1641			41642 (Reserved)								Analog Value	
1642			41643 (Reserved)								Analog Value	
1643			41644 (Reserved)								Analog Value	
1644			41645 (Reserved)								Analog Value	
1645			41646 (Reserved)								Analog Value	
1646			41647 (Reserved)								Analog Value	
1647			41648 (Reserved)								Analog Value	
1648			41649 (Reserved)								Analog Value	
1649			41650 Group 2 start operation: Zero phase difference voltage monitoring OFF: Do not use,	x	x						Analog Value	
1650			41651 Group 2 start operation: Zero phase difference voltage monitoring: Detection time	x	x						Analog Value	
1651			41652 (Reserved)								Analog Value	
1652			41653 (Reserved)								Analog Value	
1653			41654 Group 2 start operation: V0 input method 0: Use VG input terminal, 1: V0S/W	x	x						Analog Value	
1654			41655 (Reserved)								Analog Value	
1655			41656 Group 2 start operation: Voltage reading method 0: Line, 1: Phase	x	x						Analog Value	
1656			41657 Group 2 start operation: VT input 0: Three-phase, 1: Two-phase	x	x						Analog Value	
1657			41658 (Reserved)									
1658			41659 (Reserved)									
1659			41660 (Reserved)									
1660			41661 (Reserved)									
1661			41662 (Reserved)									
1662			41663 (Reserved)									
1663			41664 (Reserved)									
1664			41665 (Reserved)									
1665			41666 (Reserved)									
1666			41667 (Reserved)									
1667			41668 (Reserved)									
1668			41669 (Reserved)									
1669			41670 (Reserved)									
1670			41671 (Reserved)									
1671			41672 (Reserved)									
1672			41673 (Reserved)									
1673			41674 (Reserved)									
1674			41675 (Reserved)									
1675			41676 (Reserved)									
1676			41677 (Reserved)									
1677			41678 (Reserved)									
1678			41679 (Reserved)									







Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
3000	16	3	43001 Common setting value start operation: Operation settings group number (1 or 2)	x	x						Analog Value	With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data. With a "Set setting value" request from the master station as Function Code: 16, the slave will respond with (MODBUS send) the response data. On MODBUS: • Start address = 43001+1*j • Number of access points = 1*j • i+j<=255 (i=0 to 254, j=1 to 255) -- When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS. If out of range or out of step, the slave will respond with an error status with the 39809 completion check. When start operation for a setting value is received, the slave will respond (MODBUS send) with 05 ACKNOWLEDGE. • When any kind of data is received in a reserved area, the slave will notify the master of the error with the check common setting value data writing processing. For exclusive use of manufacturer: Items that are applicable to the VFD and not applicable to Modbus in the items list are fixed as 0 when read. They also cannot be written.
3001			43002 For exclusive use of manufacturer								Analog Value	
3002			43003 Common setting value start operation: DI detection voltage setting <selection>	x	x						Analog Value	
3003			43004 Common setting value start operation: Time before starting save waveform data (20 ms to 4500 ms)	x	x						Analog Value	
3004			43005 Common setting value start operation: Waveform data save start time	x	x						Analog Value	
3005			43006 For exclusive use of manufacturer									
3006			43007 For exclusive use of manufacturer									
3007			43008 For exclusive use of manufacturer									
3008			43009 For exclusive use of manufacturer									
3009			43010 Common setting value start operation: Initial trip count value (0 to 10,000)	x	x						Analog Value	
3010			43011 Common setting value start operation: Trip count value monitoring tap value (1 to	x	x						Analog Value	
3011			43012 Common setting value start operation: Motor operation time (L)	x	x						Analog Value	
3012			43013 Common setting value start operation: Motor operation time (H)	x	x						Analog Value	
3013			43014 Common setting value start operation: Motor operation time monitoring tap value (L)	x	x						Analog Value	
3014			43015 Common setting value start operation: Motor operation time monitoring tap value (H)	x	x						Analog Value	
3015			43016 For exclusive use of manufacturer									
3016			43017 For exclusive use of manufacturer									
3017			43018 For exclusive use of manufacturer									
3018			43019 For exclusive use of manufacturer									
3019			43020 For exclusive use of manufacturer									
3020			43021 For exclusive use of manufacturer									
3021			43022 For exclusive use of manufacturer									
3022			43023 For exclusive use of manufacturer									
3023			43024 For exclusive use of manufacturer									
3024			43025 For exclusive use of manufacturer									
3025			43026 For exclusive use of manufacturer									
3026			43027 For exclusive use of manufacturer									
3027			43028 For exclusive use of manufacturer									
3028			43029 For exclusive use of manufacturer									
3029			43030 For exclusive use of manufacturer									
3030			43031 For exclusive use of manufacturer									
3031			43032 For exclusive use of manufacturer									
3032			43033 For exclusive use of manufacturer									
3033			43034 For exclusive use of manufacturer									
3034			43035 For exclusive use of manufacturer									
3035			43036 For exclusive use of manufacturer									
3036			43037 For exclusive use of manufacturer									
3037			43038 For exclusive use of manufacturer									
3038			43039 For exclusive use of manufacturer									
3039			43040 For exclusive use of manufacturer									
3040			43041 Common setting value start operation: AI display primary value/secondary value setting <selection>	x	x						Analog Value	
3041			43042 Common setting value start operation: CT/PT0 primary value	x	x						Analog Value	
3042			43043 Common setting value start operation: CT/PT0 secondary value	x	x						Analog Value	
3043			43044 Common setting value start operation: CT/PT1 primary value	x	x						Analog Value	
3044			43045 Common setting value start operation: CT/PT1 secondary value	x	x						Analog Value	
3045			43046 Common setting value start operation: CT/PT2 primary value	x	x						Analog Value	
3046			43047 Common setting value start operation: CT/PT2 secondary value	x	x						Analog Value	
3047			43048 Common setting value start operation: CT/PT3 primary value	x	x						Analog Value	
3048			43049 Common setting value start operation: CT/PT3 secondary value	x	x						Analog Value	
3049			43050 For exclusive use of manufacturer									
3050			43051 For exclusive use of manufacturer									
3051			43052 For exclusive use of manufacturer									
3052			43053 For exclusive use of manufacturer									
3053			43054 Common setting value start operation: Tidal direction of electrical energy <selection>	x	x						Analog Value	
3054			43055 Common setting value start operation: +Pt initial setting value (L)	x	x						Analog Value	
3055			43056 Common setting value start operation: +Pt initial setting value (H)	x	x						Analog Value	
3056			43057 Common setting value start operation: -Pt initial setting value (L)	x	x						Analog Value	
3057			43058 Common setting value start operation: -Pt initial setting value (H)	x	x						Analog Value	
3058			43059 Common setting value start operation: +Qt initial setting value (L)	x	x						Analog Value	
3059			43060 Common setting value start operation: +Qt initial setting value (H)	x	x						Analog Value	
3060			43061 Common setting value start operation: -Qt initial setting value (L)	x	x						Analog Value	
3061			43062 Common setting value start operation: -Qt initial setting value (H)	x	x						Analog Value	
3062			43063 For exclusive use of manufacturer									
3063			43064 For exclusive use of manufacturer									
3064			43065 Common setting value start operation: System time zone	x	x						Analog Value	
3065			43066 Common setting value start operation: DST support	x	x						Analog Value	
3066			43067 Common setting value start operation: DST start month	x	x						Analog Value	
3067			43068 Common setting value start operation: DST start week	x	x						Analog Value	
3068			43069 Common setting value start operation: DST start day of the week	x	x						Analog Value	
3069			43070 Common setting value start operation: DST start hour	x	x						Analog Value	
3070			43071 Common setting value start operation: DST start minute	x	x						Analog Value	
3071			43072 Common setting value start operation: DST end month	x	x						Analog Value	
3072			43073 Common setting value start operation: DST end week	x	x						Analog Value	
3073			43074 Common setting value start operation: DST end day of the week	x	x						Analog Value	
3074			43075 Common setting value start operation: DST end hour	x	x						Analog Value	
3075			43076 Common setting value start operation: DST end minute	x	x						Analog Value	
3076			43077 Common setting value start operation: DST offset	x	x						Analog Value	
3077			43078 Common setting value start operation: DST base time	x	x						Analog Value	
3078			43079 Common setting value start operation: Time sync (use IRIG-B)	x	x						Analog Value	
3079			43080 Common setting value start operation: IRIG-B type	x	x						Analog Value	
3080			43081 Common setting value start operation: IEEE-1344 extension setting	x	x						Analog Value	
3081			43082 Common setting value start operation: IRIG time zone	x	x						Analog Value	
3082			43083 For exclusive use of manufacturer									
3083			43084 For exclusive use of manufacturer									
3084			43085 For exclusive use of manufacturer									
3085			43086 For exclusive use of manufacturer									

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
3086	16	3	43087									With a "Setting value" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data.
3087			43088									
3088			43089									
3089			43090									
3090			43091									
3091			43092									
3092			43093									
3093			43094									
3094			43095									
3095			43096									
3096			43097									
3097			43098									
3098			43099									
3099			43100									
3100			43101									
3101			43102									
3102			43103									
3103			43104									
3104			43105									
3105			43106									
3106			43107									
3107			43108									
3108			43109									
3109			43110									
3110			43111									
3111			43112									
3112			43113									
3113			43114									
3114			43115									
3115			43116									
3116			43117									
3117			43118									
3118			43119									
3119			43120									
3120			43121									
3121			43122									
3122			43123									
3123			43124									
3124			43125									
3125			43126									
3126			43127									
3127			43128									
3128			43129									
3129			43130									
3130			43131									
3131			43132									
3132			43133									
3133			43134									
3134			43135									
3135			43136									
3136			43137									
3137			43138									
3138			43139									
3139			43140									
3140			43141									
3141			43142									
3142			43143									
3143			43144									
3144			43145									
3145			43146									
3146			43147									
3147			43148									
3148			43149									
3149			43150									
3150			43151									
3151			43152									
3152			43153									
3153			43154									
3154			43155									
3155			43156									
3156			43157									
3157			43158									
3158			43159									
3159			43160									
3160			43161									
3161			43162									
3162			43163									
3163			43164									
3164			43165									
3165			43166									
3166			43167									
3167			43168									
3168			43169									
3169			43170									
3170			43171									
3171			43172									
3172			43173									
3173			43174									
3174			43175									
3175			43176									
3176			43177									
3177			43178									
3178			43179									
3179			43180									
3180			43181									
3181			43182									
3182			43183									
3183			43184									
3184			43185									
3185			43186									
3186			43187									
3187			43188									
3188			43189									
3189			43190									
3190			43191									
3191			43192									
3192			43193									
3193			43194									
3194			43195									
3195			43196									
3196			43197									
3197			43198									
3198			43199									
3199			43200									
3200			43201									

Serial No.	Function Code	Modbus Address (Register No.)	Description	Device Bit Status = 1	Device Bit Status = 0	Range (Min.) (Note 1)	Range (Max.) (Note 1)	Step	Engineering Unit	Scale (Note 2)	Signal Type	Remarks
3201	16	3	43202									
3202			43203									
3203			43204									
3204			43205									
3205			43206									
3206			43207									
3207			43208									
3208			43209									
3209			43210									
3210			43211									
3211			43212									
3212			43213									
3213			43214									
3214			43215									
3215			43216									
3216			43217									
3217			43218									
3218			43219									
3219			43220									
3220			43221									
3221			43222									
3222			43223									
3223			43224									
3224			43225									
3225			43226									
3226			43227									
3227			43228									
3228			43229									
3229			43230									
3230			43231									
3231			43232									
3232			43233									
3233			43234									
3234			43235									
3235			43236									
3236			43237									
3237			43238									
3238			43239									
3239			43240									
3240			43241									
3241			43242									
3242			43243									
3243			43244									
3244			43245									
3245			43246									
3246			43247									
3247			43248									
3248			43249									
3249			43250									
3250			43251									
3251			43252									
3252			43253									
3253			43254									
3254			43255									
4000	16	3	44001	x	x	0x1970	0x2069	-	No Unit	0	Analog Value	With a "Current time" request from the master station as Function Code: 3, the slave will respond with (MODBUS send) the response data. On MODBUS: • Start address = 44001+1* • Number of access points = 5 Fixed value.
4001			44002	x	x	0x0101	0x1231	-	No Unit	0	Analog Value	With a "Set setting value" request from the master station as Function Code: 16, the slave will respond with (MODBUS send) the response data.
4002			44003	x	x	0x0000	0x2359	-	No Unit	0	Analog Value	On MODBUS: • Start address = 44001+1* • Number of access points = 4 Fixed value. → When an error occurs, the slave will respond with (MODBUS send) 02: ILLEGAL DATA ADDRESS.
4003			44004	x	x	0x0000	0x5900	-	No Unit	0	Analog Value	When there is a time data error, the slave will respond with (MODBUS send) 03: ILLEGAL DATA VALUE.
4004			44005	x	x	1	4	-	No Unit	0	Analog Value	(BCD information) 1970 to 2069 (BCD information) 1/1 to 12/31 (BCD information) 0:00 to 23:59 (BCD information) 0 to 59 seconds (L is reserved)
4005			44006									(Reserved)
4006			44007									(Reserved)
4007			44008									(Reserved)
4008			44009									(Reserved)
4009			44010									(Reserved)
4089			44090									(Reserved)
4090			44091									(Reserved)
4091			44092									(Reserved)
4092			44093									(Reserved)
4093			44094									(Reserved)
4094			44095									(Reserved)
4095			44096									(Reserved)
4096			44097									(Reserved)
4097			44098									(Reserved)
4098			44099									(Reserved)
4099			44100									(Reserved)
4100			44101	x	x	0x00000000	0x3B9ACA00		No Unit		Analog Value	Get trip data (trip header/model-specific data) phenomenon number (H) request
4101			44102	x	x				No Unit		Analog Value	Get trip data (trip header/model-specific data) phenomenon number (L) request
4102			44103	x	x	1	20		No Unit		Analog Value	Get trip data (trip header/model-specific data/block number) request
4103			44104	x	x	0x00000000	0x3B9ACA00		No Unit		Analog Value	Get trip data (analog/digital data/phenomenon number) request
4104			44105	x	x				No Unit		Analog Value	Get trip data (analog/digital data/phenomenon number) request
4105			44106	x	x	1	20		No Unit		Analog Value	Get trip data (analog/digital data/block number) request
4106			44107	x	x	0	aved IT count-1		No Unit		Analog Value	Get trip data (analog/digital data/record number) request

(Note 1) The range (minimum) and range (maximum) of the setting value is a whole-number multiple of the actual setting value.  
(Note 2) The scale of the setting value indicates the number of digits after the decimal point of the actual setting value.